



Edge mark on first conductor




Cross section at flat



- Wire ————— Tinned copper
- Gauge ————— AWG 28/7 0,089 mm²
- Voltage rating ————— 300 Vr.m.s
- Current rating ————— 1,3 A at 10°C rise above ambient
- Capacity unbalanced ————— 78,7 pF/m nominal at 1MHz
- Impedance unbalanced ————— 75 Ω nominal
- Conductor resistance ————— 225 mΩ/m
- Propagation delay ————— 5,25 ns/m nominal
- Insulation material ————— PVC
- Temperature rating ————— -20°C (operating) | to +105°C
-30°C (static)
- Insulation resistance ————— 10 000 MΩ/km
- Approvals ————— UL Listed PLCC2-CL2
CSA Certified AWM FT-1

Slit section



- ① : Flat cable, AWG 28/7
- ② : Clear polyester
- ③ : Paper liner
- ④ : Outer jacket: black PVC

A

09 18 010 7011	100 m (328 feet)
09 18 010 7008	30,48 m (100 feet)
Part number	Length per reel

			Dot.	Name	<p>All Dim. in mm Orig. Size DIN A 4</p>	
			Detail.	25/10/05		JMDR
			Insp.			
			Stand.			
34612	20/09/07	PK	HARTING EURL			
33247	25/10/05	JMDR	F-95972 Paris			
Mod.	Dot.	Name				

SEK 18 round flat cable, not shielded, 10 poles	Maßstab/ Scale
TB 09 18 010 70XX	Blatt/ Page 2 / 2
Sub.	