


FMMT459

500V Silicon NPN high voltage switching transistor

Summary

$V_{(BR)CEV} > 500V$
 $V_{(BR)ECV} > 6V$
 $I_{c(cont)} = 150\text{ mA}$
 $V_{ce(sat)} = 70\text{ mV @ } 50\text{ mA}$



Description


This new high voltage transistor provides users with very efficient performance, combining low $V_{CE(SAT)}$ high H_{fe} to give extremely low on state losses at 500V operation, making it ideal for use in high efficiency Telecom and protected line switching applications.

Features

- 6V reverse blocking capability
- Low saturation voltage - 90mV @ 50mA
- $H_{fe} > 50 @ 30\text{ mA}$
- $I_C=150\text{mA}$ continuous
- SOT23 package with $P_{tot} 625\text{mW}$
- Specification can be supplied in other package outlines

Applications


- Electronic test equipment
- Offline switching circuits
- Piezo actuators
- RCD circuits



Ordering information

Device	Reel size (inches)	Tape width (mm)	Quantity per reel
FMMT459TA	7	8	3,000
FMMT459TC	13	8	10,000

Pin out - top view



Device marking

459

Absolute maximum ratings

Parameter	Symbol	Limit	Unit
Collector-base voltage	V_{CBO}	500	V
Collector-emitter voltage	V_{CEV}	500	V
Collector-emitter voltage	V_{CEO}	450	V
Emitter-base voltage	V_{EBO}	6	V
Emitter-collector voltage	V_{ECV}	6	V
Peak pulse current	I_{CM}	0.5	A
Continuous collector current*	I_C	0.15	A
Base current	I_B	0.2	A
Power dissipation @ $T_A=25^{\circ}C^*$ Linear derating factor	P_D	625 5	mW mW/ $^{\circ}C$
Power dissipation @ $T_A=25^{\circ}C^{\dagger}$ Linear derating factor	P_D	806 6.4	mW mW/ $^{\circ}C$
Operating and storage temperature range	$T_j:T_{stg}$	-55 to +150	$^{\circ}C$

Thermal resistance


Parameter	Symbol	Value	Unit
Junction to ambient*	$R_{\theta JA}$	200	$^{\circ}C/W$
Junction to ambient [†]	$R_{\theta JA}$	155	$^{\circ}C/W$

NOTES:


* For a device surface mounted on 25mm x 25mm FR4 PCB with high coverage of 1oz copper, in still air conditions

† as above measured at $t < 5$ secs.


Thermal characteristics



Safe Operating Area



Derating Curve



Transient Thermal Impedance

Electrical characteristics (at $T_{amb} = 25^{\circ}\text{C}$ unless otherwise stated)






Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions
Collector-base breakdown voltage	BV_{CBO}	500	700		V	$I_C = 100\mu\text{A}$
Collector-emitter breakdown voltage	BV_{CEV}	500	700		V	$I_C = 10\mu\text{A}$, $0.3\text{V} > V_{BE} > -1\text{V}$
Collector-emitter breakdown voltage	BV_{CEO}	450	500		V	$I_C = 10\text{mA}^*$
Emitter-base breakdown voltage	BV_{EBO}	6	8.1		V	$I_E = 100\mu\text{A}$
Emitter-base breakdown voltage (reverse blocking)	BV_{ECV}	6	8.1		V	$I_C = 1\mu\text{A}$, $0.3\text{V} > V_{BC} > -6\text{V}$
Collector-emitter cut-off current	I_{CES}			100	nA	$V_{CE}=450\text{V}$
Collector-base cut-off current	I_{CBO}			100	nA	$V_{CB}=450\text{V}$
Emitter-base cut-off current	I_{EBO}			100	nA	$V_{EB}=5\text{V}$
Static forward current transfer ratio	H_{FE}	50	120 70			$I_C = 30\text{mA}$, $V_{CE} = 10\text{V}$ $I_C = 50\text{mA}^*$, $V_{CE} = 10\text{V}$
Collector-emitter saturation voltage	$V_{CE(sat)}$		60 70	75 90	mV mV	$I_C = 20\text{mA}$, $I_B = 2\text{mA}^*$ $I_C = 50\text{mA}$, $I_B = 6\text{mA}^*$
Base-emitter saturation voltage	$V_{BE(sat)}$		0.76	0.9	V	$I_C = 50\text{mA}$, $I_B = 5\text{mA}^*$
Base-emitter turn-on voltage	$V_{BE(on)}$		0.71	0.9	V	$I_C = 50\text{mA}$, $V_{CE} = 10\text{V}^*$
Transition frequency	f_T	50			MHz	$I_C = 10\text{mA}$, $V_{CE} = 20\text{V}$ $f = 20\text{MHz}$
Output capacitance	C_{obo}			5	pF	$V_{CB} = 20\text{V}$, $f = 1\text{MHz}$
Turn-on time	$t_{(ON)}$		113		ns	$I_C = 50\text{mA}$, $V_C = 100\text{V}$ $I_{B1} = 5\text{mA}$, $I_{B2} = 10\text{mA}$
Turn-off time	$t_{(OFF)}$		3450		ns	$I_C = 50\text{mA}$, $V_C = 100\text{V}$ $I_{B1} = 5\text{mA}$, $I_{B2} = 10\text{mA}$

NOTES:


* Measured under pulsed conditions. Pulse width = $300\mu\text{s}$; duty cycle $<2\%$

Note: For high voltage applications, the appropriate industry sector guidelines should be considered with regards to voltage spacing between Terminals.

Electrical characteristics



Packaging details - SOT23



Package dimensions

Dimensions in inches are control dimensions, dimensions in millimeters are approximate.

Dim.	Millimeters		Inches		Dim.	Millimeters		Inches	
	Min.	Max.	Min.	Max.		Min.	Max.	Max.	Max.
A	2.67	3.05	0.105	0.120	H	0.33	0.51	0.013	0.020
B	1.20	1.40	0.047	0.055	K	0.01	0.10	0.0004	0.004
C	-	1.10	-	0.043	L	2.10	2.50	0.083	0.0985
D	0.37	0.53	0.015	0.021	M	0.45	0.64	0.018	0.025
F	0.085	0.15	0.0034	0.0059	N	0.95 Nom.		0.0375 Nom.	
G	1.90 Nom.		0.075 Nom.		-	-	-	-	-

Europe

Zetex GmbH
Streitfeldstraße 19
D-81673 München
Germany

Telefon: (49) 89 45 49 49 0
Fax: (49) 89 45 49 49 49
europe.sales@zetex.com

Americas

Zetex Inc
700 Veterans Memorial Highway
Hauppauge, NY 11788
USA

Telephone: (1) 631 360 2222
Fax: (1) 631 360 8222
usa.sales@zetex.com

Asia Pacific

Zetex (Asia Ltd)
3701-04 Metroplaza Tower 1
Hing Fong Road, Kwai Fong
Hong Kong

Telephone: (852) 26100 611
Fax: (852) 24250 494
asia.sales@zetex.com

Corporate Headquarters

Zetex Semiconductors plc
Zetex Technology Park, Chadderton
Oldham, OL9 9LL
United Kingdom

Telephone (44) 161 622 4444
Fax: (44) 161 622 4446
hq@zetex.com

These offices are supported by agents and distributors in major countries world-wide.

This publication is issued to provide outline information only which (unless agreed by the company in writing) may not be used, applied or reproduced for any purpose or form part of any order or contact or be regarded as a representation relating to the products or services concerned. The company reserves the right to alter without notice the specification, design, price or conditions of supply of any product or service.