CERAMICS SMD ULTRA MINIATURE QUARTZ CRYSTAL



ABM11

RoHS/RoHS II Compliant

2.0 x 1.6 x 0.59mm

Moisture Sensitivity Level (MSL) – This product is Hermetically Sealed and not Moisture Sensitive - MSL = N/A: Not Applicable

FEATURES:

- 2.0 x 1.6 x 0.59mm ultra miniature package.
- Suitable for RoHS compliant reflow.
- Seam sealed ceramic package with metal lid assures high precision and reliability.


▷ APPLICATIONS:

- Cellular telephones, Pagers.
- Communication and Test equipment.
- High Density applications
- PCMCIA and wireless applications.

STANDARD SPECIFICATIONS:

Parameters	Minimum	Typical	Maximum	Units	Notes
Frequency Range	16.000		50.000	MHz	
Operation Mode	Fundamental				
Operating Temperature	-10		+60	°C	See options
Storage Temperature	-40		+85	°C	
Frequency Tolerance @+25°C	-30		+30	ppm	See options
Frequency Stability over the Operating Temperature (ref. to +25°C)	-50		+50	ppm	See options
Equivalent series resistance (R1)			150	Ω	16.000~17.999MHz
			120		18.000~20.999MHz
			100		21.000~29.999 MHz
			80		30.000~37.999 MHz
			60		38.000~50.000 MHz
Shunt capacitance (C0)			7.0	pF	
Load capacitance (CL)	10			pF	Standard (See options if other than STD)
Drive Level		10	100	μW	
Aging	-5		+5	ppm	@25°C±3°C First year
Insulation Resistance	500			MΩ	(a) $100 \text{Vdc} \pm 15 \text{V}$

> **OPTIONS AND PART IDENTIFICATION:** (Left blank if standard)







2 Faraday, Suite# B | Irvine | CA 92618 **Revised: 06.19.15** Ph. 949.546.8000 | Fax. 949.546.8001 Visit www.abracon.com for Terms and Conditions of Sale

CERAMICS SMD ULTRA MINIATURE QUARTZ CRYSTAL





(Pb) RoHS/RoHS II Compliant

2.0 x 1.6 x 0.59mm

OUTLINE DRAWING:

ABM11






Note: Due to the availability of raw materials, this part may also be manufactured with the chamfer on pin 1 or 4. Be advised that this does not affect the electrical characteristics of the crystal in any way.

TAPE & REEL:

Option "-T": Tape and reel (1,000pcs/reel) Option "-T3": Tape and reel (3,000pcs/reel) FEEDING (PULL) DIRECTION 2.0 ± 0.7 1.75±0.1 4.0±0.1 0.3±.05 -¢ ₼ --3.5±0. 8.0±0.2 () () Temperature ø1.5 1.85 ± 0.1 $4.0\pm0.$ 0.65 ± 0.1 9.0±1.0 4 0 ø13.0±0.5 2.2±0.5 ø20.2±1 20 **Dimensions: mm**

REFLOW PROFILE:



Need a test socket for the ABM11 Series? To view compatible **PRECISION TEST & BURN-IN SOCKETS** for these parts, **click here. P/N AXS-2016-04-04C**

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.





2 Faraday, Suite# B | Irvine | CA 92618 **Revised: 06.19.15** Ph. 949.546.8000 | Fax. 949.546.8001 Visit www.abracon.com for Terms and Conditions of Sale