

E0144-C

Power PCB Relay RT1

- 1 pole 12A/16A, 1 form C (CO) or 1 form A (NO) contact
- DC or AC coil
- 5kV/10mm coil-contact, reinforced insulation
- Ambient temperature 85°C (DC coil)
- WG version: product in accordance to IEC 60335-1
- Reflow version: for THR (Through-Hole Reflow) soldering process


Typical applications


Boiler control, timers, garage door control, POS automation, interface modules

Approvals

VDE Cert. No. 40007571, cULus E214025, cCSAus 1142018 CQC 20002275223 (China production), CQC 08001027262 (China production), CQC 18002197247 (monostable) Technical data of approved types on request

Contact Dat	а	12A 16	4			
Contact arrange	ement	1 form C (CO) or 1 form A	1 form C (CO) or 1 form A (NO)			
Rated voltage		250VAC				
Max. switching	voltage	400VAC				
Rated current		12A 16A	4			
Limiting continu	ous current	12A 16A, UL	: 20A			
Limiting making	current					
max. 4s, duty	y factor 10%	25A 30A	4			
Breaking capac	ity max.	3000VA 4000	VA			
Contact materia	al	AgNi 90/10, AgNi 90/10 go	ld plated			
Frequency of op	peration, with/	without load				
DC coil		360/72000h ⁻¹				
AC coil		360/36000h ⁻¹				
Operate/release	e time max., D0	C coil 8/6ms				
Bounce time ma	, ,					
Electrical endura	ance	see electrical endurance g	raph ¹⁾			
Contact rating	IS					
Туре	Contact	Load	Cycles			
IEC 61810						
RT314 DC-coil	A (NO)	16A, 250VAC, cosφ=1, 85°C	30x10 ³			
RT314 DC-coil	C (CO)	16A, 250VAC, cosφ=1, 85°C	10x10 ³			
RT314 DC-coil	A (NO)	10A, 400VAC, cosφ=1, 85°C	150x10 ³			
RT114 DC-coil	A (NO)	12A, 250VAC, cosφ=1, 85°C	50x10 ³			
RT114 AC-coil	A (NO)	12A, 250VAC, cosφ=1, 70°C	100x10 ³			
UL 61810-1 (former UL 508)						
RT314	A/B (NO/NC)	20A, 250VAC, general purpose, 85	°C 6x10 ³			
RT334	A (NO)	16A, 250VAC, gen. purpose, 85°C	50x10 ³			
RT314	A (NO)	1hp, 240VAC, 40°C	1x10 ³			
RT314	A (NO)	FLA/LRA, 4.5/13.1A, 480VAC, 70°C	100x10 ³			
EN60947-4-1						
RT314	A (NO)	250V/2A, AC-3	6.050			





09-2022, Rev. 3 www.te.com © 2014 Tyco Electronics Corporation, a TE Connectivity Ltd. company Datasheets and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section.



Contact Data (continued)						
EN60947-5-1						
RT314 DC-coil	A/B (NO/NC)	2A, 24VDC, DC13	6.050			
RT314	A (NO)	250/3A, AC-15	6.050			
EN60730-1						
RT314 DC-coil	A (NO)	12(2)A, 250VAC, 85°C	100x10 ³			
1) For reflow solde	rable versions: ad	ctual contact performance may be influence	ed by the			
reflow soldering process.						
Mechanical end	urance					
DC coil >30x10 ⁶ operations						
AC coil >10x10 ⁶ operations						
AC coil, reflow version >5x10 ⁶ operations						
Coil Data						

Coil voltage range, DC coil/ AC coil	5 to 110VDC / 24 to 230VAC
Operative range, IEC 61810	2
Coil insulation system according UL	class F

Coil versions. DC coil

Convers	sions, DC co				
Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	$\Omega \pm 10\%^{2)}$	mW
005	5	3.5	0.5	62	403
006	6	4.2	0.6	90	400
009	9	6.3	0.9	200	400
012	12	8.4	1.2	360	400
018	18	12.6	1.8	770	420
020	20	14.0	2.0	952	420
024	24	16.8	2.4	1440	400
048	48	33.6	4.8	5520	417
060	60	42.0	6.0	8570 ²⁾	420
110	110	77.0	11.0	28800 ²⁾	420

2) Coil resistance ±12%.

All figures are given for coil without pre-energization, at ambient temperature +23°C. Other coil voltages on request.

Cail varaiana AC aail 50/60 H

Coil vers	sions, AC co	il 50/60 Hz			
Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VAC	VAC	VAC	Ω±15% ³⁾	VA
524	24	18.0	3.6	350 ³⁾	0.76
548	48	36.0	7.2	1420	0.74
615	115	86.3	17.3	8100	0.76
620	120	90.0	18.0	8800	0.75
700	200	150.0	30.0	24350	0.76
730	230	172.5	34.5	32500	0.74

3) Coil resistance ±10%


All figures are given for coil without pre-energization, at ambient temperature +23°C, 50 Hz. Other coil voltages on request.

Datasheets and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at http://relays.te.com/definitions

Datasheets, product data, 'Definitions' section, application notes and all specifications are subject to change. 1



Power PCB Relay RT1 (Continued)



0 A 40 +60 +80 +100 Ambient temperature [°C]

Insulation Data


Initial dielectric strength			
between open contacts	1000V _{rms}		
between contact and coil	5000V _{rms}		
Clearance/creepage			
between contact and coil	≥10/10mm		
Material group of insulation parts	Illa		
Tracking index of relay base	PTI 250V		
reflow version	PTI 175V		

Other Data

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customersupport/rohssupportcenter Resistance to heat and fire according EN60335, par30

VVG version or Reliow version	according EN60335, parsu
Ambient temperature	
DC coil	-40 to 85°C
AC coil	-40 to 70°C
Category of environmental protection	n, IEC 61810
standard version	RTII - flux proof, RTIII - wash tight
reflow version	RTII - flux proof
Vibration resistance (functional)	
form A/form B contact, 30 to 500	Hz 20g/5g
Shock resistance (destructive)	100g

PCB layout / terminal assignment Bottom view on solder pins



Terminal type	
standard version	PCB-THT, plug-in
reflow version	PCB-THR
Mounting distance	AC coil: ≥2.5mm
Weight	14g
Resistance to soldering heat THT, IEC	60068-2-20
RTII	270°C/10s
RTIII	260°C/5s
Resistance to soldering heat THR	
reflow soldering (for reflow version)	forced gas convection 4) or
0	vapour phase ⁵⁾
temperature profile	according EN61730
Packaging/unit	tube/20 pcs., box/500 pcs.
4) infrared heating not allowed	· ·
5) recommended fluid LS/230	

Accessories

5,04^{±0,1}

Y

14


11 14 S0418-CN

S0163-BC

S0163-BD

Accessories Industrial Power Relay RT For details see datasheet NOTE: indicated contact ratings and electrical endurance data for direct wiring of relays (according IEC 61810-1); for relays mounted on sockets deratings may apply.

*) With the recommended PCB hole sizes a grid pattern from 2.5mm to 2.54mm can be used.




09-2022, Rev. 3 www.te.com © 2014 Tyco Electronics Corporation, a TE Connectivity Ltd. company

Datasheets and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section. Datasheets and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at http://relays.te.com/definitions

Datasheets, product data, 'Definitions' section, application notes and all specifications are subject to change.



Power PCB Relay RT1 (Continued)



Datasheets and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at http://relays.te.com/definitions

Datasheets, product data, 'Definitions' section, application notes and all specifications are subject to change.

3



Power PCB Relay RT1 (Continued)

Product code	Version	Contacts C	Contact material	Coil	Version	Part Number	
FIGURE	Version	Contacts	Contact material	COII	Version	Austria	China
RT114009	12A,	1 form C (CO)	AgNi 90/10	9VDC	Standard	1393239-9	1-1649326-2
RT114012	pinning 3.5mm,	contact	5	12VDC		1419108-1	1-1649326-3
RT114012WG	flux proof			12VDC	IEC60335-1 compliant	7-1415538-6	
RT114024				24VDC	Standard	1-1393239-3	1-1649326-5
RT114024WG				24VDC	IEC60335-1 compliant	1415539-4	
RT114730				230VAC	Standard	1-1393239-9	
RT115024			AgNi 90/10 gold pl.	24VDC		2-1393239-1	3-1833000-9
RT134012		1 form A (NO)	AgNi 90/10	12VDC		2-1393239-6	3-1649326-1
RT134024		contact		24VDC		3-1393239-0	3-1649326-3
RT214012	12A,	1 form C (CO)		12VDC		5-1393239-4	1-1649327-3
RT214024	pinning 5mm,	contact		24VDC		5-1393239-5	1-1649327-5
RT214524	flux proof			24VAC		5-1393239-9	
RT214730				230VAC		1419108-6	
RT314005	16A,			5VDC		9-1393239-1	1-1649328-0
RT314006	pinning 5mm,			6VDC		9-1393239-3	1-1649328-1
RT314009	flux proof			9VDC		9-1393239-4	
RT314012				12VDC		9-1393239-5	1-1649328-3
RT314012R				12VDC	Reflow solderable	4-1415543-6	
RT314012WG				12VDC	IEC60335-1 compliant	8-1415535-6	5-1833002-0
RT314018				18VDC	Standard	9-1393239-7	1-1649328-4
RT314024				24VDC		9-1393239-8	1-1649328-5
RT314024WG				24VDC	IEC60335-1 compliant	1415538-7	5-1833002-1
RT314048				48VDC	Standard	1393240-1	1-1649328-6
RT314060				60VDC 110VDC		1-1649328-7	1-1649328-7
RT314110 RT314524				24VAC		1393240-3 1393240-4	
RT314524				48VAC		1393240-4	
RT314615				115VAC		1393240-5	
RT314013				230VAC		1393240-0	
RT314730WG				230VAC 230VAC	IEC60335-1 compliant	4-1415538-0	
				230VAC 24VDC	<u>.</u>		0 1000000 7
RT315024			AgNi 90/10 gold pl.	-	Standard	1-1393240-4	3-1833002-7
RT334009WG		1 form A (NO)	AgNi 90/10	9VDC	IEC60335-1 compliant	3-1415538-1	0.1040000.1
RT334012		contact		12VDC	Standard	4-1393240-5	3-1649328-1
RT334012WG RT334024				12VDC 24VDC	IEC60335-1 compliant Standard	1-1415527-1	5-1833002-2 3-1649328-3
					Standard	4-1393240-8	
RT334048	104			48VDC		5-1393240-0	3-1649328-4
RTB14005	12A,	1 form C (CO)		5VDC		1-1393238-2	1649326-1
RTB14012	pinning 3.5mm,	contact		12VDC		1-1393238-5	1649326-4
RTB14024	wash tight			24VDC		1-1393238-9	1649326-6
RTB14524 RTB34012		1 form A (NO)		24VAC 12VDC		2-1393238-4	2-1649326-2
	104 Engine wash					3-1393238-0	
RTC14024	12A, 5mm, wash	1 form C (CO)		24VDC		5-1393238-0	1649327-6
RTD14005	16A,	contact		5VDC		5-1393238-9	1649328-1
RTD14012	pinning 5mm,			12VDC		6-1393238-2	1649328-4
RTD14024	wash tight			24VDC		6-1393238-8	1649328-6
RTD14048				48VDC		6-1393238-9	1649328-7
RT114048	12A, pinning 3.5mm, flux proof			48VDC			1-1649326-6
RT214005	12A, pinning 5mm,			5VDC			1-1649327-0
RT234012	flux proof			12VDC			1-1649327-3
RT234024	12A, pinning 3.5mm,			24VDC	IEC 60335-1 compliant		1-1649327-5
RTB14048	wash tight			48VDC	standard		1649326-7
RTB34005	16A, pinning 5mm,			5VDC			1-1649326-9
RTD14060	wash tight			60VDC			1649328-8
RTD34012		1 form A (NO)		12VDC			2-1649328-2
RTD34024WG		contact		24VDC			3-1649328-7
RTD34015				15VDC			4-1833002-0
RTD34024				24VDC			2-1649328-4

This list represents the most common types and does not show all variants covered by this datasheet. Other types on request