

Han 16HP-HSE-M32



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 19 39 016 0527 |
| Specification | Han 16HP-HSE-M32 |
| HARTING eCatalogue | https://b2b.harting.com/19390160527 |

Identification

| | |
|--------------------------|----------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han® HP |
| Type of hood/housing | Hood |

Version

| | |
|----------------------|---------------------------------------|
| Size | 16 B |
| Version | Side entry |
| Cable entry | 1x M32 |
| Locking type | Screw locking |
| Field of application | Hoods/housings for rough environments |

Technical characteristics

| | |
|--|--|
| Tightening torque (screw locking) | 3 Nm |
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP66 IP68 IP69 / IPX9K acc. to ISO 20653 |

Material properties

| | |
|-------------------------|----------------------|
| Material (hood/housing) | Aluminium die-cast |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 7037 (dust grey) |
| Material (seal) | NBR |
| Material (locking) | Stainless steel |



Pushing Performance

Material properties

| | |
|--------------------------------------|---------------|
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Nickel |

Specifications and approvals

| | |
|----------------|-------------------------|
| Specifications | EN 60664-1 IEC 61984 |
| CE | Yes |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 281 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| eCl@ss | 27440202 Shell for industrial connectors |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19390160527](#)