


REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	MAR08/18	L-CHAN



RECOMMENDED PANEL CUTOUT



MATERIALS:

PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING UL 94V-0, COLOR: BLACK



CONTACTS:

PHOSPHOR BRONZE
PLATING: 30 μ [0.76 MICRONS]
MIN. GOLD ON MATING SURFACES.
50 μ [1.27 MICRONS]
MIN. NICKEL UNDERPLATE
100 μ [2.54 MICRONS]
MIN. MATTE TIN ON CONTACT TAILS.

SHIELD:

STAINLESS STEEL WITH TIN DIPPED ON SOLDER TAILS.
RECOMMENDED SOLDERING TEMPERATURE:
WAVE SOLDERING TEMPERATURE AT 260°C MAXIMUM
FOR 5 SEC MAXIMUM.

AMPHENOL PART NUMBER: RJHSE-3380-A1



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)

POSITION DIMENSIONS
ARE BASIC

UNLESS SPECIFIED OTHERWISE	DRAWN	W.O.I.U.	DATE
CHECKED	L-CHAN	MAR08/18	
M.E. APP'D			
Q.A. APP'D			
DWG APPR.			
ENG. REL. NO.			
REF.			
1 DECIMAL PLACES ±0.025			
2 DECIMAL PLACES ±0.020			
3 DECIMAL PLACES ±0.015			
ANGULAR DEGREES ±1.0°			

THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING	REV
		P-RJHSE-3380-A1
		DWG. NO.
		REV
		A
		DWG. NO. 03554
		SCALE N/A
		SHEET 1 OF 1

AMPHENOL CANADA CORP.
www.amphenolcanada.com
TITLE
VERTICAL SINGLE PART MODULAR JACK CONNECTOR, SHIELDED WITHOUT LEADS .130" LONG CONTACT TAILS- RoHS COMPLIANT

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.