

Energy Saving Type 2 Port Solenoid Valve

For Air/Water/Oil



*Power
consumption*

(SMC comparison)

1/3



Reduction of
running costs

Reduction of
CO₂

Reduction of
power supply capacity
for facilities

Reduction of
temperature
increase

New generation valve corresponding to energy-saving needs

• IP65 • RoHS compliance

Series VXE


CAT.EUS70-36A-UK

Series VXE

VXE2, VXED2, VXEZ2

2 port solenoid valve for various fluids
Energy saving type of the VX2, VXD2 and VXZ2 series

VXE2 Direct Operated

VXED2 Pilot Operated

VXEZ2 Zero Differential Pressure Type Pilot Operated

- The power consumption (when holding) is substantially reduced (approx. 1/3).
- Coil heat reduction



Model	Power consumption (W) (Holding)	Inrush current (A) (Inrush time: 200 ms)		Temperature increase (°C)
		24 VDC	12 VDC	
VXE□21 (VXED2130)	1.5 (1.8)	0.19 (0.23)	0.38 (0.46)	25 (30)
VXE□22	2.3	0.29	0.58	25
VXE□23	3	0.44	0.88	30

● Interchangeable

The mounting dimensions and its basic specifications are equivalent to those of conventional models.

● Replaceable coil

Possible to change the solenoid coil assembly for the VX2, VXD and VXZ with the power-saving coil type.
 (Restricted for the rated voltage 12, 24 VDC)



Body Size Variations between 1/8" to 2"

Series	Port size Orifice diameter	Thread						Flange		
		1/8	1/4	3/8	1/2	3/4	1	32A	40A	50A
VXE2 Direct Operated 	2 mmø	●	●							
	3 mmø	●	●	●						
	4.5 mmø	●	●	●						
	6 mmø		●	●						
	8 mmø		●	●						
	10 mmø		●	●	●					
VXED2 Pilot Operated 	10 mmø		●	●	●					
	15 mmø			●	●					
	20 mmø					●				
	25 mmø						●			
	35 mmø							●		
	40 mmø								●	
50 mmø									●	
VXEZ2 Zero Differential Pressure Type Pilot Operated 	10 mmø		●	●						
	15 mmø				●					
	20 mmø					●				
	25 mmø						●			



Model	VXE2
	VXED2
	VXEZ2
Specifications	
Applications	
	For Air
	For Water
	For Oil
Dimensions	Construction

Energy Saving Type

Direct Operated 2 Port Solenoid Valve

Series VXE21/22/23

For Air/Water/Oil



Single Unit

Valve

Normally closed (N.C.)

Solenoid Coil

Coil: Class B

Rated Voltage

24 VDC, 12 VDC

Material

Body — Brass (C37), Stainless steel
Seal — NBR, FKM, EPDM, PTFE


Electrical Entry

- Grommet
- Conduit
- DIN terminal
- Conduit terminal



Normally Closed (N.C.)

Model	VXE21	VXE22	VXE23		
Orifice diameter	2mmø	—	—	—	—
	3 mmø	●	—	●	—
	4.5 mmø	●	●	●	—
	6 mmø	—	●	●	—
	8 mmø	—	●	●	—
10 mmø	—	●	●	●	●
Port size	1/8	1/4	1/2	1/4	1/2
	1/4	3/8		3/8	



Manifold

Valve

Normally closed (N.C.)

Base

Common SUP
Individual SUP (Aluminum base only)

Solenoid Coil

Coil: Class B

Rated Voltage


24 VDC, 12 VDC

Material

Body — Aluminum, Brass (C37),
Stainless steel
Base — Aluminum, Brass (C37),
Stainless steel
Seal — NBR, FKM, EPDM, PTFE

Electrical Entry

- Grommet
- Conduit
- DIN terminal
- Conduit terminal



Manifold

Model	VXE21	VXE22	VXE23	
Orifice dia.	2 mmø	●	—	—
	3 mmø	●	●	●
	4.5 mmø	●	●	●
	6 mmø	—	●	●
(Common SUP) Port size	OUT port			3/8
	IN port			1/8, 1/4

Series VXE21/22/23

Common Specifications

Standard Specifications

Valve specifications	Valve construction	Direct operated poppet
	Valve type	N.C.
	Withstand pressure	5.0 MPa
	Body material	Brass (C37), Stainless steel
	Seal material	NBR, FKM, EPDM, PTFE
	Enclosure	Dust tight, Low jetproof (IP65)
	Environment	Location without corrosive or explosive gases
Coil specifications	Rated voltage	24 VDC, 12 VDC
	Allowable voltage fluctuation	±10% of rated voltage
	Allowable leakage voltage	2% or less of rated voltage
	Coil insulation type	Class B
	Surge voltage suppressor	Built-in surge voltage suppressor

Solenoid Coil Specifications

Normally Closed (N.C.)

DC Specification

Model	Power consumption (W) (Holding)	Inrush current (A) (Inrush time: 200 ms)		Temperature increase (C°) <small>Note)</small>
		24 VDC	12 VDC	
VXE21	1.5	0.19	0.38	25
VXE22	2.3	0.29	0.58	25
VXE23	3	0.44	0.88	30

Note) Value for ambient temperature at 20°C and when the rated voltage is applied.

Applicable Fluid Check List / All Options (Single Unit)

VXE2 0 - - 1 -

● Option symbol

Fluid and application	Option symbol	Seal material	Body material
Air	—	NBR	Brass (C37)
	G		Stainless steel
Medium vacuum/Non-leak/ Oil-free <small>Note 1)</small>	V <small>Note 2)</small>	FKM	Brass (C37)
	M <small>Note 2)</small>		Stainless steel
Water	—	NBR	Brass (C37)
	G		Stainless steel
Oil <small>Note 3)</small>	A	FKM	Brass (C37)
	H		Stainless steel
High corrosive/Oil-free	L <small>Note 2)</small>	FKM	Stainless steel
Copper-free/Fluoro-free <small>Note 4)</small>	J	EPDM	Stainless steel
Other combination	B	PTFE	Brass (C37)
	C		Stainless steel
	K		Stainless steel

Applicable Fluid Check List / All Options (Manifold)

VXE2 1 - - 1

● Option symbol

● Base symbol

Fluid and application	Option symbol	Base symbol	Seal material	Body material
Air	—	00	NBR	Aluminum
Medium vacuum/Non-leak/Oil-free <small>Note 1)</small>	V <small>Note 2)</small>	00	FKM	Aluminum
Water	—	—	NBR	Brass (C37)
	G			Stainless steel
Oil <small>Note 3)</small>	A	—	FKM	Brass (C37)
	H			Stainless steel
High corrosive/Oil-free	L <small>Note 2)</small>	—	FKM	Stainless steel
Non-leak/Copper-free/Oil-free <small>Note 4)</small>	R	00	FKM	Aluminum

Note 1) The leakage amount (10⁻⁶ Pa·m³/s) for V and M options is the value when the differential pressure is 0.1 MPa.

Note 2) The V, M and L options are oil-free treatment.

Note 3) The dynamic viscosity of the fluid must not exceed 50 mm²/s.

Note 4) The nuts (non-wetted parts) are nickel plated on the brass (C37) material.

* If used for other fluids, please consult with SMC.

Series VXE21/22/23


For Air /Single Unit

(Inert gas/Non-leak/Medium vacuum)

Model/Valve Specifications

N.C.

Passage symbol



Normally Closed (N.C.)

Port size	Orifice dia. (mm)	Model	Max. operating pressure differential (MPa)	Flow characteristics			Max. system pressure (MPa)	Weight (g) <small>(Note)</small>
				C[dm ³ /(s·bar)]	b	Cv		
1/8 (6A)	2	VXE2110-01	1.5	0.59	0.48	0.18	300	
	3	VXE2120-01	0.6	1.2	0.45	0.33		
	4.5	VXE2130-01	0.2	2.3	0.46	0.61		
1/4 (8A)	2	VXE2110-02	1.5	0.59	0.48	0.18	3.0	
		VXE2120-02	0.6	1.2	0.45	0.33		
	3	VXE2220-02	1.5					2.3
		VXE2320-02	3.0					
	4.5	VXE2130-02	0.2	4.1	0.30	1.10		
		VXE2230-02	0.35					
	6	VXE2330-02	0.9	6.4	0.30	1.60		
		VXE2240-02	0.15					
	8	VXE2340-02	0.35	8.8	0.30	2.00		
		VXE2250-02	0.08					
	10	VXE2350-02	0.2	11	0.30	2.20		
		VXE2260-02	0.03					
10	VXE2360-02	0.07	1.0	0.30	2.20			
	VXE2260-02	0.03						
3/8 (10A)	3	VXE2220-03	1.5	1.2	0.45	0.33	3.0	
		VXE2320-03	3.0					
	4.5	VXE2230-03	0.35	2.3	0.46	0.61		
		VXE2330-03	0.9					
	6	VXE2240-03	0.15	4.1	0.30	1.10		
		VXE2340-03	0.35					
	8	VXE2250-03	0.08	6.4	0.30	1.60		
		VXE2350-03	0.2					
	10	VXE2260-03	0.03	11	0.30	2.20		
		VXE2360-03	0.07					
10	VXE2260-03	0.03	1.0	0.30	2.20			
	VXE2360-03	0.07						
1/2 (15A)	10	VXE2260-04	0.03	11	0.30	2.20		
		VXE2360-04	0.07					



Note) Weight for the grommet type. Add 10 g for conduit, 30 g for DIN terminal, and 60 g for conduit terminal type respectively.

- Refer to "Glossary" on page 44 for details on the max. operating pressure differential and the max. system pressure.

Fluid and Ambient Temperature

Fluid temperature (°C)		Solenoid valve option symbol	Ambient temperature (°C)
Solenoid valve option symbol			
—, G	V, M		
-10 <small>Note)</small> to 60	-10 <small>Note)</small> to 60		-20 to 60



Note) Dew point temperature: -10°C or less

Valve Leakage

Internal Leakage

Seal material	Leakage	
	Air	Non-leak/ Medium vacuum <small>Note)</small>
NBR, FKM	1 cm ³ /min or less	10 ⁻⁶ Pa·m ³ /sec or less

External Leakage

Seal material	Leakage	
	Air	Non-leak/ Medium vacuum <small>Note)</small>
NBR, FKM	1 cm ³ /min or less	10 ⁻⁶ Pa·m ³ /sec or less



Note) Value for V and M options (Non-leak/Medium vacuum)

How to Order (Single Unit)

DC

VXE 21 2 0 - 01 - 5 G 1 -

Model
Refer to Table (1) shown below for availability.

Orifice diameter
Refer to Table (1) shown below for availability.

Valve/Body configuration

0	N.C. / Single unit
---	--------------------

Solenoid valve option
Refer to Table (2) shown below for availability.

Suffix

-	-
Z	Oil-free

Select "-" because the solenoid valve V, M options are oil-free treatment.

Port size
Refer to Table (1) shown below for availability.

Bracket

-	None
B	With bracket

* VX021N-12A and VX022N-12A are packed in the same container as the main body.
* Refer to Table (4) if a bracket is ordered separately.

Rated voltage

5	24 VDC
6	12 VDC

* Refer to Table (3) shown below for availability.
Refer to page 43 for ordering the coil only.

Thread type

-	Rc
T	NPTF
F	G
N	NPT

Electrical entry

G-Grommet 	C-Conduit
T -With conduit terminal TL -With conduit terminal and light 	D -DIN terminal DL -DIN terminal with light DO -For DIN terminal (without connector, with gasket)

* Refer to Table (3) for available combinations between electrical option (L) and the rated voltage.

Table (1) Model/Orifice Diameter/Port Size Normally Closed (N.C.)

Solenoid valve model (Port size)			Orifice symbol (diameter)						
Model	VXE21	VXE22	VXE23	1 (2 mmø)	2 (3 mmø)	3 (4.5 mmø)	4 (6 mmø)	5 (8 mmø)	6 (10 mmø)
Port symbol (Port size)	01 (1/8)	—	—	●	●	●	—	—	—
	02 (1/4)	—	—	●	●	●	—	—	—
	—	02 (1/4)	02 (1/4)	—	●	●	●	●	●
	—	03 (3/8)	03 (3/8)	—	●	●	●	●	●
—	04 (1/2)	04 (1/2)	—	—	—	—	—	●	

Table (2) Solenoid Valve Option

Option symbol	Seal material	Body material	Note
—	NBR	Brass (C37)	—
G		Stainless steel	
V	FKM	Brass (C37)	Non-leak (10 ⁻⁶ Pa·m ³ /sec)/Oil-free/ Medium vacuum (0.1 Pa.abs)
M		Stainless steel	

Table (3) Rated Voltage – Electrical Option

Rated voltage		L (With light)
Voltage symbol	Voltage	
5	24 VDC	●
6	12 VDC	—

Table (4) Bracket Part No.

Model	Part no.
VXE21 ₂ 0 ₃	VX021N-12A
VXE22 ₂ 3 ₄ 0 ₄	VX022N-12A
VXE23 ₂ 3 ₄ 0 ₄	
VXE22 ₅ 0 ₆	VX023N-12A-L
VXE23 ₅ 0 ₆	

Dimensions → P. 17 (Single unit)

Model
VXE2
VXED2
VXE22
Specifications
Applications
For Air
For Water
For Oil
Construction
Dimensions

Series VXE21/22/23




For Air/Manifold

(Inert gas/Non-leak/Medium vacuum)

Solenoid Valve for Manifold/Valve Specifications

N.C.

Passage symbol



Normally Closed (N.C.)

Orifice dia. (mmø)	Model	Max. operating pressure differential (MPa)	Flow characteristics			Max. system pressure (MPa)
			C[dm ³ /(s·bar)]	b	Cv	
2	VXE2111-00	1.5	0.59	0.48	0.18	3.0
3	VXE2121-00	0.6	1.2	0.45	0.33	
	VXE2221-00	1.5				
	VXE2321-00	3.0				
4.5	VXE2131-00	0.2	2.3	0.46	0.61	
	VXE2231-00	0.35				
	VXE2331-00	0.9				
6	VXE2241-00	0.15	4.1	0.30	1.10	
	VXE2341-00	0.35				

• Refer to "Glossary" on page 44 for details on the max. operating pressure differential and the max. system pressure.

Fluid and Ambient Temperature

Fluid temperature (°C)		Ambient temperature (°C)
Solenoid valve option symbol		
—, R	V	-20 to 60
-10 ^{Note)} to 60	-10 ^{Note)} to 60	

Note) Dew point temperature: -10°C or less

Valve Leakage

Internal Leakage

Seal material	Leakage	
	Air	Non-leak/ Medium vacuum ^{Note)}
NBR, FKM	1 cm ³ /min or less	10 ⁻⁶ Pa·m ³ /sec or less

External Leakage

Seal material	Leakage	
	Air	Non-leak/ Medium vacuum ^{Note)}
NBR, FKM	1 cm ³ /min or less	10 ⁻⁶ Pa·m ³ /sec or less

Note) Value for V and M options (Non-leak/Medium vacuum)

How to Order (Solenoid Valve for Manifold)

DC VXE 21 2 1 [] [] - 00 - 5 G 1

Model • Refer to Table (1) shown below for availability.

Orifice diameter • Refer to Table (1) shown below for availability.

Valve/Body configuration •

1	N.C. (for Manifold)
---	---------------------

Solenoid valve option • Refer to Table (2) shown below for availability.

Suffix •

-	-
Z	Oil-free

Select "-" because the solenoid valve V and R options are oil-free treatment.

Rated voltage •

5	24 VDC
6	12 VDC

* Refer to Table (3) shown below for availability.

Refer to page 43 for ordering the coil only.

Electrical entry •

<p>G-Grommet</p>	<p>C-Conduit</p>
<p>T -With conduit terminal TL -With conduit terminal and light</p>	<p>D -DIN terminal DL -DIN terminal with light DO -For DIN terminal (without connector, with gasket)</p>

* Refer to Table (3) for available combinations between the electrical option (L) and the rated voltage.

How to Order Manifold Bases

VVX21
VVX22 1 [] [] [] - 07 - 1
VVX23

Port size (Individual port) •

1	Rc1/8
2	Rc1/4

* Common port sizes are all Rc3/8.

Thread type •

-	Rc
T	NPTF
F	G
N	NPT

Number of manifolds •

02	2 stations
...	...
10	10 stations

Suffix •

-	-
Z	Oil-free

Base type •

-	Common SUP
V	Individual SUP

Manifold base

Blanking plate part no.
 For VXE21: VX011-001 []
 For VXE22/23: VX011-006 []

Seal material •

-	NBR
F	FKM

How to Order Manifold Assemblies (Example)

Enter the valve and blanking plate to be mounted under the manifold base part number.

Example
 VVX211-05-1 1 set "*" is the symbol for mounting.
 * VXE2111-00-1G1 ... 4 sets Add an "*" in front of the part numbers
 * VX011-001..... 1 set for solenoid valves, etc. to be mounted.

(Station) - 1 - 2 - 3 - 4 - 5 - n

Enter the product's part number in order, counting the 1st station from the left in the manifold arrangement, when viewing the individual port in front.

Table (1) Model/Orifice Diameter

Solenoid valve model	Orifice symbol (diameter)			
	1 (2 mmø)	2 (3 mmø)	3 (4.5 mmø)	4 (6 mmø)
VXE21	●	●	●	-
VXE22	-	●	●	●
VXE23	-	●	●	●

Table (2) Solenoid Valve Option

Option symbol	Body/Base material	Seal material	Note
-	-	NBR	-
V	Aluminum	FKM	Non-leak/Medium vacuum/Oil-free
R	-	-	Non-leak/Copper-free/Oil-free <small>(Note)</small>

(Note) The nuts (non-wetted parts) are nickel plated on the Brass (C37) material.

Table (3) Rated Voltage – Electrical Option

Rated voltage		L (With light)
Voltage symbol	Voltage	
5	24 VDC	●
6	12 VDC	-

Dimensions → P. 19 (Manifold)

Model VXE2 VXE22 VXE23 Specifications Applications For Air For Water For Oil Dimensions Construction


Series VXE21/22/23

For Water /Single Unit

Model/Valve Specifications

N.C.

Passage symbol



Normally Closed (N.C.)

Port size	Orifice dia. (mmø)	Model	Max. operating pressure differential (MPa)	Flow characteristics		Max. system pressure (MPa)	Note) Weight (g)	
				Av x 10 ⁻⁶ m ²	Cv converted			
1/8 (6A)	2	VXE2110-01	1.5	4.1	0.17	3.0	300	
	3	VXE2120-01	0.5	7.9	0.33			
	4.5	VXE2130-01	0.2	15.0	0.61			
1/4 (8A)	2	VXE2110-02	1.5	4.1	0.17	3.0	470	
		VXE2120-02	0.5	7.9	0.33			
		VXE2220-02	1.5					
	3	VXE2320-02	3.0	15.0	0.61			620
		VXE2130-02	0.2					300
		VXE2230-02	0.35					470
	4.5	VXE2330-02	0.9	26.0	1.10			620
		VXE2240-02	0.15					470
		VXE2340-02	0.3					620
	6	VXE2250-02	0.08	38.0	1.60			560
		VXE2350-02	0.2					700
		VXE2260-02	0.03					1.0
VXE2360-02	0.07	700						
3/8 (10A)	3	VXE2220-03	1.5	7.9	0.33	3.0	470	
		VXE2320-03	3.0					620
		VXE2230-03	0.35					15.0
	VXE2330-03	0.9	620					
	4.5	VXE2240-03	0.15	26.0	1.10			470
		VXE2340-03	0.3					620
		VXE2250-03	0.08					1.0
	VXE2350-03	0.2	700					
	6	VXE2260-03	0.03	53.0	2.20			560
		VXE2360-03	0.07					700
		VXE2260-04	0.03					1.0
	VXE2360-04	0.07	700					
1/2 (15A)	10	VXE2260-04	0.03	53.0	2.20	560		
		VXE2360-04	0.07			700		



Note) Weight for the grommet type. Add 10 g for conduit, 30 g for DIN terminal, and 60 g for conduit terminal type respectively.

- Refer to "Glossary" on page 44 for details on the max. operating pressure differential and the max. system pressure.

Fluid and Ambient Temperature

Fluid temperature (°C)	Ambient temperature (°C)
Solenoid valve option symbol	
—, G, L	-20 to 60
1 to 60	



Note) With no freezing

Valve Leakage



Internal Leakage

Seal material	Leakage (Water)
NBR, FKM	0.1 cm ³ /min or less

External Leakage

Seal material	Leakage (Water)
NBR, FKM	0.1 cm ³ /min or less

How to Order (Single Unit)



* Refer to Table (3) for available combinations between the electrical option (L) and the rated voltage.

Table (1) Model/Orifice Diameter/Port Size Normally Closed (N.C.)

Solenoid valve model (Port size)			Orifice symbol (diameter)						
Model	VXE21	VXE22	VXE23	1 (2 mmø)	2 (3 mmø)	3 (4.5 mmø)	4 (6 mmø)	5 (8 mmø)	6 (10 mmø)
Port symbol (Port size)	01 (1/8)	—	—	●	●	●	—	—	—
	02 (1/4)	—	—	●	●	●	—	—	—
	—	02 (1/4)	02 (1/4)	—	●	●	●	●	●
	—	03 (3/8)	03 (3/8)	—	●	●	●	●	●
—	04 (1/2)	04 (1/2)	—	—	—	—	—	●	

Table (3) Rated Voltage – Electrical Option

Rated voltage		L (With light)
Voltage symbol	Voltage	
5	24 VDC	●
6	12 VDC	—

Table (2) Solenoid Valve Option

Option symbol	Seal material	Body material	Note
—	NBR	Brass (C37)	—
G		Stainless steel	
L	FKM	Stainless steel	High corrosive/Oil-free

Table (4) Bracket Part No.

Model	Part no.
VXE21 $\frac{1}{8}$ 20	VX021N-12A
VXE22 $\frac{2}{4}$ 30	VX022N-12A
VXE23 $\frac{2}{4}$ 30	
VXE22 $\frac{5}{6}$ 50	VX023N-12A-L
VXE23 $\frac{5}{6}$ 50	

Dimensions → P. 17 (Single unit)

Model
VXE2
VXED2
VXE22
Specifications
Applications
For Air
For Water
For Oil
Dimensions
Construction


Series VXE21/22/23

For Oil/Manifold

Solenoid Valve for Manifold/Valve Specifications

N.C.

Passage symbol



Normally Closed (N.C.)

Orifice dia. (mmø)	Model	Max. operating pressure differential (MPa)	Flow characteristics		Max. system pressure (MPa)
			Av x 10 ⁻⁶ m ²	Cv converted	
2	VXE2111	1.5	4.1	0.17	3.0
3	VXE2121	0.5	7.9	0.33	
	VXE2221	1.5			
	VXE2321	3.0			
4.5	VXE2131	0.2	15	0.61	
	VXE2231	0.35			
	VXE2331	0.9			
6	VXE2241	0.15	26	1.10	
	VXE2341	0.3			



• Refer to "Glossary" on page 44 for details on the max. operating pressure differential and the max. system pressure.

Fluid and Ambient Temperature

Fluid temperature (°C)	Ambient temperature (°C)
Solenoid valve option symbol —, G, L	
1 to 60	-20 to 60



Note) With no freezing

Valve Leakage

Internal Leakage

Seal material	Leakage (Water)
NBR, FKM	0.1 cm ³ /min or less

External Leakage

Seal material	Leakage (Water)
NBR, FKM	0.1 cm ³ /min or less

How to Order (Solenoid Valve for Manifold)

DC VXE 21 2 1 - 5 G 1

Model • Refer to Table (1) shown below for availability.

Orifice diameter • Refer to Table (1) shown below for availability.

Valve/Body configuration •

1	N.C. (for Manifold)
---	---------------------

Solenoid valve option • Refer to Table (2)-(1) shown below for availability.

Suffix •

-	-
Z	Oil-free





 Select "-" because the solenoid valve L option is oil-free treatment.

Rated voltage •

5	24 VDC
6	12 VDC

 * Refer to Table (3) shown below for availability.

Electrical entry

<p>G-Grommet</p> 	<p>C-Conduit</p> 
<p>T -With conduit terminal TL -With conduit terminal and light</p> 	<p>D -DIN terminal DL -DIN terminal with light DO -For DIN terminal (without connector, with gasket)</p> 

* Refer to Table (3) for available combinations between electrical option (L) and rated voltage.

Refer to page 43 for ordering the coil only.

How to Order Manifold Bases

VVX21
VVX22 1 C - 07 - 1
VVX23

Port size (OUT port) •

1	Rc1/8
2	Rc1/4

 * IN port sizes are all Rc3/8.

Thread type •

-	Rc
T	NPTF
F	G
N	NPT

Number of manifolds •

02	2 stations
⋮	⋮
10	10 stations

Manifold base •

Base/Seal material • * Refer to Table (2)-(2) shown below for availability.

-	-
Z	Oil-free

Suffix •

-	-
Z	Oil-free

Blanking plate part no.
 For VXE21: VVX21-3A—
 For VXE22: VVX22-3A—
 For VXE23: VVX23-3A—

Seal material •

-	NBR
F	FKM
E	EPDM

Table (1) Model/Orifice Diameter

Solenoid valve model	Orifice symbol (diameter)			
	1 (2 mmø)	2 (3 mmø)	3 (4.5 mmø)	4 (6 mmø)
VXE21	●	●	●	—
VXE22	—	●	●	—
VXE23	—	●	●	●

Table (2) Solenoid Valve Option

Solenoid valve option symbol (1)	Base/Seal material symbol (2)	Body/Base material	Seal material	Note
-	C	Brass (C37)	NBR	—
G	S	Stainless steel		
L	SF	Stainless steel	FKM	High corrosive/Oil-free


Table (3) Rated Voltage – Electrical Option

Rated voltage		L (With light)
Voltage symbol	Voltage	
5	24 VDC	●
6	12 VDC	—

How to Order Manifold Assemblies (Example)

Enter the valve and blanking plate to be mounted under the manifold base part number.

Example
 VVX211C-05-1 1 set "*" is the symbol for mounting.
 * VXE2111-1G1 4 sets Add an "*" in front of the part numbers for solenoid valves, etc. to be mounted.
 * VVX21-3A 1 set



Enter the product's part number in order, counting the 1st station from the left in the manifold arrangement, when viewing the individual port in front.

Dimensions → P. 19 (Manifold)

Series VXE21/22/23

For Oil /Single Unit


⚠ When the fluid is oil.

The dynamic viscosity of the fluid must not exceed 50 mm²/s.

Model/Valve Specifications

N.C.

Passage symbol



Normally Closed (N.C.)

Port size	Orifice dia. (mmø)	Model	Max. operating pressure differential (MPa)	Flow characteristics		Max. system pressure (MPa)	Note) Weight (g)
				Av x 10 ⁻⁶ m ²	Cv converted		
1/8 (6A)	2	VXE2110-01	1.5	4.1	0.17	3.0	300
	3	VXE2120-01	0.5	7.9	0.33		
	4.5	VXE2130-01	0.15	15	0.61		
1/4 (8A)	2	VXE2110-02	1.5	4.1	0.17	3.0	470
		VXE2120-02	0.5	7.9	0.33		
		VXE2220-02	1.2				
	3	VXE2320-02	2.0	15	0.61	3.0	620
		VXE2130-02	0.15				
		VXE2230-02	0.3				
	4.5	VXE2330-02	0.85	26	1.10	1.0	470
		VXE2240-02	0.1				
		VXE2340-02	0.3				
	6	VXE2250-02	0.08	38	1.60	1.0	620
		VXE2350-02	0.2				
		VXE2260-02	0.03				
8	VXE2360-02	0.07	46	1.90	1.0	700	
	VXE2250-03	0.08					
	VXE2350-03	0.2					
3/8 (10A)	3	VXE2260-03	0.03	53	2.20	1.0	560
		VXE2360-03	0.07				
	4.5	VXE2220-03	1.2	7.9	0.33	3.0	470
		VXE2320-03	2.0				
	6	VXE2230-03	0.3	15	0.61	3.0	620
		VXE2330-03	0.85				
8	VXE2240-03	0.1	26	1.10	1.0	470	
	VXE2340-03	0.3					
10	VXE2250-03	0.08	38	1.60	1.0	560	
	VXE2350-03	0.2					
1/2 (15A)	10	VXE2260-04	0.03	53	2.20	1.0	700
		VXE2360-04	0.07				



Note) Weight for the grommet type. Add 10 g for conduit, 30 g for DIN terminal, and 60 g for conduit terminal type respectively.

- Refer to "Glossary" on page 44 for details on the max. operating pressure differential and the max. system pressure.

Fluid and Ambient Temperature

Fluid temperature (°C)	Ambient temperature (°C)
Solenoid valve option symbol A, H	
-5 Note) to 60	-20 to 60



Note) Dynamic viscosity: 50 mm²/s or less

Valve Leakage

Internal Leakage

Seal material	Leakage (Oil)
FKM	0.1 cm ³ /min or less

External Leakage

Seal material	Leakage (Oil)
FKM	0.1 cm ³ /min or less

How to Order (Single Unit)

DC **VXE** **21** **2** **0** **A** **01** **5** **G** **1**

Model
Refer to Table (1) shown below for availability.

Orifice diameter
Refer to Table (1) shown below for availability.

Valve/Body configuration

0	N.C. / Single unit
---	--------------------

Solenoid valve option
Refer to Table (2) shown below for availability.

Suffix

-	-
Z	Oil-free

Port size
Refer to Table (1) shown below for availability.

Bracket

-	None
B	With bracket

* VX021N-12A and VX022N-12A are packed in the same container as the main body.
* Refer to Table (4) if a bracket is ordered separately.

Rated voltage

5	24 VDC
6	12 VDC

* Refer to Table (3) shown below for availability.
 Refer to page 43 for ordering the coil only.

Thread type

-	Rc
T	NPTF
F	G
N	NPT

Electrical entry

<p>G-Grommet</p>	<p>C-Conduit</p>
<p>T -With conduit terminal TL -With conduit terminal and light</p>	<p>D -DIN terminal DL -DIN terminal with light DO -For DIN terminal (without connector, with gasket)</p> <p style="text-align: right;">Connector</p>

* Refer to Table (3) for available combinations between the electrical option (L) and the rated voltage.

Table (1) Model/Orifice Diameter/Port Size Normally Closed (N.C.)

Solenoid valve model (Port size)				Orifice symbol (diameter)					
Model	VXE21	VXE22	VXE23	1 (2 mmø)	2 (3 mmø)	3 (4.5 mmø)	4 (6 mmø)	5 (8 mmø)	6 (10 mmø)
Port symbol (Port size)	01 (1/8)	—	—	●	●	●	—	—	—
	02 (1/4)	—	—	●	●	●	—	—	—
	—	02 (1/4)	02 (1/4)	—	●	●	●	●	●
	—	03 (3/8)	03 (3/8)	—	●	●	●	●	●
—	04 (1/2)	04 (1/2)	—	—	—	—	—	—	●

Normally Open (N.O.)

Solenoid valve model (Port size)			Orifice symbol (diameter)				
Model	VXE21	VXE22	VXE23	1 (2 mmø)	2 (3 mmø)	3 (4.5 mmø)	4 (6 mmø)
Port symbol (Port size)	01 (1/8)	—	—	●	●	●	—
	02 (1/4)	—	—	●	●	●	—
	—	02 (1/4)	02 (1/4)	—	●	●	●
	—	03 (3/8)	03 (3/8)	—	●	●	●

Table (3) Rated Voltage – Electrical Option

Rated voltage		L (With light)
Voltage symbol	Voltage	
5	24 VDC	●
6	12 VDC	—

Table (2) Solenoid Valve Option

Option symbol	Seal material	Body material
A	FKM	Brass (C37)
H		Stainless steel

The additives contained in oil are different depending on the type and manufacturers, so the durability of the seal materials will vary. For details, please consult with SMC.

Table (4) Bracket Part No.

Model	Part no.
VXE21 $\frac{1}{8}$ 0	VX021N-12A
VXE22 $\frac{2}{4}$ 0	VX022N-12A
VXE23 $\frac{3}{4}$ 0	
VXE22 $\frac{5}{8}$ 0	VX023N-12A-L
VXE23 $\frac{3}{8}$ 0	

Dimensions → P. 17 (Single unit)

Model
 VXE2
 VXE22
 VXE23
 Specifications
 Applications
 For Air
 For Water
 For Oil
 Dimensions
 Construction

For Oil/Manifold


⚠ When the fluid is oil.

The dynamic viscosity of the fluid must not exceed 50 mm²/s.

Solenoid Valve for Manifold/Valve Specifications

N.C.

Passage symbol



Common SUP



Normally Closed (N.C.)

Orifice dia. (mmø)	Model	Max. operating pressure differential (MPa)	Flow characteristics		Max. system pressure (MPa)
			Av x 10 ⁻⁶ m ²	Cv converted	
2	VXE2111	1.5	4.1	0.17	3.0
3	VXE2121	0.5	7.9	0.33	
	VXE2221	1.2			
	VXE2321	2.0			
4.5	VXE2131	0.15	15	0.61	
	VXE2231	0.3			
	VXE2331	0.85			
6	VXE2241	0.1	26	1.10	
	VXE2341	0.3			



• Refer to "Glossary" on page 44 for details on the max. operating pressure differential and the max. system pressure.

Fluid and Ambient Temperature

Fluid temperature (°C)	Ambient temperature (°C)
Solenoid valve option symbol A, H	
-5 ^{Note)} to 60	-20 to 60



Note) Dynamic viscosity: 50 mm²/s or less

Valve Leakage

Internal Leakage

Seal material	Leakage (Oil)
FKM	0.1 cm ³ /min or less

External Leakage

Seal material	Leakage (Oil)
FKM	0.1 cm ³ /min or less

How to Order (Solenoid Valve for Manifold)

DC VXE 21 2 1 A - 5 G 1

- Model**
Refer to Table (1) shown below for availability.
- Orifice diameter**
Refer to Table (1) shown below for availability.
- Valve/Body configuration**
1 N.C. (for Manifold)
- Solenoid valve option**
Refer to Table (2)-(1) shown below for availability.
- Suffix**
Z Oil-free
- Rated voltage**
5 24 VDC
6 12 VDC
* Refer to Table (3) shown below for availability.

Refer to page 43 for ordering the coil only.

Electrical entry

G-Grommet 	C-Conduit
T -With conduit terminal TL -With conduit terminal and light 	D -DIN terminal DL -DIN terminal with light DO -For DIN terminal (without connector, with gasket)

* Refer to Table (3) for available combinations between the electrical option (L) and the rated voltage.

How to Order Manifold Bases

VVX21 VVX22 VVX23 1 - CF - 07 - 1

- Port size (OUT port)**
1 Rc1/8
2 Rc1/4
* IN port sizes are all Rc3/8.
- Thread type**
- Rc
T NPTF
F G
N NPT
- Number of manifolds**
02 2 stations
: :
10 10 stations
- Suffix**
- -
Z Oil-free
- Base/Seal material**
* Refer to Table (2)-(2) shown below for availability.
- Manifold base**
- Blanking plate part no.**
For VXE21: VVX21-3A-F
For VXE22: VVX22-3A-F
For VXE23: VVX23-3A-F
- Seal material: FKM**

Table (1) Model/Orifice Diameter

Solenoid valve model	Orifice symbol (diameter)			
	1 (2 mmø)	2 (3 mmø)	3 (4.5 mmø)	4 (6 mmø)
VXE21	●	●	●	—
VXE22	—	●	●	●
VXE23	—	●	●	●

Table (2) Solenoid Valve Option

Solenoid valve option symbol (1)	Base/Seal material symbol (2)	Body/Base material	Seal material
A	CF	Brass (C37)	FKM
H	SF	Stainless steel	

The additives contained in oil are different depending on the type and manufacturers, so the durability of the seal materials will vary. For details, please consult with SMC.



Table (3) Rated Voltage – Electrical Option

Rated voltage		L (With light)
Voltage symbol	Voltage	
5	24 VDC	●
6	12 VDC	—

How to Order Manifold Assemblies (Example)

Enter the valve and blanking plate to be mounted under the manifold base part number.

Example
 VVX211CF-05-1 1 set "*" is the symbol for mounting.
 * VXE2111A-1G1 4 sets Add an "*" in front of the part numbers
 * VVX21-3A-F 1 set for solenoid valves, etc. to be mounted.



Enter the product's part number in order, counting the 1st station from the left in the manifold arrangement, when viewing the individual port in front.

Dimensions → P. 19 (Manifold)

Model VXE2 VXE22 VXE23
 Specifications
 Applications For Air For Water For Oil
 Dimensions Construction


Series VXE21/22/23

For Air/Water/Oil

Construction: Single Unit

Normally closed (N.C.)

Body material: Brass (C37), Stainless steel



Component Parts

No.	Description	Material	
		Brass (C37) body specification	Stainless steel body specification
1	Body	Brass (C37)	Stainless steel
2	Tube assembly	Stainless steel	
3	Armature assembly	(NBR, FKM, EPDM, PTFE) Stainless steel, PPS	
4	Return spring	Stainless steel	
5	Solenoid coil	—	
6	O-ring	(NBR, FKM, EPDM, PTFE)	
7	Clip	SK	
8	Nut	Brass (C37)	Brass (C37), Ni plated

The materials in parentheses are (No. 6) seal materials.


Construction: Manifold

Normally closed (N.C.)


Base material: Aluminum

Fluid: Air

Common SUP




Individual SUP



Base material: Brass (C37), Stainless steel

Fluid: Water/Oil

Common SUP



Component Parts

No.	Description	Material		
		Aluminum base specification	Brass (C37) base specification	Stainless steel base specification
1	Body	Aluminum	Brass (C37)	Stainless steel
2	Tube assembly	Stainless steel		
3	Armature assembly	(NBR, FKM, EPDM, PTFE) Stainless steel, PPS		
4	Return spring	Stainless steel		
5	Solenoid coil	—		
6	O-ring	(NBR, FKM, EPDM, PTFE)		
7	Clip	SK		
8	Base	Aluminum	Brass (C37)	Stainless steel
9	Nut	Brass (C37), (Ni plated)	Brass (C37)	Brass (C37), Ni plated

The materials in parentheses are (No. 6) seal materials.

Model

VXE2

VXED2

VXEZ2

Specifications

Applica-
tions

For Air

For Water

For Oil

Construction

Dimensions




Series VXE21/22/23

For Air/Water/Oil




Dimensions: Single Unit/Body Material: Brass (C37), Stainless Steel

VXE21□0/22□0/23□0




Grommet: G






Conduit: C



DIN terminal: D



Conduit terminal: T



(mm)

Model	Orifice diameter	Port size P	A	B	C	D	E	F	H	Mounting dimension		Electrical entry											
												Grommet		Conduit		DIN terminal			Conduit terminal				
N.C.										J	K	M	Q	R	Q	R	Q	R	S	Q	R	S	T
VXE21□0	ø2, ø3, ø4.5	1/8, 1/4	18	40	68	30	9	19.5	27	M4	6	12.8	30	46	48.5	41	65.5	42	53.5	100.5	41	69.5	82
VXE22□0	ø3, ø4.5, ø6	1/4, 3/8	22	45	78	35	10.5	22.5	32	M5	8	19	33	56	51.5	51	68.5	52	56.5	103.5	51	72.5	93.5
VXE22□0	ø8, ø10	1/4, 3/8, 1/2	30	50	85		14			M5	8	23	33	59	51.5	54	68.5	55	56.5	103.5	54	72.5	100
VXE23□0	ø3, ø4.5, ø6	1/4, 3/8	22	45	85.5	40	10.5	25	36	M5	8	19	36	62	54	57	71	58	59	106	57	75	99.5
VXE23□0	ø8, ø10	1/4, 3/8, 1/2	30	50	92		14			M5	8	23	36	65	54	60	71	61	59	106	60	75	106

Dimensions: Single Unit/Body Material: Brass (C37), Stainless Steel

VXE21□0/22□0/23□0



Specifications with bracket

Orifice: $\phi 2$, $\phi 3$, $\phi 4.5$, $\phi 6$

(Packed in the same container)

Orifice: $\phi 8$, $\phi 10$

(Assembled at the shipment)



(mm)

Model	Orifice diameter	Port size P	Bracket mounting dimension			
			U	W	X	Y
VXE21□0	$\phi 2$, $\phi 3$, $\phi 4.5$	1/8, 1/4	46	36	11	15
VXE22□0	$\phi 3$, $\phi 4.5$, $\phi 6$	1/4, 3/8	56	46	13	17.5
VXE22□0	$\phi 8$, $\phi 10$	1/4, 3/8, 1/2	—	—	—	—
VXE23□0	$\phi 3$, $\phi 4.5$, $\phi 6$	1/4, 3/8	56	46	13	17.5
VXE23□0	$\phi 8$, $\phi 10$	1/4, 3/8, 1/2	—	—	—	—

Model

VXE2

VXED2

VXEZ2

Specifications

Applications

For Air

For Water

For Oil

Construction




Dimensions

Series VXE21/22/23

For Air

Dimensions: Manifold/Base Material: Aluminum

Normally closed (N.C.): VXE21/22/23



(mm)

Model	Dimension	n (stations)								
		2	3	4	5	6	7	8	9	10
VVXE21	L ₁	86	122	158	194	230	266	302	338	374
	L ₂	100	136	172	208	244	280	316	352	388
VVXE22	L ₁	108	154	200	246	292	338	384	430	476
VVXE23	L ₂	126	172	218	264	310	356	402	448	494

(mm)





Model	A	B	(B) Individual SUP	C	D	E	F	H	J	K	M	N	Electrical entry									
													Grommet		Conduit		DIN terminal			Conduit terminal		
													Q	R	S	T	U	V	T	W	X	Y
VVXE21	38	20.5	17.5	10.5	11	25	32	36	12	7	6.5	57.5	30	44.5	48.5	40	53.5	65.5	41	69.5	100.5	72
VVXE22	49	26.5	22.5	13	13	30	40	46	15	9	8.5	66.5	33	54.5	51.5	50	56.5	68.5	51	72.5	103.5	82
VVXE23	49	26.5	22.5	13	13	30	40	46	15	9	8.5	71.5	36	59	54	54	59	71	55	75	106	86

Direct Operated 2 Port Solenoid Valve *Series VXE21/22/23*

For Water/Oil

Dimensions: Manifold/Base Material: Brass (C37), Stainless Steel

VXE21/22/23



Model	Dimension	n (stations)									
		2	3	4	5	6	7	8	9	10	
VXE21	L ₁	69	103.5	138	172.5	207	241.5	276	310.5	345	
	L ₂	81	115.5	150	184.5	219	253.5	288	322.5	357	
	L ₃	93	127.5	162	196.5	231	265.5	300	334.5	369	
VXE22	L ₁	77	115.5	154	192.5	231	269.5	308	346.5	385	
	L ₂	89	127.5	166	204.5	243	281.5	320	358.5	397	
	L ₃	101	139.5	178	216.5	255	293.5	332	370.5	409	
VXE23	L ₁	83	124.5	166	207.5	249	290.5	332	373.5	415	
	L ₂	95	136.5	178	219.5	261	302.5	344	385.5	427	
	L ₃	107	148.5	190	231.5	273	314.5	356	397.5	439	
Manifold construction		2 stations x 1	3 stations x 1	2 stations x 2	2 stations + 3 stations	3 stations x 2	2 stations x 2 + 3 stations	2 stations + 3 stations x 2	3 stations x 3	2 stations x 2 + 3 stations x 2	

Model	A	B	C	D	E	F	H	J	N	Electrical entry									
										Grommet		Conduit		DIN terminal			Conduit terminal		
										Q	R	S	T	U	V	T	W	X	Y
VXE21	49	24.5	20	28	4.5	38	17.3	34.5	56	30	43	48.5	38	53.5	65.5	39	69.5	100.5	70
VXE22	57	28.5	25.5	30	5.5	42	19.3	38.5	64.5	33	52.5	51.5	47.5	56.5	68.5	48.5	72.5	103.5	80
VXE23	57	28.5	25.5	30	5.5	42	20.8	41.5	72.5	36	60	54	55	59	71	56	75	106	87

Model

VXE2

VXED2

VXE22

Specifications

Applications

For Air

For Water

For Oil

Construction

Dimensions

Energy Saving Type

Pilot Operated 2 Port Solenoid Valve

Series VXED21/22/23

For Air/Water/Oil



Valve

Normally closed (N.C.)

Solenoid Coil

Coil: Class B

Rated Voltage

24 VDC, 12 VDC

Material

Body — Brass (C37)/Bronze (CAC407), Stainless steel
Seal — NBR, FKM, EPDM

Electrical Entry

- Grommet
- Conduit
- DIN terminal
- Conduit terminal



Model	VXED2130	VXED2140	VXED2150	VXED2260
Orifice dia.	10 mmø	●	—	—
	15 mmø	—	●	—
	20 mmø	—	—	●
	25 mmø	—	—	●
Port size (Thread)	1/4	3/8	3/4	1
	3/8	1/2		
	1/2			

Model	VXED2270	VXED2380	VXED2390
Orifice dia.	35 mmø	●	—
	40 mmø	—	●
	50 mmø	—	●
Port size (Flange)	32A	40A	50A

Series VXED21/22/23

Common Specifications

Standard Specifications

Valve specifications	Valve construction	Pilot operated 2 port diaphragm type
	Valve type	N.C.
	Withstand pressure	8A to 25A: 5.0 MPa, 32A to 50A: 2.0 MPa
	Body material	Brass (C37), Stainless steel, Bronze (CAC407)
	Seal material	NBR, FKM, EPDM
	Enclosure	Dust tight, Low jetproof (IP65)
	Environment	Location without corrosive or explosive gases
Coil specifications	Rated voltage	24 VDC, 12 VDC
	Allowable voltage fluctuation	±10% of rated voltage
	Allowable leakage voltage	2% or less of rated voltage
	Coil insulation type	Class B
	Surge voltage suppressor	Built-in surge voltage suppressor

Solenoid Coil Specifications

Normally Closed (N.C.)

DC Specification

Model	Power consumption (W) (Holding)	Inrush current (A) (Inrush time: 200 ms)		Temperature increase (C°) <small>Note)</small>
		24 VDC	12 VDC	
VXED2130	1.8	0.23	0.46	30
VXED2140/2150	1.5	0.19	0.38	25
VXED2260/2270	2.3	0.29	0.58	25
VXED2380/2390	3	0.44	0.88	30

Note) Value for ambient temperature at 20°C and when the rated voltage is applied.

Applicable Fluid Check List / All Options (8A to 25A)

VXED2 ³₂ ¹₄ ⁵₀ - - 1 -

● Option symbol

Fluid and application	Option symbol	Seal material	Body material
Air	—	NBR	Brass (C37)
	G		Stainless steel
Water	—	NBR	Brass (C37)
	G		Stainless steel
Oil <small>Note 2)</small>	A	FKM	Brass (C37)
	H		Stainless steel
High corrosive/Oil-free	L <small>Note 1)</small>	FKM	Stainless steel
Copper-free/Fluoro-free <small>Note 3)</small>	J	EPDM	Stainless steel
Other combination	B	EPDM	Brass (C37)

Note 1) The L option is oil-free treatment.

Note 2) The dynamic viscosity of the fluid must not exceed 50 mm²/s.

Note 3) The nuts (non-wetted parts) are nickel plated on the Brass (C37) material.

* If using for other fluids, please consult with SMC.

Applicable Fluid Check List / All Options (32A to 50A)

VXED2 ²₃ ⁷₈ ⁹₀ - - 1 -

● Option symbol

Fluid and application	Option symbol	Seal material	Body material
Air	—	NBR	Bronze (CAC407)
Water	—	NBR	
Oil <small>Note 2)</small>	A	FKM	
Other combination	B	EPDM	

Note 1) The L option is oil-free treatment.

Note 2) The dynamic viscosity of the fluid must not exceed 50 mm²/s or less.

* If using for other fluids, please consult with SMC.

Series VXED21/22/23


For Air

(Inert gas)

Model/Valve Specifications

N.C.

Passage symbol



Port size		Orifice dia. (mmø)	Model	Min. operating pressure differential (MPa)	Max. operating pressure differential (MPa)	Flow characteristics			Max. system pressure (MPa)	Weight (g) ^{Note)}
						C	b	Cv		
Thread (Nominal size)	1/4 (8A)	10	VXED2130-02	0.02	0.7	8.5	0.35	2.0	1.5	420
	3/8 (10A)	10	VXED2130-03			9.2		2.4		
		15	VXED2140-03		1.0	5.0				
	1/2 (15A)	10	VXED2130-04		0.7	9.2		2.4		
		15	VXED2140-04		1.0	20.0		5.5		
	3/4 (20A)	20	VXED2150-06		1.0	38.0		0.30		

Port size		Orifice dia. (mmø)	Model	Min. operating pressure differential (MPa)	Max. operating pressure differential (MPa)	Flow characteristics	Max. system pressure (MPa)	Weight (g) ^{Note)}
						Effective area (mm ²)		
Thread (Nominal size)	1 (25A)	25	VXED2260-10	0.02	1.0	225	1.5	1650
Flange	32A	35	VXED2270-32	0.03		415		5400
	40A	40	VXED2380-40			560		6800
	50A	50	VXED2390-50			880		8400



Note) Weight for the grommet type. Add 10 g for conduit, 30 g for DIN terminal, and 60 g for conduit terminal type respectively.
 • Refer to "Glossary" on page 44 for details on the max. operating pressure differential and the max. system pressure.

Fluid and Ambient Temperature

Fluid temperature (°C)	Ambient temperature (°C)
Solenoid valve option symbol —, G	
-10 to 60	-10 to 60

Note) Dew point temperature: -10°C or less

Valve Leakage

Internal Leakage

Seal material	Leakage (Air)	
	1/4 to 1	32A to 50A
NBR	2 cm ³ /min or less	10 cm ³ /min or less

External Leakage

Seal material	Leakage (Air)	
	1/4 to 1	32A to 50A
NBR	1 cm ³ /min or less	1 cm ³ /min or less

How to Order

DC **VXED** **21** **3** **0** **02** **5** **G1**

Model
Refer to Table (1) shown below for availability.

Orifice diameter
Refer to Table (1) shown below for availability.

Valve/Body configuration

0	N.C. / Single unit
---	--------------------

Solenoid valve option
Refer to Table (2) shown below for availability.

Suffix

-	-
Z	Oil-free


Port size
Refer to Table (1) shown below for availability.

Thread type

-	Rc
T	NPTF
F	G
N	NPT

Rated voltage

5	24 VDC
6	12 VDC





* Refer to Table (3) shown below for availability.
 Refer to page 43 for ordering the coil only.

Bracket

-	None
B	With bracket

* Removal of the bracket is not possible.

Electrical entry

G-Grommet 	C-Conduit 
T -With conduit terminal TL -With conduit terminal and light 	D -DIN terminal DL -DIN terminal with light DO -For DIN terminal (without connector, with gasket) 

* Refer to Table (3) for available combinations between the electrical option (L) and the rated voltage.

Table (1) Model/Orifice Diameter/Port Size Normally Closed (N.C.)

Model		Solenoid valve model (Port size)									Material			
		VXED21	VXED22	VXED23	3 (10 mmø)	4 (15 mmø)	5 (20 mmø)	6 (25 mmø)	7 (35 mmø)	8 (40 mmø)	9 (50 mmø)	Body	Seal	
Port symbol (Port size)	Thread	02 (1/4)	—	—	●	—	—	—	—	—	—	Brass (C37)	NBR	
		03 (3/8)	—	—	●	—	—	—	—	—	—			
		04 (1/2)	—	—	●	—	—	—	—	—	—			
		06 (3/4)	—	—	—	—	●	—	—	—	—			
	Flange	—	10 (1)	—	—	—	—	●	—	—	—			Stainless steel
		—	32 (32A)	—	—	—	—	—	●	—	—			
		—	—	40 (40A)	—	—	—	—	—	●	—			
		—	—	50 (50A)	—	—	—	—	—	—	●			

Table (2) Solenoid Valve Option

Option symbol	Seal material	Body material
—	NBR	Brass (C37), Bronze (CAC407)
G (Note)		Stainless steel

Note) The G option (stainless steel specification) is for port size 1/4 to 1 only.

Table (3) Rated Voltage – Electrical Option

Rated voltage		L (With light)
Voltage symbol	Voltage	
5	24 VDC	●
6	12 VDC	—


Model
VXE2
VXED2
VXE22
Specifications
Applications
For Air
For Water
For Oil
Dimensions
Construction

Series VXED21/22/23

For Water

Model/Valve Specifications

N.C.



Port size	Orifice dia. (mmø)	Model	Min. operating pressure differential (MPa)	Max. operating pressure differential (MPa)	Flow characteristics		Max. system pressure (MPa)	Weight (g) ^(Note)
					Av x 10 ⁻⁶ m ²	Cv converted		
Thread (Nominal size)	1/4 (8A)	VXED2130-02	0.02	0.5	46	1.9	1.5	420
	3/8 (10A)	VXED2130-03			58	2.4		670
		15		VXED2140-03	1.0	110		4.5
	1/2 (15A)	10		VXED2130-04		58		2.4
		15		VXED2140-04	1.0	130		5.5
	3/4 (20A)	20		VXED2150-06		230		9.5
Flange	1 (25A)	VXED2260-10	0.03	1.0	310	13	5400	
	32A	VXED2270-32			550	23	6800	
	40A	VXED2380-40			740	31	8400	
	50A	VXED2390-50			1200	49	8400	

Note) Weight for the grommet type. Add 10 g for conduit, 30 g for DIN terminal, and 60 g for conduit terminal type respectively.
 • Refer to "Glossary" on page 44 for details on the max. operating pressure differential and the max. system pressure.

Fluid and Ambient Temperature

Fluid temperature (°C)	Ambient temperature (°C)
Solenoid valve option symbol	
—, G, L	-10 to 60
1 to 60	

Note) With no freezing

Valve Leakage



Internal Leakage

Seal material	Leakage (Water)	
	1/4 to 1	32A to 50A
NBR, FKM	0.2 cm ³ /min or less	1 cm ³ /min or less

External Leakage

Seal material	Leakage (Water)	
	1/4 to 1	32A to 50A
NBR, FKM	0.1 cm ³ /min or less	0.1 cm ³ /min or less

How to Order



* Refer to Table (3) for available combinations between the electrical option (L) and the rated voltage.

Table (1) Model/Orifice Diameter/Port Size
Normally Closed (N.C.)

Solenoid valve model (Port size)				Orifice diameter							Material	
Model	VXED21	VXED22	VXED23	3 (10 mmø)	4 (15 mmø)	5 (20 mmø)	6 (25 mmø)	7 (35 mmø)	8 (40 mmø)	9 (50 mmø)	Body	Seal
Port symbol (Port size)	Thread	02 (1/4)	—	—	●	—	—	—	—	—	Brass (C37) Stainless steel	NBR FKM
		03 (3/8)	—	—	●	●	—	—	—	—		
		04 (1/2)	—	—	●	●	—	—	—	—		
	06 (3/4)	—	—	—	—	●	—	—	—			
	—	10 (1)	—	—	—	—	●	—	—			
	—	32 (32A)	—	—	—	—	—	●	—			
Flange	—	—	40 (40A)	—	—	—	—	—	●	Bronze (CAC407)		
	—	—	50 (50A)	—	—	—	—	—	●			
	—	—	—	—	—	—	—	—	●			

Table (2) Solenoid Valve Option

Option symbol	Seal material	Body material	Note
—	NBR	Brass (C37), Bronze (CAC407)	—
G (Note)		Stainless steel	
L (Note)	FKM	Stainless steel	High corrosive/Oil-free

Note) The G and L options (stainless steel specification) are for port size 1/4 to 1 only.

Table (3) Rated Voltage – Electrical Option

Rated voltage		L (With light)
Voltage symbol	Voltage	
5	24 VDC	●
6	12 VDC	—

Model

VXE2

VXED2

VXE22

Specifications

Applications

For Air

For Water

For Oil

Construction

Dimensions


⚠ When the fluid is oil.

The dynamic viscosity of the fluid must not exceed 50 mm²/s.

For Oil

Model/Valve Specifications

N.C.



Port size	Orifice dia. (mmø)	Model	Min. operating pressure differential (MPa)	Max. operating pressure differential (MPa)	Flow characteristics		Max. system pressure (MPa)	Weight (g) ^(Note)
					Av x 10 ⁻⁶ m ²	Cv converted		
Thread (Nominal size)	1/4 (8A)	VXED2130-02	0.02	0.4	46	1.9	1.5	420
	3/8 (10A)	VXED2130-03			58	2.4		670
		VXED2140-03		110	4.5	500		
	1/2 (15A)	VXED2130-04		58	2.4	670		
		VXED2140-04		130	5.5	1150		
	3/4 (20A)	VXED2150-06		230	9.5	1650		
Flange	1 (25A)	VXED2260-10	0.03	0.7	310	13	5400	
	32A	VXED2270-32			550	23	6800	
	40A	VXED2380-40		740	31	8400		
	50A	VXED2390-50		1200	49	8400		

Note) Weight for the grommet type. Add 10 g for conduit, 30 g for DIN terminal, and 60 g for conduit terminal type respectively.
• Refer to "Glossary" on page 44 for details on the max. operating pressure differential and the max. system pressure.

Fluid and Ambient Temperature

Fluid temperature (°C)	Ambient temperature (°C)
Solenoid valve option symbol	
A, H	
-5 to 60	-10 to 60

Note) Dynamic viscosity: 50 mm²/s or less

Valve Leakage

Internal Leakage

Seal material	Leakage (Oil)	
	1/4 to 1	32A to 50A
FKM	0.2 cm ³ /min or less	1 cm ³ /min or less

External Leakage

Seal material	Leakage (Oil)	
	1/4 to 1	32A to 50A
FKM	0.1 cm ³ /min or less	0.1 cm ³ /min or less

How to Order

DC VXED 21 3 0 - 02 - 5 G 1 -

Model
Refer to Table (1) shown below for availability.

Orifice diameter
Refer to Table (1) shown below for availability.

Valve/Body configuration
0 N.C. / Single unit

Solenoid valve option
Refer to Table (2) shown below for availability.

Suffix

-	-
Z	Oil-free

Port size
Refer to Table (1) shown below for availability.

Thread type

-	Rc
T	NPTF
F	G
N	NPT

Rated voltage

5	24 VDC
6	12 VDC

* Refer to Table (3) shown below for availability.





Bracket

-	None
B	With bracket

* Removal of bracket is not possible.

* Refer to page 43 for ordering the coil only.

Electrical entry

G-Grommet 	C-Conduit 
T -With conduit terminal TL -With conduit terminal and light 	D -DIN terminal DL -DIN terminal with light DO -For DIN terminal (without connector, with gasket) 

* Refer to Table (3) for available combinations between the electrical option (L) and the rated voltage.

Table (1) Model/Orifice Diameter/Port Size
Normally Closed (N.C.)

Solenoid valve model (Port size)				Orifice diameter							Material	
Model	VXED21	VXED22	VXED23	3 (10 mmø)	4 (15 mmø)	5 (20 mmø)	6 (25 mmø)	7 (35 mmø)	8 (40 mmø)	9 (50 mmø)	Body	Seal
Port symbol (Port size)	Thread	02 (1/4)	—	—	●	—	—	—	—	—	Brass (C37) Stainless steel FKM	FKM
		03 (3/8)	—	—	●	●	—	—	—	—		
		04 (1/2)	—	—	●	●	—	—	—	—		
	06 (3/4)	—	—	—	—	●	—	—	—			
	—	10 (1)	—	—	—	—	●	—	—	—		
	—	32 (32A)	—	—	—	—	—	●	—	—		
Flange	—	—	40 (40A)	—	—	—	—	—	●	—	Bronze (CAC407)	FKM
	—	—	50 (50A)	—	—	—	—	—	—	●		
	—	—	—	—	—	—	—	—	—	—		

Table (2) Solenoid Valve Option

Option symbol	Seal material	Body material
A	FKM	Brass (C37), Bronze (CAC407)
H (Note)		Stainless steel

Note) The H option (stainless steel specification) is for port size 1/4 to 1 only.

Table (3) Rated Voltage – Electrical Option

Rated voltage		L (With light)
Voltage symbol	Voltage	
5	24 VDC	●
6	12 VDC	—

Model

VXE2

VXED2

VXE2

Specifications

Applications

For Air

For Water

For Oil

Construction

Dimensions

Series VXED21/22/23

For Air/Water/Oil



Construction

Normally closed (N.C.)


Body material: Brass (C37) (32A or more: Bronze (CAC407), Stainless steel (32A or more: not available)

VXED2130 (8A/10A)

VXED2140/2150/2260
(10A to 25A)



VXED2270/2380/2390 (32A to 50A)



Working principle

<Valve opened>

When the coil ⑪ is energised, the armature assembly ⑨ is attracted into the core of the tube assembly ⑧ and the pilot valve ① opens. Then the pressure in the pressure action chamber ② falls to open the main valve ③.

<Valve closed>

When the coil ⑪ is not energised, the pilot valve ① is closed and the pressure in the pressure action chamber ② rises and the main valve ③ closes.

Component Parts

No.	Description	Size	Material	
			Brass (C37), Bronze (CAC407) body specification	Stainless steel body specification
1	Body	8A to 25A	Brass (C37)	Stainless steel
		32A to 50A	Bronze (CAC407)	—
2	Bonnet	8A to 25A	Brass (C37)	Stainless steel
		32A to 50A	Bronze (CAC407)	—
3	Nut	8A to 50A	Brass (C37)	Brass (C37), Ni plated
4	O-ring	32A to 50A	(NBR, FKM, EPDM)	
5	O-ring	8A to 50A	(NBR, FKM, EPDM)	
6	Diaphragm assembly	8A to 25A	(NBR, FKM, EPDM) Stainless steel	
		32A to 50A	(NBR, FKM, EPDM) Stainless steel, Brass (C37)	(NBR, FKM, EPDM) Stainless steel
7	Valve spring	8A to 50A	Stainless steel	
8	Tube assembly	8A to 50A	Stainless steel	
9	Armature assembly	8A to 50A	(NBR, FKM, EPDM) Stainless steel, PPS	
10	Return spring	8A to 50A	Stainless steel	
11	Solenoid coil	8A to 50A	—	
12	Clip	8A to 50A	SK	



The materials in parentheses are seal materials.

Dimensions: Single Unit/Body Material: Brass (C37), Stainless Steel

VXED2130



Grommet: G

Conduit: C





DIN terminal: D

Conduit terminal: T



With bracket



Model	Port size P	A	B	K	L	M	Electrical entry									Bracket mounting dimension		
							Grommet		Conduit		DIN terminal			Conduit terminal			a	b
							T	U	T	U	T	U	V	T	U	V		
N.C.							T	U	T	U	T	U	V	T	U	V	a	b
VXED2130	1/4, 3/8	80.5	11	20	30	22	58	30	53	48.5	54	65.5	53.5	53	100.5	69.5	26	32
	1/2	86	14.5	24	26	28	60	30	55	48.5	56	65.5	53.5	55	100.5	69.5	28	34

(mm)

Model

VXE2

VXED2

VXEZ2

Specifications

Applications

For Air

For Water

For Oil

Construction

Dimensions


Series VXED21/22/23

For Air/Water/Oil


Dimensions: Single Unit/Body Material: Brass (C37), Stainless Steel

VXED2140/2150/2260


Grommet: G




Conduit: C




DIN terminal: D



Conduit terminal: T



With bracket



Model	Port size P	A	B	C	D	E	F	H	I	J	K	L	M	Electrical entry						Bracket mounting dimension								
														Grommet		Conduit		DIN terminal		Conduit terminal		a	b	d	e	f		
														T	U	T	U	T	U	V	T	U	V					
VXED2140	3/8, 1/2	103.5	24	30	63	19.5	3.5	27	14	44.5	29	34	28	67.5	30	62.5	48.5	63.5	65.5	53.5	62.5	100.5	69.5	42	66	57	34	39
VXED2150	3/4	115	29	30	80	19.5	4.5	27	17	51.5	37	43	35	74	30	69	48.5	70	65.5	53.5	69	100.5	69.5	51	78	74	51	45.5
VXED2260	1	133	33	35	90	22.5	4.5	32	20	60	43	47	42	88	33	83	51.5	84	68.5	56.5	83	103.5	72.5	56	86	81	58	49.5



Pilot Operated 2 Port Solenoid Valve *Series VXED21/22/23*

For Air/Water/Oil


Dimensions: Single Unit/Body Material: Brass (C37), Stainless Steel

VXED2270/2380/2390


Grommet: G




Conduit: C



DIN terminal: D



Conduit terminal: T




Model	Applicable flange	Body Dimensions (mm)											Electrical entry													
		A	B	C	D	E	F	H	N	Q	R	S	Grommet			Conduit			DIN terminal			Conduit terminal				
		T	U	T	U	T	U	V	T	U	V	T	U	V	T	U	V	T	U	V						
N.C.																										
VXED2270	32A	172.5	67.5	35	160	22.5	51.5	32	135	12	100	36	93	33	88	51.5	89	68.5	56.5	88	103.5	72.5				
VXED2380	40A	185	70	40	170	25	54.5	36	140	14	105	42	103	36	98	54	99	71	59	98	106	75				
VXED2390	50A	198	77.5	40	180	25	59	36	155	14	120	52	108.5	36	103.5	54	104.5	71	59	103.5	106	75				

Energy Saving Type

Zero Differential Pressure Type Pilot Operated 2 Port Solenoid Valve

Series VXEZ22/23

For Air/Water/Oil



■ Valve

Normally closed (N.C.)

■ Solenoid Coil


Coil: Class B

■ Rated Voltage

24 VDC, 12 VDC

■ Material

Body — Brass (C37), Stainless steel
Seal — NBR, FKM, EPDM



■ Electrical Entry

- Grommet
- Conduit
- DIN terminal
- Conduit terminal

Model		VXEZ2230	VXEZ2240	VXEZ2350	VXEZ2360
Orifice dia.	10 mmø	●	—	—	—
	15 mmø	—	●	—	—
	20 mmø	—	—	●	—
	25 mmø	—	—	—	●
Port size (Nominal size)		1/4 (8A) 3/8 (10A)	1/2 (15A)	3/4 (20A)	1 (25A)

Series VXEZ22/23

Common Specifications

Standard Specifications

Valve specifications	Valve construction	Zero differential pressure type pilot operated 2 port diaphragm type
	Valve type	N.C.
	Withstand pressure	5.0 MPa
	Body material	Brass (C37), Stainless steel
	Seal material	NBR, FKM, EPDM
	Enclosure	Dust tight, Low jetproof (IP65)*
	Environment	Location without corrosive or explosive gases
Coil specifications	Rated voltage	24 VDC, 12 VDC
	Allowable voltage fluctuation	±10% of rated voltage
	Allowable leakage voltage	2% or less of rated voltage
	Coil insulation type	Class B
	Surge voltage suppressor	Built-in surge voltage suppressor

Solenoid Coil Specifications

DC Specification (Class B coil only)

Model	Power consumption (W) (Holding)	Inrush current (A) (Inrush time: 200 ms)		Temperature increase (C°) <small>Note)</small>
		24 VDC	12 VDC	
VXEZ22	2.3	0.29	0.58	25
VXEZ23	3	0.44	0.88	30

Note) Value for ambient temperature at 20°C and when the rated voltage is applied.

Applicable Fluid Check List / All Options

VXEZ2 0 - - 1 -

• Option symbol

Fluid and application	Option symbol	Seal material	Body material
Air	—	NBR	Brass (C37)
	G		Stainless steel
Water	—	NBR	Brass (C37)
	G		Stainless steel
Oil <small>Note 2)</small>	A	FKM	Brass (C37)
	H		Stainless steel
High corrosive/Oil-free	L <small>Note 1)</small>	FKM	Stainless steel
Copper-free/Fluoro-free <small>Note 3)</small>	J	EPDM	Stainless steel
Other combination	B	EPDM	Brass (C37)

Note 1) The L option is oil-free treatment.

Note 2) The dynamic viscosity of the fluid must not exceed 50 mm²/s or less.

Note 3) The nuts (non-wetted parts) are nickel plated on the brass (C37) material.

* If used for other fluids, please consult with SMC.

Series VXEZ22/23


For Air

(Inert gas)

Model/Valve Specifications

N.C.

Passage symbol



Normally Closed (N.C.)

Port size (Nominal size)	Orifice dia. (mmø)	Model	Min. operating pressure differential (MPa)	Max. operating pressure differential (MPa)	Flow characteristics			Max. system pressure (MPa)	Weight (g)
					C	b	Cv		
1/4 (8A)	10	VXEZ2230-02	0	0.7	8.5	0.44	2.4	1.5	550
3/8 (10A)		VXEZ2230-03			11.0	0.42	2.8		
1/2 (15A)	VXEZ2240-04	23.0			0.34	6.0	760		
3/4 (20A)	VXEZ2350-06	38.0			0.20	9.5			1300

Port size (Nominal size)	Orifice dia. (mmø)	Model	Min. operating pressure differential (MPa)	Max. operating pressure differential (MPa)	Flow characteristics	Max. system pressure (MPa)	Weight (g)
					Effective area (mm ²)		
1 (25A)	25	VXEZ2360-10	0	0.7	215	1.5	1480

* Weight for the grommet type. Add 10 g for conduit, 30 g for DIN terminal, and 60 g for conduit terminal type respectively.

• Refer to "Glossary" on page 44 for details on the max. operating pressure differential and the max. system pressure.

Fluid and Ambient Temperature

Fluid temperature (°C)	Ambient temperature (°C)
Solenoid valve option symbol —, G	
–10 to 60 ^{Note)}	–10 to 60

Note) Dew point temperature: –10°C or less

Valve Leakage

Internal Leakage

Seal material	Leakage (Air)
NBR	1 cm ³ /min or less

External Leakage

Seal material	Leakage (Air)
NBR	1 cm ³ /min or less

How to Order

DC

VXEZ

22

3

0

-

02

-

5

G

1

-

-

Model
Refer to Table (1) shown below for availability.

Orifice diameter
Refer to Table (1) shown below for availability.

Valve/Body configuration

0	N.C. / Single unit
---	--------------------

Solenoid valve option
Refer to Table (2) shown below for availability.

Suffix

-	-
Z	Oil-free

Port size
Refer to Table (1) shown below for availability.

Thread type

-	Rc
T	NPTF
F	G
N	NPT

Rated voltage

5	24 VDC
6	12 VDC

* Refer to Table (3) shown below for availability.
 Refer to page 43 for ordering coil only.

Bracket

-	None
B	With bracket

* Removal of bracket is not possible.

Electrical entry

G-Grommet 	C-Conduit
T -With conduit terminal TL -With conduit terminal and light 	D -DIN terminal DL -DIN terminal with light DO -For DIN terminal (without connector, with gasket)

* Refer to Table (3) for available combinations between the electrical option (L) and the rated voltage.

**Table (1) Model/Orifice Diameter/Port Size
Normally Closed (N.C.) / Normally Open (N.O.)**

Solenoid valve model (Port size)		Orifice symbol (diameter)				
Model	VXEZ22	VXEZ23	3 (10 mmø)	4 (15 mmø)	5 (20 mmø)	6 (25 mmø)
Port symbol (Port size)	02 (1/4)	—	●	—	—	—
	03 (3/8)	—	●	—	—	—
	04 (1/2)	—	—	●	—	—
	—	06 (3/4)	—	—	●	—
—	10 (1)	—	—	—	●	—

Table (2) Solenoid Valve Option

Option symbol	Seal material	Body material	Note
—	NBR	Brass (C37)	—
G		Stainless steel	

Table (3) Rated Voltage – Electrical Option

Rated voltage		L (With light)
Voltage symbol	Voltage	
5	24 VDC	●
6	12 VDC	—

Model
VXE2
VXED2
VXEZ2
Specifications
Applications
For Air
For Water
For Oil
Dimensions
Construction


Series VXEZ22/23

For Water

Model/Valve Specifications

N.C.

Passage symbol



Normally Closed (N.C.)

Port size (Nominal size)	Orifice dia. (mmø)	Model	Min. operating pressure differential (MPa)	Max. operating pressure differential (MPa)	Flow characteristics		Max. system pressure (MPa)	Weight (g)
					Av x 10 ⁻⁶ m ²	Cv converted		
1/4 (8A)	10	VXEZ2230-02	0	0.7	46	1.9	1.5	550
3/8 (10A)		VXEZ2230-03			58	2.4		
1/2 (15A)	VXEZ2240-04	130			5.3			
3/4 (20A)	VXEZ2350-06	220		9.2				
1 (25A)	VXEZ2360-10	290		12.0				

* Weight for the grommet type. Add 10 g for conduit, 30 g for DIN terminal, and 60 g for conduit terminal type respectively.

• Refer to "Glossary" on page 44 for details on the max. operating pressure differential and the max. system pressure.

Fluid and Ambient Temperature

Fluid temperature (°C)	Ambient temperature (°C)
Solenoid valve option symbol —, G, L	
1 to 60	-10 to 60



* With no freezing

Valve Leakage

Internal Leakage

Seal material	Leakage (Water)
NBR, FKM	0.1 cm ³ /min or less

External Leakage

Seal material	Leakage (Water)
NBR, FKM	0.1 cm ³ /min or less

How to Order

DC

VXEZ 22 3 0 [] [] - 02 [] - 5 G 1 - []

Model

Model
Refer to Table (1) shown below for availability.

Orifice diameter
Refer to Table (1) shown below for availability.

Valve/Body configuration
0 N.O. / Single unit

Solenoid valve option
Refer to Table (2) shown below for availability.

Suffix

-	-
Z	Oil-free

Select "-" because the solenoid valve L option is oil-free treatment.

Port size
Refer to Table (1) shown below for availability.

Thread type

-	Rc
T	NPTF
F	G
N	NPT

Rated voltage

5	24 VDC
6	12 VDC

* Refer to Table (3) shown below for availability.

Refer to page 43 for ordering the coil only.

Bracket

-	None
B	With bracket

* Removal of the bracket is not possible.

Electrical entry

<p>G- Grommet</p>	<p>C- Conduit</p>
<p>T -With conduit terminal TL -With conduit terminal and light</p>	<p>D -DIN terminal DL -DIN terminal with light DO -For DIN terminal (without connector, with gasket)</p> <p>Connector</p>

* Refer to Table (3) for available combinations between the electrical option (L) and the rated voltage.

**Table (1) Model/Orifice Diameter/Port Size
Normally Closed (N.C.) / Normally Open (N.O.)**

Solenoid valve model (Port size)		Orifice symbol (diameter)				
Model	VXEZ22	VXEZ23	3 (10 mmø)	4 (15 mmø)	5 (20 mmø)	6 (25 mmø)
Port symbol (Port size)	02 (1/4)	—	●	—	—	—
	03 (3/8)	—	●	—	—	—
	04 (1/2)	—	—	●	—	—
	—	06 (3/4)	—	—	●	—
	—	10 (1)	—	—	—	●

Table (2) Solenoid Valve Option

Option symbol	Seal material	Body material	Note
—	NBR	Brass (C37)	—
G		Stainless steel	
L	FKM	Stainless steel	High corrosive/Oil-free

Table (3) Rated Voltage – Electrical Option

Rated voltage		L (With light)
Voltage symbol	Voltage	
5	24 VDC	●
6	12 VDC	—

Model

VXE2

VXED2

VXEZ2

Specifications

Applications

For Air

For Water

For Oil

Construction

Dimensions

Series VXEZ22/23


For Oil

⚠ When the fluid is oil.
The dynamic viscosity of the fluid must not exceed 50 mm²/s.

Model/Valve Specifications

N.C.

Passage symbol



Normally Closed (N.C.)

Port size (Nominal size)	Orifice dia. (mmø)	Model	Min. operating pressure differential (MPa)	Max. operating pressure differential (MPa)	Flow characteristics		Max. system pressure (MPa)	Weight (g)
					Av x 10 ⁻⁶ m ²	Cv converted		
1/4 (8A)	10	VXEZ2230-02	0	0.7	46	1.9	1.5	550
3/8 (10A)		VXEZ2230-03			58	2.4		
1/2 (15A)	VXEZ2240-04	130			5.3			
3/4 (20A)	VXEZ2350-06	220			9.2			
1 (25A)	VXEZ2360-10	290			12.0			

- * Weight for the grommet type. Add 10 g for conduit, 30 g for DIN terminal, and 60 g for conduit terminal type respectively.
- Refer to "Glossary" on page 44 for details on the max. operating pressure differential and the max. system pressure.

Fluid and Ambient Temperature

Fluid temperature (°C)	Ambient temperature (°C)
Solenoid valve option symbol A, H	
-5 to 60	-10 to 60



Note) Dynamic viscosity: 50 mm²/s or less

Valve Leakage

Internal Leakage

Seal material	Leakage (Oil)
FKM	0.1 cm ³ /min or less

External Leakage

Seal material	Leakage (Oil)
FKM	0.1 cm ³ /min or less

How to Order

DC **VXEZ** **22** **3** **0** **-02** **-5** **G** **1**

Model
Refer to Table (1) shown below for availability.

Orifice diameter
Refer to Table (1) shown below for availability.

Valve/Body configuration
0 N.C. / Single unit

Solenoid valve option
Refer to Table (2) shown below for availability.

Suffix

-	-
Z	Oil-free

Port size
Refer to Table (1) shown below for availability.

Bracket

-	None
B	With bracket

* Removal of the bracket is not possible.

Rated voltage

5	24 VDC
6	12 VDC

* Refer to Table (3) shown below for availability.

Refer to page 43 for ordering the coil only.

Thread type

-	Rc
T	NPTF
F	G
N	NPT

Electrical entry

<p>G- Grommet</p>	<p>C-Conduit</p>
<p>T -With conduit terminal TL -With conduit terminal and light</p>	<p>D -DIN terminal DL -DIN terminal with light DO -For DIN terminal (without connector, with gasket)</p>

* Refer to Table (3) for available combinations between the electrical option (L) and the rated voltage.

**Table (1) Model/Orifice Diameter/Port Size
Normally Closed (N.C.) / Normally Open (N.O.)**

Solenoid valve model (Port size)		Orifice symbol (diameter)				
Model	VXEZ22	VXEZ23	3 (10 mmø)	4 (15 mmø)	5 (20 mmø)	6 (25 mmø)
Port symbol (Port size)	02 (1/4)	—	●	—	—	—
	03 (3/8)	—	●	—	—	—
	04 (1/2)	—	—	●	—	—
	—	06 (3/4)	—	—	●	—
	—	10 (1)	—	—	—	●

Table (2) Solenoid Valve Option

Option symbol	Seal material	Body material
A	FKM	Brass (C37)
H		Stainless steel

Table (3) Rated Voltage – Electrical Option

Rated voltage		L (With light)
Voltage symbol	Voltage	
5	24 VDC	●
6	12 VDC	—

Model

VXE2

VXED2

VXEZ2

Specifications

Applications

For Air

For Water

For Oil

Dimensions

Construction


Series VXEZ22/23

For Air/Water/Oil

Construction

Normally closed (N.C.)

Body material: Brass (C37), Stainless steel



Working principle

<Valve opened – when there is pressure>

When the coil ⑨ is energised, the armature assembly ⑦ is attracted into the core of the tube assembly ⑧ and the pilot valve ① is opened.

When the pilot valve is opened, the pressure inside the pilot chamber ⑥ decreases, resulting in the pressure difference from the inlet pressure. Then the diaphragm assembly ③ is lifted and the main valve ② is opened.

<Valve opened – when there is no pressure or under low minute pressure>

The armature assembly ⑦ and the diaphragm assembly ③ are connected to each other with the lift spring ⑩. When the armature assembly is attracted, the diaphragm assembly is pulled up and the main valve ② is opened.

<Valve closed>

When the coil ⑨ is de-energised, the armature assembly ⑦ returns by the reacting force of the return spring ④ and the pilot valve ① is closed.

When the pilot valve is closed, the pressure inside the pilot chamber ⑥ increases, resulting in the loss of pressure difference from the inlet and the main valve ② is closed.

Component Parts


No.	Description	Material	
		Brass (C37) body specification	Stainless steel body specification
1	Body	Brass (C37)	Stainless steel
2	Bonnet	Brass (C37)	Stainless steel
3	Diaphragm assembly	(NBR, FKM, EPDM) Stainless steel	
4	Return spring	Stainless steel	
5	O-ring	(NBR, FKM, EPDM)	
6	Nut	Brass (C37)	Brass (C37), Ni plated
7	Armature assembly	(NBR, FKM, EPDM) Stainless steel, PPS	
8	Tube assembly	Stainless steel	
9	Solenoid coil	—	
10	Lift spring	Stainless steel	
11	Hexagon socket bolt	Stainless steel	
12	Clip	SK	

The materials in parentheses are seal materials.


Dimensions: Body Material: Brass (C37), Stainless Steel

VXEZ22□0/23□0


Grommet: G




Conduit: C




DIN terminal: D



Conduit terminal: T



With bracket



(mm)

Model	Port size P	A	B	C	D	E	F	H	J	K
N.C.										
VXEZ2230	1/4, 3/8	90	11	35	50	22.5	30	20	22	40
VXEZ2240	1/2	98	14	35	63	22.5	37	26	29.5	52
VXEZ2350	3/4	110	18	40	80	25	47.5	32.5	36	65
VXEZ2360	1/1	116.5	21	40	90	25	55	35	40.5	70

(mm)

Model	Port size P	a	b	d	e	f	g	h	i	Electrical entry									
										Grommet		Conduit		DIN terminal			Conduit terminal		
N.C.										L	M	L	M	L	M	N	L	M	N
VXEZ2230	1/4, 3/8	52	67	14	1.6	26	5.5	7.5	28	77.5	33	72.5	51.5	73.5	68.5	56.5	72.5	103.5	72.5
VXEZ2240	1/2	60	75	17	2.3	33	6.5	8.5	35	85.5	33	80.5	51.5	81.5	68.5	56.5	80.5	103.5	72.5
VXEZ2350	3/4	68	87	22	2.6	40	6.5	9	43	97.5	36	92.5	54	93.5	71	59	92.5	106	75
VXEZ2360	1/1	73	92	22	2.6	45.5	6.5	9	45	104	36	99	54	100	71	59	99	106	75

Series VXE□21/22/23

For Air/Water/Oil

Replacement Parts

● Solenoid coil assembly part no.

VXE02 **1** N-**1** G E-□

Series

1	VXE□21
2	VXE□22□□
3	VXE□23□□

Valve

Symbol	Model
Z	VXED2130
—	Others

Rated voltage (Note)

5	24 VDC
6	12 VDC

Note) Refer to Table (1) for available combinations.

Electrical entry

<p>G-Grommet</p>	<p>C-Conduit</p>
<p>T - With conduit terminal TL - With conduit terminal and light</p>	<p>D - DIN terminal DL - DIN terminal with light DO - For DIN terminal (without connector, with gasket)</p> <p>Connector</p>


* Refer to Table (1) for available combinations between the electrical option and the rated voltage.

● Clip part no.

For VXE□21: VX021N-10

For VXE□22: VX022N-10


For VXE□23: VX023N-10



● DIN connector part no.

Without electrical option **GDM2A**

With electrical option **GDM2A-□□**



Electrical option

L With light

* Refer to Table (1) for available combinations between electrical option (L) and rated voltage.

Rated voltage

5	24 VDC
6	12 VDC

Table (1) Rated Voltage – Electrical Option

Rated voltage		L (With light)
Voltage symbol	Voltage	
5	24 VDC	●
6	12 VDC	—

● Gasket part no. for DIN connector **VCW20-1-29-1**

● Name plate part no.

AZ-T-VX Valve model

↑ Enter by referring to "How to Order" (Single Unit).

AZ-T-VXE □□□□□□□□ - □□ - □□□□□□ 1-□

Valve model

Glossary

Pressure Terminology

1. Maximum operating pressure differential

The maximum pressure differential (the difference between the inlet and outlet pressure) which is allowed for operation, with the valve closed or open. When the outlet pressure is 0 MPa, this becomes the maximum operating pressure.

2. Minimum operating pressure differential

The minimum pressure differential (the difference between the inlet pressure and outlet pressure) required to keep the main valve fully opened.

3. Maximum system pressure

The maximum pressure that can be applied inside the pipelines (line pressure).
(The pressure differential of the solenoid valve portion must be less than the maximum operating pressure differential.)

4. Proof pressure

The pressure at which the valve must be withstood without a drop in performance after holding for one minute under the prescribed pressure and returning to the operating pressure range. (value under the prescribed conditions)

Electrical Terminology

1. Surge voltage

A high voltage which is momentarily generated by shutting off the power in the shut-off area.

2. Enclosure

A degree of protection defined in the "JIS C 0920: Waterproof test of electric machinery/appliance and the degree of protection against the intrusion of solid foreign objects".

IP65: Dust tight, Low jetproof type

"Low jetproof type" means that no water intrudes inside an equipment that could hinder from operating normally by means of applying water for 3 minutes in the prescribed manner. Take appropriate protection measures, since a device is not usable in an environment where a droplet of water is splashed.

Others

1. Material

NBR: Nitrile rubber

FKM: Fluoro rubber – Trade name: Viton®, Dai-el®, etc.

EPDM: Ethylene propylene rubber

PTFE: Polytetrafluoroethylene resin – Trade name: Teflon®, Polyflon®, etc.

2. Oil-free treatment

The degreasing and washing of wetted parts.

3. Passage symbol

In the JIS symbol (□□□[⊕]) IN and OUT are in a blocked condition (⊕), but actually in the case of reverse pressure (OUT>IN), there is a limit to the blocking.

(◇) is used to indicate that blocking of reverse pressure is not possible.






Series VXE

Safety Instructions

These safety instructions are intended to prevent a hazardous situation and/or equipment damage. These instructions indicate the level of potential hazard by labels of "Caution", "Warning" or "Danger". To ensure safety, be sure to observe ISO 4414 ^{Note 1)}, JIS B 8370 ^{Note 2)} and other safety practices.

■ Explanation of the Labels

Labels	Explanation of the labels
 Danger	In extreme conditions, there is a possible result of serious injury or loss of life.
 Warning	Operator error could result in serious injury or loss of life.
 Caution	Operator error could result in injury ^{Note 3)} or equipment damage. ^{Note 4)}

Note 1) ISO 4414: Pneumatic fluid power – General rules relating to systems

Note 2) JIS B 8370: General Rules for Pneumatic Equipment

Note 3) Injury indicates light wounds, burns and electrical shocks that do not require hospitalisation or hospital visits for long-term medical treatment.

Note 4) Equipment damage refers to extensive damage to the equipment and surrounding devices.

■ Selection/Handling/Applications

1. The compatibility of equipment is the responsibility of the person who designs the system or decides its specifications.

Since the products specified here are used in various operating conditions, their compatibility with a specific system must be based on specifications, post analysis and/or tests to meet a specific requirement. The expected performance and safety assurance will be the responsibility of the person who has determined the compatibility of the system. This person should continuously review the suitability of all items specified, referring to the latest catalog information and taking into consideration the possibility of equipment failure when configuring a system. Be particularly careful in determining the compatibility with the fluid to be used.

2. Only trained personnel should operate machinery and equipment.

Fluids can be dangerous if handled incorrectly. Assembly, handling or maintenance of the system should be performed by trained and experienced operators.

3. Do not service machinery/equipment or attempt to remove components until the safety is confirmed.

1. Inspection and maintenance of machinery/equipment should only be performed once measures to prevent falling or runaway of the driven object have been confirmed. Measures to prevent danger from a fluid should also be confirmed.
2. When equipment is to be removed, confirm the safety processes mentioned above, release the fluid pressure and be certain there is no danger from fluid leakage or fluid remaining in the system.
3. Carefully restart the machinery, confirming that safety measures are being implemented.

4. If the equipment will be used in the following conditions or environment, please contact SMC first and be sure to take all necessary safety precautions.

1. Conditions and environments beyond the given specifications, or if product is used outdoors.
2. With fluids whose application causes concern due to the type of fluid or additives, etc.
3. An application which has the possibility of having a negative effect on people and/or property, and therefore requires special safety analysis.

■ Exemption from Liability

1. SMC, its officers and employees shall be exempted from liability for any loss or damage arising out of earthquakes or fire, action by a third person, accidents, customer error with or without intention, product misuse, and any other damages caused by abnormal operating conditions.

2. SMC, its officers and employees shall be exempted from liability for any direct or indirect loss or damage, including consequential loss or damage, loss of profits or loss of chance, claims, demands, proceedings, costs, expenses, awards, judgments and any other liability whatsoever including legal costs and expenses which may be suffered or incurred, whether in tort (including negligence), contract, breach of statutory duty, equity or otherwise.

3. SMC is exempted from liability for any damages caused by operations not contained in the catalogues and/or instruction manuals, and operations outside of the specification range.

4. SMC is exempted from liability for any loss or damage whatsoever caused by malfunctions of its products when combined with other devices or software.



2 Port Solenoid Valve for Fluid Control

Precautions 1

Be sure to read this before handling.

For detailed precautions on each series, refer to the main text.

Design

Warning

1. Cannot be used as an emergency shutoff valve, etc.

The valves presented in this catalog are not designed for safety applications such as an emergency shutoff valve. If the valves are used in this type of system, other reliable safety assurance measures should also be adopted.

2. Extended periods of continuous energisation

The solenoid coil will generate heat when continuously energised. Avoid using in a tightly shut container. Install it in a well-ventilated area. Furthermore, do not touch it while it is being energised or right after it is energised.

3. This solenoid valve cannot be used for explosion proof applications.

4. Maintenance space

The installation should allow sufficient space for maintenance activities.

5. Liquid rings

In case of with a flowing liquid, provide a by-pass valve in the system to prevent the liquid from entering the liquid seal circuit.

6. Actuator drive

When an actuator, such as a cylinder, is to be driven using a valve, take appropriate measures to prevent potential danger caused by actuator operation.

7. Pressure (including vacuum) holding

It is not usable for applications such as holding the pressure (including vacuum) inside of a pressure vessel because air leakage is entailed in a valve.

8. When the conduit type is used as equivalent to an IP65 enclosure, install a wiring conduit, etc.

9. When an impact, such as water hammer, etc., caused by the rapid pressure fluctuation is applied, the solenoid valve may be damaged. Give attention to it.

Selection

Warning

1. Confirm the specifications.

Give careful consideration to the operating conditions such as the application, fluid and environment, and use within the operating ranges specified in this catalogue.

2. Fluid

1. Type of fluid

Before using a fluid, confirm whether it is compatible with the materials from each model by referring to the fluids listed in this catalogue. Use a fluid with a dynamic viscosity of 50 mm²/s or less. If there is something you do not know, please contact us.

2. Flammable oil, Gas,

Confirm the specification for leakage in the interior and/or exterior area.

Selection

Warning

3. Corrosive gas

Cannot be used since it will lead to cracks by stress, corrosion or result in other incidents.

4. Use an oil-free specification when any oily particle must not enter the passage.

5. Applicable fluid on the list may not be used depending on the operating condition.

Give adequate confirmation, and then determine a model, just because the compatibility list shows the general case.

3. Fluid quality

The use of a fluid which contains foreign matter can cause problems such as malfunction and seal failure by promoting wear of the valve seat and armature, and by sticking to the sliding parts of the armature, etc. Install a suitable filter (strainer) immediately upstream the valve. As a general rule, use 80 to 100 mesh.

When used to supply water to boilers, substances such as calcium and magnesium which generate hard scale and sludge are included. Since this scale and sludge can cause the valve to malfunction, install water softening equipment, and a filter (strainer) directly upstream the valve to remove these substances.

4. Air quality

1. Use clean air.

Do not use compressed air which includes chemicals, synthetic oils containing organic solvents, salt or corrosive gases, etc., as it can cause damage or malfunction.

2. Install air filters.

Install air filters close to valves at their upstream side. A filtration degree of 5 µm or less should be selected.

3. Install an air dryer or after cooler, etc.

Compressed air that includes excessive drainage may cause malfunction of valves and other pneumatic equipment. To prevent this, install an air dryer or after cooler, etc.

4. If excessive carbon powder is generated, eliminate it by installing mist separators at the upstream side of the valves.

If excessive carbon powder is generated by the compressor, it may adhere to the inside of the valves and cause a malfunction.

Refer to SMC's Best Pneumatics catalogue for further details on compressed air quality.

5. Ambient environment

Use within the operable ambient temperature range. Confirm the compatibility between the product's composition materials and the ambient atmosphere. Be sure that the fluid used does not touch the external surface of the product.

6. Countermeasures against static electricity

Take measures to prevent static electricity since some fluids can cause static electricity.

7. For the low particle generation specification, confirm us separately.



2 Port Solenoid Valve for Fluid Control Precautions 2

Be sure to read this before handling.


For detailed precautions on each series, refer to the main text.

Selection

⚠ Caution

1. Leakage voltage

Particularly when using a resistor in parallel with a switching element and using a C-R element (surge voltage suppressor) to protect the switching element, take note that the leakage current will flow through the resistor, C-R element, etc., creating a possible danger that the valve may not turn off.



DC coil: 2% or less of rated voltage

2. Low temperature operation

1. The valve can be used in an ambient temperature of between -10 to -20°C . However, take measures to prevent freezing or solidification of impurities, etc.
2. When using valves for water applications in cold climates, take appropriate countermeasures to prevent the water from freezing in the tubing after cutting the water supply from the pump, by draining the water, etc.

When warming by a heater, etc., be careful not to expose the coil portion to the heater. Installation of a dryer, heat retaining of the body are recommended to prevent a freezing condition in which the dew point temperature is high and the ambient temperature is low, and the high flow runs.

Mounting

⚠ Warning

1. If air leakage increases or equipment does not operate properly, stop operation.

After mounting is completed, confirm that it has been done correctly by performing a suitable function test.

2. Do not apply external force to the coil section.

When tightening is performed, apply a wrench or other tool to the outside of the piping connection parts.

3. Be sure not to position the coil downwards.

When mounting a valve with its coil positioned downwards, foreign objects in the fluid will adhere to the iron core leading to malfunction.

4. Do not warm the coil assembly with a heat insulator, etc.

Use tape, heaters, etc., for freeze prevention on the piping and body only. They can cause the coil to burn out.

5. Secure with brackets, except in case of steel piping and copper fittings.

6. Avoid sources of vibration, or adjust the arm from the body to the minimum length so that resonance will not occur.

7. Painting and coating

Warnings or specifications printed or labeled on the product should not be erased, removed or covered up.

Piping

⚠ Caution


1. Preparation before piping

Before piping is connected, it should be thoroughly blown out with air (flushing) or washed to remove chips, cutting oil and other debris from inside the pipe.

Install piping so that it does not apply pulling, pressing, bending or other forces on the valve body.

2. Wrapping of pipe tape

When connecting pipes, fittings, etc., be sure that chips from the pipe threads and sealing material do not enter the valve. Furthermore, when pipe tape is used, leave 1.5 to 2 thread ridges exposed at the end of the threads.



3. Avoid connecting ground lines to piping, as this may cause electric corrosion of the system.

4. Always tighten threads with the proper tightening torque.

When attaching fittings to valves, tighten to the proper tightening torque shown below.

Tightening Torque for Piping

Connection threads	Proper tightening torque N·m
Rc1/8	7 to 9
Rc1/4	12 to 14
Rc3/8	22 to 24
Rc1/2	28 to 30
Rc3/4	28 to 30
Rc1	36 to 38

5. Connection of piping to products

When connecting piping to a product, refer to its instruction manual to avoid mistakes regarding the supply port, etc.

6. Steam generated in a boiler contains a large amount of drainage.

Be sure to operate it with a drain trap installed.

7. In applications such as vacuum and non-leak specifications, use caution specifically against the contamination of foreign matters or airtightness of the fittings.



2 Port Solenoid Valve for Fluid Control Precautions 3

Be sure to read this before handling.

For detailed precautions on each series, refer to the main text.

Wiring

⚠ Caution


1. As a rule, use electrical wire with a cross sectional area of 0.5 to 1.25 mm² for wiring. Furthermore, do not allow excessive force to be applied to the lines.
2. Use electrical circuits which do not generate chattering in their contacts.
3. Use voltage which is within $\pm 10\%$ of the rated voltage. In cases with a DC power supply where importance is placed on responsiveness, stay within $\pm 5\%$ of the rated value. The voltage drop is the value in the lead wire section connecting the coil.
4. When a surge from the solenoid affects the electrical circuitry, install a surge absorber, etc., in parallel with the solenoid. Or, adopt an option that comes with the surge voltage protection circuit. (However, a surge voltage occurs even if the surge voltage protection circuit is used. For details, please consult with SMC.)

Electrical Connections

⚠ Caution

Grommet

AWG20 Insulator O.D. 2.5 mm




Lead wire color	
①	②
Black	Red

* There is no polarity.

DIN terminal (Class B only)


Since internal connections are as shown below for the DIN terminal, make connections to the power supply accordingly.



Terminal no.	1	2
DIN terminal	+ (-)	- (+)

* There is no polarity.

- Use compatible heavy duty cords with cable O.D. of $\phi 6$ to 12 mm.
- Use the tightening torques below for each section.



Note) For an outside cable diameter of $\phi 9$ to 12 mm, remove the internal parts of the rubber seal before using.



2 Port Solenoid Valve for Fluid Control

Precautions 4

Be sure to read this before handling.

For detailed precautions on each series, refer to the main text.


Electrical Connections

Caution

Conduit terminal

In case of the conduit terminal, make connections according to the marks shown below.

- Use the tightening torques below for each section.
- Properly seal the terminal connection (G1/2) with the special wiring conduit, etc.




View A-A

(Internal connection diagram)

Conduit

When used as an IP65 equivalent, use seal (part no. VCW20-15-6) to install the wiring conduit. Also, use the tightening torque below for the conduit.

AWG20 Insulator O.D. 2.5 mm



Wiring conduit
(Port size G1/2)
Tightening torque 0.5 to 0.6 N·m

Lead wire color	
①	②
Black	Red

* There is no polarity for DC.


Description	Part no.
Seal	VCW20-15-6

Note) Please order separately.


Electrical Circuits

Caution

Without electrical option



With light





2 Port Solenoid Valve for Fluid Control

Precautions 5

Be sure to read this before handling.

For detailed precautions on each series, refer to the main text.

Operating Environment

⚠ Warning

1. Do not use the valves in atmospheres having corrosive gases, chemicals, salt water, water, water steam, or where there is direct contact with any of these.
2. Do not use in explosive atmospheres.
3. Do not use in locations subject to vibration or impact.
4. Do not use in locations where radiated heat is received from nearby heat sources.
5. Employ suitable protective measures in locations where there is contact with water droplets, oil or welding spatter, etc.

Lubrication

⚠ Caution

1. This solenoid valve can be operated without lubrication.

If a lubricant is used in the system, use turbine oil Class 1, ISO VG32 (with no additive). But do not lubricate a valve with EPDM seals.

Refer to the table of brand name of lubricants compliant to Class 1 turbine oil (with no additive), ISO VG32.

Class 1 Turbine Oil (with no additive), ISO VG32

Classification of viscosity (cst) (40°C)	Viscosity according to ISO Grade	32
Idemitsu Kosan Co.,Ltd.		Turbine oil P-32
Nippon Oil Corp.		Turbine oil 32
Cosmo Oil Co.,Ltd.		Cosmo turbine 32
Japan Energy Corp.		Kyodo turbine 32
Kygnus Oil Co.		Turbine oil 32
Kyushu Oil Co.		Stork turbine 32
Nippon Oil Corp.		Mitsubishi turbine 32
Showa Shell Sekiyu K.K.		Turbine 32
Tonen General Sekiyu K.K.		General R turbine 32
Fuji Kosan Co.,Ltd.		Fucoal turbine 32

Please contact SMC regarding Class 2 turbine oil (with additives), ISO VG32.

Maintenance

⚠ Warning

1. Removing the product

Valves reach high temperatures when used with high temperature fluids. Confirm that the valve temperature has dropped sufficiently before performing work. If touched inadvertently, there is a danger of being burnt.

1. Shut off the fluid supply and release the fluid pressure in the system.
2. Shut off the power supply.
3. Dismount the product.

2. Low frequency operation

Switch valves at least once every 30 days to prevent malfunction. Also, in order to use it under the optimum state, conduct a regular inspection every 6 months.

Maintenance

⚠ Caution

1. Filters and strainers

1. Be careful regarding clogging of filters and strainers.
2. Replace filter elements after one year of use, or earlier if the pressure drop reaches 0.1 MPa.
3. Clean strainers when the pressure drop reaches 0.1 MPa.

2. Lubrication

When using after lubricating, never forget to lubricate continuously.

3. Storage

In case of long term storage after use with heated water, thoroughly remove all moisture to prevent rust and deterioration of rubber materials, etc.

4. Exhaust the drain from an air filter periodically.

Operating Precautions

⚠ Warning

1. Valves reach high temperatures from high temperature fluids. Use caution, as there is a danger of being burnt if a valve is touched directly.



EUROPEAN SUBSIDIARIES:



Austria

SMC Pneumatik GmbH (Austria).
Girakstrasse 8, A-2100 Korneuburg
Phone: +43 2262-62280, Fax: +43 2262-62285
E-mail: office@smc.at
<http://www.smc.at>



France

SMC Pneumatique, S.A.
1, Boulevard de Strasbourg, Parc Gustave Eiffel
Bussy Saint Georges F-77607 Mame La Vallée Cedex 3
Phone: +33 (0)1-6476 1000, Fax: +33 (0)1-6476 1010
E-mail: contact@smc-france.fr
<http://www.smc-france.fr>



Netherlands

SMC Pneumatics BV
De Ruyterkade 120, NL-1011 AB Amsterdam
Phone: +31 (0)20-5318888, Fax: +31 (0)20-5318880
E-mail: info@smcpneumatics.nl
<http://www.smcpneumatics.nl>



Spain

SMC España, S.A.
Zuazobidea 14, 01015 Vitoria
Phone: +34 945-184 100, Fax: +34 945-184 124
E-mail: post@smc.smces.es
<http://www.smces.es>



Belgium

SMC Pneumatics N.V./S.A.
Nijverheidsstraat 20, B-2160 Wommelgem
Phone: +32 (0)3-355-1464, Fax: +32 (0)3-355-1466
E-mail: post@smcpneumatics.be
<http://www.smcpneumatics.be>



Germany

SMC Pneumatik GmbH
Boschring 13-15, D-63329 Egelsbach
Phone: +49 (0)6103-4020, Fax: +49 (0)6103-402139
E-mail: info@smc-pneumatik.de
<http://www.smc-pneumatik.de>



Norway

SMC Pneumatics Norway A/S
Vollsveien 13 C, Granfos Næringspark N-1366 Lysaker
Tel: +47 67 12 90 20, Fax: +47 67 12 90 21
E-mail: post@smc-norge.no
<http://www.smc-norge.no>



Sweden

SMC Pneumatics Sweden AB
Ekhagsvägen 29-31, S-141 71 Huddinge
Phone: +46 (0)8-603 12 00, Fax: +46 (0)8-603 12 90
E-mail: post@smcpneumatics.se
<http://www.smc.nu>



Bulgaria

SMC Industrial Automation Bulgaria EOOD
16 Kliment Ohridski Blvd., fl.13 BG-1756 Sofia
Phone: +359 2 9744492, Fax: +359 2 9744519
E-mail: office@smc.bg
<http://www.smc.bg>



Greece

SMC Hellas EPE
Anagenniseos 7-9 - P.C. 14342. N. Philadelphia, Athens
Phone: +30-210-2717265, Fax: +30-210-2717766
E-mail: sales@smchellas.gr
<http://www.smchellas.gr>



Poland

SMC Industrial Automation Polska Sp.z.o.o.
ul. Poloneza 89, PL-02-826 Warszawa,
Phone: +48 22 211 9600, Fax: +48 22 211 9617
E-mail: office@smc.pl
<http://www.smc.pl>



Switzerland

SMC Pneumatik AG
Dorfstrasse 7, CH-8484 Weisslingen
Phone: +41 (0)52-396-3131, Fax: +41 (0)52-396-3191
E-mail: info@smc.ch
<http://www.smc.ch>



Croatia

SMC Industrijska automatika d.o.o.
Cromerac 12, 10000 ZAGREB
Phone: +385 1 377 66 74, Fax: +385 1 377 66 74
E-mail: office@smc.hr
<http://www.smc.hr>



Hungary

SMC Hungary Ipari Automatizálási Kft.
Budafoki út 107-113, H-1117 Budapest
Phone: +36 1 371 1343, Fax: +36 1 371 1344
E-mail: office@smc.hu
<http://www.smc.hu>



Portugal

SMC Sucursal Portugal, S.A.
Rua de Engº Ferreira Dias 452, 4100-246 Porto
Phone: +351 22-610-89-22, Fax: +351 22-610-89-36
E-mail: postpt@smc.smces.es
<http://www.smces.es>



Turkey

Entek Pnömatik San. ve Tic. A*.
Perpa Ticaret Merkezi B Blok Kat:11 No: 1625, TR-34386, Okmeydanı, Istanbul
Phone: +90 (0)212-444-0762, Fax: +90 (0)212-221-1519
E-mail: smc@entek.com.tr
<http://www.entek.com.tr>



Czech Republic

SMC Industrial Automation CZ s.r.o.
Hudcova 78a, CZ-61200 Brno
Phone: +420 5 414 24611, Fax: +420 5 412 18034
E-mail: office@smc.cz
<http://www.smc.cz>



Ireland

SMC Pneumatics (Ireland) Ltd.
2002 Citywest Business Campus, Naas Road, Saggart, Co. Dublin
Phone: +353 (0)1-403 9000, Fax: +353 (0)1-464-0500
E-mail: sales@smcpneumatics.ie
<http://www.smcpneumatics.ie>



Romania

SMC Romania srl
Str Frunzei 29, Sector 2, Bucharest
Phone: +40 213205111, Fax: +40 213261489
E-mail: smcromania@smcromania.ro
<http://www.smcromania.ro>



UK

SMC Pneumatics (UK) Ltd
Vincent Avenue, Crownhill, Milton Keynes, MK8 0AN
Phone: +44 (0)800 1382930 Fax: +44 (0)1908-555064
E-mail: sales@smcpneumatics.co.uk
<http://www.smcpneumatics.co.uk>



Denmark

SMC Pneumatik A/S
Knudsminde 4B, DK-8300 Odder
Phone: +45 70252900, Fax: +45 70252901
E-mail: smc@smc-pneumatik.dk
<http://www.smc.dk>



Italy

SMC Italia S.p.A
Via Garibaldi 62, I-20061 Carugate, (Milano)
Phone: +39 (0)2-92711, Fax: +39 (0)2-9271365
E-mail: mailbox@smcitalia.it
<http://www.smcitalia.it>



Russia

SMC Pneumatik LLC.
4B Sverdlovskaja nab, St. Petersburg 195009
Phone: +7 812 718 5445, Fax: +7 812 718 5449
E-mail: info@smc-pneumatik.ru
<http://www.smc-pneumatik.ru>



Estonia

SMC Pneumatics Estonia OÜ
Laki 12, 106 21 Tallinn
Phone: +372 6510370, Fax: +372 65110371
E-mail: smc@smcpneumatics.ee
<http://www.smcpneumatics.ee>



Latvia

SMC Pneumatics Latvia SIA
Smerla 1-705, Riga LV-1006
Phone: +371 781-77-00, Fax: +371 781-77-01
E-mail: info@smclv.lv
<http://www.smc.lv>



Slovakia

SMC Priemyselná Automatizácia, s.r.o.
Námestie Matina Benku 10, SK-81107 Bratislava
Phone: +421 2 444 56725, Fax: +421 2 444 56028
E-mail: office@smc.sk
<http://www.smc.sk>



Finland

SMC Pneumatics Finland Oy
PL72, Tiistinniityntie 4, SF-02231 ESPOO
Phone: +358 207 513513, Fax: +358 207 513595
E-mail: smcfi@smc.fi
<http://www.smc.fi>



Lithuania

SMC Pneumatics Lietuva, UAB
Oslo g.1, LT-04123 Vilnius
Phone: +370 5 264 81 26, Fax: +370 5 264 81 26



Slovenia

SMC industrijska Avtomatika d.o.o.
Mirnska cesta 7, SLO-8210 Trebnje
Phone: +386 7 3885412 Fax: +386 7 3885435
E-mail: office@smc.si
<http://www.smc.si>



OTHER SUBSIDIARIES WORLDWIDE:

ARGENTINA, AUSTRALIA, BOLIVIA, BRASIL, CANADA, CHILE,
CHINA, HONG KONG, INDIA, INDONESIA, MALAYSIA, MEXICO,
NEW ZEALAND, PHILIPPINES, SINGAPORE, SOUTH KOREA,
TAIWAN, THAILAND, USA, VENEZUELA

<http://www.smc.eu>
<http://www.smcworld.com>