

## Conductor marking - UCT-WMCO 4.1 (12X4) - 0830784

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marking, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: clip on, cable diameter range: 3.5 ... 4.1 mm, lettering field size: 12 x 4 mm

### Your advantages

- ✓ The UCT-WMCO ... UniCard labeling range includes markers for the subsequent labeling of conductors by simply snapping on
- ✓ Large-surface labeling option in a space-saving design
- ✓ Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- ✓ Secure tight fit even in the event of vibrations
- ✓ The format automatically ensures printing with a high degree of positioning accuracy

### Key Commercial Data

Packing unit	6 pc
Minimum order quantity	6 pc
GTIN	 4 046356 772402
GTIN	4046356772402
Weight per Piece (excluding packing)	11.100 g
Custom tariff number	39269097
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	12 mm
Width (a)	4 mm
Cable diameter	3.5 mm ... 4.1 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

# Conductor marking - UCT-WMCO 4.1 (12X4) - 0830784

## Technical data

### General

Color	white
Type	Card form
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	V0
Material	PC
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	32
Number of individual labels per row	8
Printability	Thermal transfer
	UV LED technology
Device	5146464 THERMOMARK CARD
	5147888 BLUEMARK LED
	5147999 BLUEMARK CLED
Ink ribbon	0801371 THERMOMARK-RIBBON 110-TC
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Marking mounting type	clip on
Result	Test passed
Oxygen index (DIN EN ISO 4589-2)	32.4 %
R22	HL 1 - HL 3
R23	HL 1 - HL 3
R24	HL 1 - HL 3
Min. cross section	2.5 mm <sup>2</sup>
Max. cross section	4 mm <sup>2</sup>

### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3

## Conductor marking - UCT-WMCO 4.1 (12X4) - 0830784

### Classifications

#### eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

#### ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530
ETIM 6.0	EC001530
ETIM 7.0	EC001530

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504

### Accessories

#### Accessories

#### Magazine

Magazine - TMP-UCT-MAG25 - 0803369



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-WMCO ... (12x4)