Taiwan Semiconductor

200mA, 30V Schottky Barrier Diode

FEATURES

- Fast switching speed
- Surface mound device type

SEMICONDUCTOR

- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant

TAIWAN

• Halogen-free according to IEC 61249-2-21

APPLICATIONS

- Adapters
- For switching power supply
- Inverter

MECHANICAL DATA

- Case: SOT-23
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 1A whisker test
- Weight: 8.00mg (approximately)

KEY PARAMETERS				
PARAMETER	VALUE	UNIT		
I _F	200	mA		
V _{RRM}	30	V		
I _{FSM}	600	mA		
V_F at I_F = 100mA	1	V		
T _{J MAX}	125	°C		
Package	SOT-23			





SOT-23

ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise noted)						
PARAMETER	SYMBOL	BAT54	BAT54A	BAT54C	BAT54S	UNIT
Marking code on the device		KL1	KL2	KL3	KL4	
Power dissipation	PD	200 mW			mW	
Repetitive peak reverse voltage	V _{RRM}	30 \			V	
Repetitive peak forward current (tp≤1s;δ≤0.5)	I _{FRM}	300			mA	
Forward current	I _F	200 m			mA	
Non-Repetitive peak forward surge current @ t<1.0s	I _{FSM}	600 r		mA		
Junction temperature range	ΤJ	-55 to +125 °C		°C		
Storage temperature range	T _{STG}	-55 to +125 °C			°C	





THERMAL PERFORMANCE				
PARAMETER	SYMBOL	ТҮР	UNIT	
Junction-to-ambient thermal resistance	R _{ƏJA}	500	°C/W	

ELECTRICAL SPECIFICATIONS (T _A = 25°C unless otherwise noted)					
PARAMETER	CONDITIONS	SYMBOL	MIN	MAX	UNIT
	$I_F = 0.1 \text{mA}, T_J = 25^{\circ}\text{C}$		-	0.24	V
	$I_{F} = 1mA, T_{J} = 25^{\circ}C$		-	0.32	V
Forward voltage per diode ⁽¹⁾	$I_F = 10 \text{mA}, T_J = 25^{\circ}\text{C}$	V _F	-	0.40	V
	$I_F = 30 \text{mA}, T_J = 25^{\circ}\text{C}$		-	0.50	V
	$I_F = 100 \text{mA}, T_J = 25^{\circ}\text{C}$		-	1.00	V
Reverse voltage	$I_R = 100 \ \mu A, \ T_J = 25^{\circ}C$	V _R	30	-	V
Reverse current @ rated V _R per diode ⁽²⁾	$V_{R} = 25 \text{ V}, \text{ T}_{J} = 25^{\circ}\text{C}$	I _R	-	2	μA
Junction capacitance	$f = 1MHz, V_R = 1V$	CJ	-	10	pF
Reverse recovery time	$I_F = I_R = 10 \text{mA},$ $R_L = 100\Omega, I_{rr} = 1 \text{mA}$	t _{rr}	-	5	ns

Notes:

1. Pulse test with PW = 0.3ms

2. Pulse test with PW = 30ms

ORDERING INFORMATION			
ORDERING CODE ⁽¹⁾⁽²⁾	PACKAGE	PACKING	
BAT5x RF	SOT-23	3K / 7" Reel	
BAT5x RFG	SOT-23	3K / 7" Reel	

Notes:

- 1. "x" defines part no. from "4" to "4S"
- 2. "G" means green compound (halogen-free)



CHARACTERISTICS CURVES

(T_A = 25°C unless otherwise noted)




Fig.1 Typical Forward Characteristics






Fig.2 Typical Reverse Characteristics

Fig.3 Admissible Power Dissipation Curve


Fig.4 Typical Junction Capacitance






PACKAGE OUTLINE DIMENSION


SOT-23



DIM.	Unit (mm)		Unit ((inch)
	Min.	Min. Max.		Max.
A	0.89	1.12	0.035	0.044
b	0.30	0.50	0.012	0.020
с	0.08	0.20	0.003	0.008
D	2.80	3.04	0.110	0.120
E	2.10	2.64	0.083	0.104
E1	1.20	1.40	0.047	0.055
е	1.90 BSC		0.07	5 BSC
L1	0.54 REF.		0.021	I REF.




SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	1.00	0.039
В	0.85	0.033
С	2.10	0.083
D	3.10	0.122
E	0.98	0.039

PIN CONFIGURATION





Taiwan Semiconductor

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.