



solenoid valve

VUVG-BK10-M52-AT-F-1R8L-S

Part number: 8042559

★ Core product range

FESTO



Data sheet

Feature	Value
Valve function	5/2 monostable
Type of actuation	electrical
Valve size	10 mm
Standard nominal flow rate	160 l/min
Operating pressure	2.5 ... 7 bar
Design structure	Piston slide
Type of reset	Air spring
Protection class	IP65
Exhaust-air function	throttleable
Sealing principle	soft
Assembly position	Any
Manual override	detenting Pushing
Type of piloting	Piloted
Pilot air supply	Internal
Flow direction	non reversible
Signal status display	LED
Max. switching frequency	2 Hz
Switching time off	17 ms
Switching time on	14 ms
Duty cycle	100%
Max. positive test pulse with logic 0	1,600 µs
Max. negative test pulse with logic 1	3,000 µs
Characteristic coil data	24 V DC: 0.8 W
Permissible voltage fluctuation	+/- 10 %
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Vibration resistance	Transport application test at severity level 1 in accordance with FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 1 in accordance with FN 942017-5 and EN 60068-2-27
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Medium temperature	-5 ... 50 °C
Pilot medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Ambient temperature	-5 ... 50 °C
Product weight	50 g
Electrical connection	Plug M8x1 A-coded to EN 61076-2-104 3-pin
Mounting type	on manifold rail with through hole
Pneumatic connection, port 2	Flange
Pneumatic connection, port 4	Flange
Materials note	Contains PWIS substances Conforms to RoHS
Material seals	HNBR NBR
Material housing	Wrought Aluminium alloy