

## Within Series Adaptor 31\_QLA-01-0-1/112\_N

### Description

Adaptor jack/jack  
QLA-01 jack (female) / QLA-01 jack (female)

Interface standard  
Series QLA-01 - NIM-CAMAC-Standard CD/N549



### Technical Data

#### Electrical Data

Impedance other  $\Omega$   
Interface frequency max. 1.4 GHz

#### Mechanical Data

Number of matings 10000  
Weight 0.0042 kg

#### Environmental Data

Operating temperature -55 °C to 150 °C  
2011/65/EU (RoHS - including compliant  
2015/863 and 2017/2102)

#### Material Data

Interface - QLA-01 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Bronze	Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	

Interface - QLA-01 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Bronze	Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	

### Related Documents

Catalogue drawing DCA-00013895

### Ordering Information

Single package 31\_QLA-01-0-1/112\_NE