OSRAM SFH 3015 FA Datasheet

Discontinued

Published by ams-OSRAM AG Tobelbader Strasse 30, 8141 Premstaetten, Austria Phone +43 3136 500-0 ams-osram.com © All rights reserved





Chip LED SFH 3015 FA

Silicon NPN Phototransistor





Applications

- Access Control & Security
- Appliances & Tools

- Body Tracking
- Factory Automation

Features

- Package: black epoxy
- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)
- Spectral range of sensitivity: (typ) 770 ... 1090 nm
- Narrow half angle (± 13°)
- Low profile sidelooker (1.6mm)
- Emitter in similar package available: SFH 4045N



Ordering Information

Туре	Photocurrent ¹⁾	Photocurrent ²⁾	Ordering Code
	5E 6	typ. $V_{_{CE}} = 5 \text{ V}; \lambda = 950 \text{ nm}; \text{ E}_{_{e}} = 0.1 \text{ mW/cm}$	1 ²
	cm² I _{PCE}	I _{PCE}	
SFH 3015 FA	180 710 μA	480 µA	Q65110A9730

Only one bin within one packing unit (variation less than 2:1)



Maximum Ratings

T _A = 25 °C			
Parameter	Symbol		Values
Operating temperature	T _{op}	min.	-25 °C
		max.	85 °C
Storage temperature	T _{stg}	min.	-40 °C
	3	max.	85 °C
Collector-emitter voltage	V _{CE}	max.	15 V
Collector-emitter voltage pulse	$V_{CE \ pulse}$	max.	30 V
t ≤ 10 µs; T _A = 25 °C			
Collector current	Ι _c	max.	15 mA
Collector surge current	I _{cs}	max.	75 mA
τ ≤ 10 μs			
Emitter-collector voltage	V _{EC}	max.	7 V
ESD withstand voltage	V _{ESD}	max.	2 kV
acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)	200		



Characteristics

T _A = 25 °C			
Parameter	Symbol	Values	
Wavelength of max sensitivity	$\lambda_{_{Smax}}$	typ.	870 nm
Spectral range of sensitivity	$\lambda_{_{10\%}}$	typ.	770 1090 nm
Dimensions of chip area	L×W	typ.	0.35 x 0.35 mm x mm
Radiant sensitive area	А	typ.	0.04 mm²
Half angle	φ	typ.	13 °
Rise time I _c = 1 mA; λ = 950 nm; V _{ce} = 5 V; R _L = 1 kΩ	t _r	typ.	7 µs
Fall time I _c = 1 mA; λ = 950 nm; V _{ce} = 5 V; R _L = 1 kΩ	t _r	typ.	7 µs
Collector-emitter saturation voltage ³⁾ $I_{c} = I_{PCE,min} X 0.3; \lambda = 950 \text{ nm}; E_{e} = 0.1 \text{ mW/cm}^{2}$	V_{CEsat}	typ.	170 mV
Capacitance $V_{CE} = 0 V; f = 1 MHz; E = 0$	C _{CE}	typ.	2.4 pF




Photocurrent Groups $T = 25 \degree C$

Photocurrent ¹⁾	Photocurrent ¹⁾
V_{ce} = 5 V; λ = 950 nm; E_{e} = 0.1 mW/cm ²	$V_{_{CE}}$ = 5 V; λ = 950 nm; $E_{_{e}}$ = 0.1 mW/cm ²
min.	max.
I _{PCE}	I _{PCE}
180 µA	280 μA
280 μA	450 µA
450 μΑ	710 µA
	Photocurrent ¹⁾ V _{CE} = 5 V; λ = 950 nm; E _e = 0.1 mW/cm ² min. I _{PCE} 180 μA 280 μA




Relative Spectral Sensitivity ^{4), 5)}

 $S_{rel} = f(\lambda)$



Directional Characteristics ^{4), 5)}


 $S_{rel} = f(\phi)$



SFH 3015 FA DATASHEET




Photocurrent ^{4), 5)}



Photocurrent ^{4), 5)}

 $I_{PCE} = f(V_{CE}); E_{e} = Parameter$




Dark Current ^{4), 5)}

 $I_{CE0} = f(V_{CE}); E = 0$




Collector-Emitter Capacitance ^{4), 5)}

 $C_{CE} = f(V_{CE}); f = 1 MHz; E = 0$




Dark Current ⁴⁾

 $I_{_{\rm CE0}}$ = f (T_A); V_{CE} = 5 V; E_e = 0 mW/cm²




Photocurrent ⁴⁾

 $I_{PCE,rel} = f(T_A); V_{CE} = 5 V$





Dimensional Drawing ⁶⁾




Further Information:

Approximate Weight:	14.0 mg
Package marking:	Collector

Pin	Description
1	Emitter
2	Collector


Recommended Solder Pad⁶⁾





Reflow Soldering Profile






Profile Feature	Symbol	Pb	b-Free (SnAgCu) Assembly		Unit
		Minimum	Recommendation	Maximum	
Ramp-up rate to preheat ^{•)} 25 °C to 150 °C			2	3	K/s
Time t _s T _{smin} to T _{smax}	t _s	60	100	120	S
Ramp-up rate to peak ^{*)} T_{smax} to T_{p}			2	3	K/s
Liquidus temperature	TL		217		°C
Time above liquidus temperature	t		80	100	S
Peak temperature	Τ _Ρ		245	260	°C
Time within 5 °C of the specified peak temperature T_p - 5 K	t _P	10	20	30	S
Ramp-down rate* T _P to 100 °C			3	6	K/s
Time 25 °C to T _P				480	S

All temperatures refer to the center of the package, measured on the top of the component * slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range

SFH 3015 FA DATASHEET




Taping ⁶⁾



C63062-A4082-B1-02



Tape and Reel 7)



Reel Dimensions


А	W	N _{min}	W ₁	$W_{2 \max}$	Pieces per PU
180 mm	8 + 0.3 / - 0.1 mm	60 mm	8.4 + 2 mm	14.4 mm	1500



Barcode-Product-Label (BPL)



Dry Packing Process and Materials ⁶⁾



Discontinued

Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.



Notes

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

For further application related information please visit www.osram-os.com/appnotes



Disclaimer

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version on our website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

Our components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

Our products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using our components in product safety devices/ applications or medical devices/applications, buyer and/or customer has to inform our local sales partner immediately and we and buyer and /or customer will analyze and coordinate the customer-specific request between us and buyer and/or customer.



Glossary

- ¹⁾ **Photocurrent:** The photocurrent values are measured (by irradiating the devices with a homogenous light source and applying a voltage to the device) with a tolerance of ±11 %.
- ²⁾ Tolerance of Measure: Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.
- ³⁾ **IPCEmin:** IPCEmin is the min. photocurrent of the specified group.
- ⁴⁾ Typical Values: Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- ⁵⁾ **Testing temperature:** TA = 25°C (unless otherwise specified)
- ⁶⁾ **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.
- ⁷⁾ **Tape and Reel:** All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.



Revision History

Version	Date	Change	
1.5	2019-07-11	Electro - Optical Characteristics (Diagrams)	
1.6	2020-11-20	Schematic Transportation Box Dimensions of Transportation Box Electro - Optical Characteristics (Diagrams)	
1.7	2021-10-01	Brand	
1.8	2022-09-22	Discontinued New Layout Applications	

Discontinued



EU RoHS and China RoHS compliant product 此产品符合欧盟 RoHS 指令的要求; 按照中国的相关法规和标准, 不含有毒有害物质或元素。

Published by ams-OSRAM AG Tobelbader Strasse 30, 8141 Premstaetten, Austria Phone +43 3136 500-0 ams-osram.com © All rights reserved

