








Extruded heatsinks for PCB mounting

for semiconductor screw-mounting





			
	 <p>... STS</p>	 <p>... STIS</p>	 <p>... STSB</p>
art. no.	↔ [mm]	R_{th} [K/W]	⊕
SK 104 25,4 ...	25.4	14	TO 220/ SOT 32/ TO 3 P
SK 104 38,1 ...	38.1	11	TO 220/ SOT 32/ TO 3 P
SK 104 50,8 ...	50.8	9	TO 220/ SOT 32/ TO 3 P
SK 104 63,5 ...	63.5	8	TO 220/ SOT 32/ TO 3 P
please indicate:			
	... mounting method STS =with solder pin STIS =with solder pins and insulating washer STSB=with threaded bolt M 3, brass		

E = mounting method

special lengths and transistor drillings on request

surface treatment: black anodised

horizontal for semiconductor screw-mounting

			
art. no.	↔ [mm]	R_{th} [K/W]	⊕
SK 104 25,4 LS	25.4	14	TO 220/ SOT 32/ TO 3 P
SK 104 38,1 LS	38.1	11	TO 220/ SOT 32/ TO 3 P
SK 104 50,8 LS	50.8	9	TO 220/ SOT 32/ TO 3 P
SK 104 63,5 LS	63.5	8	TO 220/ SOT 32/ TO 3 P

special lengths and transistor drillings on request

surface treatment: black anodised