# 6.2×3mm Side Push Mid-mount Type (Surface Mount Type)

# Mid-mount type with height of 1.35mm above the PC board when installed





# ■ Typical Specifications

Items	Specifications
Rating (max.)	50mA 16V DC (SKSNLAE: 50mA 12V DC)
Rating (min.)	10μA 1V DC
Initial contact resistance	100mΩ Max
Travel (mm)	0.2

# ■ Product Line

Product No.	Operating force	Operating direction	Operating life (5mA 5V DC)	Minimum order unit (pcs.)		
T TOUGOT TWO.	Operating force	Operating direction		Japan	Export	
SKSNLAE010	2.4N		500,000 cycles			
SKSNLKE010	4.5N	Side push	100,000 cycles	2,500	2,500	
SKSNLHE010	5N					

# ■ Packing Specifications


# Taping

Number of packages (pcs.)			Tape width	Export package
1 reel	1 case / Japan	1 case / export packing	(mm)	measurements (mm)
2,500	25,000	25,000	12	395×395×205


# Unit:mm Reel size

# Note

For reels of 330mm diameter, please inquire.



# Circuit Diagram





	Туре		Sharp Feeling Type							
		21/2=			1	e Mount		21/=2	21/21	
	Series	SKST	SKRA	SKHM	SKHU	SKTD	SKSN	SKTG	SKSL	
	Photo	-	V		N. Carlotte				01	
	Features	Middl	e travel	_	_	Low-profile	Mid-mount	Half-n	nount	
	Water-proof	_	0	_	0	•	_	•	_	
	Dustproof	_	0	_	0	•	_	•	_	
	IP standard	_	67 equivalent	_	_	67 equivalent	_	67 equivalent	_	
Operatir	Top push	•	•	•	•	_	_	_	_	
directio		_	_	_	_	•	•	•	•	
	W			6.2	6.2	3.9	6.2	5.2	4.5	
Dimension (mm)		□8.5	□6.2	6.5	6.3	2.9	3	3.5	2.6	
(11111)	Н	3.95	3.5/5.2	3.1	2.5/3.1	1.55	3.5	1.55	2.2	
Operation force coverage	2N to 3N	4N to 10N		1	1	<b>\$</b>		<b>‡</b>	1	
	Travel (mm)	0.9	See the relevant pages for respective product description	0	.25	0.15	0.2	0.	15	
G	round terminal	_	— UGGGTP1011	•	•	•	•	•	•	
Operatin	ating temperature range −40°C to +90°C		to +90℃	-40℃ to +85℃		−30°C to +85°C	-40℃ to +85℃	-30°C to	o +85℃	
А	utomotive use	•	0	_	•	_	0	_	0	
	Life Cycle	*3	*3	*3	*3	<b>*</b> 2	<b>*</b> 2	<b>*</b> 2	<b>*</b> 2	
	Rating (max.) (Resistive load)	50mA 16V DC	50mA 16V 50mA 12V DC							
Electrical	Rating (min.) (Resistive load)				10μΑ	V IV DC				
performance	Insulation resistar	nce	100MΩ min. 100V DC 1min.							
	Voltage proof						100V AC 1min.			
Durability	Vibration		10 to 55 to 10Hz/min., the amplitude is 1.5mm for all the frequencies, in the 3 direction of X, Y and Z for 2 hours respectively							
Durability	Lifetime		Shall be in accordance with individual specifications.							
	Cold	-40°0	C 1,000h		-40°C 96h					
Environmental performance	Dry heat	90℃	90°C 1,000h		90°C 96h		90℃ 96h	85℃ 96h	90℃ 96h	
	Damp heat		to 95%RH )00h			60°C, 90 to	95%RH 96h			
	Page	216	217	218	219	221	222	223	224	

W: Width. The most outer dimension excluding terminal portion.

### Notes


 $<sup>\</sup>mathsf{D}:\mathsf{Depth}.$  The most outer dimension excluding terminal portion. H: Height. The minimum dimension if there are variances.

<sup>1.</sup> The automotive operating temperature range to be individually discussed upon request.

<sup>2. •</sup> Indicates applicability to all products in the series, while O indicates applicability to some products in the series.

# TACT Switch™ / Soldering Conditions

# ■ Condition for Reflow Available for Surface Mount Type. Temperature profile



# Notes

- 1. Please confirm the specifications of our product for the detailed condition.
- 2. Soldering conditions differ depending on reflow soldering machines. Prior verification of soldering condition is highly recommended.

# ■ Conditions for Auto-dip

Available for Snap-in Type and Radial Type.

Items	Condition
Flux built-up	Mounting surface should not be exposed to flux
Preheating temperature	Ambient temperature of the soldered surface of PC board. 100°C max.
Preheating time	60s max.
Soldering temperature	260°C max.
Duration of immersion	5s max.
Number of soldering	2times max.

# **SKHH Series**

Items	Condition
Flux built-up	Mounting surface should not be exposed to flux
Preheating temperature	Ambient temperature of the soldered surface of PC board. 110℃ max.
Preheating time	60s max.
Soldering temperature	260°C max.
Duration of immersion	5s max.
Number of soldering	2times max.

# SKHL Top Push Type, SKQJ Series

Items	Condition
Flux built-up	Mounting surface should not be exposed to flux
Preheating temperature	Ambient temperature of the soldered surface of PC board. 100℃ max.
Preheating time	45s max.
Soldering temperature	255℃ max.
Duration of immersion	5s max.
Number of soldering	2times max.

# ■ Manual Soldering

Items	Condition
Soldering temperature	350℃ max.
Duration of soldering	3s max.
Capacity of soldering iron	60W max.

# SKHH, SKHW Series

Items	Condition
Soldering temperature	360℃ max.
Duration of soldering	3s max.
Capacity of soldering iron	60W max.

### SKTD, SKTG, SKQJ, SKSN Series

Items	Condition
Soldering temperature	350℃ max.
Duration of soldering	3s max.
Capacity of soldering iron	20W max.

# Notes

- 1. Prevent flux penetration from the top side of the TACT Switch $^{TM}$ .
- 2. Switch terminals and a PC board should not be coated with flux prior to soldering.
- 3. The second soldering should be done after the switch is stable with normal temperature.
- 4. Use the flux with a specific gravity of min 0.81.

(EC-19S-8 by TAMURA CORPORATION, or equivalents.)