






SLF12565T-330M2R8-PF

Applications		Commercial Grade
Feature		Wire Wound
		Magnetic Shield
		Ferrite Core
Series	SLF Series / SLF12565 Type	
Status	Production	



Size	
Length(L)	12.50mm +/-0.30mm
Width(W)	12.50mm +/-0.30mm
Thickness(T)	6.50mm +/-0.35mm
Recommended Land Pattern (A)	2.60mm Nom.
Recommended Land Pattern (B)	8.50mm Nom.
Recommended Land Pattern (C)	3.20mm Nom.


Electrical Characteristics	
Inductance	33uH +/-20% at 1kHz
Rated Current (L Change) [Max.]	2.8A (10% Down)
Rated Current (Temperature Rise) [Max.]	
DC Resistance [Nom.]	40.6mΩ
DC Resistance [Max.]	48.7mΩ

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-40 to 105degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	No
Packing	Blister (Plastic)Taping [330mm Reel]
Package Quantity	500Pcs Min.
Weight	3.2g


•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

SLF12565T-330M2R8-PF


Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




SLF12565T-330M2R8-PF



SLF12565T-330M2R8-PF



SLF12565T-330M2R8-PF





SLF12565T-330M2R8-PF


- This PDF document was created based on the data listed on the TDK Corporation website.
- All specifications are subject to change without notice.

SLF12565T-330M2R8-PF

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)



SLF12565T-330M2R8-PF(DC = 0A) SLF12565T-330M2R8-PF(DC = 1.4A)



- This PDF document was created based on the data listed on the TDK Corporation website.
- All specifications are subject to change without notice.