


5.1 Dosing Tanks And Bunds PE

5.1.1 Dosing Tanks PE

Made of UV-stabilised polyethylene with scale for litres and US gallons and screw cap (35 l drum with push cap) integral sintered threaded bushes for the assembly of ProMinent® electronic metering pumps, mounting flange with integral sintered threaded bushes for manual or electric stirrers. All tanks designed for extreme robustness with ProMinent® logo and 3 lateral flats for mounting drum.

Natural coloured/transparent PE dosing tank



pk_3_0001_1a

Usable capacity l	D mm	H mm	Threaded bush for the dosing pumps	Weight empty kg	Order no.
35	350	485	without threaded bushes	3.5	791993
60	410	590	gamma/ L, D_4a	5.0	791994
100	500	760	alpha, Beta®, gamma/ L, D_4a	7.0	1001490
140	500	860	gamma/ L, D_4a	9.5	791995
250	650	1,100	alpha, Beta®, gamma/ L, D_4a, Sigma/ 1/ 2/ 3, delta®	17.5	1023175
500	820	1,190	2 x gamma/ L, 2 x D_4a, 2 x Sigma/ 1, delta®	24.5	791997
1,000	1,070	1,260	2 x gamma/ L, 2 x D_4a, 2 x Sigma/ 1/ 2/ 3, delta®	51.0	1010909

Natural coloured/transparent PE dosing tank

prepared for the installation of a hand operated or electronic stirrer.

Usable capacity l	with an opening for	Order no.
60	A hand operated stirrer	792104
60	An electric stirrer	792105
100	A hand operated stirrer	1002034
100	An electric stirrer	1002033
140	A hand operated stirrer	792106
140	An electric stirrer	792107
250	A hand operated stirrer	792108
250	An electric stirrer	792109
500	A hand operated stirrer	792110
500	An electric stirrer	792111
1,000	A hand operated stirrer	1010910
1,000	An electric stirrer	1010911


A threaded socket R 3/4" is cast into the tanks of 35-1,000 litres for emptying purposes, which can be drilled out to a Ø of 10 mm should the customer require this. A sealing plug made out of PE R 3/4" fitted with a seal can be screwed in (accessory order number 200692).

Metering tanks without ProMinent® logo are available on request.

5.1 Dosing Tanks And Bunds PE

5.1.2 Stackable Bunds For Dosing Tanks PE

Made of UV stabilised polyethylene, stackable, with ProMinent® logo. Incorporating 2 lateral flats for mounting bund.



PE colourless/transparent stackable bunds

Usable capacity l	Material	D2 mm	D1 mm	H mm	Order no.
35	PE	565	507	220	1010879
60	PE	680	607	270	1010880
100	PE	802	727	320	1010881
140	PE	811	727	370	1010882
250	PE	917	807	520	1010883
500	PE	1,155	1,009	670	1010884

PE black stackable bunds

Usable capacity l	Material	D2 mm	D1 mm	H mm	Order no.
35	PE	565	507	220	1010885
60	PE	680	607	270	1010886
100	PE	802	727	320	1010887
140	PE	811	727	370	1010888
250	PE	917	807	520	1010889
500	PE	1,155	1,009	670	1010890

PE blue stackable bunds

Usable capacity l	Material	D2 mm	D1 mm	H mm	Order no.
35	PE	565	507	220	1010891
60	PE	680	607	270	1010892
100	PE	802	727	320	1010893
140	PE	811	727	370	1010894
250	PE	917	807	520	1010895
500	PE	1,155	1,009	670	1010896

PE yellow stackable bunds

Usable capacity l	Material	D2 mm	D1 mm	H mm	Order no.
35	PE	565	507	220	1010897
60	PE	680	607	270	1010898
100	PE	802	727	320	1010899
140	PE	811	727	370	1010900
250	PE	917	807	520	1010901
500	PE	1,155	1,009	670	1010902