

# PolarHT™ Power MOSFET

**IXTA 36N30P**  
**IXTP 36N30P**  
**IXTQ 36N30P**


$V_{DSS} = 300 \text{ V}$   
 $I_{D25} = 36 \text{ A}$   
 $R_{DS(on)} \leq 110 \text{ m}\Omega$

N-Channel Enhancement Mode  
Avalanche Rated




| Symbol     | Test Conditions  | Maximum Ratings |                  |
|------------|--|-----------------|------------------|
| $V_{DSS}$  | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$  | 300             | V                |
| $V_{DGR}$  | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$ ; $R_{GS} = 1 \text{ M}\Omega$   | 300             | V                |
| $V_{GS}$   | Continuous   | $\pm 30$        | V                |
| $V_{GSM}$  | Transient  | $\pm 40$        | V                |
| $I_{D25}$  | $T_C = 25^\circ\text{C}$   | 36              | A                |
| $I_{DM}$   | $T_C = 25^\circ\text{C}$ , pulse width limited by $T_{JM}$   | 90              | A                |
| $I_{AR}$   | $T_C = 25^\circ\text{C}$   | 36              | A                |
| $E_{AR}$   | $T_C = 25^\circ\text{C}$   | 30              | mJ               |
| $E_{AS}$   | $T_C = 25^\circ\text{C}$   | 1.0             | J                |
| $dv/dt$    | $I_S \leq I_{DM}$ , $di/dt \leq 100 \text{ A}/\mu\text{s}$ , $V_{DD} \leq V_{DSS}$ ,<br>$T_J \leq 150^\circ\text{C}$ , $R_G = 10 \Omega$ | 10              | V/ns             |
| $P_D$      | $T_C = 25^\circ\text{C}$   | 300             | W                |
| $T_J$      |  | -55 ... +150    | $^\circ\text{C}$ |
| $T_{JM}$   |  | 150             | $^\circ\text{C}$ |
| $T_{stg}$  |  | -55 ... +150    | $^\circ\text{C}$ |
| $T_L$      | 1.6 mm (0.062 in.) from case for 10 s  | 300             | $^\circ\text{C}$ |
| $T_{SOLD}$ | Plastic body for 10 s  | 260             | $^\circ\text{C}$ |
| $M_d$      | Mounting torque (TO-3P / TO-220)   | 1.13/10         | Nm/lb.in.        |
| Weight     | TO-3P  | 5.5             | g                |
|            | TO-220   | 4               | g                |
|            | TO-263   | 3               | g                |


TO-263 (IXTA)



TO-220 (IXTP)



TO-3P (IXTQ)



G = Gate      D = Drain  
S = Source      TAB = Drain

## Features

- <sup>1</sup> International standard packages
- <sup>1</sup> Unclamped Inductive Switching (UIS) rated
- <sup>1</sup> Low package inductance
  - easy to drive and to protect


## Advantages

- <sup>1</sup> Easy to mount
- <sup>1</sup> Space savings
- <sup>1</sup> High power density

| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified)                                     | Characteristic Values |      |                      |
|--------------|---|-----------------------|------|----------------------|
|              |   | Min.                  | Typ. | Max.                 |
| $BV_{DSS}$   | $V_{GS} = 0 \text{ V}$ , $I_D = 250 \mu\text{A}$  | 300                   |      | V                    |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 250 \mu\text{A}$   | 3.0                   |      | 5.5 V                |
| $I_{GSS}$    | $V_{GS} = \pm 20 V_{DC}$ , $V_{DS} = 0$   |                       |      | $\pm 100 \text{ nA}$ |
| $I_{DSS}$    | $V_{DS} = V_{DSS}$<br>$V_{GS} = 0 \text{ V}$<br>$T_J = 125^\circ\text{C}$                                       |                       |      | 1 $\mu\text{A}$      |
|              |   |                       |      | 200 $\mu\text{A}$    |
| $R_{DS(on)}$ | $V_{GS} = 10 \text{ V}$ , $I_D = 0.5 I_{D25}$<br>Pulse test, $t \leq 300 \mu\text{s}$ , duty cycle $d \leq 2\%$ | 92                    | 110  | $\text{m}\Omega$     |


| Symbol       | Test Conditions  | Characteristic Values<br>( $T_j = 25^\circ\text{C}$ , unless otherwise specified) |      |                        |
|--------------|--|---|------|------------------------|
|              |  | Min.  | Typ. | Max.                   |
| $g_{fs}$     | $V_{DS} = 10\text{ V}$ ; $I_D = 0.5 I_{D25}$ , pulse test  | 12  | 22   | S                      |
| $C_{iss}$    | $V_{GS} = 0\text{ V}$ , $V_{DS} = 25\text{ V}$ , $f = 1\text{ MHz}$                                |   | 2250 | pF                     |
| $C_{oss}$    |  |   | 370  | pF                     |
| $C_{rss}$    |  |   | 90   | pF                     |
| $t_{d(on)}$  | $V_{GS} = 10\text{ V}$ , $V_{DS} = 0.5 V_{DSS}$ , $I_D = I_{D25}$<br>$R_G = 10\ \Omega$ (External) |   | 24   | ns                     |
| $t_r$        |  |   | 30   | ns                     |
| $t_{d(off)}$ |  |   | 97   | ns                     |
| $t_f$        |  |   | 28   | ns                     |
| $Q_{g(on)}$  | $V_{GS} = 10\text{ V}$ , $V_{DS} = 0.5 V_{DSS}$ , $I_D = 0.5 I_{D25}$                              |   | 70   | nC                     |
| $Q_{gs}$     |  |   | 17   | nC                     |
| $Q_{gd}$     |  |   | 35   | nC                     |
| $R_{thJC}$   |  |   |      | $0.42^\circ\text{C/W}$ |
| $R_{thCS}$   | (TO-3P)  | 0.21  |      | $^\circ\text{C/W}$     |
|              | (TO-220)   | 0.25  |      | $^\circ\text{C/W}$     |

| Symbol   | Test Conditions  | Characteristic Values<br>( $T_j = 25^\circ\text{C}$ , unless otherwise specified) |      |               |
|----------|--|---|------|---------------|
|          |  | Min.  | Typ. | Max.          |
| $I_S$    | $V_{GS} = 0\text{ V}$  |   |      | 36 A          |
| $I_{SM}$ | Repetitive   |   |      | 90 A          |
| $V_{SD}$ | $I_F = I_S$ , $V_{GS} = 0\text{ V}$ ,<br>Pulse test, $t \leq 300\ \mu\text{s}$ , duty cycle $d \leq 2\%$ |   |      | 1.5 V         |
| $t_{rr}$ | $I_F = 25\text{ A}$ , $-di/dt = 100\text{ A}/\mu\text{s}$  |   | 250  | ns            |
| $Q_{RM}$ | $V_R = 100\text{ V}$ , $V_{GS} = 0\text{ V}$   |   | 2.0  | $\mu\text{C}$ |

**TO-3P (IXTQ) Outline**



- 1 - GATE  
2 - DRAIN (COLLECTOR)  
3 - SOURCE (EMITTER)  
4 - DRAIN (COLLECTOR)

| SYM | INCHES   |      | MILLIMETERS |       |
|-----|----------|------|-------------|-------|
|     | MIN      | MAX  | MIN         | MAX   |
| A   | .185     | .193 | 4.70        | 4.90  |
| A1  | .051     | .059 | 1.30        | 1.50  |
| A2  | .057     | .065 | 1.45        | 1.65  |
| b   | .035     | .045 | 0.90        | 1.15  |
| b2  | .075     | .087 | 1.90        | 2.20  |
| b4  | .114     | .126 | 2.90        | 3.20  |
| c   | .022     | .031 | 0.55        | 0.80  |
| D   | .780     | .799 | 19.80       | 20.30 |
| D1  | .665     | .677 | 16.90       | 17.20 |
| E   | .610     | .622 | 15.50       | 15.80 |
| E1  | .531     | .539 | 13.50       | 13.70 |
| e   | .215 BSC |      | 5.45 BSC    |       |
| L   | .779     | .795 | 19.80       | 20.20 |
| L1  | .134     | .142 | 3.40        | 3.60  |
| øP  | .126     | .134 | 3.20        | 3.40  |
| øP1 | .272     | .280 | 6.90        | 7.10  |
| S   | .193     | .201 | 4.90        | 5.10  |

**TO-220 (IXTP) Outline**


- Pins: 1 - Gate 2 - Drain

| SYM | INCHES   |      | MILLIMETERS |       |
|-----|----------|------|-------------|-------|
|     | MIN      | MAX  | MIN         | MAX   |
| A   | .170     | .190 | 4.32        | 4.83  |
| b   | .025     | .040 | 0.64        | 1.02  |
| b1  | .045     | .065 | 1.15        | 1.65  |
| c   | .014     | .022 | 0.35        | 0.56  |
| D   | .580     | .630 | 14.73       | 16.00 |
| E   | .390     | .420 | 9.91        | 10.66 |
| e   | .100 BSC |      | 2.54 BSC    |       |
| F   | .045     | .055 | 1.14        | 1.40  |
| H1  | .230     | .270 | 5.85        | 6.85  |
| J1  | .090     | .110 | 2.29        | 2.79  |
| k   | 0        | .015 | 0           | 0.38  |
| L   | .500     | .550 | 12.70       | 13.97 |
| L1  | .110     | .230 | 2.79        | 5.84  |
| øP  | .139     | .161 | 3.53        | 4.08  |
| Q   | .100     | .125 | 2.54        | 3.18  |


**TO-263 (IXTA) Outline**


| SYM | INCHES   |      | MILLIMETERS |       |
|-----|----------|------|-------------|-------|
|     | MIN      | MAX  | MIN         | MAX   |
| A   | .160     | .190 | 4.06        | 4.83  |
| A1  | .080     | .110 | 2.03        | 2.79  |
| b   | .020     | .039 | 0.51        | 0.99  |
| b2  | .045     | .055 | 1.14        | 1.40  |
| c   | .016     | .029 | 0.40        | 0.74  |
| c2  | .045     | .055 | 1.14        | 1.40  |
| D   | .340     | .390 | 8.64        | 9.65  |
| D1  | .315     | .350 | 8.00        | 8.89  |
| E   | .380     | .410 | 9.65        | 10.41 |
| E1  | .245     | .320 | 6.22        | 8.13  |
| e   | .100 BSC |      | 2.54 BSC    |       |
| L   | .575     | .625 | 14.61       | 15.88 |
| L1  | .090     | .110 | 2.29        | 2.79  |
| L2  | .040     | .055 | 1.02        | 1.40  |
| L3  | .050     | .070 | 1.27        | 1.78  |
| L4  | 0        | .005 | 0           | 0.13  |


IXYS reserves the right to change limits, test conditions, and dimensions.

|  |           |           |           |              |              |             |              |
|--|-----------|-----------|-----------|--------------|--------------|-------------|--------------|
| IXYS MOSFETs and IGBTs are covered by 4,835,592      | 4,931,844 | 5,049,961 | 5,237,481 | 6,162,665    | 6,404,065 B1 | 6,683,344   | 6,727,585    |
| one or more of the following U.S. patents: 4,850,072 | 5,017,508 | 5,063,307 | 5,381,025 | 6,259,123 B1 | 6,534,343    | 6,710,405B2 | 6,759,692    |
| 4,881,106  | 5,034,796 | 5,187,117 | 5,486,715 | 6,306,728 B1 | 6,583,505    | 6,710,463   | 6,771,478 B2 |


**Fig. 1. Output Characteristics**  
@ 25°C




**Fig. 2. Extended Output Characteristics**  
@ 25°C




**Fig. 3. Output Characteristics**  
@ 125°C




**Fig. 4.  $R_{DS(on)}$  Normalized to 0.5  $I_{D25}$  Value vs. Junction Temperature**




**Fig. 5.  $R_{DS(on)}$  Normalized to 0.5  $I_{D25}$  Value vs.  $I_D$**




**Fig. 6. Drain Current vs. Case Temperature**




**Fig. 7. Input Admittance**




**Fig. 8. Transconductance**




**Fig. 9. Source Current vs. Source-To-Drain Voltage**



**Fig. 10. Gate Charge**



**Fig. 11. Capacitance**



**Fig. 12. Forward-Bias Safe Operating Area**




Fig. 13. Maximum Transient Thermal Resistance

