

■ ELECTRICAL CHARACTERISTICS TEST

TEST ITEM:

TEST INSTRUMENT MODE: 250B

Frequency: 27.600000 MHz

Load Capacitance: 10 pF

Drive Level: 100 uW

Resistance: 60 Ohms

Quantity: 10 PCS

TEST CONDITIONS:

Temperature: 25°C ±5°C

Humidity: 40~70% RH

No.	FR	FL	RR	C ₀	C ₁	L ₁	TS	SPDB
	MHz	ppm	Ohms	pF	fF	mH	ppm/pF	dB
1	27.596186	5.99	14.12	0.83	3.13	10.63	13.33	-9999.00
2	27.596103	4.61	14.01	0.84	3.16	10.51	13.46	-9999.00
3	27.596194	5.07	14.77	0.85	3.10	10.71	13.19	-9999.00
4	27.596181	5.49	14.33	0.86	3.13	10.63	13.27	-9999.00
5	27.596129	4.84	15.60	0.87	3.16	10.53	13.37	-9999.00
6	27.596072	2.78	15.06	0.85	3.15	10.56	13.37	-9999.00
7	27.596329	10.56	14.12	0.85	3.12	10.65	13.27	-9999.00
8	27.596097	3.05	14.44	0.84	3.13	10.61	13.35	-9999.00
9	27.596164	5.83	14.65	0.85	3.14	10.58	13.37	-9999.00
10	27.596148	4.38	15.26	0.85	3.13	10.64	13.29	-9999.00
MAX	27.596329	10.56	15.60	0.87	3.16	10.71	13.46	-9999.00
MIN	27.596072	2.78	14.01	0.83	3.10	10.51	13.19	-9999.00
AVG	27.596160	5.26	14.64	0.85	3.14	10.61	13.33	-9999.00
STD	0.000072	2.15	0.54	0.01	0.02	0.06	0.07	0.00

APPROVE	REPORT
<i>Wenyuan Zhang</i>	<i>Biqin Xu</i>
30-Jun-17	30-Jun-17