




3159
OSCILLATING COMPACT ELBOW
BSP TAPER STUD

3159

maximum working pressure	bar 20	MPa 2,0	psi 290
working temperature	°C (Celsius) From -20 to 80	F (Fahrenheit) From -4 to 176	K (Kelvin) From 253 to 353
vacuum capability	mm Hg vacuum level of 755,000		
body	engineering grade polymer		
sub-base	nickel-plated brass		
'O'-rings	nitrile		
gripping ring	stainless steel		



		ØD (mm)	C	E (mm)	F (mm)	ØG (mm)	H (mm)	K (mm)	L (mm)	(kg)
3159 04 10		4	R1/8	7,5	12,0	11,0	22,0	13,0	17,5	0,012
3159 06 10		6	R1/8	7,5	14,0	14,0	26,5	15,0	20,5	0,014
3159 06 13		6	R1/4	11,0	14,0	14,0	23,5	15,0	20,5	0,022
3159 08 10		8	R1/8	7,5	17,0	16,0	32,0	18,5	23,5	0,036
3159 08 13		8	R1/4	11,0	17,0	16,0	29,0	18,5	23,5	0,037
3159 08 17		8	R3/8	11,5	17,0	16,0	25,0	18,5	23,5	0,033
3159 10 13		10	R1/4	11,0	19,0	19,5	37,5	21,0	29,0	0,053
3159 10 17		10	R3/8	11,5	19,0	19,5	33,5	21,0	29,0	0,045
3159 12 13		12	R1/4	11,0	21,0	22,0	44,5	23,0	33,5	0,080
3159 12 17		12	R3/8	11,5	21,0	22,0	41,0	23,0	33,5	0,070