# **Ceramic Trimmer Capacitors**



# **TZC3 Series**


#### ■ Features

- 1. Small size with external dimension of 3.2(W)x4.5(L)x1.6(H)mm.
- 2. Color coded stator permits easy identification of capacitance and reduces mounting errors.
- 3. Can be adjusted with conventional adjustment tools having a thickness of 0.5mm.
- 4. Designed for automatic placement in surface mount applications.
- 5. Heat resistant resin withstands reflow soldering temperatures.

# ■ Applications

- 1. Compact radios
- 2. Headphones
- 3. Pagers
- 4. Portable radio equipment
- 5. Hybrid ICs
- 6. Cellular telephones
- 7. Cordless telephones
- 8. Remote keyless entry systems






	Part Number	C min. (max.) (pF)	C max. (pF)	тс	Q	Rated Voltage	Withstanding Voltage	Stator/Case Color
1	ZC3Z030A110	1.4	3.0 +50/-0%	NP0±300ppm/°C	300min. at 1MHz, Cmax.	100Vdc	220Vdc	Brown
1	ZC3Z060A110	2.0	6.0 +50/-0%	NP0±300ppm/°C	500min. at 1MHz, Cmax.	100Vdc	220Vdc	Blue
1	ZC3R100A110	3.0	10.0 +50/-0%	N750±300ppm/°C	500min. at 1MHz, Cmax.	100Vdc	220Vdc	White
1	ZC3P200A110	5.0	20.0 +50/-0%	N1200±500ppm/°C	300min. at 1MHz, Cmax.	100Vdc	220Vdc	Red
_1	ZC3P300A110	6.5	30.0 +50/-0%	N1200±500ppm/°C	300min. at 1MHz, Cmax.	100Vdc	220Vdc	Green

Insulation Resistance: 10000M ohm Torque: 1.5 to 9.8mNm Operating Temperature Range: -25 to +85°C


#### ■ Construction






# **■** Temperature Characteristics


#### TZC3Z030




#### TZC3Z060



#### TZC3R100




#### TZC3P200




# **■** Frequency Characteristics

# TZC3Z030



#### TZC3Z060




Continued on the following page.







Continued from the preceding page.

# **■** Frequency Characteristics






# ■ Land Pattern



# **■** Temperature Profile

# Reflow Soldering Profile

①Soldering profile for Lead-free solder (96.5Sn/3Ag/0.5Cu)




Standard Profile							
Pre-h	eating	Heating		Peak temperature	Cycle		
Temp. (T1)	Time (t1)	Temp. (T2)	Time (t2)	(T3)	of reflow		
150 to 180°C	60 to 120sec.	220°C	30 to 60sec.	245±3°C	2 times		

Limit Profile						
Pre-h	eating	Heating		Peak temperature	Cycle	
Temp. (T1)	Time (t1)	Temp. (T4)	Time (t3)	(T5)	of reflow	
150 to 180°C	60 to 120sec.	230°C	30 to 50sec.	260 +5/-0°C	2 times	

# ②Soldering profile for Eutectic solder (63Sn/37Pb)

(Limit profile: refer to 1)



Standard Profile					
Pre-h	eating	Hea	ting	Peak	Cycle of reflow
Temp. (T1)	Time (t1)	Temp. (T2)	Time (t2)	temperature (T3)	
150°C	60 to 120sec.	183°C	30sec.	230 +5/-0°C	1 time

# Soldering Iron

Standard Profile						
Temperature of soldering iron tip	Soldering time	Soldering iron power output	Cycle of soldering iron			
350±10°C	3sec. max.	30W max.	1 time			



#### ■ Notice (Storage and Operating Conditions)

- Do not use the trimmer capacitor under atmosphere of RTV silicone rubber (Room Temperature Vulcanizing Silicone Rubber) except Acetone liberating silicone sealant.
- 2. Before using trimmer capacitors, please store under the conditions of -10 to +40°C and 30 to 85%RH.
- 3. Do not store in or near corrosive gasses.
- 4. Use within 6 months of delivery.
- 5. Do not store under direct sunlight.

#### ■ Notice (Soldering and Mounting)

- 1. Soldering
- TZC3 series can be soldered by reflow soldering method and soldering iron. Do not use flow soldering method (dipping).
- (2) Soldering conditions Refer to the temperature profile. If the soldering conditions are not suitable, e.g., excessive time and/or excessive temperature, the trimmer capacitor may deviate from the specified characteristics.
- (3) The amount of solder is critical.
- (4) The thickness of solder paste should be printed from 150 micro m to 200 micro m and the dimension of land pattern should be Murata's standard land pattern used at reflow soldering. Insufficient amounts of solder can lead to insufficient soldering strength on PCB. Excessive amounts of solder may cause bridging between the terminals or contact failure due to flux wicking up.
- (5) When using soldering iron, the diameter of the string solder shall be less than 0.5mm. The string solder shall be applied to the lower part of the terminal only. Do not apply flux except to the terminals. Excessive amounts of solder and/or applying solder to the upper part of the terminal may cause fixed metal rotor or contact failure due to flux invasion into the movable part and/or the contact point. The

#### ■ Notice (Handling)

- 1. Use suitable screwdrivers that fit comfortably in driver slot.
- (1) Recommended screwdriver for manual adjustment Standard type --> MURATA: KMDR010 Cross slot type --> VESSEL: NO.9000+1.7×30 (Murata P/N is KMDR080)
- (2) Recommended screwdriver bit for automatic adjustment Standard type --> MURATA: KMBT010 Cross slot type --> VESSEL: No.CA-11 (Murata P/N is KMBT080)

# ■ Notice (Other)

Before using trimmer capacitors, please test after assembly in your particular mass production system.

- Do not use the trimmer capacitor under the conditions listed below.
- Corrosive gasses atmosphere
  (ex. Chlorine gas, Hydrogen sulfide gas, Ammonia gas, Sulfuric acid gas, Nitric oxide gas, etc.)
- (2) In liquid (ex. water, oil, medical liquid, organic solvent, etc.)
- (3) Dusty / dirty atmosphere
- (4) Direct sunlight
- (5) Static voltage or electric/magnetic fields
- (6) Direct sea breeze
- (7) Other variations of the above
  - soldering iron should not come in contact with the stator of the trimmer capacitor. If such contact does occur, the trimmer capacitor may be damaged.
- (6) Our recommended chlorine content of solder is as follows.
  - (a) Solder paste: 0.2wt% max.
  - (b) String solder: 0.5wt% max.
- (7) Do not use water-soluble flux (for water cleaning). To prevent the deterioration of trimmer capacitor characteristics, apply flux only to terminals.
- (8) When soldering the TZC3 series, the solder should not flow into the staking part of the substrate. If such flow does occur, driver slot rotation will be damaged.

#### 2. Mounting

- Do not apply excessive force (preferably 5.0 N [Ref: 500gf] max.), when the trimmer capacitor is mounted on the PCB.
- (2) Do not warp and/or bend PCB to protect trimmer capacitor from breakage.
- (3) Use a pick-up nozzle of a suitable dimension. (2.5mm external diameter and 1.5mm bore diameter.)
- 3. Cleaning

This product cannot be cleaned because of open construction.

4. Other

Note the polarity of the trimmer capacitor to minimize influence by stray capacitance. (Refer to the dimensions concerning the polarity.)

- When adjusting with a screwdriver, do not apply excessive force (preferably 1.0 N [Ref: 100gf] max.) to minimize capacitance drift. Excessive force applied to the screwdriver slot may cause deformation of the products.
- Do not apply adhesive, lock paints, or any other substances to the trimmer capacitor to secure the rotor position. They may cause corrosion or electrical contact problems.