

- Features:
- 20 pieces of each standard value for sizes 0603 and larger
 - 30 pieces of each standard value for 0402 size
 - 96 values (1 decade) in each 1% tolerance kit
 - 48 values (2 decades) in each 5% tolerance kit
 - Packaged in cut tape
 - RoHS compliant
 - [RMCF data specification link](#)



| Available Kits | | | | | |
|-----------------------|-----------|------------------|--------------------|----------------|---|
| Stackpole Part Number | Tolerance | Number of Values | Quantity Per Value | Total Quantity | Description |
| KIT-RMCF0402FT-02 | 1% | 96 | 30 | 2880 | Each E96 value from 10-97.6 ohm |
| KIT-RMCF0402FT-03 | 1% | 96 | 30 | 2880 | Each E96 value from 100-976 ohm |
| KIT-RMCF0402FT-04 | 1% | 96 | 30 | 2880 | Each E96 value from 1K-9.76K ohm |
| KIT-RMCF0402FT-05 | 1% | 96 | 30 | 2880 | Each E96 value from 10K-97.6K ohm |
| KIT-RMCF0402FT-06 | 1% | 96 | 30 | 2880 | Each E96 value from 100K-976K ohm |
| KIT-RMCF0402JT-12 | 5% | 48 | 30 | 1440 | Each E24 value from 10-910 ohm |
| KIT-RMCF0402JT-13 | 5% | 48 | 30 | 1440 | Each E24 value from 1K-91K ohm |
| KIT-RMCF0603FT-02 | 1% | 96 | 20 | 1920 | Each E96 value from 10-97.6 ohm |
| KIT-RMCF0603FT-03 | 1% | 96 | 20 | 1920 | Each E96 value from 100-976 ohm |
| KIT-RMCF0603FT-04 | 1% | 96 | 20 | 1920 | Each E96 value from 1K-9.76K ohm |
| KIT-RMCF0603FT-05 | 1% | 96 | 20 | 1920 | Each E96 value from 10K-97.6K ohm |
| KIT-RMCF0603FT-06 | 1% | 96 | 20 | 1920 | Each E96 value from 100K-976K ohm |
| KIT-RMCF0603JT-12 | 5% | 48 | 20 | 960 | Each E24 value from 10-910 ohm |
| KIT-RMCF0603JT-13 | 5% | 48 | 20 | 960 | Each E24 value from 1K-91K ohm |
| KIT-RMCF0603JT-14 | 5% | 48 | 20 | 960 | Each E24 value from 100K-10M ohm (excluding 9.1M) |
| KIT-RMCF0805FT-02 | 1% | 96 | 20 | 1920 | Each E96 value from 10-97.6 ohm |
| KIT-RMCF0805FT-03 | 1% | 96 | 20 | 1920 | Each E96 value from 100-976 ohm |
| KIT-RMCF0805FT-04 | 1% | 96 | 20 | 1920 | Each E96 value from 1K-9.76K ohm |
| KIT-RMCF0805FT-05 | 1% | 96 | 20 | 1920 | Each E96 value from 10K-97.6K ohm |
| KIT-RMCF0805FT-06 | 1% | 96 | 20 | 1920 | Each E96 value from 100K-976K ohm |
| KIT-RMCF0805JT-12 | 5% | 48 | 20 | 960 | Each E24 value from 10-910 ohm |
| KIT-RMCF0805JT-13 | 5% | 48 | 20 | 960 | Each E24 value from 1K-91K ohm |
| KIT-RMCF0805JT-14 | 5% | 48 | 20 | 960 | Each E24 value from 100K-10M ohm (excluding 9.1M) |
| KIT-RMCF1206FT-02 | 1% | 96 | 20 | 1920 | Each E96 value from 10-97.6 ohm |
| KIT-RMCF1206FT-03 | 1% | 96 | 20 | 1920 | Each E96 value from 100-976 ohm |
| KIT-RMCF1206FT-04 | 1% | 96 | 20 | 1920 | Each E96 value from 1K-9.76K ohm |
| KIT-RMCF1206FT-05 | 1% | 96 | 20 | 1920 | Each E96 value from 10K-97.6K ohm |
| KIT-RMCF1206FT-06 | 1% | 96 | 20 | 1920 | Each E96 value from 100K-976K ohm |
| KIT-RMCF1206JT-12 | 5% | 48 | 20 | 960 | Each E24 value from 10-910 ohm |
| KIT-RMCF1206JT-13 | 5% | 48 | 20 | 960 | Each E24 value from 1K-91K ohm |
| KIT-RMCF1206JT-14 | 5% | 48 | 20 | 960 | Each E24 value from 100K-10M ohm (excluding 9.1M) |