

# Type 0680H

## Enhanced-breaking Capability Brick Fuse

**HF** 0680H Series – 2410 Size

RoHS Compliant

### Features

- Slow Blow, 2410 SMD
- Compatible with 260°C, IR Pb-free solder process
- Wide range of current rating from 500mA to 15A
- Wide operating temperature range, -55°C to 125°C
- Tape & Reel for auto-insert SMD process
- RoHS compliant with exemption 7(a)
- Full compliance with EU Directive 2011/65/EU and amending directive 2015/863
- Halogen Free, (MSL = 1)
- AEC-Q Compliant
- Meets Bel automotive qualification\*
- \* - Largely based on internal AEC-Q test plan



UK  
CA  
AEC-Q Compliant

UL  
c  
UL  
US  
CE

### Applications

- Notebook
- LCD monitor
- PC computer
- Office electronic equipment
- Industrial equipment
- Medical equipment
- POE, POE+
- LCD / LED monitor
- Power supply
- LCD / LED TV
- Storage system
- Telecom system
- Wireless basestation
- White goods
- Game console
- Battery charging circuit protection

HALOGEN FREE = **HF**

### Electrical Characteristics

(UL/CSA/STD.248-14)

Testing Current	Blow Time	
	Minimum	Maximum
100%	4 Hrs.	N/A
200%	N/A	120 Sec

### Safety Agency Approvals

Safety Agency	Safety Agency Certificate	Ampere Rating/ Voltage Rating	Ampere Range / Volt @ I.R. ability*
	E506667	500mA-7A/125V AC 125V DC >7A-15A/125V AC 125V DC	500mA-7A/125V AC @100A 125V DC @500A 72V DC @5000A >7A-15A/100V AC @150A 125V AC @50A 125V DC @500A 72V DC @5000A

\*I.R.= Interrupting Rating = Short Circuit Rating(Amps)


### Physical Specifications

Materials	Body : Ceramic
	Terminations : Silver Plated Caps /Gold Plated Caps/Palladium Plated Caps
Marking	On Fuse :
	"Current Rating", "S", "H"—laser marked on ceramic tube, "bel" stamped in end caps.
	On Label :
	"bel", "0680H", "Current Rating", "Voltage Rating", "Interrupting Rating", "Appropriate Safety Logos" and "", "" (China RoHS compliant).

## Environmental Specifications

Shock Resistance	MIL-STD-202G Method 213, Test condition A (50G's peak for 11 milliseconds : Half-sine waveform )	High temperature storage	MIL-STD-202 Method 108
Vibration Resistance	MIL-STD-202G, Method 201A (10-55 Hz, 0.06 inch, total excursion).	Temperature cycling	JESD22 Method JA-104, Test Condition B
Salt Spray Resistance	MIL-STD-202G, Method 101E, Test Condition B (48 hrs.).	Biased humidity	MIL-STD-202 Method 103, 85C/85% RH with 10% operating power for 1000 hrs.
Insulation Resistance	MIL-STD-202G, Method 302, Test Condition A (After Opening) 10,000 ohms minimum.	Operational life	MIL-STD-202 Method 108, Test Condition D
Thermal Shock	MIL-STD-202G, Method 107G, Test Condition B (-65°C to +125°C).	Resistance to solvents	MIL-STD-202 Method 215
Operating Temperature	-55°C to +125°C	Mechanical shock	MIL-STD-202 Method 213, Test Condition C
Moisture Sensitivity Level	1 (According to IPC J-Std-020)	Vibration	MIL-STD-202G Method 204 Test condition D ( 10-2k HZ , 20G's for 20minutes )
		Resistance to soldering heat	MIL-STD-202 Method 210, Test condition B
		Thermal shock	MIL-STD-202 Method 107
		Solderability	J-STD-002 Test B
		Board flex(SMD)	AEC-Q200-005
		Terminal strength	AEC-Q200-006
		Electrical characterization	3 Temperature Electrical

## Electrical Specifications

Part Number	Ampere Rating	Typical Cold Resistance (ohms)	Nominal Volt-drop @ 100% In (Volt)	Voltage and Interrupting Ratings	Nominal melting I²T @ 10 In (A² Sec)	Nominal melting I²T <10ms (A² Sec)	Nominal Power Dissipation (W)	Agency Approvals
								
0680H0500-XX	500mA	1.1	1.5	See Table of Safety Approvals on Page 1 for Voltage and associated Interrupting Ratings	0.13	0.10	0.75	Y
0680H0630-XX	630mA	0.83	1.1		0.20	0.13	0.69	Y
0680H0750-XX	750mA	0.53	0.85		0.28	0.29	0.64	Y
0680H1000-XX	1A	0.33	0.65		0.79	0.80	0.65	Y
0680H1500-XX	1.5A	0.175	0.60		1.7	1.8	0.90	Y
0680H2000-XX	2A	0.095	0.40		3.6	3.9	0.80	Y
0680H2500-XX	2.5A	0.065	0.38		5.9	6.1	0.95	Y
0680H3000-XX	3A	0.051	0.34		8.3	8.7	1.0	Y
0680H3500-XX	3.5A	0.042	0.32		12	15	1.1	Y
0680H4000-XX	4A	0.032	0.31		15	18	1.2	Y
0680H5000-XX	5A	0.026	0.30		24	26	1.5	Y
0680H6300-XX	6.3A	0.023	0.28		32	34	1.8	Y
0680H7000-XX	7A	0.015	0.25		48	52	1.8	Y
0680H8000-XX	8A	0.012	0.23		59	65	1.8	Y
0680H9100-XX	10A	0.0096	0.23		98	102	2.3	Y
0680H9120-XX	12A	0.0077	0.22		141	146	2.6	Y
0680H9150-XX	15A	0.0066	0.20		207	213	3.0	Y

Consult manufacturer for other ratings  
 XX - Packaging code (see "ordering information")

**NOTES 1:**

All tests were conducted with the fuses soldered to a printed circuit boards with a nominal thickness of 1.6 mm. The copper test circuit trace was a printed circuit with an overall length of 100 mm, copper thickness/width as described below. The printed circuit boards were mounted by screws to a test fixture having brass blocks for connection of the test leads. All samples were soldered to the test boards by the manufacturer.

Fuse rating	Test Board Trace Dimensions
500mA-5A	1 oz. copper, 5mm wide.
6A-15A	3 oz. copper, 10mm wide.

**NOTES 2:**

Conventional (Ambient Pressure) Reflow Process is recommended for this device. The sale and use of product is subject to bel terms and condition of sale. unless otherwise agreed .User should independently evaluate the suitability of and test each product selected for their own application. product are not designed for , and may not be used in. all applications.

**Caution:**

- Minimum fusing point:

The 0680H Series fuse are NOT intended to be operated at currents between 100% and 200% of ampere rating. Prolonged operation at currents in this range may result in overheating of the fuse and/or desoldering of the fuse caps from the PCB pad.




Specifications subject to change without notice


**Bel Fuse Inc.**  
 206 Van Vorst Street  
 Jersey City, NJ 07302 USA

+1 201.432.0463  
 Bel.US.CS@belf.com  
[belfuse.com/circuit-protection](http://belfuse.com/circuit-protection)

## Temperature Derating Curve




## Average Time Current Curve



## Soldering Parameters

IR Reflow Profile (IPC/JEDEC J-STD-020D)	
<b>Preheat &amp; Soak</b>	
Temperature min ( $T_{smin}$ )	150°C
Temperature max ( $T_{smax}$ )	200°C
Time ( $T_{smin}$ to $T_{smax}$ ) ( $t_s$ )	60-120 seconds
Average ramp-up rate ( $T_{smax}$ to $T_p$ )	3°C/second max.
Liquidous temperature ( $T_L$ )	217°C
Time at liquidous ( $t_L$ )	60-150 seconds
Peak temperature ( $T_p$ )	260°C max
Time ( $t_p$ ) within 5°C of the specified classification temperature ( $T_c$ )	30 seconds
Average ramp-down rate ( $T_p$ to $T_{smax}$ )	6°C/second max.
Time 25°C to peak temperature	8 minutes max.



Specifications subject to change without notice

Bel Fuse Inc.  
206 Van Vorst Street  
Jersey City, NJ 07302 USA

+1 201.432.0463  
Bel.US.CS@belf.com  
[belfuse.com/circuit-protection](http://belfuse.com/circuit-protection)

