

EP / AP SERIES HIGH POWER CONNECTORS

The EP Series incorporates a rugged zinc diecast shell to give it maximum durability when used in demanding situations. The EP cable connector cable flex relief design minimises cable bend stress at point of entry into the connector housing.

The AP Series Shell is manufactured from tough, durable thermoplastic, and ideal for fixed indoor installations. Both the EP and AP Series utilise the same contact and insulator components.

Features

- High current contacts for distortion free signal.
- Tough, durable zinc diecast shell for the EP series.
- Cost effective durable thermoplastic shell for the AP series.
- EP series available in 3, 4, 5, 6 and 8 contact arrangements
- AP series available in 4, 5, 6, and 8 contact arrangements.
- Cable clamp capable of supporting cables from 9mm (0.35") to 16mm (0.63") in diameter
- Quick release, vibration resistant latch lock.
- EP Cable Connectors are supplied with two different boots for different cable diameters.
- AP & EP Series are completely intermatable.

Options

- · Solder Bucket termination
- · Nickel Plated Zinc Alloy shell
- · Black finished Zinc Alloy shell
- · Precision machined contacts
- Thermoplastic shell

Ordering Codes

We have listed the more common ordering codes in each section. Please contact us if you need any further assistance.

Simple steps to guide you in using this catalogue

- Identify the product group listed in Contents on Page 1 and go directly to that page number.
- 2) Each product group cover page then details information and options available.
- 3) Refer to the product detail pages and identify the product you require pictorially.
- 4) Read the product description column for the products standard features.
- 5) Use variations column to determine your choice.
- 6) Identify part number.
- 7) In the event the particular option you require is not listed please refer to the part number breakdown page at the end of each section.
- 8) Please contact us directly if you have any further problems.



METAL TYPE - SOLDER



The EP Series has set the standard in high performance speaker connectors. Apart from its durability and strength, it offers consistent superior power handling capabilities.

Features:

- Solder Bucket connections.
- Precision machined contacts.
- Diecast Metal Housings
- · High current contacts
- Male and female cable and chassis connectors available.
- EP Cable Connectors are supplied with two different boots for different cable diameters.

Options: Black Finish Shell. Specifications: Page 57-58
Panel Cutouts: Page 58

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER			
		>	EP Male cable connector,	3 pole nickel finish	EP-3-12			
		Machined contacts, Metal Shell Section 1	EP-3-12B					
	64.0 [2.521"]————————————————————————————————————		4 pole nickel finish	EP-4-12				
			4 pole black finish	EP-4-12B				
		TOR TOR	5 pole nickel finish	EP-5-12				
	PIN INSULA	TOR -SHELL	5 pole black finish	EP-5-12B				
ISO ASSEMBLY OF EP MALE				6 pole nickel finish	EP-6-12			
LF WALL					EP-6-12B			
			8 pole nickel finish	EP-8-12				
				8 pole black finish	EP-8-12B			
		EP Female cable connector,	3 pole nickel finish	EP-3-11P				
	Machi	Machined contacts, Metal Shell	3 pole black finish					
		4 pole nickel finish EP-4-11F						
	88.0	[3.465*]		4 pole black finish	h EP-4-11PB			
ISO ASSEMBLY OF EP FEMALE			a pushing	5 pole nickel finish EP-5-11P				
	PIN INSU	ATOR SHELL	AMP_BUSHING	5 pole black finish	EP-5-11PB			
			6 pole nickel finish	EP-6-11P				
	6.6			6 pole black finish	n EP-6-11PB			
				8 pole nickel finish EP-8-11P	EP-8-11P			
				8 pole black finish	EP-8-11PB			



EP AP

Amphenol

METAL TYPE - SOLDER

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
	29.2 [1.148"]	Π	EP Male chassis mount, Round Flange, Machined contacts,	3 pole nickel finish	EP-3-14
		1.132"}		3 pole black finish	EP-3-14B
		028.8 [01.132];	Metal Shell	4 pole nickel finish	ckel finish EP-4-14
O increased	29.2 [1.148"]-	3.5 [.138"]		4 pole black finish	EP-4-14B
	ø50.8 [ø2"]	⇒ 31.8 [1.252"] →		5 pole nickel finish	EP-5-14
				5 pole black finish	EP-5-14B
				6 pole nickel finish	EP-6-14
				6 pole black finish	EP-6-14B
				8 pole nickel finish	EP-8-14
				8 pole black finish	EP-8-14B
100		7.5 [.295*]	EP Female chassis 3 pole nic mount,	3 pole nickel finish	EP-3-13P
	0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	\rangle	Round Flange, Machined contacts,	3 pole black finish	EP-3-13PB
		38.3 (1.5087)-	Metal Shell	4 pole nickel finish	EP-4-13P
	AMPHENOL	4 pole black fini	4 pole black finish	EP-4-13PB	
	ø50.8 [2*]			5 pole nickel finish	EP-5-13P
				5 pole black finish	EP-5-13PB
				6 pole nickel finish	EP-6-13P
				6 pole black finish	EP-6-13PB
				8 pole nickel finish	EP-8-13PT
				8 pole black finish	EP-8-13PBT
	0, 0, 0, 0, 0, 0, 0, 0, 0, 0, 0, 0, 0, 0	7.5 [.295"]	EP Female chassis mount, Round Flange, Stamped contacts, Metal Shell	8 pole nickel finish	EP-8-13P
Q MELIBRON	######################################			8 pole black finish	EP-8-13PB

THERMOPLASTIC TYPE - SOLDER



The AP Series provides the same power handling performance as the EP Series in a cost effective, yet durable Thermoplastic housing.

Features:

- Solder Bucket connections.
- Precision machined contacts.
- Thermoplastic Housings
- High current contacts
- Male & Female Cable and Chassis connectors available.

Specifications: Page 57-58
Panel Cutouts: Page 58

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
	28.8 [1.135*]		AP Male cable connector, Machined contacts, Thermoplastic Black shell.	4 pole	AP-4-12
				5 pole	AP-5-12
13				6 pole	AP-6-12
•	100.0 [3.937	·*]		8 pole	AP-8-12
			AP Female cable connector,	4 pole	AP-4-11
The same of the sa		Ø28.8 (1.132*)	Machined contacts, Thermoplastic Black	5 pole	AP-5-11
(6)			shell.	6 pole	AP-6-11
	98.7 [3.886*]]		8 pole	AP-8-11
			AP Male chassis mount,	4 pole	AP-4-14
	-29.2 [1.15]	30.6 [1.204"	Round Flange, Machined contacts,	5 pole	AP-5-14
			Thermoplastic Black shell.	6 pole	AP-6-14
	-29.2 [1.15"]		SHOII.	8 pole AP-8-14	AP-8-14
	640-	AP Female chassis mount,	4 pole	AP-4-13	
	Round Flange, Machined contacts, Thermoplastic Black shell.	4 (91.276°)-	Round Flange, Machined contacts, Thermoplastic Black 5 pole 6 pole	5 pole	AP-5-13
				6 pole	AP-6-13
		SHEII.	8 pole	AP-8-13	
			AP Male chassis mount,	4 pole	AP-4-22 AP-5-22 AP-6-22
	28.2 [1.148] So.0 [1.968]	932.4 [91.276 ⁻]-	Rectangular Flange, Machined contacts,	5 pole	
	AMPHRASIC T	<u>- </u>	Thermoplastic Black shell.	6 pole	
	40.0 [1.575"]———————————————————————————————————	31.8 [1.252"]———————————————————————————————————	JIIVII.	8 pole	AP-8-22
Ó.		7.5 [.295*]	AP Female chassis mount,	ale chassis 4 pole AP-4-21	AP-4-21
	0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	38.3 [1.5087] -	Rectangular Flange, Machined contacts,	5 pole	AP-5-21
	APPRIOR S		Thermoplastic Black shell.	6 pole	AP-6-21
	29.2 [1.148*] — — 40.0 [1.575*] ——	2.8 [.11"] 		8 pole	AP-8-21





STANDARD DATA EP/AP

		VALUE					
GENERAL CHARACTERISTICS	Number of contacts	3	4	5	6	8	
CHARACTERISTICS	Contact Arrangements (Front view of pin insert)	1 3 0 0 0 0 0 0 0 0 0 0	1 4 0 2 3 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	2 4	0 6 6 6 6 6 6 6 6 6 6 6 6 6 6 6 6 6 6 6	9 8 6 9 9 9 9 9 9 9 9 9 9 9 9 9 9 9 9 9	
	Termination	SOLDER					
	Wire Gauge - Stranded wire:	12AWG	12AWG	12AWG	12AWG	14AWG	
	Flammability	UL94V-0					
	Environmental	Complies with RoHS Directive 2002/95/EC					
ELECTRICAL	Service Voltage RMS ¹⁾	460V	660V	200V	200V	100V	
CHARACTERISTICS	Test Voltage AC RMS	2400V	3000V	1600V	1600V	1300V	
	Current carrying capacity	20A	20A	20A	20A	15A	
	Typicial Contact Resistance	≤ 3mΩ					
	Insulation Resistance	≥ 1000MΩ					
CLIMATIC CHARACTERISTICS	Protection Class	IP40					
CHARACIERISTICS	Operating Temperature	-25°C to +75°C (-13°F to +167°F)					
MECHANICAL	Weight - EP 11 & 12 ²⁾	80g	84g	86g	86g		
CHARACTERISTICS		(0.176lb)	(0.185lb)	(0.189lb)	(0.189lb)		
	Weight - EP 13 & 14 ²⁾	48g	50g	54g	54g		
		(0.105lb)	(0.110lb)	(0.119lb)	(0.119lb)		
	Weight - AP 11 & 12 ²⁾	N/A	42g	44g	44g		
			(0.092lb)	(0.097lb)	(0.097lb)		
	Weight - AP 13, 14, 21 & 22 ²⁾	N/A	26g	30g	30g		
			(0.057lb)	(0.066lb)	(0.066lb)		
	Typical Cable retention force	22Kg to 44Kg (50lb to 100lb) - Dependant on cable material and diameter					
	Mechanical operations	1000 mating cycles					

Not suitable for domestic applications above 50V

²⁾ Approximate weight only, does not include packaging. Please contact us for exact weight for shipping purposes.

STANDARD DATA


STANDARD DATA EP/AP (CONT'D)

		DETAILS		
MATERIALS TYPE		AP	EP	
	Connector shell	Modified PPE Resin	Diecast Zinc Alloy	
	Shell finish	Black	Satin Nickel or Black	
	Insulators	UL94V-0 PBT Resin		
	Cable Bushing	Silicon Rubber	UL94 HB Thermoplastic Elastomer	
	Male contact Machined - Solder			
	Material / Plating	Brass / Bright Tin		
Female contact Machined - Solder				
	Material / Plating	Brass / Bright Tin		
CLAMPING	Cable OD Range	11mm to 17mm	9mm to 16mm	
CHARACTERISTICS		(0.43" to 0.67")	(0.35" to 0.63")	
	Retention Method	Two opposing plastic screws	Metal saddle clamp	



EP/AP SERIES PANEL CUTOUT DATA - FRONT VIEW

EP 13/AP 13/AP 21



EP 14/AP 14/AP 22

