

Product Search Data Sheet

Note: This datasheet may be out of date.

Please download the latest datasheet of DLW5BTH251TQ2#from the official website of Murata Manufacturing Co., Ltd.

https://www.murata.com/en-global/products/productdetail?partno=DLW5BTH251TQ2%23


DLW5BTH251TQ2#

"#" indicates a package specification code.

In Production RoHS REACH AEC-

< List of part numbers with package codes > DLW5BTH251TQ2K DLW5BTH251TQ2L DLW5BTH251TQ2B

Appearance & Shape



Features

Features

- 1. Low profile (h=2.5mm)
- 2. Small size (5.0x5.0mm) and high rated current (1.5 to 4A)
- 3. High common mode Impedance (max. 1400 ohm, at 100MHz)
- 4. Operating Temperature Range -40°C to +125°C

Applications

Automotive Usage	Powertrain/Safety
---------------------	-------------------

Packaging Information

Packaging	Specifications	Minimum Order Quantity
К	330mm Embossed Tape	2500
L	180mm Embossed Tape	700
В	Bulk(Bag)	100

1 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



Note: This datasheet may be out of date

Please download the latest datasheet of DLW5BTH251TQ2#from the official website of Murata Manufacturing Co. Ltd.

Co., Ltd. https://www.murata.com/en-global/products/productdetail?partno=DLW5BTH251TQ2%23

DLW5BTH251TQ2#

"#" indicates a package specification code.

Specifications

Shape	SMD	DC Resistance	0.020Ω max.
Size Code (in mm)	5050	Insulation Resistance(min.)	10ΜΩ
Size Code (in inch)	2020	Operating Temperature Range	-40°C to 125°C
Length	5.0mm	Mass(typ.)	0.21g
Length Tolerance	±0.3mm	Number of Circuit	1
Width	5.0mm	Operating Temperature Range(Self- temperature rise is included)	No
Width Tolerance	±0.3mm		
Thickness	2.35mm		
Thickness Tolerance	±0.15mm		
Common Mode Impedance (at 100MHz)	250Ω		
Common Mode Impedance (at 100MHz) Tolerance	(Тур.)		
Common Mode Impedance (at 10MHz)	20Ω		
Common Mode Impedance (at 10MHz) Tolerance	min.		
Rated Current	ЗА		
Rated Voltage	50Vdc		
Withstanding Voltage	125Vdc		
DC Resistance(max.)	0.02Ω		

2 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued with the specification of the specificati

without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering





Note: This datasheet may be out of date


Please download the latest datasheet of DLW5BTH251TQ2#from the official website of Murata Manufacturing Co., Ltd.


https://www.murata.com/en-global/products/productdetail?partno=DLW5BTH251TQ2%23

DLW5BTH251TQ2#


"#" indicates a package specification code.








Impedance-Frequency Characteristics (Main Items)



Impedance-Frequency Characteristics

In operating temperature exceeding +105°C, derating of current is necessary for DLW5BTH_TQ2 series. Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current



Derating of Rated Current

Equivalent Circuit

3 of 3

Attention

 This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

