



# Speed Controller with Indicator New


Numerical indication of handle rotation for flow rate

RoHS

## reduces flow setting time and setting errors!




Indicator window	Body size 1		Body size 2 or larger	
	Indicator window	Number of needle rotations	Indicator window	Number of needle rotations
 Numerical indication of handle rotation	1	1	1	1
	2	2	2	2
	⋮	⋮	⋮	⋮
	⋮	⋮	⋮	⋮
	8	8	10	10




**Larger push-lock type handle**

Easy to lock

**Locked**




**Unlocked**



---

Easy to operate with the larger handle and marking every 90° mark



Body size	øD (mm)
1	9.4
2	12 (Port size 1/8) 13 (Port size 1/4)
3	16.6
4	18.8



New types added!



Made to Order added

- Vaseline/-X12
- Grease-free + Restrictor/-X21
- Restrictor/-X214
- Clean Series/10-


## Series AS-FS

## Flow rate reproducibility













### Improved reproducibility of flow rate



Stable handle position when fully closed (no flow rate) onto the contact face stopper (rotating stopper). Small variations in flow rate depending on the number of handle rotations



## Easy identification of product type

Series	Release button colour			
	Meter-out	Meter-in	Metric	Inch
 AS-FS    AS-FS-U□	Grey 	Light blue 	Light gray 	Orange 
 AS-FSG	Grey 	Light blue 	White 	White 

## Easier to insert and remove the tube!



Tubing diameter	Thread	Model	Model
ø4	M5	AS12□1FS-M5□-04	AS12□1F-M5-04

Tubing diameter	Thread	Model	Model
ø6	1/4	AS22□1FS-02-06S	AS22□1F-02-06

## Series Variations


Image	Seal method	Body size	Port size	Applicable tubing O.D.												Metal parts material	Applicable tubing material						
				Metric size						Inch size													
				2	3.2	4	6	8	10	12	16	1/8"	5/32"	1/4"	5/16"			3/8"	1/2"				
		1	M5 x 0.8	•	•	•	•					•	•	•									
			10-32UNF	•	•	•	•					•	•	•									
		2	R	1/8	•	•	•	•	•				•	•	•								
				1/4	•	•	•	•	•			•	•	•	•	•							
		3	NPT	1/4			•	•	•	•	•				•	•	•	•					
				3/8			•	•	•	•	•				•	•	•	•					
4		1/2					•	•	•						•	•			•	•			
		2	G*1	1/8		•	•	•	•	•				•	•	•	•						
				1/4		•	•	•	•	•													
		3	G*1	1/4			•	•	•	•	•												
				3/8			•	•	•	•	•												
4		1/2					•	•	•														
		2	Uni	1/8		•	•	•	•	•				•	•	•	•						
				1/4		•	•	•	•	•				•	•	•	•	•					
		3	Uni	1/4			•	•	•	•	•					•	•	•	•				
				3/8			•	•	•	•	•						•	•	•	•			
4		1/2					•	•	•										•	•			

\*1 Face seal type is applicable only to the G thread type. \*2 "Without sealant" type can be selected as a standard option.

- ⊙ Electroless nickel plating type is standardised.
- ⊙ Stainless steel type is standardised.
- ⊙ G thread (Face seal) type is standardised.



# Speed Controller with Indicator/ Elbow Type Series AS-FS



## Model

Model	Port size	Seal method	Applicable tubing O.D.											Note 3) Max. number of rotations			
			Metric size						Inch size								
Elbow type			2 <sup>Note 2)</sup>	3.2	4	6	8	10	12	16	1/8"	5/32"	1/4"	5/16"	3/8"	1/2"	
AS12□1FS□-M5□	M5 x 0.8	Gasket seal	●	●	●	●					●	●	●				8
AS12□1FS□-U10/32□	10-32UNF		●	●	●	●					●	●	●				
AS22□1FS□-□01	R NPT	Note 1) Sealant		●	●	●	●	●			●	●	●	●			10
AS22□1FS□-□02			1/8		●	●	●	●	●			●	●	●	●	●	
AS22□1FS□-□02			1/4		●	●	●	●	●			●	●	●	●	●	
AS32□1FS□-□02			1/4				●	●	●	●			●	●	●	●	
AS32□1FS□-□03			3/8				●	●	●	●			●	●	●	●	
AS42□1FS□-□04	1/2							●	●	●				●	●		
AS22□1FS□-G01	G	Face seal		●	●	●	●	●									10
AS22□1FS□-G02			1/8		●	●	●	●	●								
AS32□1FS□-G02			1/4				●	●	●	●							
AS32□1FS□-G03			3/8				●	●	●	●							
AS42□1FS□-G04			1/2							●	●	●					


Note 1) "Without sealant" type can be selected as a standard option.

Note 2) Only polyurethane tubing is applicable for ø2.

Note 3) There are differences in actual rate as by the indicator window over the maximum number of rotations depending on the individual product.

## Specifications

### Flow Direction Symbol on Body



Fluid	Air
Proof pressure	1.5 MPa
Max. operating pressure	1 MPa
Min. operating pressure	0.1 MPa
Ambient and fluid temperature	-5 to 60°C (No freezing)
Applicable tubing material	Nylon, Soft nylon, Polyurethane <sup>Note)</sup> , FEP, PFA

Note) Use caution at the max. operating pressure when using soft nylon or polyurethane tubing. (Refer to the **WEB catalogue** for details.)

## ⚠ Caution

Be sure to read this before handling. Refer to the back cover for Safety Instructions. For Flow Control Equipment Precautions, refer to "Handling Precautions for SMC Products" and the Operation Manual.


## Flow-rate and Sonic Conductance

Model	AS12□1FS-M5□	AS22□1FS-01		AS22□1FS-02			AS32□1FS		AS42□1FS						
Tubing O.D.	Metric size	ø2	ø3.2 ø4 ø6	ø3.2	ø4	ø6 ø8 ø10	ø3.2	ø4	ø6	ø8 ø10	ø6	ø8	ø10 ø12	ø10	ø12 ø16
	Inch size	—	ø1/8" ø1/4" ø5/32"	ø1/8"	ø5/32"	ø1/4" ø5/16"	ø1/8"	ø5/32"	—	ø1/4" ø5/16" ø3/8"	ø1/4"	ø5/16"	ø3/8"	ø3/8"	ø1/2"
C values: Sonic conductance [dm <sup>3</sup> /(s·bar)]	Free flow	0.2	0.3	0.4	0.6	0.6	0.7	1.0	1.3	1.5	1.6	1.7	2.5	4.4	4.8
	Controlled flow	0.2	0.3	0.4	0.7	0.8	0.6	0.9	1.3	2.1	2.4	3.3	4.4	4.9	
b values: Critical pressure ratio	Free flow	0.3	0.4	0.2	0.3	0.3	0.3	0.4	0.4	0.3	0.3				
	Controlled flow	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3				

Note 1) 10-32UNF has the same specification as M5.

Note 2) C and b values are for controlled flow with the needle fully open and free flow with the needle fully closed.

# Speed Controller with Indicator/Elbow Type *Series AS-FS*



## How to Order



### Width across flats (H)

E	8 mm
—	9 mm

### Body size

1	M5 x 0.8 10-32UNF
---	----------------------

### Port size

M5	M5 x 0.8
U10/32	10-32UNF

### Applicable tubing O.D. <sup>Note 1)</sup>

Metric size		Inch size	
02	ø2	01	ø1/8"
23	ø3.2 <sup>Note 2)</sup>	03	ø5/32"
04	ø4	07	ø1/4"
06	ø6		

Note 1) For selecting applicable tubing O.D., refer to the "Model" on page 3.  
Metric size and inch size types can be visually identified by colour of the release button.  
Metric size: Light grey  
Inch size: Orange

Note 2) Use ø1/8" tube.

Body size 1

AS 1 2 0 1F S — M5 E — 06 —

Body size 2/3/4

AS 2 2 0 1F S — 01 — 06 S —

### Body size

2	1/8, 1/4
3	3/8
4	1/2

With indicator

### Type

2	Elbow
---	-------

### Control type <sup>Note)</sup>

0	Meter-out
1	Meter-in

Note) Meter-out and meter-in types can be visually identified by colour of the handle.  
Meter-out: Grey  
Meter-in: Light blue

### Indicator direction

—	0°	
1	180°	

Note) Orientation of indicator direction is fixed when manufacturing, and cannot be changed by the user.

• **Made to Order**  
Refer to page 10 for details.

### Seal method

—	Without sealant
S	With sealant

Note) Face seal type is used for the G thread type.  
Select "—/Without sealant" option.

Example) AS2201FS-G01-06

### Applicable tubing O.D. <sup>Note 1)</sup>

Metric size		Inch size <sup>Note 3)</sup>	
23	ø3.2 <sup>Note 2)</sup>	01	ø1/8"
04	ø4	03	ø5/32"
06	ø6	07	ø1/4"
08	ø8	09	ø5/16"
10	ø10	11	ø3/8"
12	ø12	13	ø1/2"
16	ø16		

Note 1) For selecting applicable tubing O.D., refer to the "Model" on page 3.

Note 2) Use ø1/8" tube.

Note 3) Only the metric size is available for the G thread type.

### Port size

01	1/8
02	1/4
03	3/8
04	1/2

### Thread type

—	R
N	NPT
G	G

AS-FS

AS-FSG


Uni-AS-FS



# Series AS-FS


## Needle Valve/Flow-rate Characteristics

AS1201FS□-M5□, AS1211FS□-M5□




Note) -U10/32 has the same specification as M5.


AS2201FS□-01, AS2211FS□-01




AS2201FS□-02, AS2211FS□-02



AS3201FS□, AS3211FS□




AS4201FS□, AS4211FS□



Note) The numbers above the flow-rate characteristic curves in the charts show the applicable tubing outside diameter as defined by the product number.


## Construction

**Seal method: Gasket seal**  
For M5, 10-32UNF




Meter-in type      Meter-out type

**Seal method: Sealant**  
For R, NPT thread



Meter-in type      Meter-out type

**Seal method: Face seal**  
For G thread



Meter-in type      Meter-out type

## Component Parts

No.	Description	Material	Note
1	Body A	PBT	
2	Body B	Brass	Electroless nickel plating
3	Handle	POM	
4	Needle	PBT	
5	Needle guide	Brass	Electroless nickel plating
6	U seal	HNBR	
7	O-ring	NBR	
8	O-ring	NBR	
9	Cassette	—	
10	Seal	NBR	
11	Bonnet A	POM	
12	Bonnet B	POM	
13	Gear	POM	
14	Indicator gear	POM	
15	Clip	Stainless steel	
16	Gasket	NBR/Stainless steel	
17	Seal	NBR	

# Series AS-FS


## Dimensions

Seal method: Gasket seal  
For M5, 10-32UNF



Indicator direction: 180°

Indicator direction: 0°



### Metric Size

Model	d	T	H	D1	D3	L1	L2	L3	L4 Note 1)		A Note 2)		M	W1	W2	X	Y	Weight [g]														
									Unlocked	Locked	Unlocked	Locked																				
AS12□1FS□-M5E-02	2	M5 x 0.8 10/32UNF	8	5.8	9.4	15.8	20.3	16.9	39	36.5	35	33.5	11.9	13.6	15.1	5.5	9.6	7														
AS12□1FS□-U10/32E-02				7.2		17.2	21.7																									
AS12□1FS□-M5E-23	3.2			8.2															18.6	23.1	16.5											
AS12□1FS□-U10/32E-23	4			10.4																												
AS12□1FS□-M5E-04	6																															
AS12□1FS□-U10/32E-04																																
AS12□1FS□-M5E-06																																
AS12□1FS□-U10/32E-06																																

Note 1) Reference dimensions

Note 2) Reference dimensions of threads after installation

### Inch Size

Model	d	T	H	D1	D3	L1	L2	L3	L4 Note 1)		A Note 2)		M	W1	W2	X	Y	Weight [g]																	
									Unlocked	Locked	Unlocked	Locked																							
AS12□1FS□-M5E-01	1/8"	M5 x 0.8 10/32UNF	8	7.2	9.4	17.2	21.7	16.9	39.0	36.5	35	33.5	13.3	13.6	15.1	5.5	9.6	7																	
AS12□1FS□-U10/32E-01				8.2		18.6	23.1												16.5																
AS12□1FS□-M5E-03	5/32"																																		
AS12□1FS□-U10/32E-03	1/4"																																		
AS12□1FS□-M5E-07																																			
AS12□1FS□-U10/32E-07																																			

Note 1) Reference dimensions

Note 2) Reference dimensions of threads after installation







## Dimensions

Seal method: Sealant  
For R, NPT thread

Indicator direction: 180°



Indicator direction: 0°



## Metric Size

Model	d	T (R, NPT)	H	D1	D3	L1	L2	L3	L4 Note 1)		A Note 2)		M	W1	W2	X	Y	Weight [g]			
									Unlocked	Locked	Unlocked	Locked									
AS22□1FS□-01-23(S)	3.2	1/8	13 (12.7)	7.2	12	19.1	26.1 (26)	19.1	43.9	42.4	40.8	39.3	13.3	20	21.5	6.5	15	13 (13)			
AS22□1FS□-01-04(S)	4			8.2														22.4	29.4 (29.3)	14.2	15 (14)
AS22□1FS□-01-06(S)	6			10.4														25.3	32.3 (32.2)	15.6	16 (15)
AS22□1FS□-01-08(S)	8			13.2																	
AS22□1FS□-01-10(S)	10	15.9																			
AS22□1FS□-02-23(S)	3.2	1/4	17 (17.5)	7.2	13	20.9	30 (30.3)	22.6	49.7	48.3	44.2	42.8	13.3	21.5	24	7.8	16.2	23 (24)			
AS22□1FS□-02-04(S)	4			8.2														23.4	32.5 (32.8)	14.2	24 (25)
AS22□1FS□-02-06(S)	6			10.4														23.9	33 (33.3)	15.6	25 (26)
AS22□1FS□-02-08(S)	8			13.2														26.9	36 (36.3)		
AS22□1FS□-02-10(S)	10	15.9																			
AS32□1FS□-02-06(S)	6	1/4	19	10.4	16.6	21.8	32.1	36.4	63.1	61.7	57.9	56.5	13.3	24.5	28.5	9.3	19.2	47 (48)			
AS32□1FS□-02-08(S)	8			13.2														22.7	33	14.2	38 (39)
AS32□1FS□-02-10(S)	10			15.9														26.7	37	15.6	50 (51)
AS32□1FS□-02-12(S)	12			18.5														29.7	40	17	
AS32□1FS□-03-06(S)	6	3/8	19	10.4	16.6	21.8	32.1	28.7	55.4	54	50.2	48.8	13.3	24.5	28.5	9.3	19.2	38 (39)			
AS32□1FS□-03-08(S)	8			13.2														22.7	33	14.2	39 (40)
AS32□1FS□-03-10(S)	10			15.9														26.7	37	15.6	41 (42)
AS32□1FS□-03-12(S)	12			18.5														29.7	40	17	
AS42□1FS□-04-10(S)	10	1/2	24 (23.8)	15.9	18.8	27.4	40.3 (40.2)	36.2	64.1	62.5	57	55.4	15.6	26	29	10	19	62 (61)			
AS42□1FS□-04-12(S)	12			18.5														30.8	43.7 (43.6)	35.1	64 (63)
AS42□1FS□-04-16(S)	16			23.8														34.8	47.7 (47.6)	32.7	68 (67)

Note 1) Reference dimensions Note 2) Reference dimensions of threads after installation Note 3) ( ) are the dimensions of NPT thread.

## Inch Size

Model	d	T (R, NPT)	H	D1	D3	L1	L2	L3	L4 Note 1)		A Note 2)		M	W1	W2	X	Y	Weight [g]															
									Unlocked	Locked	Unlocked	Locked																					
AS22□1FS□-01-01(S)	1/8"	1/8	13 (12.7)	7.2	12	19.1	26.1 (26)	19.1	43.8	42.4	40.7	39.3	13.3	20	21.5	6.5	15	13 (13)															
AS22□1FS□-01-03(S)	5/32"			8.2														20.8	27.8 (27.7)	14.2	14 (13)												
AS22□1FS□-01-07(S)	1/4"			11.2														22.4	29.4 (29.3)	15.6	15 (14)												
AS22□1FS□-01-09(S)	5/16"			13.2																													
AS22□1FS□-02-01(S)	1/8"	1/4	17 (17.5)	7.2	13	20.9	30 (30.3)	22.6	49.7	48.3	44.2	42.8	13.3	21.5	24	7.8	16.2	23 (24)															
AS22□1FS□-02-03(S)	5/32"			8.2														23.4	32.5 (32.8)	14.2	24 (24)												
AS22□1FS□-02-07(S)	1/4"			11.2														23.9	33 (33.3)	15.6	24 (25)												
AS22□1FS□-02-09(S)	5/16"			13.2														26.4	35.5 (35.8)	17	25 (26)												
AS22□1FS□-02-11(S)	3/8"	15.5																															
AS32□1FS□-02-07(S)	1/4"	1/4	19	11.2	16.6	21.8	32.1	28.7	63.1	61.7	57.9	56.5	13.3	24.5	28.5	9.3	19.2	47 (48)															
AS32□1FS□-02-09(S)	5/16"			13.2														22.7	33	14.2	48 (49)												
AS32□1FS□-02-11(S)	3/8"			15.5														26.7	37	15.6													
AS32□1FS□-03-07(S)	1/4"			11.2														21.8	32.1	28.7													
AS32□1FS□-03-09(S)	5/16"	3/8	19	13.2	16.6	22.7	33	28.7	55.4	54	50.2	48.8	13.3	24.5	28.5	9.3	19.2	38 (39)															
AS32□1FS□-03-11(S)	3/8"			15.5														26.7	37	28.2	39 (40)												
AS42□1FS□-04-11(S)	3/8"			24 (23.8)														15.5	27.4	40.3 (40.2)	36.2	64.1	62.5	57	55.4	15.6	26	29	10	19	62 (61)		
AS42□1FS□-04-13(S)	1/2"			19.3														30.9	43.8 (43.7)	34.7	64 (63)												

Note 1) Reference dimensions Note 2) Reference dimensions of threads after installation Note 3) ( ) are the dimensions of NPT thread.


# Series AS-FS

## Dimensions

Seal method: Face seal  
For G thread

Indicator direction: 180°

Indicator direction: 0°



## Metric Size

Model	d	T	H	D1	D3	L1	L2	L3	L4 Note 1)		A Note 2)		M	W1	W2	X	Y	Weight [g]			
									Unlocked	Locked	Unlocked	Locked									
AS22□1FS□-G01-23	3.2	1/8	13	7.2	12	19.1	26.1	18.8	43.8	42.4	38.3	36.9	13.3	20	21.5	6.5	15	14			
AS22□1FS□-G01-04	4			8.2																	
AS22□1FS□-G01-06	6			10.4																	
AS22□1FS□-G01-08	8			13.2																	
AS22□1FS□-G01-10	10	15.9	25.3	32.3																	
AS22□1FS□-G02-23	3.2	1/4	17	7.2	13	20.9	30	22.6	49.7	48.3	43.2	41.8	13.3	21.5	24	7.8	16.2	26			
AS22□1FS□-G02-04	4			8.2																	
AS22□1FS□-G02-06	6			10.4															23.4	32.5	
AS22□1FS□-G02-08	8			13.2															23.9	32.6	
AS22□1FS□-G02-10	10	15.9	26.9	36																	
AS32□1FS□-G02-06	6	1/4	21	10.4	16.6	21.8	33	28.7	63.1	61.7	54.6	53.2	13.3	24.5	28.5	9.3	19.2	55			
AS32□1FS□-G02-08	8			13.2															22.7	33.9	
AS32□1FS□-G02-10	10			15.9															26.7	37.9	28
AS32□1FS□-G02-12	12			18.5															29.7	40.9	26.8
AS32□1FS□-G03-06	6	3/8	21	10.4	16.6	21.8	33	28.7	55.4	54	47.9	46.5	13.3	24.5	28.5	9.3	19.2	45			
AS32□1FS□-G03-08	8			13.2															22.7	33.9	
AS32□1FS□-G03-10	10			15.9															26.7	37.9	28
AS32□1FS□-G03-12	12			18.5															29.7	40.9	26.8
AS42□1FS□-G04-10	10	1/2	27	15.9	18.8	27.4	41.8	36.2	64.1	62.5	55.1	53.5	15.6	26	29	10	19	80			
AS42□1FS□-G04-12	12			18.5															30.8	45.2	35.1
AS42□1FS□-G04-16	16			23.8															34.8	49.2	32.7


Note 1) Reference dimensions

Note 2) Reference dimensions of threads after installation


# Series AS-FS

## Made to Order

Please contact SMC for detailed dimensions, specifications and delivery.




### 1 Lubricant: Vaseline -X12



Example) AS2201FS-01-04S-X12


### 2 Grease-free (Seal: Fluorine-coated) + Restrictor (Without check valve) -X21



Example) AS2201FS-01-04S-X21

- Note 1) Not particle-free
- Note 2) The restrictor is only compatible with the part number of the meter-out type.
- Note 3) Only the needle and O-ring are fluorine-coated.


### 3 Restrictor (Without check valve) -X214



Example) AS2201FS-01-04S-X214

Note) The restrictor is only compatible with the part number of the meter-out type.

### 4 Clean Series 10-




Example) 10-AS2201FS-01-04S

- Note 1) Fluorine grease is used.
- Note 2) The particulate generation grade is 3.

AS-FS  
AS-FSG  
Uni-AS-FS

# Speed Controller with Indicator/ Elbow Type: Stainless Steel Type Series AS-FSG



## Model

Model	Port size	Seal method	Applicable tubing O.D.										Note 3) Max. number of rotations				
			Metric size					Inch size									
Elbow type			2 Note 2)	3.2	4	6	8	10	12	16	1/8"	5/32"	1/4"	5/16"	3/8"	1/2"	
AS12□1FSG□-M5	M5 x 0.8	Gasket seal	●	●	●	●					●	●	●				8
AS12□1FSG□-U10/32	10-32UNF		●	●	●	●					●	●	●				
AS22□1FSG□-□01	R NPT	Note 1) Sealant		●	●	●	●	●			●	●	●	●			10
AS22□1FSG□-□02			1/8		●	●	●	●	●			●	●	●	●	●	
AS32□1FSG□-□02			1/4		●	●	●	●	●	●			●	●	●	●	
AS32□1FSG□-□03			1/4				●	●	●	●	●			●	●	●	
AS32□1FSG□-□03			3/8				●	●	●	●	●			●	●	●	
AS42□1FSG□-□04			1/2							●	●	●				●	
AS22□1FSG□-G01	G	Face seal		●	●	●	●	●									10
AS22□1FSG□-G02			1/8		●	●	●	●	●								
AS32□1FSG□-G02			1/4				●	●	●	●	●						
AS32□1FSG□-G03			1/4				●	●	●	●	●						
AS32□1FSG□-G03			3/8				●	●	●	●	●						
AS42□1FSG□-G04			1/2							●	●	●					


Note 1) "Without sealant" type can be selected as a standard option.

Note 2) Only polyurethane tubing is applicable for ø2.

Note 3) There are differences in actual rate as by the indicator window over the maximum number of rotations depending on the individual product.

## Specifications

### Flow Direction Symbol on Body



<b>Fluid</b>	Air
<b>Proof pressure</b>	1.5 MPa
<b>Max. operating pressure</b>	1 MPa
<b>Min. operating pressure</b>	0.1 MPa
<b>Ambient and fluid temperature</b>	-5 to 60°C (No freezing)
<b>Applicable tubing material</b>	Nylon, Soft nylon, Polyurethane <sup>Note)</sup> , FEP, PFA

Note) Use caution at the max. operating pressure when using soft nylon or polyurethane tubing. (Refer to the **WEB catalogue** for details.)

## ⚠ Caution

Be sure to read this before handling. Refer to the back cover for Safety Instructions. For Flow Control Equipment Precautions, refer to "Handling Precautions for SMC Products" and the Operation Manual.


## Flow-rate and Sonic Conductance

Model	AS12□1FSG□-M5	AS22□1FSG□-01	AS22□1FSG□-02	AS32□1FSG□	AS42□1FSG□
Tubing O.D.	Metric size	ø2 ø3.2 ø4 ø6	ø3.2 ø4 ø6 ø8 ø10	ø3.2 ø4 ø6 ø8 ø10	ø6 ø8 ø10 ø12 ø10 ø12 ø16
	Inch size	— ø1/8" ø1/4" ø5/32"	ø1/8" ø5/32" ø1/4" ø5/16"	ø1/8" ø5/32" — ø1/4" ø5/16" ø3/8"	ø1/4" ø5/16" ø3/8" ø3/8" ø1/2"
C values: Sonic conductance [dm <sup>3</sup> /(s·bar)]	Free flow	0.2 0.3	0.4 0.6 0.6	0.7 1.0 1.3 1.5	1.6 1.7 2.5 4.4 4.8
	Controlled flow	0.2 0.3	0.4 0.7 0.8	0.6 0.9 1.3	2.1 2.4 3.3 4.4 4.9
b values: Critical pressure ratio	Free flow	0.3 0.4	0.2 0.3	0.3 0.4	0.4 0.3 0.3
	Controlled flow	0.2	0.2 0.3	0.3	0.3 0.3

Note 1) 10-32UNF has the same specification as M5.

Note 2) C and b values are for controlled flow with the needle fully open and free flow with the needle fully closed.

# Speed Controller with Indicator/Elbow Type Stainless Steel Type **Series AS-FSG**




## How to Order



### Applicable tubing O.D. <sup>Note 1)</sup>

Metric size		Inch size	
02	ø2	01	ø1/8"
23	ø3.2 <sup>Note 2)</sup>	03	ø5/32"
04	ø4	07	ø1/4"
06	ø6		

Note 1) For selecting applicable tubing O.D., refer to the "Model" on page 11.  
Metric size and inch size types can be visually identified by colour of the release button.  
Stainless steel type: White  
White is also used for inch size.  
Note 2) Use ø1/8" tube.




AS-FS  
AS-FSG  
Uni-AS-FS

# Series AS-FSG


## Needle Valve/Flow-rate Characteristics

AS1201FSG□-M5, AS1211FSG□-M5




Note) -U10/32 has the same specification as M5.


AS2201FSG□-01, AS2211FSG□-01




AS2201FSG□-02, AS2211FSG□-02



AS3201FSG□, AS3211FSG□



AS4201FSG□, AS4211FSG□




Note) The numbers above the flow-rate characteristic curves in the charts show the applicable tubing outside diameter as defined by the product number.




## Construction

**Seal method: Gasket seal**  
For M5, 10-32UNF




Meter-in type    Meter-out type

**Seal method: Sealant**  
For R, NPT thread



Meter-in type    Meter-out type

**Seal method: Face seal**  
For G thread



Meter-in type    Meter-out type

## Component Parts

No.	Description	Material	Note
1	Body A	PBT	
2	Body B	Stainless steel	
3	Handle	POM	
4	Needle	PBT	
5	Needle guide	Stainless steel	
6	U seal	HNBR	
7	O-ring	NBR	
8	O-ring	NBR	
9	Cassette	—	
10	Seal	NBR	
11	Bonnet A	POM	
12	Bonnet B	POM	
13	Gear	POM	
14	Indicator gear	POM	
15	Clip	Stainless steel	
16	Gasket	NBR/Stainless steel	
17	Seal	NBR	

# Series AS-FSG




## Dimensions

Seal method: Gasket seal  
For M5, 10-32UNF



Indicator direction: 180°

Indicator direction: 0°



### Metric Size

Model	d	T	H	D1	D3	L1	L2	L3	L4 Note 1)		A Note 2)		M	W1	W2	X	Y	Weight [g]	
									Unlocked	Locked	Unlocked	Locked							
AS12□1FSG□-M5-02	2	M5 x 0.8 10/32UNF	8	5.8	9.4	15.8	20.3	16.9	39	36.5	35	33.5	13.3	13.6	15.1	5.5	9.6	7	
AS12□1FSG□-U10/32-02				7.2															
AS12□1FSG□-M5-23	3.2			8.2															
AS12□1FSG□-U10/32-23				10.4															
AS12□1FSG□-M5-04	4			18.6		23.1	16.5												8
AS12□1FSG□-U10/32-04	6																		
AS12□1FSG□-M5-06																			
AS12□1FSG□-U10/32-06																			

Note 1) Reference dimensions

Note 2) Reference dimensions of threads after installation

### Inch Size

Model	d	T	H	D1	D3	L1	L2	L3	L4 Note 1)		A Note 2)		M	W1	W2	X	Y	Weight [g]		
									Unlocked	Locked	Unlocked	Locked								
AS12□1FSG□-M5-01	1/8"	M5 x 0.8 10/32UNF	8	7.2	9.4	17.2	21.7	16.9	39.0	36.5	35	33.5	13.3	13.6	15.1	5.5	9.6	7		
AS12□1FSG□-U10/32-01				8.2																
AS12□1FSG□-M5-03	5/32"			11.2		18.6	23.1												16.5	8
AS12□1FSG□-U10/32-03																				
AS12□1FSG□-M5-07	1/4"																			
AS12□1FSG□-U10/32-07																				

Note 1) Reference dimensions


Note 2) Reference dimensions of threads after installation

# Speed Controller with Indicator/Elbow Type Stainless Steel Type *Series AS-FSG*



## Dimensions

Seal method: Sealant  
For R, NPT thread



### Metric Size

Model	d	T (R, NPT)	H	D1	D3	L1	L2	L3	L4 Note 1)		A Note 2)		M	W1	W2	X	Y	Weight [g]
									Unlocked	Locked	Unlocked	Locked						
AS22□1FSG□-01-23(S)	3.2	1/8	13 (12.7)	7.2	12	19.1	26.1 (26)	19.1	43.9	42.4	40.8	39.3	13.3	20	21.5	6.5	15	13 (13)
AS22□1FSG□-01-04(S)	4			14 (13)														
AS22□1FSG□-01-06(S)	6			15 (14)														
AS22□1FSG□-01-08(S)	8			16 (15)														
AS22□1FSG□-01-10(S)	10			15.9		25.3	32.3 (32.2)						15.6					16 (15)
AS22□1FSG□-02-23(S)	3.2	1/4	17 (17.5)	7.2	13	20.9	30 (30.3)	22.6	49.7	48.3	44.2	42.8	13.3	21.5	24	7.8	16.2	23 (24)
AS22□1FSG□-02-04(S)	4			24 (25)														
AS22□1FSG□-02-06(S)	6			25 (26)														
AS22□1FSG□-02-08(S)	8																	
AS22□1FSG□-02-10(S)	10			15.9		26.9	36 (36.3)						15.6					25 (26)
AS32□1FSG□-02-06(S)	6	1/4	19	10.4	16.6	21.8	32.1	36.4	63.1	61.7	57.9	56.5	13.3	24.5	28.5	9.3	19.2	47 (48)
AS32□1FSG□-02-08(S)	8			38 (39)														
AS32□1FSG□-02-10(S)	10			50 (51)														
AS32□1FSG□-02-12(S)	12																	
AS32□1FSG□-03-06(S)	6	3/8	19	10.4	16.6	21.8	32.1	28.7	55.4	54	50.2	48.8	13.3	24.5	28.5	9.3	19.2	38 (39)
AS32□1FSG□-03-08(S)	8			29 (40)														
AS32□1FSG□-03-10(S)	10			41 (42)														
AS32□1FSG□-03-12(S)	12																	
AS42□1FSG□-04-10(S)	10	1/2	24 (23.8)	15.9	18.8	27.4	40.3 (40.2)	36.2	64.1	62.5	57	55.4	15.6	26	29	10	19	62 (61)
AS42□1FSG□-04-12(S)	12			64 (63)														
AS42□1FSG□-04-16(S)	16			68 (67)														

Note 1) Reference dimensions Note 2) Reference dimensions of threads after installation Note 3) ( ) are the dimensions of NPT thread.

### Inch Size

Model	d	T (R, NPT)	H	D1	D3	L1	L2	L3	L4 Note 1)		A Note 2)		M	W1	W2	X	Y	Weight [g]
									Unlocked	Locked	Unlocked	Locked						
AS22□1FSG□-01-01(S)	1/8"	1/8	13 (12.7)	7.2	12	19.1	26.1 (26)	19.1	43.8	42.4	40.7	39.3	13.3	20	21.5	6.5	15	13 (13)
AS22□1FSG□-01-03(S)	5/32"			14 (13)														
AS22□1FSG□-01-07(S)	1/4"			15 (14)														
AS22□1FSG□-01-09(S)	5/16"			16 (15)														
AS22□1FSG□-02-01(S)	1/8"	1/4	17 (17.5)	7.2	13	20.9	30 (30.3)	22.6	49.7	48.3	44.2	42.8	13.3	21.5	24	7.8	16.2	23 (24)
AS22□1FSG□-02-03(S)	5/32"			24 (25)														
AS22□1FSG□-02-07(S)	1/4"			25 (26)														
AS22□1FSG□-02-09(S)	5/16"																	
AS22□1FSG□-02-11(S)	3/8"			15.5		26.4	35.5 (35.8)						15.6					25 (26)
AS32□1FSG□-02-07(S)	1/4"	3/8	19	11.2	16.6	21.8	32.1	28.7	63.1	61.7	57.9	56.5	13.3	24.5	28.5	9.3	19.2	47 (48)
AS32□1FSG□-02-09(S)	5/16"			38 (39)														
AS32□1FSG□-02-11(S)	3/8"			48 (49)														
AS32□1FSG□-03-07(S)	1/4"																	
AS32□1FSG□-03-09(S)	5/16"	3/8	19	11.2	16.6	21.8	32.1	28.7	55.4	54	50.2	48.8	13.3	24.5	28.5	9.3	19.2	38 (39)
AS32□1FSG□-03-11(S)	3/8"			39 (40)														
AS42□1FSG□-04-11(S)	3/8"																	
AS42□1FSG□-04-13(S)	1/2"	1/2	24 (23.8)	15.5	18.8	27.4	40.3 (40.2)	36.2	64.1	62.5	57	55.4	15.6	26	29	10	19	62 (61)
	1/2"			64 (63)														


Note 1) Reference dimensions Note 2) Reference dimensions of threads after installation Note 3) ( ) are the dimensions of NPT thread.

# Series AS-FSG


## Dimensions

Seal method: Face seal  
For G thread

Indicator direction: 180°



Indicator direction: 0°



### Metric Size

Model	d	T	H	D1	D3	L1	L2	L3	L4 Note 1)		A Note 2)		M	W1	W2	X	Y	Weight [g]			
									Unlocked	Locked	Unlocked	Locked									
AS22□1FSG□-G01-23	3.2	1/8	13	7.2	12	19.1	26.1	18.8	43.8	42.4	38.3	36.9	13.3	20	21.5	6.5	15	14			
AS22□1FSG□-G01-04	4			8.2																	
AS22□1FSG□-G01-06	6			10.4															22.4	29.4	14.2
AS22□1FSG□-G01-10	10			15.9															25.3	32.3	15.6
AS22□1FSG□-G02-23	3.2	1/4	17	7.2	13	20.9	30	22.6	49.7	48.3	43.2	41.8	13.3	21.5	24	7.8	16.2	26			
AS22□1FSG□-G02-04	4			8.2																	
AS22□1FSG□-G02-06	6			10.4															23.4	32.5	14.2
AS22□1FSG□-G02-08	8			13.2															23.9	32.6	15.6
AS22□1FSG□-G02-10	10	15.9	26.9	36	15.6																
AS32□1FSG□-G02-06	6	1/4	21	10.4	16.6	21.8	33	28.7	63.1	61.7	54.6	53.2	13.3	24.5	28.5	9.3	19.2	55			
AS32□1FSG□-G02-08	8			13.2															22.7	33.9	14.2
AS32□1FSG□-G02-10	10			15.9															26.7	37.9	15.6
AS32□1FSG□-G02-12	12			18.5															29.7	40.9	17
AS32□1FSG□-G03-06	6	3/8	21	10.4	16.6	21.8	33	28.7	55.4	54	47.9	46.5	13.3	24.5	28.5	9.3	19.2	45			
AS32□1FSG□-G03-08	8			13.2															22.7	33.9	14.2
AS32□1FSG□-G03-10	10			15.9															26.7	37.9	15.6
AS32□1FSG□-G03-12	12			18.5															29.7	40.9	17
AS42□1FSG□-G04-10	10	1/2	27	15.9	18.8	27.4	41.8	36.2	64.1	62.5	55.1	53.5	15.6	26	29	10	19	80			
AS42□1FSG□-G04-12	12			18.5									30.8					45.2	35.1	17	82
AS42□1FSG□-G04-16	16	23.8	34.8	49.2	32.7	20.6	86														

Note 1) Reference dimensions

Note 2) Reference dimensions of threads after installation


# Series AS-FSG

## Made to Order

Please contact SMC for detailed dimensions, specifications and delivery.




### 1 Lubricant: Vaseline -X12



Example) AS2201FSG-01-04S-X12


### 2 Grease-free (Seal: Fluorine-coated) + Restrictor (Without check valve) -X21



Example) AS2201FSG-01-04S-X21

- Note 1) Not particle-free
- Note 2) The restrictor is only compatible with the part number of the meter-out type.
- Note 3) Only the needle and O-ring are fluorine-coated.


### 3 Restrictor (Without check valve) -X214



Example) AS2201FSG-01-04S-X214

Note) The restrictor is only compatible with the part number of the meter-out type.

### 4 Clean Series 10-




Example) 10-AS2201FSG-01-04S


- Note 1) Fluorine grease is used.
- Note 2) The particulate generation grade is 3.

AS-FS  
AS-FSG  
Uni-AS-FS

# Speed Controller with Indicator/ Elbow Type: Uni Thread Type Series AS-FS



New-stand male threads for piping that reduces the screw-in time by 1/3.



## Shape of Uni thread ridge


Use of the chamfered surface of the female thread as the seat surface and adoption of gaskets made by laminating NBR on both surfaces of stainless steel plates achieve secure sealing regardless of the difference of diameters due to the female thread type, deviations due to the tolerance, or the size of the chamfered corner.

(Any standard chamfered female thread can be used.)

A ridge shape has been created as a Uni thread for common applications for Rc, G, NPT and NPTF.

The male thread for piping drastically cuts piping man-hours.

## Flow Direction Symbol on Body



## Caution

Be sure to read this before handling. Refer to the back cover for Safety Instructions. For Flow Control Equipment Precautions, refer to "Handling Precautions for SMC Products" and the Operation Manual.

## Model

Model	Uni thread port size	Applicable tubing O.D.												
		Metric size						Inch size						
		3.2	4	6	8	10	12	16	1/8"	5/32"	1/4"	5/16"	3/8"	1/2"
AS22□1FS□-U01	1/8	●	●	●	●	●			●	●	●	●		
AS22□1FS□-U02	1/4	●	●	●	●	●			●	●	●	●	●	
AS32□1FS□-U02	1/4			●	●	●	●				●	●	●	
AS32□1FS□-U03	3/8			●	●	●	●				●	●	●	
AS42□1FS□-U04	1/2					●	●	●					●	●

## Specifications

Fluid	Air
Proof pressure	1.5 MPa
Max. operating pressure	1 MPa
Min. operating pressure	0.1 MPa
Ambient and fluid temperature	-5 to 60°C (No freezing)
Applicable tubing material	Nylon, Soft nylon, Polyurethane <sup>Note)</sup> , FEP, PFA

Note) Use caution at the max. operating pressure when using soft nylon or polyurethane tubing. (Refer to the WEB catalogue for details.)


## Flow-rate and Sonic Conductance

Model	AS22□1FS□-U01	AS22□1FS□-U02	AS32□1FS□	AS42□1FS□
Tubing O.D.	Metric size	ø3.2 ø4 ø6 ø8 ø10	ø3.2 ø4 ø6 ø8 ø10	ø6 ø8 ø10 ø12 ø10 ø12 ø16
	Inch size	ø1/8" ø5/32" ø1/4" ø5/16"	ø1/8" ø5/32" — ø1/4" ø5/16" ø3/8"	ø1/4" ø5/16" ø3/8" ø3/8" ø1/2"
C values: Sonic conductance [dm <sup>3</sup> /(s·bar)]	Free flow	0.4 0.6 0.6 0.7 1.0 1.3 1.5	1.6 1.7 2.5 4.4 4.8	1.6 1.7 2.5 4.4 4.8
	Controlled flow	0.4 0.7 0.8 0.6 0.9 1.3	2.1 2.4 3.3 4.4 4.9	2.1 2.4 3.3 4.4 4.9
b values: Critical pressure ratio	Free flow	0.2 0.3 0.3 0.4	0.4 0.3 0.3	0.4 0.3 0.3
	Controlled flow	0.2 0.3 0.3 0.3	0.3 0.3 0.3	0.3 0.3 0.3

Note) C and b values are for controlled flow with the needle fully open and free flow with the needle fully closed.



# Speed Controller with Indicator/Elbow Type Uni Thread Type **Series AS-FS**



## How to Order

**AS 2 2 0 1 F S** - **U01** - **06**

**Body size**

2	1/8, 1/4
3	3/8
4	1/2


**Type**

2	Elbow
---	-------

**Control type** (Note)

0	Meter-out
1	Meter-in

Note) Meter-out and meter-in types can be visually identified by colour of the handle.  
 Meter-out: Grey  
 Meter-in: Light blue



Note) Orientation of indicator direction is fixed when manufacturing, and cannot be changed by the user.

**Port size**

U01	Uni 1/8
U02	Uni 1/4
U03	Uni 3/8
U04	Uni 1/2


• **Applicable tubing O.D.** (Note 1)

Metric size		Inch size	
Tubing O.D.		Tubing O.D.	
23	ø3.2 (Note 2)	01	ø1/8"
04	ø4	03	ø5/32"
06	ø6	07	ø1/4"
08	ø8	09	ø5/16"
10	ø10	11	ø3/8"
12	ø12	13	ø1/2"
16	ø16		


Note 1) For selecting applicable tubing O.D., refer to the "Model" on page 19.  
 Metric size and inch size types can be visually identified by colour of the release button.  
 Metric size: Light grey  
 Inch size: Orange  
 Note 2) Use ø1/8" tube.

## Needle Valve/Flow-rate Characteristics


AS2201FS□-U01, AS2211FS□-U01




AS2201FS□-U02, AS2211FS□-U02



AS3201FS□, AS3211FS□



AS4201FS□, AS4211FS□




Note) The numbers above the flow-rate characteristic curves in the charts show the applicable tubing outside diameter as defined by the product number.

# Series AS-FS

## Construction

### Elbow type

AS22□1FS□-U01-06A




### Component Parts

No.	Description	Material	Note
1	Body A	PBT	
2	Body B	Brass	Electroless nickel plating
3	Handle	POM	
4	Needle	PBT	
5	Needle guide	Brass	Electroless nickel plating
6	U seal	HNBR	
7	O-ring	NBR	
8	O-ring	NBR	
9	Cassette	—	
10	Seal	NBR	
11	Bonnet A	POM	
12	Bonnet B	POM	
13	Gear	POM	
14	Indicator gear	POM	
15	Clip	Stainless steel	
16	Gasket	NBR/Stainless steel	

**Dimensions**

Seal method: Gasket seal  
For Uni thread



**Metric Size**

Model	d	T	H	D1	D3	L1	L2	L3	L4 Note 1)		A Note 2)		M	W1	W2	X	Y	Weight [g]															
									Unlocked	Locked	Unlocked	Locked																					
AS22□1FS□-U01-23	3.2	1/8	13 (12.7)	7.2	12	19.1	26.1 (26)	19.1	43.9	42.4	40.8	39.3	13.3	20	21.5	6.5	15	13 (13)															
AS22□1FS□-U01-04	4			8.2														22.4	29.4 (29.3)	14.2	15 (14)												
AS22□1FS□-U01-06	6			10.4														25.3	32.3 (32.2)	15.6	16 (15)												
AS22□1FS□-U01-08	8			13.2																													
AS22□1FS□-U01-10	10			15.9																													
AS22□1FS□-U02-23	3.2	1/4	17 (17.5)	7.2	13	20.9	30 (30.3)	22.6	49.7	48.3	44.2	42.8	13.3	21.5	24	7.8	16.2	24 (25)															
AS22□1FS□-U02-04	4			8.2														23.4	32.5 (32.8)	14.2	25 (26)												
AS22□1FS□-U02-06	6			10.4														23.9	33 (33.3)	15.6	26 (27)												
AS22□1FS□-U02-08	8			13.2														26.9	36 (36.3)														
AS22□1FS□-U02-10	10			15.9																													
AS32□1FS□-U02-06	6	1/4	19	10.4	16.6	21.8	32.1	36.4	63.1	61.7	57.9	56.5	13.3	24.5	28.5	9.3	19.2	47 (48)															
AS32□1FS□-U02-08	8			13.2														22.7	33	14.2	48 (49)												
AS32□1FS□-U02-10	10			15.9														26.7	37	15.6	50 (51)												
AS32□1FS□-U02-12	12			18.5														29.7	40	17													
AS32□1FS□-U03-06	6			3/8														19	10.4	16.6	21.8	32.1	28.7	55.4	54	50.2	48.8	13.3	24.5	28.5	9.3	19.2	36 (37)
AS32□1FS□-U03-08	8	13.2	22.7		33	14.2	39 (40)																										
AS32□1FS□-U03-10	10	15.9	26.7		37	15.6	41 (42)																										
AS32□1FS□-U03-12	12	18.5	29.7		40	17																											
AS42□1FS□-U04-10	10	1/2	24 (23.8)		15.9	18.8	27.4	40.3 (40.2)	36.2	64.1	62.5	57	55.4	15.6	26	29	10		19														60 (59)
AS42□1FS□-U04-12	12			18.5	30.8													43.7 (43.6)		35.1	17	62 (61)											
AS42□1FS□-U04-16	16			23.8	34.8													47.7 (47.6)		32.7	20.6	66 (65)											

Note 1) Reference dimensions Note 2) Reference dimensions of threads after installation Note 3) ( ) are the dimensions of NPT thread.

**Inch Size**

Model	d	T	H	D1	D3	L1	L2	L3	L4 Note 1)		A Note 2)		M	W1	W2	X	Y	Weight [g]															
									Unlocked	Locked	Unlocked	Locked																					
AS22□1FS□-U01-01	1/8"	1/8	13 (12.7)	7.2	12	19.1	26.1 (26)	19.1	43.8	42.4	40.7	39.3	13.3	20	21.5	6.5	15	13 (13)															
AS22□1FS□-U01-03	5/32"			8.2														20.8	27.8 (27.7)	14.2	14 (13)												
AS22□1FS□-U01-07	1/4"			11.2														22.4	29.4 (29.3)	15.6	15 (14)												
AS22□1FS□-U01-09	5/16"			13.2																													
AS22□1FS□-U02-01	1/8"	1/4	17 (17.5)	7.2	13	20.9	30 (30.3)	22.6	49.7	48.3	44.2	42.8	13.3	21.5	24	7.8	16.2	23 (24)															
AS22□1FS□-U02-03	5/32"			8.2														23.4	32.5 (32.8)	14.2	24 (24)												
AS22□1FS□-U02-07	1/4"			11.2														23.9	33 (33.3)	15.6	24 (25)												
AS22□1FS□-U02-09	5/16"			13.2														26.4	35.5 (35.8)	17	25 (26)												
AS22□1FS□-U02-11	3/8"			15.5																													
AS32□1FS□-U02-07	1/4"	3/8	19	11.2	16.6	21.8	32.1	28.7	63.1	61.7	57.9	56.5	13.3	24.5	28.5	9.3	19.2	47 (48)															
AS32□1FS□-U02-09	5/16"			13.2														22.7	33	14.2	48 (49)												
AS32□1FS□-U02-11	3/8"			15.5														26.7	37	15.6													
AS32□1FS□-U03-07	1/4"			3/8														19	11.2	16.6	21.8	32.1	28.7	55.4	54	50.2	48.8	13.3	24.5	28.5	9.3	19.2	36 (37)
AS32□1FS□-U03-09	5/16"	13.2	22.7		33	14.2	37 (38)																										
AS32□1FS□-U03-11	3/8"	15.5	26.7		37	15.6																											
AS42□1FS□-U04-11	3/8"	1/2	24 (23.8)		15.5	18.8	27.4	40.3 (40.2)	36.2	64.1	62.5	57	55.4	15.6	26	29	10		19														60 (59)
AS42□1FS□-U04-13	1/2"			19.3	30.9													43.8 (43.7)		34.7	17	62 (61)											

Note 1) Reference dimensions Note 2) Reference dimensions of threads after installation Note 3) ( ) are the dimensions of NPT thread.



## Series AS-FS

# Specific Product Precautions 1

Be sure to read this before handling. Refer to the back cover for Safety Instructions. For Flow Control Equipment Precautions, refer to “Handling Precautions for SMC Products” for Flow Control Equipment Precautions and the Operation Manual.

### Design and Selection

#### ⚠ Warning

##### 1. Check the specifications.

The products in this catalogue are designed to be used in compressed air systems (including vacuum) only.

If the products are used in an environment where pressure or temperature is out of the specified range, damage and/or malfunction may result. Do not use under such conditions. (Refer to the specifications.)

Please contact SMC when using a fluid other than compressed air (including vacuum).

We do not guarantee against any damage if the product is used outside of the specification range.

##### 2. The products in this catalogue are not designed for the use as stop valve with zero air leakage.

A certain amount of leakage is allowed in the product's specifications.

Tightening the needle to reduce leakage to zero may result in equipment damage.

##### 3. Do not disassemble the product or make any modifications, including additional machining.

It may cause human injury and/or an accident.

##### 4. The flow-rate characteristics for each product are representative values.

The flow-rate characteristics are characteristics of each individual product. Actual values may differ depending on the piping, circuitry, pressure conditions, etc.

##### 5. Sonic conductance (C) and critical pressure ratio (b) values for products are representative values.

The speed controller's controlled flow values are with the needle fully open and free flow with the needle fully closed.

##### 6. Check if PTFE can be used in application.

PTFE powder (Polytetrafluoroethylene resin) is included in the seal material for piping taper thread of male thread type. Confirm that the use of it will not cause any adverse effect on the system.

Please contact SMC if the Material Safety Data Sheet (MSDS) is required.

### Mounting

#### ⚠ Warning

##### 1. Operation Manual

Install the products and operate them only after reading the Operation Manual carefully and understanding its contents. Also, keep the Operation Manual where it can be referred to as necessary.

##### 2. Ensure sufficient space for maintenance activities.

When installing the products, allow access for maintenance.

##### 3. Tighten threads with the proper tightening torque.

When installing the products, follow the listed proper torque.

### Mounting

#### ⚠ Warning

##### 4. After pushing the handle down to lock, confirm that it is locked.

It should not be possible to rotate the handle to the right or to the left. If the handle is pulled with force, it may break. Do not pull the handle with excessive force.



Locked

Unlocked

##### 5. Check the degree of rotation of the needle valve.

The products in this catalogue are retainer type so that the needle is not removed completely. Over rotation will cause damage.

##### 6. Do not use tools such as pliers to rotate the handle.

It can cause idle rotation of the handle or damage.

##### 7. Verify the air flow direction.

Mounting backward is dangerous, because the speed adjustment needle will not work and the actuator may lurch suddenly.

##### 8. Adjust the speed by opening the needle slowly from the fully closed state.

Loose needle valves may cause unexpected sudden actuator lurching.

When a needle valve is turned clockwise, it is closed and actuator speed decreases. When a needle valve is turned counter-clockwise, it is open and actuator speed increases.

##### 9. Do not apply excessive force or shock to the body or fittings with an impact tool.

It can cause damage or air leakage.

##### 10. Refer to One-touch fittings catalogue for more details about their piping and mounting precautions.

##### 11. Tubing O.D. $\varnothing 2$

Tubing other than that from SMC cannot be used, because it may result in inability to connect the tube, air leakage after connecting the tube or disconnection of the tube.

##### 12. To install/remove the product, use an appropriate wrench to tighten/loosen at the supplied nut on body B.

Do not apply torque at other points as the product may be damaged. Rotate body A manually for positioning after installation.



# Series AS-FS Specific Product Precautions 2


Be sure to read this before handling. Refer to the back cover for Safety Instructions. For Flow Control Equipment Precautions, refer to “Handling Precautions for SMC Products” for Flow Control Equipment Precautions and the Operation Manual.

## Mounting

### Warning

13. Do not use body A for applications involving continuous rotation.

Body A and the fitting section may be damaged.



### Caution

#### For M5, 10-32UNF

##### Tightening method


First, tighten it by hand, then give it an additional 1/6 turn to 1/4 turn with a wrench. A reference value for the tightening torque is 1 to 1.5 N·m.

Note) Excessive tightening may damage the thread portion or deform the gasket and cause air leakage.

If the screw is too shallowly screwed in, it may come loose or air may leak.

##### Chamfered area for female thread

1. Confirming to ISO 16030 (air pressure fluid dynamics – connection – ports and stud ends), the chamfered dimensions shown in the table below are recommended.



Female thread port size	Chamfered dimension $\phi D$ (Recommended value)
M5	5.1 to 5.4
10-32UNF	5.0 to 5.3

#### For R, NPT Thread (With sealant)


##### Tightening method

1. The proper tightening torques of the fittings are as shown in the table below. As a guide, tighten by hand, then turn it two or three turns with a wrench. Check the dimensions of each product for the hexagon width across flats.

Connection thread port size	Proper tightening torque [N·m]
NPT, R1/8	3 to 5
NPT, R1/4	8 to 12
NPT, R3/8	15 to 20
NPT, R1/2	20 to 25

##### Chamfered area for female thread

By chamfering as shown in the table below, machining of threads is easier and effective for burr prevention.



Connection thread port size	Chamfered dimension $\phi D$ (Recommended value)	
	Rc	NPT, NPTF
1/8	10.2 to 10.4	10.5 to 10.7
1/4	13.6 to 13.8	14.1 to 14.3
3/8	17.1 to 17.3	17.4 to 17.6
1/2	21.4 to 21.6	21.7 to 21.9

\* For Uni thread, Rz 12.5 is necessary for sealing at the chamfered part.



# Series AS-FS Specific Product Precautions 3

Be sure to read this before handling. Refer to the back cover for Safety Instructions.  
For Flow Control Equipment Precautions, refer to “Handling Precautions for SMC Products” for Flow Control Equipment Precautions and the Operation Manual.

## Mounting

### ⚠ Caution

#### For G Thread (Face seal type)


##### Tightening method

First, tighten the threaded portion by hand, then use a proper wrench, which could be suitable for the width across flats of the hexagon body, to tighten it further at a wrench tightening angle shown in the table below. For a tightening torque guide, refer to the table below. Check the dimensions of each product for the hexagon width across flats.

Connection thread port size	Wrench tightening angle after tightened by hand [deg]	Proper tightening torque [N·m]
G1/8	10 to 20	3 to 4
G1/4	15 to 35	4 to 5
G3/8	15 to 35	8 to 9
G1/2	15 to 35	14 to 15

##### Chamfered area for female thread (Recommended value)

- Confirming to 16030-2001, the chamfered dimensions shown in the table below are recommended. By chamfering as shown in the table below, machining of threads is easier and effective for burr prevention.



Nominal thread port size	Chamfered dimension øD	
	Min.	Max.
1/8	9.8	10.2
1/4	13.3	13.7
3/8	16.8	17.2
1/2	21.0	21.4

- Use G external threads with G internal threads.

#### For Uni Thread

##### Tightening method

- First, tighten the threaded portion by hand, then use a proper wrench, which could be suitable for the width across flats of the hexagon body, to tighten it further at a wrench tightening angle shown in the table below. For a tightening torque guide, refer to the table below.

##### Connection Female Thread: Rc, NPT, NPTF

Uni thread port size	Wrench tightening angle after tightened by hand [deg]	Tightening torque [N·m]
1/8	30 to 60	3 to 5
1/4	30 to 60	8 to 12
3/8	15 to 45	14 to 16
1/2	15 to 30	20 to 22


##### Connection Female Thread: G

Uni thread port size	Wrench tightening angle after tightened by hand [deg]	Tightening torque [N·m]
1/8	30 to 45	3 to 4
1/4	15 to 30	4 to 5
3/8	15 to 30	8 to 9
1/2	15 to 30	14 to 15

- The gasket can be reused up to 6 to 10 times.

##### Chamfered area for female thread

By chamfering as shown in the table below, machining of threads is easier and effective for burr prevention.



Connection thread port size	Chamfered dimension øD (Recommended value)		
	G	Rc	NPT, NPTF
1/8	10.2 to 10.6	10.2 to 10.4	10.5 to 10.7
1/4	13.6 to 14.0	13.6 to 13.8	14.1 to 14.3
3/8	17.1 to 17.5	17.1 to 17.3	17.4 to 17.6
1/2	21.4 to 21.8	21.4 to 21.6	21.7 to 21.9

- \* For Uni thread, Rz 12.5 is necessary for sealing at the chamfered part.





# Series AS-FS Specific Product Precautions 4

Be sure to read this before handling. Refer to the back cover for Safety Instructions. For Flow Control Equipment Precautions, refer to “Handling Precautions for SMC Products” for Flow Control Equipment Precautions and the Operation Manual.


## Mounting

### ⚠ Caution

1. This product has a stopper for fully close in rotating direction. Excess torque may break the stopper. Table below shows the maximum allowable torque of the handle.

Body size	Maximum allowable torque (N·m)
M5	0.05
1/8	0.07
1/4	0.16
3/8	0.2
1/2	0.4

When performing the piping work, turn the tightening tool in the horizontal direction to the hexagon across flats of the body B so that any moment is not applied to the body A. If the tool is in contact with the body A, this may cause the body B to come off.



2. Actuator speed needs to be checked each time the setting is changed.

Individual product difference due to tolerance of the components, individual actuator difference, operating conditions and temperature, etc. may cause a large variation in the actuator speed, and for this reason, the final actuator speed needs to be checked every time the setting is changed.

3. Force for lifting the handle is specified as shown in the table below.

Larger lifting force than specified in the table below will cause removal of the handle, flow rate not according to the flow-rate characteristics curve, incorrect flow indication with the indicator or damage to the product.

Port size	Handle lifting force
M5 10-32/UNF	1 to 1.5 N
1/8, 1/4, 3/8, 1/2	3.5 to 4 N

4. Do not rotate the product by the indicator part.

Use a wrench for mounting the product. Otherwise, it may cause damage to the product.

## Piping Threads with Sealant

### ⚠ Caution

1. If the fitting is tightened with excessive torque, a large amount of sealant will seep out. Remove the excess sealant.
2. Insufficient tightening may loosen the threads, or cause air leakage.
3. Reuse
  - 1) Normally, fittings with a sealant can be reused 2 to 3 times.
  - 2) To prevent air leakage through the sealant, remove any loose sealant stuck to the fitting by blowing air over the threaded portion.
  - 3) If the sealant no longer provides effective sealing, wrap sealing tape over the sealant before reusing. Do not use the sealant in any form other than a tape type.
4. Once the fitting has been tightened, backing it out to its original position often causes the sealant to become defective. Air leakage will occur.
5. Use R external threads with Rc internal threads and NPT external threads with NPT internal threads.


## Piping

### ⚠ Caution

1. Refer to One-touch fittings catalogue for more details about their piping and mounting precautions.
2. Preparation before piping
 




Before piping is connected, it should be thoroughly blown out with air (flushing) or washed to remove chips, cutting oil and other debris from inside the pipe.
3. Wrapping of sealant tape
 

When screwing together pipes and fittings, etc., be certain that chips from the pipe threads and sealing material do not get inside the pipe. Also, when the sealant tape is used, leave approx. 1 thread ridge exposed at the end of the threads.



## Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of “Caution,” “Warning” or “Danger.” They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)\*1), and other safety regulations.

-  **Caution:** Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.
-  **Warning:** Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.
-  **Danger:** Danger indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.

- \*1) ISO 4414: Pneumatic fluid power – General rules relating to systems.
- ISO 4413: Hydraulic fluid power – General rules relating to systems.
- IEC 60204-1: Safety of machinery – Electrical equipment of machines. (Part 1: General requirements)
- ISO 10218-1: Manipulating industrial robots - Safety. etc.

### Warning

- The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.**  
Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalogue information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.
- Only personnel with appropriate training should operate machinery and equipment.**  
The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.
- Do not service or attempt to remove product and machinery/equipment until safety is confirmed.**
  - The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
  - When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
  - Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.
- Contact SMC beforehand and take special consideration of safety measures if the product is to be used in any of the following conditions.**
  - Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
  - Installation on equipment in conjunction with atomic energy, railways, air navigation, space, shipping, vehicles, military, medical treatment, combustion and recreation, or equipment in contact with food and beverages, emergency stop circuits, clutch and brake circuits in press applications, safety equipment or other applications unsuitable for the standard specifications described in the product catalogue.
  - An application which could have negative effects on people, property, or animals requiring special safety analysis.
  - Use in an interlock circuit, which requires the provision of double interlock for possible failure by using a mechanical protective function, and periodical checks to confirm proper operation.

## Limited warranty and Disclaimer/ Compliance Requirements

The product used is subject to the following “Limited warranty and Disclaimer” and “Compliance Requirements”.  
Read and accept them before using the product.

### Limited warranty and Disclaimer

- The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first.\*2)  
Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
- For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalogue for the particular products.

\*2) Vacuum pads are excluded from this 1 year warranty.

A vacuum pad is a consumable part, so it is warranted for a year after it is delivered. Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

### Caution

- The product is provided for use in manufacturing industries.**  
The product herein described is basically provided for peaceful use in manufacturing industries.  
If considering using the product in other industries, consult SMC beforehand and exchange specifications or a contract if necessary.  
If anything is unclear, contact your nearest sales branch.

### Caution

- SMC products are not intended for use as instruments for legal metrology.**  
Measurement instruments that SMC manufactures or sells have not been qualified by type approval tests relevant to the metrology (measurement) laws of each country. Therefore, SMC products cannot be used for business or certification ordained by the metrology (measurement) laws of each country.

## Safety Instructions

Be sure to read “Handling Precautions for SMC Products” (M-E03-3) before using.

### SMC Corporation (Europe)

Austria	☎ +43 (0)2262622800	www.smc.at	office@smc.at	Lithuania	☎ +370 5 2308118	www.smolt.lt	info@smclt.lt
Belgium	☎ +32 (0)33551464	www.smcpnematics.be	info@smcpneumatics.be	Netherlands	☎ +31 (0)205318888	www.smcpnematics.nl	info@smcpneumatics.nl
Bulgaria	☎ +359 (0)2807670	www.smc.bg	office@smc.bg	Norway	☎ +47 67129020	www.smc-norge.no	post@smc-norge.no
Croatia	☎ +385 (0)13707288	www.smc.hr	office@smc.hr	Poland	☎ +48 (0)222119616	www.smc.pl	office@smc.pl
Czech Republic	☎ +420 541424611	www.smc.cz	office@smc.cz	Portugal	☎ +351 226166570	www.smc.eu	postpt@smc.smces.es
Denmark	☎ +45 70252900	www.smcdk.com	smc@smcdk.com	Romania	☎ +40 213205111	www.smcromania.ro	smcromania@smcromania.ro
Estonia	☎ +372 6510370	www.smcpnematics.ee	smc@smcpneumatics.ee	Russia	☎ +7 8127185445	www.smc-pneumatik.ru	info@smc-pneumatik.ru
Finland	☎ +358 207513513	www.smc.fi	smc@smc.fi	Slovakia	☎ +421 (0)413213212	www.smc.sk	office@smc.sk
France	☎ +33 (0)164761000	www.smc-france.fr	promotion@smc-france.fr	Slovenia	☎ +386 (0)73885412	www.smc.si	office@smc.si
Germany	☎ +49 (0)61034020	www.smc.de	info@smc.de	Spain	☎ +34 902184100	www.smc.eu	post@smc.smces.es
Greece	☎ +30 210 2717265	www.smchellas.gr	sales@smchellas.gr	Sweden	☎ +46 (0)86031200	www.smc.nu	post@smc.nu
Hungary	☎ +36 23511390	www.smc.hu	office@smc.hu	Switzerland	☎ +41 (0)523963131	www.smc.ch	info@smc.ch
Ireland	☎ +353 (0)14039000	www.smcpnematics.ie	sales@smcpneumatics.ie	Turkey	☎ +90 212 489 0 440	www.smcpnomatik.com.tr	info@smcpnomatik.com.tr
Italy	☎ +39 0292711	www.smcitalia.it	mailbox@smcitalia.it	UK	☎ +44 (0)845 121 5122	www.smcpnematics.co.uk	sales@smcpneumatics.co.uk
Latvia	☎ +371 67817700	www.smc.lv	info@smclv.lv				

SMC CORPORATION Akihabara UDX 15F, 4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN Phone: 03-5207-8249 FAX: 03-5298-5362