VO618A

ee

ROHS COMPLIANT

HALOGEN


FREE <u>GREEN</u>

(5-2008)



Vishay Semiconductors

Optocoupler, Phototransistor Output, High Reliability, 5300 V_{RMS}, Low Input Current



DESCRIPTION

The 110 °C rated VO618A feature a high current transfer ratio, low coupling capacitance and high isolation voltage. These couplers have a GaAs infrared diode emitter, which is optically coupled to a silicon planar phototransistor detector, and is incorporated in a plastic DIP-4 package.

The coupling devices are designed for signal transmission between two electrically separated circuits.

The couplers are end-stackable with 2.54 mm spacing.

Creepage and clearance distances of > 8.0 mm are achieved with option 6 and 8. This version complies with IEC 60950 (DIN VDE 0805) for reinforced insulation up to an operation voltage of 400 V_{RMS} or DC. Specifications subject to change.

FEATURES

- Operating temperature from -55 °C to +110 °C
- Good CTR linearity depending on forward current
- Isolation test voltage, 5300 V_{RMS}
- High collector emitter voltage, V_{CEO} = 80 V
- Low saturation voltage
- Fast switching times
- Low CTR degradation
- Temperature stable
- Low coupling capacitance
- End stackable, 0.100" (2.54 mm) spacing
- High common mode interference immunity
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

- AC adapters
- SMPS
- PLC
- Factory automation
- Game consoles

AGENCY APPROVALS

- UL1577, file no. E52744
- cUL tested to CSA 22.2 bulletin 5A
- DIN EN 60747-5-5 (VDE 0884-5), available with option 1
- BSI IEC 60950; IEC 60065
- FIMKO EN 60065, EN 60950-1
- CQC GB8898-2001

ORDERING INFORMATION				
VO61	B A - #		# T ON TAPE AND REEL	7 Option 9 Option 8
AGENCY CERTIFIED/PACKAGE		CTF	R (%)	
Adenor Gentineb/FAGRAde		1 r	mA	
UL, cUL, BSI, FIMKO	50 to 600	63 to 125	100 to 200	160 to 320
DIP-4	VO618A	VO618A-2	VO618A-3	VO618A-4
SMD-4, option 9	-	VO618A-2X009T	-	-
VDE, UL, cUL, BSI, FIMKO	50 to 600	63 to 125	100 to 200	160 to 320
DIP-4, 400 mil, option 6	-	-	-	VO618A-4X016
SMD-4, option 7	-	VO618A-2X017T	VO618A-3X017T	VO618A-4X017T
SMD-4, option 8	-	-	VO618A-3X018T	-

Note

Additional options may be possible, please contact sales office.

Rev. 1.9, 27-Aug-15

1

For technical questions, contact: optocoupleranswers@vishay.com



ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)					
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
INPUT					
Reverse voltage		V _R	6	V	
Forward current		I _F	60	mA	
Forward surge current	$t_p \le 10 \ \mu s$	I _{FSM}	1.5	А	
LED power dissipation	at 25 °C	P _{diss}	70	mW	
OUTPUT					
Collector emitter voltage		V _{CEO}	80	V	
Emitter collector voltage		V _{ECO}	7	V	
Collector current		Ι _C	50	mA	
Collector peak current	$t_p/T=0.5,t_p\leq 10\ ms$	I _{CM}	100	mA	
Ouput power dissipation	at 25 °C	P _{diss}	150	mW	
COUPLER					
Isolation test voltage (RMS)	t = 1 min	V _{ISO}	5300	V _{RMS}	
Total power dissipation		P _{tot}	200	mW	
Operation temperature		T _{amb}	-55 to +110	°C	
Storage temperature range		T _{stg}	-55 to +150	°C	
Soldering temperature	2 mm from case, \leq 10 s	T _{sld}	260	°C	

Note

Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not
implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute
maximum ratings for extended periods of the time can adversely affect reliability.




Fig. 1 - Total Power Dissipation vs. Ambient Temperature




ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
INPUT				-		
Forward voltage	I _F = 5 mA	V _F	1	1.1	1.65	V
Reverse current	$V_R = 6 V$	I _R		0.01	10	μA
Junction capacitance	$V_R = 0 V$, f = 1 MHz	Cj		13		pF
OUTPUT						
Collector emitter leakage current	V _{CE} = 10 V	I _{CEO}		10	200	nA
Collector emitter capacitance	$V_{CE} = 5 V$, f = 1 MHz	C _{CE}		5.2		pF
Collector emitter breakdown voltage	$I_{\rm C} = 1 \rm{mA}$	BV _{CEO}	80			V
Emitter collector breakdown voltage	I _E = 100 μA	BV _{ECO}	7			V
COUPLER						
Collector emitter saturation voltage	I _F = 1 mA, I _C = 2.5 mA	V _{CEsat}		0.25	0.4	V
Coupling capacitance	f = 1 MHz	C _C		0.4		pF

Note

• Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering evaluation. Typical values are for information only and are not part of the testing requirements.

CURRENT TRANSFER RATIO (T _{amb} = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
	I _F = 1 mA, V _{CE} = 5 V	VO618A	CTR	50		600	%
1.71		VO618A-2	CTR	63		125	%
I _C /I _F		VO618A-3	CTR	100		200	%
		VO618A-4	CTR	160		320	%

SWITCHING CHARACTERISTICS ($T_{amb} = 25 \text{ °C}$, unless otherwise specified)							
PARAMETER	TEST CONDITION	CTR BIN	SYMBOL	MIN.	TYP.	MAX.	UNIT
NON-SATURATED							
Rise and fall time	I_F = 1 mA, V_{CC} = 5 V, R_L = 75 Ω		t _r , t _f		2		μs
Turn-on time	$I_{\rm E} = 1 \text{ mA}, V_{\rm CC} = 5 \text{ V}, \text{ R}_{\rm I} = 75 \Omega$		t _{on}		3		μs
Turn-off time	$I_F = 1 IIIA, V_{CC} = 5 V, H_L = 75 \Omega_2$		t _{off}		2.3		μs
Cut-off frequency	$I_F = 1$ mA, $V_{CC} = 5$ V, $R_L = 75$ Ω		f _{ctr}		100		kHz
SATURATED							
Turn-on time	I _F = 1 mA		t _{on}		4.2		μs
Turn-off time	I _F = 1 mA		t _{off}		23		μs
Rise time	I _F = 1 mA		t _r		3		μs
Fall time	I _F = 1 mA		t _f		14		μs




www.vishay.com

95 10804-3

ISHA

Fig. 2 - Test Circuit, Non-Saturated Operation






Fig. 4 - Switching Times

PARAMETER		SYMBOL	VALUE	UNIT
		STIVIDOL	VALUE	UNIT
MAXIMUM SAFETY RATINGS				-
Output safety power		P _{SO}	265	mW
Input safety current		I _{si}	130	mA
Safety temperature		Τ _S	150	°C
Comparative tracking index		CTI	175	
INSULATION RATED PARAMETERS				
Maximum withstanding isolation voltage		V _{ISO}	5300	V _{RMS}
Maximum transient isolation voltage			8000	V _{peak}
Maximum repetitive peak isolation voltage			890	V _{peak}
Insulation resistance	$T_{amb} = 25 \text{ °C}, V_{DC} = 500 \text{ V}$	R _{IO}	≥ 10 ¹²	Ω
Isolation resistance	$T_{amb} = 100 \ ^{\circ}C, \ V_{DC} = 500 \ V$	R _{IO}	≥ 10 ¹¹	Ω
Climatic classification (according to IEC	68 part 1)		55/110/21	
Environment (pollution degree in accorda	ance to DIN VDE 0109)		2	
	Standard DIP-4, option 7 and option 9		≥ 7	mm
Internal and external creepage 400 mil DIP-4 and option 8			≥ 8	mm
Standard DIP-4, option 7 and option 9			≥ 7	mm
Clearance	400 mil DIP-4 and option 8		≥ 8	mm
Insulation thickness		DTI	0.4	mm

Note

• As per DIN EN 60747-5-5, § 7.4.3.8.2, this optocoupler is suitable for "safe electrical insulation" only within the safety ratings. Compliance with the safety ratings shall be ensured by means of protective circuits.

Rev. 1.9, 27-Aug-15 4

Document Number: 83432



TYPICAL CHARACTERISTICS ($T_{amb} = 25$ °C, unless otherwise specified)




Fig. 5 - Forward Voltage vs. Forward Current




Fig. 6 - Collector Current vs. Collector Emitter Voltage




Fig. 7 - Collector Emitter Current vs. Ambient Temperature




Fig. 8 - Collector Current vs. Collector Emitter Voltage






Fig. 9 - Collector Emitter Voltage vs. Ambient Temperature





Rev. 1.9, 27-Aug-15

5 For technical questions, contact: <u>optocoupleranswers@vishay.com</u> Document Number: 83432

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000






Fig. 11 - Normalized Current Transfer Ratio vs. Ambient Temperature (non-sat.)




Fig. 12 - Current Transfer Ratio vs. Forward Current (sat.)




Fig. 13 - Current Transfer Ratio vs. Forward Current (non-sat.)




Fig. 14 - Cut-Off Frequency vs. Collector Current




Fig. 15 - Phase Angle vs. Frequency





Fig. 16 - Switching Time vs. Load Resistance

Rev. 1.9, 27-Aug-15

6

For technical questions, contact: <u>optocoupleranswers@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>







Fig. 17 - Voltage Gain vs. Frequency

PACKAGE DIMENSIONS in millimeters

VISHAY



7 For technical questions, contact: <u>optocoupleranswers@vishay.com</u>



PACKAGE MARKING (Example of VO618A-3X017T)



Notes

- The VDE logo is only marked on option 1 parts. Option information is not marked on the part.
- Tape and reel suffix (T) is not part of the package marking.

PACKING INFORMATION

DEVICE PER TUBE			
ТҮРЕ	UNITS/TUBE	TUBES/BOX	UNITS/BOX
DIP-4	100	40	4000




Fig. 18 - Tape and Reel Shipping Medium (1000 units per reel)




Fig. 19 - Tape and Packing for Option 7 and Option 9

For technical questions, contact: <u>optocoupleranswers@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



TAPE AND REEL

Option 8






Fig. 20 - Default Orientation, 2000 units/reel

DESCRIPTION	SYMBOL	DIMENSIONS in mm (inch)
Tape width	W	24 ± 0.3 (0.63)
Pitch of spocket holes	P0	4 ± 0.1 (0.15)
Distance of comportment	F	11.5 ± 0.1 (0.295)
Distance of compartment	P2	2 ± 0.1 (0.079)
Distance of compartment to compartment	P1	8 ± 0.1 (0.472)

SOLDER PROFILES




Fig. 21 - Wave Soldering Double Wave Profile According to J-STD-020 for DIP-8 Devices

HANDLING AND STORAGE CONDITIONS

ESD level: HBM class 2

Floor life: unlimited

Conditions: $T_{amb} < 30$ °C, RH < 85 %

Moisture sensitivity level 1, according to J-STD-020




Fig. 22 - Lead (Pb)-free Reflow Solder Profile According to J-STD-020 for SMD-8 Devices

Rev. 1.9, 27-Aug-15

9

Document Number: 83432



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.