



## DEWALT 110V 32mm 4kg SDS Plus Combination Hammer

D25417KT-LX



- Brushed motor delivers power up to 1000W for optimum performance, with a no load speed of 820 rpm and 4.2J impact energy
- 3 mode selector hammer and rotary, rotary only, hammer only for various jobsite applications
- Rotation stop mode for light chiselling in soft masonry, plaster, tiles and light concrete and impact-stop mode for rotary only drilling in wood and metal
- An anti-rotation system detects a loss of tool control and reacts by instantly cutting the power for enhanced safety
- Active vibration control system (8.2m/s<sup>2</sup>) incorporating a floating rear handle to reduce fatigue for increased safety, comfort and productivity
- Quick change 3 jawed chuck provides speed, precision and flexibility when drilling in wood, ceramic and steel
- Large hammer mechanism construction guarantees longer tool life and superior performance
- Electronic variable speed switch for total control
- Ideal for drilling large anchor, fixing and through holes in concrete and masonry from 6 to 32 mm in diameter
- Includes TSTAK, gloves, glasses, 15 bits and chisels

### Description:

The DEWALT 110V 32mm 4KG SDS Plus Combination Hammer Drill with Quick Change Chuck is a powerful heavy duty tool designed for high performance drilling. The 1000W motor and best in class impact energy of 4.2J offers improved performance and drilling. It has a rotation stop mode for light chiselling applications in brick, soft masonry and concrete. The drill is ideal for drilling anchors and fixing holes into concrete, brick and masonry up to 32mm. Perform & protect delivers minimal vibration at 8.2m/s<sup>2</sup>, reducing user fatigue during extended operating periods. The kit includes a TSTAK Box, gloves, glasses and 15 drill bits and chisels, allowing you to tackle any jobsite.

### Supplied With:

- 2 x Flatwood drill bits
- 4 x Brad point wood drill bits
- 1 x TSTAK I Kit Box
- 1 x Multi-position side handle
- 2 x SDS+ drill bits
- 1 x Quick release 3 jaw removeable chuck
- 1 x Quick release SDS+ removeable tool holder
- 1 x Quick release 3 jaw removeable chuck
- 1 x SDS+ Chisel
- 4 x HSS drill bits
- 1 x Safety glasses
- 1 x Gloves

Specifications	
Power Source	Corded
Voltage	110 V
Power Input	1000 W
Tool Holder	SDS-Plus
Impact energy (EPTA 05/2009)	4.2 J
No Load Speed	0-820 rpm
Vibration Control	Yes
Anti Rotation System	Yes
Perform & Protect	Yes
Quick Change Chuck	Yes
Hammer Drilling Mode	Yes
Chipping Mode	Yes
Rotation Only Mode	Yes
Max. Drilling Capacity (Concrete)	32 mm
Max. Drilling Capacity (Core bit)	100 mm
Max. Drilling Capacity (Metal)	13 mm
Max. Drilling Capacity (Wood)	32 mm
Weight	4.3 kg

Height	250 mm
Length	370 mm
Width	85 mm
Hand/Arm Vibration - Hammer drilling into concrete	8.2 m/s <sup>2</sup>