

**SY6281**

Low Loss Power Distribution Switch
TARGET DESIGN SPECIFICATION
Preliminary Spec

General Description

The SY6281 develops ultra-low R_{d(on)} switch with programmable current limiting to protect the power source from over current and short circuit conditions. It integrates the over temperature protection and discharges the output capacitor during the shutdown. In case the output is pulled higher than the input voltage under the shutdown, the SY6281 can block the current flowing from the output to the input.

Ordering Information

SY6281 □(□□)□

Temperature Code
Package Code
Optional Spec Code

Temperature Range: -40°C to 85°C

Ordering Number	Package type	Note
SY6281AAC	SOT23-5	----

Features

- Distribution voltages: 2.4V to 5.5V
- Programmable current limit
- Enable polarity: active low
- Over temperature shutdown and automatic retry
- Reverse blocking (no body diode)
- At shutdown, OUT can be forced higher than IN
- Automatic output discharge at shutdown
- Compact SOT23 packages minimize the board space.

Applications

- USB 3G Datacard
- USB Dongle
- MiniPCI Accessories

Typical Applications





Figure 1. Schematic Diagram



SY6281

Pinout (top view)



Top mark: FHxyz (Device code: FH, x=year code, y=week code, z=lot number code)

Pin Name	Pin number	Pin Description
IN	5	Input pin
GND	2	Ground pin
OUT	1	Output pin
ENB	4	ON/OFF control. Pull low to enable IC. Do not float.
ISET	3	Current limit programming pin. Connect a resistor Rset from this pin to GND to program the current limit: $I_{lim} (A) = 6800/Rset (\text{ohm})$

Absolute Maximum Ratings (Note 1)

All pins	6V
Power Dissipation, PD @ TA = 25°C SOT23-5,	0.6W
Package Thermal Resistance (Note 2)	
θ_{JA}	200°C/W
θ_{JC}	130°C/W
Junction Temperature Range	150°C
Lead Temperature (Soldering, 10 sec.)	260°C
Storage Temperature Range	-65°C to 150°C

Recommended Operating Conditions (Note 3)

IN	2.4V to 5.5V
All other pins	0-5.5V
Junction Temperature Range	-40°C to 125°C
Ambient Temperature Range	-40°C to 85°C



SILERGY

SY6281

Electrical Characteristics





($V_{IN} = 5V$, $C_L = 1\mu F$, per channel, $T_A = 25^\circ C$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Input Voltage Range	V_{IN}		2.4		5.5	V
Shutdown Input Current	I_{SHDN}	Open load, IC Disabled.		0.1	1	μA
Quiescent Supply Current	I_Q	Open load, IC Enabled.		25		μA
FET RON	$R_{DS(ON)1}$			80		$m\Omega$
ENB Rising Threshold	$V_{ENB(H)}$		2			V
ENB Falling Threshold	$V_{ENB(L)}$				0.8	V
ENB Leakage	I_{ENB}	$V_{ENB}=5.5V$			1	μA
IN UVLO Threshold	$V_{IN\cdot UVLO}$				2.3	V
IN UVLO Hysteresis	$V_{IN\cdot HYS}$			0.1		V
Over Current Limit	I_{LIM}	$R_{SET}=6.8k\Omega$	0.75	1	1.25	A
	$I_{LIM(min)}$			0.4		A
	$I_{LIM(max)}$			2		A
Turn-ON Time	T_{ON}	$R_L=10\Omega$		120		us
Turn-OFF Time	T_{OFF}	$R_L=10\Omega$, $C_L=1\mu F$		10		us
OUT Shutdown Discharge Resistance	R_{DIS}			150		Ω
Thermal Shutdown Temperature	T_{SD}			130		$^\circ C$
Thermal Shutdown Hysteresis				20		$^\circ C$

Note 1: Stresses listed as the above “Absolute Maximum Ratings” may cause permanent damage to the device. These are for stress ratings. Functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may remain possibility to affect device reliability.

Note 2: θ_{JA} is measured in the natural convection at $T_A = 25^\circ C$ on a low effective single layer thermal conductivity test board of JEDEC 51-3 thermal measurement standard. Pin 2 of SOT23-5 packages is the case position for θ_{JC} measurement.

Note 3: The device is not guaranteed to function outside its operating conditions

SOT23-5 Package outline & PCB layout design**Recommended Pad Layout**

Notes: All dimensions are in millimeters.

All dimensions don't include mold flash & metal burr.