


Technische Daten/TECHNICAL DATA		
Steckverbinder-Norm	IEC 60603-7-51	CONNECTOR STANDARD
Mechanische Eigenschaften		MECHANICAL CHARACTERISTICS
Steckkraft	< 30 N	INSERTION FORCE
Lebensdauer	> 750	LIFE
Kabelabzugskraft	min. 50 N	CABLE TO PLUG TENSILE STRENGTH
Werkstoffe		MATERIALS
Steckergehäuse	Zinkdruckguß vernickelt / ZINC DIECAST Ni PLATED	CONNECTING HOUSING
Kontaktgehäuse	PC UL 94 V0 glasklar / CRYSTAL CLEAR	CONTACT HOUSING
Adernvorsortierung	PC UL94 V0 weiss / WHITE	WIRE PRESORTING
Zugentlastung	PBT IL94 V0 schwarz / BLACK	STRAIN RELIEF
Verriegelungshebel, Staubschutzkappe	PBT UL94 V0 schwarz / BLACK	HOOK, PROTECTION CAP
Schirmblech	Federstahl, SPRING STEEL	SCREENING SHIELD
Leiterplatte	FR4 UL94 V0	PCB
Durchdring-Kontakte	Phosphor Bronze, min. 3...6 µm Sn	PIERCING CONTACTS
Schirmkontakt	Messing / BRASS 2,5µm N1	SHIELD CONTACT
Kontakte	Federstahl / SPRING STEEL 0,8 µm Au; 1,2 µm Ni	CONTACTS
Richtlinie 2011/65/EU (RoHS)	RoHS-konform / RoHS-COMPLIANT	DIRECTIVE 2001/65/EU (RoHS)
Adernanschluss		WIRE CONNECTION
Cu-Leiterdurchmesser (1300478009)	Massiv / SOLID 0,51 - 0,64 mm AWG24 - AWG 22/1 Litze / STRANDED 0,46 - 0,76 mm AWG27 - AWG22/7 *Litze / STRANDED 0,61 - 0,78 mm AWG24-AWG22/19	Cu-CONDUCTOR DIAMETER
Cu-Leiterdurchmesser (1300478011)	Massiv / SOLID 0,41 - 0,51 mm AWG26 - AWG24/1 Litze / STRANDED 0,46 - 0,61 mm AWG27 - AWG24/7 *Litze / STRANDED 0,51 mm AWG26/19	Cu-CONDUCTOR DIAMETER
Aderndurchmesser (1300478009)	1,0 - 1,6 mm	CORE DIAMETER
Aderndurchmesser (1300478011)	0,85 - 1,1 mm	INSULATION DIAMETER
Kabeldurchmesser	5,5 - 10,0 mm	CABLE DIAMETER

Anschluss / CONNECTION		Anwendung / APPLICATION					
Farbcode / COLOUR OF CODE T568		Profinet	RJ45 PIN Nr./NO.	10 BT / 100 BT	1 Gigabit/ 10 Gigabit Ethernet	Token Ring ISDN/So	Upo / TEL
A	B						
W - G	W - O	YE	1	•	•		
G	O	OG	2	•	•		
W - O	W - G	WH	3	•	•	•	
BL	BL	-	4	•	•	•	•
W - BL	W - BL	-	5	•	•	•	•
O	G	BU	6	•	•	•	
W - BR	W - BR	-	7		•		
BR	BR	-	8		•		

ENG.-NO: E6AS07-5





FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	CURRENT REV DESC: SUPPLIER 3D-MODELS UPDATED		molex	
	DIMENSION UNITS	SCALE	EC NO: 749863		
GENERAL TOLERANCES (UNLESS SPECIFIED)	mm	2:1	DRWN: RSCHIEBER	2023/05/16	PRODUCT CUSTOMER DRAWING
ANGULAR TOL	± 1.0 °		CHK'D: RSILLER	2023/05/17	
DIVISIONAL SYMBOLS	4 PLACES ±		APPR: RSILLER	2023/05/17	DOCUMENT NUMBER
	3 PLACES ±		INITIAL REVISION:		
	2 PLACES ± 0.05		DRWN: KGRUEDL	2015/11/25	1300478009
	1 PLACE ± 0.3		APPR: CBRUNS	2016/04/07	
	0 PLACES ± 0.5		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DOC TYPE
THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	DOC PART
Third Angle Projection Symbol	A3-SIZE	130047	SEE TABLE 1		REVISION
					PSD 000 A2
					SHEET NUMBER
					1 OF 2




Technische Daten/TECHNICAL DATA		
Umweltanforderungen		EINVIENVIRONMENTAL REQUIREMENTS
Schutz vor Eindringen		PROTECTION AGAINST INGRESS
Eindringen von Teilchen / Wasser / Untertauchen	IP20	PARTICULATE INGRESS/ WATER/IMMERSION
Klimatisch und chemisch		CLIMATICAL AND CHEMICAL
Umgebungstemperatur	-40°C bis / TO +85°C	AMBIENT TEMPERATURE
Elektrische Eigenschaften		ELECTRICAL CHARACTERISTICS
Kontaktwiderstand	≤ 20 mΩ	CONTACT RESISTANCE
Isolationswiderstand	≥ 500MΩ	INSULATION RESISTANCE
Spannungsfestigkeit		VOLTAGE PROOF
Kontakt-Kontakt	≥ 1000 V, DC	CONTACT-CONTACT
Kontakt-Schirm	≥ 1500 V, DC	CONTACT-SHIELD
Strombelastbarkeit bei 50°C	1 A	CURRENT CARRYING CAPACITY AT 50°C
PoE+ gemäß IEEE 802.3at	Geeignet für Power over Ethernet+ ADEQUATE FOR POWER OVER ETHERNET+	POE+ ACCORDING TO IEEE 802.3AT
Übertragungstechnische Eigenschaften**		TRANSMISSION PERFORMANCE **
10 Gigabit Ethernet gemäß IEEE 802.3an	Geeignet für 10 Gigabit Ethernet ADEQUATE FOR 10 GIGABIT ETHERNET	10 GIGABIT ETHERNET ACC. TO IEEE 802.3AN
Kategorie 6A	ISO/IEC 11801; DIN EN 50173 - 1	CATEGORY 6A
Klasse EA	ISO/IEC 11801; DIN EN 50173 - 1	CLASS 6A
Kategorie 6A	ANSI/ITA/EIA-568-C.2	CATEGORY 6A
Normen		STANDARDS
IP-Schutzarten	IEC 60529	DEGREES OF PROTECTION PROVIDED BY ENCLOSURES (IP CODE)
Anwendungsneutrale Kommunikationsanlagen	ANSI/TIA/EIA-568-C.2;ISO/IEC 11801; DIN EN 50173-1	GENERIC CABLE SYSTEMS
Zulassung		APPROVAL
UL-gelistet	E361772	UL LISTED

TABLE 1

MATERIAL NO. / Material Nr.	DESCRIPTION / Beschreibung	AWG / Litzenquerschnitt	COLOR CODE / Farbcode
1300478009	FA RJ45 CAT6A 8P MA RA SHLD IPC AWG22	AWG24 - AWG22/1 / AWG27 - AWG22/7	T 568 B
1300478011	FA RJ45 CAT6A 8P MA RA SHLD IPC AWG26	AWG26 - AWG24/1 / AWG27 - AWG24/7	T 568 B



SCALE 1:1



FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		
	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	SCALE	1:1
GENERAL TOLERANCES (UNLESS SPECIFIED)	CURRENT REV DESC: SUPPLIER 3D-MODELS UPDATED		
ANGULAR TOL ± 1.0 °	EC NO: 749863		
4 PLACES ±	DRWN: RSCHIEBER 2023/05/16		
3 PLACES ±	CHK'D: RSILLER 2023/05/17		
2 PLACES ± 0.05	APPR: RSILLER 2023/05/17		
1 PLACE ± 0.3	INITIAL REVISION:		
0 PLACES ± 0.5	DRWN: KGRUEDL 2015/11/25		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	APPR: CBRUNS 2016/04/07		
THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER
	A3-SIZE	130047	SEE TABLE 1
CUSTOMER		DOC TYPE	DOC PART
1300478009		PSD	000
2015/11/25		REVISION	
2016/04/07		A2	
SHEET NUMBER		2 OF 2	