



## DEWALT 18V XR Brushless Compact Twin Pack (DCD709 & DCF809) - 2x 4Ah

DCK2062M2T



- DCD709: Only 175mm in length, allowing you to get in to even smaller spaces
- DCD709: Only 1.2kg (tool only) for ultimate portability and ease of use
- DCD709: Efficient Brushless motor delivers high performance, extends tool life and allows for a much shorter design
- DCD709: Foot LED with delay feature for better workpiece illumination
- DCD709: 15 position adjustable torque control for consistent screw driving into a variety of materials
- DCD709: 65Nm torque allows you to achieve tough applications
- DCF809: Only 131mm in length, allowing you to get into even smaller spaces
- DCF809: Only 1.0kg (tool only) for ultimate portability
- DCF809: Up to 190Nm torque allows you to achieve tough applications
- DCF809: Efficient Brushless motor delivers high performance, extends tool life and allows for a much shorter design
- DCF809: 'Drop and Load' bit holder for one-handed operation
- Includes 2 x DCB182 4Ah batteries, DCB115 multi-voltage charger and TSTAK

### Description:

The DEWALT 18V XR Brushless Hammer Drill and Impact Driver have been constructed to be heavy duty yet lightweight and compact. The Brushless motors run cooler and more efficiently, enabling more power to be delivered during application, resulting in less wear. The powerful hammer drill is compact with a length of 175mm. The 2 speed Brushless motor delivers 65Nm of torque and extended runtime, this drill is capable of even the most demanding applications. The 131mm impact driver is our most compact driver ever, delivering a max torque of up to 190 Nm for the toughest of applications and extended runtime.

**Supplied With:**

- 2 x 18V XR 4Ah Batteries
- 1 x Battery Charger
- 1 x T-STAK Kitbox

<b>Specifications</b>	
Battery	XR Lithium-Ion
Voltage	18 V
<b>DCD709: Hammer Drill</b>	
Max Torque (Hard)	65 Nm
Chuck Capacity	1.5-13 mm
No of Speeds	2
No Load Speed (Drilling/ Driving/ Hammer Mode)	0-450/0-1650 rpm
Beats Per Minute	0-7650/0-28050 bpm
Max Drilling Capacity [Wood]	30 mm
Max Drilling Capacity [Metal]	13 mm
Max Drilling Capacity [Masonry]	13 mm
Length	175 mm
<b>DCF809: Impact Driver</b>	
Power Output	300 W
Max Torque	190 Nm
No Load Speed	0-2800 rpm
Impacts per Minute	0-3200 ipm
Bit Holder	6.35 mm
Length	131 mm