



preci-dip

# PCB CONNECTORS



**SERIES**  
**831**

**831-PP-NNN-30-001101**

Single row

2 mm, Surface mount perpendicular gull-wing

“Hard metric” PCB socket connectors SMD perpendicular mount.



## TECHNICAL SPECS.:

<b>Insulator</b>	Black glass filled polymer LCP-GF30-FR
<b>Flammability</b>	UL 94V-O
<b>Sleeve</b>	Brass CuZn36Pb3 (C36000)
<b>Contact</b>	Clip (6 finger): Beryllium copper (C17200)
<b>Mating pin Ø</b>	0.40 to 0.56 mm, 0.50 mm square
<b>Insertion force</b>	0.7 N typ.
<b>Withdrawal force</b>	0.4 N typ. (polished steel gauge Ø 0.46 mm)
<b>Mechanical life</b>	Min. 500 cycles
<b>Rated current</b>	3 A
<b>Contact resistance</b>	Max. 10 m
<b>Dielectric strength</b>	Min. 1000 V RMS
<b>Coplanarity SMD terminations</b>	Max. 0.1 mm (measured on 25 mm long connectors)

## ORDERING INFORMATION:

PP Plating code	Sleeve	Clip
87	Tin	Gold flash
83	Tin	Gold 0.75 µm

NNN number of poles. Replace NNN with the requested number of poles, e.g. 833-87-NNN-30-001101 for a double row version with 16 pins becomes 833-87-016-30-001101

# TECHNICAL ASSISTANCE

## GENERAL SPECIFICATIONS:

The values listed below are general specs applying for PRECI-DIP socket and pin connectors. Please see individual catalog page for additional and product specific technical data.

Operating temperature range	-55 ... +125 °C
Climatic category (IEC)	55/125/21
Operating humidity range	annual mean 75 %
Max working voltage	100 VRMS/150 VDC (2.54 mm grid)

PRECI-DIP sockets are recognized by Underwriters Laboratories Inc. and listed under "Connectors for Use in Data, Signal, Control and Power Applications", File Nr. E174442

## MECHANICAL CHARACTERISTICS:

Clip retention	Min. 40 N (no displacement under axial force applied)
Contact (sleeve / clip) retention	Min. 3.3 N acc. to MIL-DTL-83734, pt 4.6.4.2

## ELECTRICAL CHARACTERISTICS:

Insulation resistance between any two adjacent contacts	Min. 10'000 M at 500 V AC
Capacitance between any two adjacent contacts	Max. 1 pF

### Air and creepage distances between any two adjacent contacts :

SERIES	3xx/4xx/7xx	80x	83x	85x	86x
mm	0.7	0.85 / 0.7	0.5	0.4 / 0.5	0.5

## ENVIRONMENTAL CHARACTERISTICS:

The sockets withstand the following environmental tests without mechanical and electrical defects:

- Dry heat steady state IEC 60512-11-9.11i / 60068-2-2.Bb: 125 °C, 16h
- Damp heat cyclic IEC 60512-11-12.11m / 60068-2-30.Db: 25/55 °C, 90 – 100 %rH, 1 cycle of 24 h
- Cold steady state IEC 60512-11-10.11j / 60068-2-1.A: -55 °C, 2 h
- Thermal shock IEC 60512-11-4.11d / 60068-2-14.Na: -55/125 °C, 5 cycles 30 min
- Sinusoidal vibrations IEC 60512-6-4.6d / 60068-2-6.Fc: 10 to 500 Hz, 10 g, 1 octave/min, 10 cycles for each axis
- Shock IEC 60512-6-3.6c / 60068-2-27.Ea: 50 g, 11 ms, 3 shocks in three axis

During the above two tests no contact interruption >50 ns does appear.

- Solderability J-STD-002A, Test A, 245°C, 5 s solder alloy SnAg3.8Cu0.7
- Resistance to soldering heat J-STD-0020C, 260°C, 20 s
- Moisture sensitivity J-STD-020C level 1
- Resistance to corrosion :
  - 1) Salt spray test IEC 60068-2-11.Ka: 48 h
  - 2) Sulfur dioxide (SO<sub>2</sub>) test IEC 60068-2-42 Kc: 96 h at 25 ppm SO<sub>2</sub>, 25 °C, 75 %rH
  - 3) Hydrogen sulfide (H<sub>2</sub>S) test IEC 60068-2-43 Kd: 96 h at 12 ppm H<sub>2</sub>S, 25 °C, 75 %rH

## SOLDERLESS COMPLIANT PRESS-FIT CHARACTERISTICS:

### PRESS-FIT CHARACTERISTICS MEASURED ACC. TO IEC 60352-5

- Press-in force: 90 N max. (at min. hole dia.) / 65 N typ.
- Push-out force: 30 N min. (at max. hole dia.) / 50 N typ.
- Push-out 3rd cycle: 20 N min. (at max. hole dia.)

## PCB HOLE DIMENSIONS

- 2 mm grid: Finished hole  $\varnothing$ :  $0.7 + 0.09/-0.06$  mm | Drilled hole  $\varnothing$ :  $0.8 \pm 0.02$  mm
- 2.54 mm grid: Finished hole  $\varnothing$ :  $1 + 0.09/-0.06$  mm | Drilled hole  $\varnothing$ :  $1.15 \pm 0.02$  mm

## PCB HOLE PLATING

- PCB surface finish: Hole plating
- Tin: 5-15  $\mu\text{m}$  tin over min. 25  $\mu\text{m}$  copper
- Copper: min. 25  $\mu\text{m}$  copper
- Gold over nickel: 0.05-0.2  $\mu\text{m}$  gold over 2.5-5  $\mu\text{m}$  nickel over min. 25  $\mu\text{m}$  copper

## PACKAGING:

Standard connector packaging is card box.

SMD mount connectors available on request with Tape & Reel packaging acc. to EIA Standard 481.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Preci-dip:

[831-83-033-30-001101](#) [831-83-044-30-001101](#) [831-83-043-30-001101](#) [831-83-042-30-001101](#) [831-83-041-30-001101](#) [831-83-040-30-001101](#) [831-83-039-30-001101](#) [831-83-038-30-001101](#) [831-83-037-30-001101](#) [831-83-036-30-001101](#) [831-83-022-30-001101](#) [831-83-034-30-001101](#) [831-83-047-30-001101](#) [831-83-031-30-001101](#) [831-83-030-30-001101](#) [831-83-029-30-001101](#) [831-83-028-30-001101](#) [831-83-027-30-001101](#) [831-83-026-30-001101](#) [831-83-025-30-001101](#) [831-83-024-30-001101](#) [831-83-035-30-001101](#) [831-87-009-30-001101](#) [831-87-021-30-001101](#) [831-87-020-30-001101](#) [831-87-019-30-001101](#) [831-87-018-30-001101](#) [831-87-017-30-001101](#) [831-87-016-30-001101](#) [831-87-015-30-001101](#) [831-87-014-30-001101](#) [831-87-013-30-001101](#) [831-87-012-30-001101](#) [831-83-045-30-001101](#) [831-87-010-30-001101](#) [831-83-046-30-001101](#) [831-87-008-30-001101](#) [831-87-007-30-001101](#) [831-87-006-30-001101](#) [831-87-005-30-001101](#) [831-87-004-30-001101](#) [831-87-003-30-001101](#) [831-83-050-30-001101](#) [831-83-049-30-001101](#) [831-83-048-30-001101](#) [831-83-021-30-001101](#) [831-87-011-30-001101](#) [831-83-023-30-001101](#) [831-83-008-30-001101](#) [831-83-020-30-001101](#) [831-83-019-30-001101](#) [831-83-018-30-001101](#) [831-83-017-30-001101](#) [831-83-016-30-001101](#) [831-83-015-30-001101](#) [831-83-014-30-001101](#) [831-83-013-30-001101](#) [831-83-012-30-001101](#) [831-83-011-30-001101](#) [831-83-009-30-001101](#) [831-83-007-30-001101](#) [831-83-006-30-001101](#) [831-83-005-30-001101](#) [831-83-004-30-001101](#) [831-83-003-30-001101](#) [831-87-024-30-001101](#) [831-83-010-30-001101](#) [831-87-022-30-001101](#) [831-87-034-30-001101](#) [831-87-045-30-001101](#) [831-87-044-30-001101](#) [831-87-043-30-001101](#) [831-87-042-30-001101](#) [831-87-041-30-001101](#) [831-87-040-30-001101](#) [831-87-039-30-001101](#) [831-87-038-30-001101](#) [831-87-037-30-001101](#) [831-87-047-30-001101](#) [831-87-035-30-001101](#) [831-87-048-30-001101](#) [831-87-033-30-001101](#) [831-87-032-30-001101](#) [831-87-031-30-001101](#) [831-87-030-30-001101](#) [831-87-029-30-001101](#) [831-87-028-30-001101](#) [831-87-027-30-001101](#) [831-87-026-30-001101](#) [831-87-025-30-001101](#) [831-87-036-30-001101](#) [831-87-023-30-001101](#) [831-87-046-30-001101](#) [831-87-050-30-001101](#) [831-87-049-30-001101](#)