





Standard type

ML • LWL



Tapered rail specification
LWL...N



Shape	1	2	3	5	7
Size	9	12	15	20	25

Identification number	Interchangeable		Mass (Ref.) g		Dimensions of assembly mm					Dimensions of side unit mm					Dimensions of track rail mm					Appended mounting bolt for track rail (2) mm		Basic static load rating (4)		Static moment rating (4)					
	ML series	LWL series (No C-Lube)	Slide unit	Track rail (per 100 mm)	H	H1	N	W2	W3	W4	L1	L2	L3	M1 × depth	H3	W	H4	M2	d3	d4	h	E	F	Bolt size × ℓ	C	C0	T0	Tx	Ty
MLC 5		LWLC 5-B	○	12			3.4	12	8	2	16	9.6			1.2	5	3.7	2.4	3.6	0.8		15		Cross-recessed head screw for precision equipment M2×6	562	841	2.2	1.4	1.2
		LWLC 5-N*	-	13	6	1	4.3	12	8		19		M2×1.5					M2.5 Through	-	-	7.5			M2.5 × ℓ (3) (Not appended)	676	1 090	2.9	1.3	1.9
ML 5		LWL 5-B	○	12			4.4					12.6						M2.5 Through	2.4	3.6	0.8			Cross-recessed head screw for precision equipment M2×6				12.8	10.8
		LWL 5-N*	-	13														M2.5 Through	-	-	-			(Not appended)				14.9	
MLC 7		LWLC 7-B	○	22			6.7				19	9.6						2.4	4.2	2.3				Hexagon socket head bolt M2×6	937	1 140	4.1	1.8	1.5
		LWLC 7-N*	-	24			7.1											M3 Through	-	-	-			(Not appended)				28.2	23.6
ML 7		LWL 7-B	○	22	8	1.5	9.1	17	12	2.5	23.5	8	14.3	M2×2.5	1.5	7	5	2.4	4.2	2.3	7.5	15		Hexagon socket head bolt M2×6	1 330	1 890	6.9	4.7	3.9
		LWL 7-N*	-	24			10											M3 Through	-	-	-			(Not appended)				50.7	42.5
MLG 7		LWLG 7-B	○	22			13				31	12	21.6					2.4	4.2	2.3				Hexagon socket head bolt M2×6	1 690	2 650	9.7	8.9	7.4
		LWLG 7-N*	-	24			14											M3 Through	-	-	-			(Not appended)				42.5	

Notes (1) Track rail lengths L are shown in Table 3.1 on page II-10.

(2) The appended track rail mounting bolts are hexagon socket head bolts equivalent to JIS B 1176 or cross recessed head screws for precision equipment.


(3) Choose screws whose dimension allow fixing thread depth into track rail ℓ to be less than H4.

(4) The direction of basic dynamic load rating (C), basic static load rating (C0), and static moment rating (Tx, Ty, Ty) are shown in the sketches below.

The upper values of Tx and Ty are for one slide unit and the lower values are for two slide units sticking.

Remarks 1. The hybrid C-Lube Linear Way specification (supplemental code "/HB") is selected in MLC7, ML7, and MLG7, see Table 10 on page II-17.

2. The identification numbers with * are our semi-standard items.



Example of identification number of assembled set

Model code	Dimensions	Part code	Model code	Preload symbol	Classification symbol	Interchangeable code	Special application
ML C	7	C2	R120	T1	P	S1	/D
	1	2	4	5	6	8	9
	1	2	4	5	6	8	9

① Model	ML	④ Size	5, 7
LWL...B	Standard type	⑦ Preload amount	To: Clearance T1: Standard Light preload
LWL...N	Standard type	⑧ Accuracy class	H: High P: Precision
② Length of slide unit	C	⑤ Number of slide unit (2)	
No symbol	Short	⑥ Length of track rail (120 mm)	
Standard	Standard		
Long	Long		
③ Interchangeable	S1	⑨ Special specification	A, BS, D, E, HB, I, LR MN, N, O, RE, S, W, Y
S2	Special specification		
No symbol	No interchangeability		