



DCH253N

**18V XR Li-Ion Heavy Duty 3 Mode
Dedicated Cordless Hammer Bare Unit**

Selling Proposition

- Ideal for drilling anchors and fixing holes into concrete, brick and masonry from 4mm to 24mm
- Rotation stop mode for light chiselling in plaster, tiles and render
- Best in class vibration, 6.6m/s² reduces user fatigue and maximises operating periods
- Bright white LED with delay feature improves visibility and provides flashlight functionality

Standard Equipment

- Multi-position side handle

Warranty Specifications

- 30 Day No Risk Satisfaction Guarantee
- 3 year limited warranty
- 1 Year Warranty

Specifications	
Battery chemistry	XR Li-Ion
Voltage	18 V
Kapazität	N/A Ah
Abgabeleistung	400 Watt
No Load Speed	0-1200 rpm
Impact energy (EPTA 05/2009)	2.1 J
Blows per Minute	0-4500 bpm
Tool Holder	SDS-Plus