

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



QUICKON cable connector, black, 3+PE-pos., 0.75 mm² ... 1.5 mm² /500 V/15 A, for a cable diameter of 6 mm ... 12 mm.

Why buy this product

- Innovative and time saving QUICKON fast connection for time saving of up to 80 % for on-site connection
- Convenient: quick and easy assembly without special tools
- Robust throughout: housing with IP68/IP69K and IK07 protection for a wide range of applications
- Safer connection thanks to polarization against mismatching and touch-proof protection according to DIN EN 0105
- Easy and safe with the cable connector, you can repair or extend cables quickly, in combination with the connector as well as the coupling connection



Key Commercial Data

Packing unit	1 STK
Weight per Piece (excluding packing)	37.3 g
Custom tariff number	85366990
Country of origin	Poland

Technical data

General

Connection	If the conductor is reconnected, it must be cut off above the last contact point. QUICKON components may only be operated when under no load.
Color	black
Connection method	QUICKON connection
	IDC connection
Number of positions	4
Wrench size, union nut	19 mm



Technical data

General

Tightening torque, union nut	3 Nm
Wrench size, contact carrier	24 mm
Conductor cross section flexible min.	0.75 mm ²
Conductor cross section flexible max.	1.5 mm ²
Conductor cross section solid min.	0.75 mm ²
Conductor cross section solid max.	1 mm ²
Conductor cross section AWG min.	18
Conductor cross section AWG max.	16

Cabel

Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	VDE 0295 class 1 to 6/min. 0.15 mm
Wire insulation material	PVC/PE
Wire diameter including insulation	1.8 mm 3 mm
External cable diameter	6 mm 12 mm

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-40 $^\circ\text{C}$ 80 $^\circ\text{C}$ (specifications of the cable manufacturer must also be observed)
Ambient temperature (storage/transport)	-40 °C 80 °C
Temperature when conductor connected	-5 $^\circ\text{C}$ 50 $^\circ\text{C}$ (specifications of the cable manufacturer must also be observed)

Electrical characteristics

Nominal current I _N	15 A
Rated current	15 A
Rated voltage (III/3)	500 V
Rated voltage (III/2)	800 V
Rated voltage (II/2)	1000 V
Rated surge voltage (III/3)	6 kV
Rated surge voltage (III/2)	6 kV
Rated surge voltage (II/2)	6 kV

Mechanical characteristics

QUICKON connectability	max. 10
Impact category	3

Material data

Contact material	CuZn
Contact surface material	Tin-plated




Technical data

Material data


Contact carrier material	РА
Insulating material	РА
Flammability rating according to UL 94	V0
Overvoltage category	III
Degree of pollution	3
Standards and Regulations	

Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0

Drawings



Dimensional drawing



Classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27440605
eCl@ss 9.0	27440605

ETIM

ETIM 2.0	EC000516
ETIM 3.0	EC000516



Classifications

ETIM

ETIM 4.0	EC000516
ETIM 5.0	EC002560

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Approvals

Approvals

Approvals

UL Recognized / VDE Zeichengenehmigung / cUL Recognized / EAC / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

Γ

Г

Nominal current IN	15 A
Nominal voltage UN	250 V

VDE Zeichengenehmigung 🚳	
mm²/AWG/kcmil	0.75-1.5
Nominal voltage UN	500 V

08/11/2016 Page 4 / 6

٦

٦



Conductor connectors - Q 1,5/4IDC/24-24KU-KU BK PE - 1642182

Approvals

cUL Recognized		
Nominal current IN	11 A	
Nominal voltage UN	250 V	

EAC

Γ

EAC

cULus Recognized

Accessories

Accessories

Electronics pliers

Diagonal cutter - MICROFOX-SB - 1212489



Electronic diagonal cutter, round head, without chamfer, with opening spring, mirror-polished and oiled, 2-component grip, cutting capacity: soft 0.2 - 2.0 mm; medium hard 1.2 mm; hard 0.5 mm diameter

Sealing plugs

Closing cap - SEALING PLUG 12X22 RD - 1400260



Sealing plug, for sealing unused bore holes in multiple grommets and cable glands, diameter: 12 mm

Socket spanner

08/11/2016 Page 5 / 6



Accessories

Socket wrench - QSS 19 - 1670895



Socket wrench, for tightening and unscrewing the QUICKON union nut, wrench size 19 mm

Phoenix Contact 2016 © - all rights reserved http://www.phoenixcontact.com