



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	JASON KUNTZ	Contact Title	Product Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2015-06-08	Contact Email	jp.kuntz@te.com				
Contact Phone Number	717-986-5932								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	6364372-2	Amount	3146.24956	Version	-	Identity			
Manufacturer Item Name	RCPT ASSY, R/A, 4P, THRU-HOLE, USB, LF	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	RCPT SHELL, R/A, 4 PSN, USB, S				1.0	2385.25	mg	
Material	2	Tin Plate				1.0	54.35	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.35	1.0	0.19023	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.2	1.0	0.1087	mg	
Substance	3	Copper	Supplier	7440-50-8	1.5	1.0	0.81525	mg	
Substance	3	Tin	Supplier	7440-31-5	97.85	1.0	53.18148	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.05435	mg	
Material	2	Phos Bronze				1.0	2330.9	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	2206.9777	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.46618	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.23309	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	104.8905	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.34963	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	2.3309	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.23309	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.023309	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	6.9927	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	2.3309	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	2.3309	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.23309	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	1.16545	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	2.3309	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0116545	mg	
Sub-Item	1	USB A R/A RCPT SUB-ASSY, LEAD FREE				1.0	760.99956	mg	
Material	2	Nickel Plate				1.0	1.552	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.003104	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.001552	mg	

Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	1.54734	mg	
Material	2	LCP				1.0	618.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	185.4	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with [1,1-biphenyl]-4,4-diol, 4-hydroxybenzoic acid, 6-hydroxy-2-naphthalenecarboxylic acid and N-(4-hydroxyphenyl)acetamide	Supplier	147310-94-9	69.7	1.0	430.746	mg	
Substance	3	Octadecanoic acid, 1,1-[2,2-bis[[[1-oxooctadecyl]oxy]methyl]-1,3-propanediyl] ester	Supplier	115-83-3	0.3	1.0	1.854	mg	
Material	2	Tin Plate				1.0	0.2024	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	2.022E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	0.2022	mg	
Material	2	Palladium-Nickel Plate				1.0	0.03812	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	1.0	0.030496	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	1.0	0.007624	mg	
Material	2	Gold Plate				1.0	0.00704	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.00701888	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	2.112E-5	mg	
Material	2	Phos Bronze				1.0	141.2	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	133.6931	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.02824	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.01412	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	6.354	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.02118	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.1412	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.01412	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.001412	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	0.4236	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.1412	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.1412	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.01412	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.0706	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.1412	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	7.06E-4	mg	