

1	2	3	4	5	6	7
A	<p>NOTES:</p> <p>MATERIAL</p> <p>1. Insulator Material: Black; NYLON+G/F UL 94V-0 Ⓜ</p> <p>2. Contact Material: Copper Alloy</p> <p>Ⓜ 3. Plating: 1u" Gold Plating</p> <p>4. Waterproof Rate: IP67</p> <p>5. Do Mating Test After Glued</p> <p>6. Applicable Wire Range: 22AWG-26AWG</p>					
B	<p>Panel Thickness</p> <p>Screw L=5.0 For Panel Thickness Under 1.2mm</p> <p>Screw L=6.0 For Panel Thickness Between 1.2-2.0mm</p> <p>X(MAX.)</p> <p>Recommended Panel Cut-Out</p> <p>With Liquid Glue</p> <p>Ⓜ Electrical</p> <p>1. Contact resistance: 20mΩ max.</p> <p>2. Insulation resistance: 500MΩ min. at DC500V</p> <p>3. Dielectric withstanding voltage: 500V AC 1 minute</p> <p>4. Rating current: 2A</p> <p>5. Durability: 500 cycles</p> <p>6. Temperature range: -20°C ~ +85°C</p>					
C						
D						
E						
F						
G	<p>Scale Free</p> <p>TOLERANCE</p> <p>X.X ±0.25</p> <p>X.XX ±0.10</p> <p>X.XXX ±0.05</p> <p>DIM TOL</p> <p>Angle ±1°</p> <p>Id.</p> <p>① Drawn</p> <p>② Add notes</p> <p>③ Add the screw spec on page 2</p> <p>Date 24.01.2018</p> <p>Date 03.08.2020</p> <p>Name Segal</p> <p>Name JACK</p> <p>Date 24.12.2008</p> <p>Date 03.08.2020</p> <p>Name JACK</p> <p>Name Segal</p> <p>Description: 25 Pin Female Connector</p> <p>ASSMANN WSW-No.</p> <p>A-DF 25 LL-WP</p> <p>Drawing-No. ASS 3260 CO</p> <p>Customer-No.</p> <p>rev03</p> <p>SHEET 1 / 2</p>					
H	<p>RoHS compliant</p> <p>Unit:mm</p> <p>1 2 3 4 5 6 7</p> <p>ASSMANN components</p>					
1	2	3	4	5	6	7

	1	2	3	4	5	6	7					
A	<p>ASCW-000-01EB10</p>											
B	<p>ASCW-000-01EB11</p>											
C	<p>Technical requirements:</p> <p>1. Material: Brass C3604;</p> <p>2. Requirements: Bright nickel 100u" Min, salt spray 48H.</p>											
D	<p>Scale Free</p> <p>TOLERANCE</p> <table border="1"> <tr> <td>.X</td> <td>±0.15</td> </tr> <tr> <td>.XX</td> <td>±0.10</td> </tr> </table> <p>DIM TOL</p> <p>③ Add the screw spec on page 2</p> <p>② Add notes</p> <p>① Drawn</p> <p>Angle TOL</p> <p>Id.</p> <p>Modification</p> <p>Date</p> <p>Name</p>							.X	±0.15	.XX	±0.10	
.X	±0.15											
.XX	±0.10											
E	<p>1. Material: Brass C3604;</p> <p>2. Requirements: Bright nickel 100u" Min, salt spray 48H.</p>											
F	<p>1. Material: Brass C3604;</p> <p>2. Requirements: Bright nickel 100u" Min, salt spray 48H.</p>											
G	<p>1. Material: Brass C3604;</p> <p>2. Requirements: Bright nickel 100u" Min, salt spray 48H.</p>											
H	<p>1. Material: Brass C3604;</p> <p>2. Requirements: Bright nickel 100u" Min, salt spray 48H.</p>											