


MIL-STD-1553 TRANSFORMERS

Dual Ratio THT QPL Pulse Transformers



- ⊗ Certified QPL MIL-STD-1553 applications
- ⊗ Designed, built and tested to MIL-PRF-21038
- ⊗ Dual Ratio, Single Package
- ⊗ Product Levels:
 - ⊗ Level C: for high reliability commercial/industrial applications
 - ⊗ Level M: for general purpose military applications
 - ⊗ Level T: for high reliability critical military applications
- ⊗ Two Packages Available:
 - ⊗ Package A: without standoffs
 - ⊗ Package G: with standoffs
- ⊗ Moisture Sensitivity Level: 1
- ⊗ Applicable Standards:
 - ⊗ MIL-STD-1553B
 - ⊗ MIL-PRF-21038
 - ⊗ MIL-STD-202

Summary Performance Specifications

Droop	20% MAX
Overshoot	±1V MAX
Common Mode Rejection (CMR)	45dB MIN
Frequency Range (no load)	75kHz - 1MHz
Operating and Storage Temperature Range	-55°C to +130°C
Weight	5 grams MAX
Insulation Resistance (MIN)	10K MΩ @ 250Vdc
Dielectric Withstanding Voltage	100Vrms

Electrical Specifications @ 25°C

Part Number	Level	Military Designation No.	Package	Height MAX	Terminals	Ratio (±3%)	RDC MAX (Ω)	Impedance MIN ¹ (Ω)
				IN. [mm]				
QC1553-1	C	M21038/27-01C	A	0.250 [6.35]	1-3:4-8 1-3:5-7	1CT:1CT 1CT:0.707CT	1-3 = 3.0 4-8 = 3.0	(1-3) 4,000
Q1553-1	M	M21038/27-01						
QT1553-1	T	M21038/27-01T						
QC1553-2	C	M21038/27-02C	A	0.250 [6.35]	1-3:4-8 1-3:5-7	1.40CT:1CT 2CT:1CT	1-3 = 3.5 4-8 = 3.0	(1-3) 7,200
Q1553-2	M	M21038/27-02						
QT1553-2	T	M21038/27-02T						
QC1553-3	C	M21038/27-03C	A	0.250 [6.35]	1-3:4-8 1-3:5-7	1.25CT:1CT 1.66CT:1CT	1-3 = 3.2 4-8 = 3.0	(1-3) 4,000
Q1553-3	M	M21038/27-03						
QT1553-3	T	M21038/27-03T						
QC1553-5*	C	M21038/27-10C	A	0.250 [6.35]	1-3:4-8 1-3:5-7	1CT:2.12CT 1CT:1.50CT	1-3 = 1.0 4-8 = 3.5	(4-8) 4,000
Q1553-5*	M	M21038/27-10						
QT1553-5*	T	M21038/27-10T						
QC1553-81	C	M21038/27-21C	G	0.275 [6.985]	1-3:4-8 1-3:5-7	1CT:1CT 1CT:0.707CT	1-3 = 3.0 4-8 = 3.0	(1-3) 4,000
Q1553-81	M	M21038/27-21						
QT1553-81	T	M21038/27-21T						
QC1553-82	C	M21038/27-22C	G	0.275 [6.985]	1-3:4-8 1-3:5-7	1.40CT:1CT 2CT:1CT	1-3 = 3.5 4-8 = 3.0	(1-3) 7,200
Q1553-82	M	M21038/27-22						
QT1553-82	T	M21038/27-22T						
QC1553-83	C	M21038/27-23C	G	0.275 [6.985]	1-3:4-8 1-3:5-7	1.25CT:1CT 1.66CT:1CT	1-3 = 3.2 4-8 = 3.0	(1-3) 4,000
Q1553-83	M	M21038/27-23						
QT1553-83	T	M21038/27-23T						
QC1553-84*	C	M21038/27-24C	G	0.275 [6.985]	1-3:4-8 1-3:5-7	1CT:2.12CT 1CT:1.50CT	1-3 = 1.0 4-8 = 3.5	(4-8) 4,000
Q1553-84*	M	M21038/27-24						
QT1553-84*	T	M21038/27-24T						
QC1553-85*	C	M21038/27-25C	G	0.275 [6.985]	1-3:4-8 1-3:5-7	1CT:2.50CT 1CT:1.79CT	1-3 = 1.0 4-8 = 3.5	(4-8) 4,000
Q1553-85*	M	M21038/27-25						
QT1553-85*	T	M21038/27-25T						
QC1553-45*	C	M21038/27-26C	A	0.250 [6.35]	1-3:4-8 1-3:5-7	1CT:2.50CT 1CT:1.79CT	1-3 = 1.0 4-8 = 3.5	(4-8) 4,000
Q1553-45*	M	M21038/27-26						
QT1553-45*	T	M21038/27-26T						

* Designed for transceivers utilizing a single supply voltage (+5V).

¹ Impedance is tested at 75 kHz and at 1 MHz at -55°C ±2°C; +25°C ± 2°C; and +130°C ±2°C.



Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2020. iNRCORE, LLC. All rights reserved.




M224.F (07/22)

Mechanicals

Electrical Schematics

Package A

Dimensions: inch [mm]
Tolerance (unless otherwise specified): ± 0.010 [0.25]






Mechanicals

Electrical Schematics

Package G

Dimensions: inch [mm]
Tolerance (unless otherwise specified): ± 0.010 [0.25]



MIL-PRF-21038/27 Inspection, Sampling, Testing

Table 1 - Group A Inspection					
Level "C" **		Level "M"		Level "T"	
Tests	Sampling Plan	Tests	Sampling Plan	Tests	Sampling Plan
N/A	N/A	Electrical Characteristics per MIL-PRF-21038/27	Sample per Table 3	Thermal Shock	100%
N/A	N/A	Visual & Mechanical Inspection	Sample per Table 3	Winding Continuity	100%
N/A	N/A	N/A	N/A	Electrical Characteristics per MIL-PRF-21038/27	100%
N/A	N/A	N/A	N/A	Impedance	Sample per Table 3
N/A	N/A	N/A	N/A	Visual & Mechanical Inspection	Sample per Table 3

Table 2 - Group B Inspection					
Level "C" **		Level "M"		Level "T"	
Tests	Sampling Plan	Tests	Sampling Plan	Tests	Sampling Plan
N/A	N/A	Dielectric Withstanding Voltage	Sample per Table 3	Dielectric Withstanding Voltage	Sample per Table 3
N/A	N/A	Insulation Resistance	Sample per Table 3	Insulation Resistance	Sample per Table 3

Table 3 - Sampling Plans for Group A and Group B Inspections		
Lot Size	Group A, Group II Inspections	Group B
1 to 5	All	All
6 to 13	All	5
14 to 50	13	5
51 to 90	13	7
91 to 150	13	11
151 to 280	20	13
281 to 500	29	16
501 to 1,200	34	19
1,201 to 3,200	42	23
3,201 to 10,000	50	29

** Parts ordered to Level C are certified to comply with MIL-PRF-21038 Level C, however testing is performed per manufacturer's internal requirements and sampling rates.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[iNRCORE:](#)

[Q1553-2](#) [Q1553-45](#) [Q1553-85](#) [Q1553-1](#) [QT1553-45](#)