

DCF801

No Load Speed 2850rpm
Weight 0.8Kg
Dimensions: 125 x 188mm

DCD706

Power Output 250 W
Impact Rate 25500 bpm
Chuck Capacity 1.5-10mm
Max Drilling Wood 20 mm
Max Drilling Metal 10 mm
Weight 1Kg

DCD706

12V tools and batteries are compatible with 10.8V products
LED light on tool foot for high visibility
Charge indicator allows you to check the battery level
Brushless motor provides 15% more runtime
15 position adjustable torque control
25500 BPM hammer excellent when working with masonry drilling