

Technical Data Data Sheet N0386, Rev. C






SDUR6060W ULTRAFAST RECTIFIER



Applications

- Antiparallel diode for high frequency switching devices
- Anti saturation diode
- Snubber diode
- Free wheeling diode in converters and motor control circuits
- Rectifiers in switch mode power supplies (SMPS)
- Inductive heating and melting
- Uninterruptible power supplies (UPS)
- Ultrasonic cleaners and welders

Circuit Diagram



Features

- Ultra-Fast switching
- High current capability
- Low reverse leakage current
- High surge current capability
- This is a Pb free device
- All SMC parts are traceable to the wafer lot
- Additional testing can be offered upon request

Maximum Ratings:

Characteristics	Symbol	Condition	Max.	Units
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM} V _{RWM} V _R	-	600	V
Average Rectified Forward Current	I _{F (AV)}	50% duty cycle @Tc=70°C, rectangular wave form	60	Α
Peak One Cycle Non-Repetitive Surge Current	I _{FSM}	8.3ms, Half Sine pulse	600	Α

Electrical Characteristics:

Characteristics	Symbol	Condition	Тур.	Max.	Units
Forward Voltage Drop*	V _{F1}	@30A, Pulse, T _J = 25°C	1.44	-	1/
	VF1	@ 60A, Pulse, T _J = 25°C	-	2.0	V
Reverse Current*	I _{R1}	$@V_R = \text{rated } V_R$ $T_J = 25^{\circ}C$	0.9	100	uA
	I _{R2}	$@V_R = \text{rated } V_R$ $T_J = 125^{\circ}C$	0.26	14	mA
Reverse Recovery Time	t _{rr}	I _F =500mA,I _R =1A,and I _m =250mA	47.7	50	ns

^{*} Pulse width < 300 μ s, duty cycle < 2%

- China Germany Korea Singapore United States
 - http://www.smc-diodes.com sales@ smc-diodes.com •



Technical Data Data Sheet N0386, Rev. C






Thermal-Mechanical Specifications:

Characteristics	Symbol	Condition	Specification	Units
Junction Temperature	TJ	-	-55 to +150	°C
Storage Temperature	T _{stg}	-	-55 to +150	°C
Typical Thermal Resistance Junction to Case	R _θ JC	DC operation	0.75	°C/W
Approximate Weight	wt	-	6.28	g
Case Style	TO-247AC			

Ratings and Characteristics Curves



[•] China - Germany - Korea - Singapore - United States •

[•] http://www.smc-diodes.com - sales@ smc-diodes.com •




Technical Data Data Sheet N0386, Rev. C






Mechanical Dimensions TO-247AC




CVMDOL	Millimeters			
SYMBOL	MIN.	TYP.	MAX.	
Α	4.80	5.00	5.20	
A1	2.20	2.41	2.61	
A2	1.90	2.00	2.10	
b	1.10	1.20	1.35	
b1	1.80	2.00	2.20	
С	0.50	0.60	0.75	
D	20.30	21.00	21.20	
D1		16.58		
D2		1.17		
D2 E	15.60	15.80	16.00	
E1		14.02		
E2		5.00		
E3		2.50		
е		5.44		
L	19.42	19.92	20.42	
L1		4.13		
Р	3.50	3.60	3.70	
P1	7.1	7.19	7.40	
P2		2.50		
Q		5.80		
Q S T	6.05	6.15	6.25	
T		10.00		
U		6.20		

Note: Date code is after 17441, please use this new TO-247AC mechanical dimensions.

Tube Specification



Marking Diagram



Where XXXXX is YYWWL

 SDUR
 = Device Type

 60
 = Forward Current (60A)

 60
 = Reverse Voltage (600V)

 W
 = Configuration

 SSG
 = SSG

 SSG
 = SSG

 YY
 = Year

 WW
 = Week

 L
 = Lot Number

Cautions: Molding resin Epoxy resin UL:94V-0

Ordering Information

Device	Package	Shipping	
SDUR6060W	TO-247AC(Pb-Free)	25pcs / tube	

For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification.

- China Germany Korea Singapore United States
 - http://www.smc-diodes.com sales@ smc-diodes.com •

SDUR6060W



Technical Data Data Sheet N0386, Rev. C





DISCLAIMER:

- 1- The information given herein, including the specifications and dimensions, is subject to change without prior notice to improve product characteristics. Before ordering, purchasers are advised to contact the SMC Diode Solutions sales department for the latest version of the datasheet(s).
- 2- In cases where extremely high reliability is required (such as use in nuclear power control, aerospace and aviation, traffic equipment, medical equipment, and safety equipment), safety should be ensured by using semiconductor devices that feature assured safety or by means of users' fail-safe precautions or other arrangement.
- 3- In no event shall SMC Diode Solutions be liable for any damages that may result from an accident or any other cause during operation of the user's units according to the datasheet(s). SMC Diode Solution assumes no responsibility for any intellectual property claims or any other problems that may result from applications of information, products or circuits described in the datasheets.
- 4- In no event shall SMC Diode Solutions be liable for any failure in a semiconductor device or any secondary damage resulting from use at a value exceeding the absolute maximum rating.
- 5- No license is granted by the datasheet(s) under any patents or other rights of any third party or SMC Diode Solutions.
- 6- The datasheet(s) may not be reproduced or duplicated, in any form, in whole or part, without the expressed written permission of SMC Diode Solutions.
- 7- The products (technologies) described in the datasheet(s) are not to be provided to any party whose purpose in their application will hinder maintenance of international peace and safety nor are they to be applied to that purpose by their direct purchasers or any third party. When exporting these products (technologies), the necessary procedures are to be taken in accordance with related laws and regulations..