


Desoldering Tips

for MFR-DSX, -DSI, -SDX and -SDI Systems



Part No.	Description	Ø A	Ø B
DFP-CN2	Desolder Tip	0.67mm (.026")	0.67mm (.026")
DFP-CN3	Desolder Tip	0.79mm (.031")	2.05mm (.080")
DFP-CN4	Desolder Tip	1.05mm (.041")	2.30mm (.090")
DFP-CN5	Desolder Tip	1.31mm (.052")	2.65mm (.104")
DFP-CN6	Desolder Tip	1.55mm (.061")	2.85mm (.112")
DFP-CN7	Desolder Tip	2.44mm (.096")	3.65mm (.143")
DFP-CNL3	Desolder Tip Long Reach	0.79mm (.031")	2.05mm (.080")
DFP-CNL4	Desolder Tip Long Reach	1.05mm (.041")	2.30mm (.090")
DFP-CNL5	Desolder Tip Long Reach	1.31mm (.052")	2.65mm (.104")

The second digit denotes substrate material (damage tolerance). **F**= FR4 / Glass Fiber, for most standard applications. Also available in C Series, **C** = Ceramic.

Soldering Tips

for MFR-PST and PS-800E Systems with MFR-CA2 and PS-CA2 coils

EASY ACCESS SOLDERING TIPS for longer reach touch up applications

	SFV-CN05A Conical Solder Tip 0.5mm (.02")		SFV-CH18A Fine Solder Tip 1.8mm (.07")
	SFV-CNL10A Conical Long Solder Tip 1.0mm (.04")		SFV-CH15A Chisel Solder Tip 1.5mm (.06")
	SFV-CH50A Chisel Solder Tip 5.0mm (.197")		SFV-CNL03A Conical Long Solder Tip 0.3mm (.01")
	SFV-CH25A Chisel Solder Tip 2.5mm (.10")		SFV-CNB04A Conical Bent Solder Tip 0.4mm (.016")
	SFV-CH10A Chisel Solder Tip 1.0mm (.04")		SFV-DRH430A Drag Solder Tip Hoof, 3.0mm (.12")
	SFV-DRH420A Hoof Solder Tip 45° 2.0mm (.08")		SFV-DRK45A Knife Solder Tip 4.5mm (.177")
			SFV-DRK30A Knife Solder Tip 3.0mm (.12")


SOLDERING TIPS for heavy duty applications

	SFV-CH10 Chisel Solder Tip 30° 1.0mm (.04")		SFV-CNL10 Conical Long Solder Tip 1.0mm (.04")
	SFV-CH20 Chisel Solder Tip 2.0mm (.08")		SFV-CNL14 Conical Long Solder Tip 1.4mm (.056")
	SFV-CH25 Chisel Solder Tip 2.5mm (.10")		SFV-DRH20 Conical Bevel Solder Tip 2.0mm (.08")


Soldering Tips

for MFR-PST and PS-800E Systems with MFR-CA2 and PS-CA2 coils


SOLDERING TIPS *for heavy duty applications*




SFV-CH50
Extra Large Chisel Solder Tip
5.0mm (.20")




SFV-DRK50
Knife Solder Tip
5.0mm (.20")




SFV-CHB15
Chisel Bent 30° Solder Tip
1.5mm (.06")




SFV-CNL04
Conical Long Solder Tip
0.4mm (.016")




SFV-CN05
Conical Solder Tip
0.5mm (.02")



SFV-DRK50S
Drag Soldering Tip
Knife 5.0mm (.20")



SFV-CNB05
Conical Bent Solder Tip
0.5mm (.02")




SFV-CNL20
Conical Tip Long
2.0mm (.08")

The second digit denotes substrate material (damage tolerance). **F**= FR4 / Glass Fiber, for most standard applications. Two other series are also available, just replace F with either T or C. **T** = Temperature Sensitive, **C** = Ceramic


Soldering Tips

for PS-800 System with PS-CA1 Coil


SOLDERING TIPS *ideal for light to medium loads*




PHT-750315
Chisel Fine 30°
1.0mm (.04")




PHT-753035
Conical 30°
0.5mm (.02")




PHT-750326
Chisel Fine/Bent 30°
1.5mm (.06")




PHT-753067
Conical Long
1.0mm (.04")




PHT-750335
Chisel Fine 30°
1.78mm (.07")




PHT-753077
Power Conical
1.0mm (.04")




PHT-751355
Chisel 30°
2.5mm (.10")




PHT-754627
Mini Hoof 60°
1.0mm (.04")




PHT-750325
Chisel 60°
1.5mm (.06")




PHT-754667
Hoof 60°
2.0mm (.08")




PHT-751367
Chisel 30°
3.0mm (.12")




PHT-754487
Hoof 45°
3.0mm (.12")




PHT-751384
Chisel 30°
5.0mm (.197")



PHT-754687
Hoof 60°
3.0mm (.12")



PHT-752017
Conical 60°
0.25mm (.01")



PHT-754467F
Hoof 45° Face Only
2.0mm (.08")

75 = 750 Series for most standard applications. 65 = 650 Series also available for temperature sensitive applications. To order this series, replace 75 with 65.