

KEMET Part Number: ALS80A113NF250
(A381TM113M250A)

ALS80, Aluminum Electrolytic, 11,000 uF, 20%, 250 VDC, -40/+105°C



General Information

Supplier:	KEMET
Series:	ALS80
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
AEC-Q200:	No
Notes:	Dimensions D And L Include Slewing. MS (MxH) = M12x16. Mounting Clip (Sold Separately): V11

Dimensions

D	77mm +/-1mm
L	105mm +/-2mm
T	5.5mm +/-0.5mm
S	31.8mm +/-0.5mm
DT	13mm +/-0.5mm
LT	110.5mm NOM
TD	10mm MIN
V	19mm NOM
Z	10mm NOM

Specifications

Capacitance:	11,000 uF
Capacitance Tolerance:	20%
Voltage DC:	250 VDC, 287.5 VDC (Surge)
Temperature Range:	-40/+105°C
Rated Temperature:	105°C
Life:	9000 Hrs (Rated Voltage And Ripple Current At 105C), 15000 Hrs (Rated Voltage At 105C)
Resistance:	27 mOhms (100Hz 20C), 19 mOhms (10kHz 20C)
Ripple Current:	15.1 Amps (100Hz 105C), 19.9 Amps (10 kHz 105C)
Leakage Current:	6000 uA

Packaging Specifications

Weight:	690 g
Slewing:	Yes
Packaging:	Tray