


# Technical data sheet

## Reduction, PG thread

Item no. 2089297



Reduction (Part H) to DIN 46320, with Pg thread to DIN 40430, as a transition from a PG thread hole to a smaller cable gland.

\* Prices according to DEL notation.


CE Pg

|      |               |
|------|---------------|
| CuZn | Brass         |
| N    | Nickel-plated |

### Master data

|                          |                  |
|--------------------------|------------------|
| Item no.                 | 2089297          |
| Type                     | 167 R MS PG29-16 |
| Description 1            | Reduction        |
| Dimension                | PG29-PG16        |
| Material                 | Brass            |
| Material symbol          | CuZn             |
| Surface                  | Nickel-plated    |
| Surface symbol           | N                |
| Smallest sales unit (VG) | 50,00 Piece      |
| Weight                   | 6,56 kg/100 pc.  |

### Technical data



|                                |                                     |
|--------------------------------|-------------------------------------|
| Dimension D                    | 39,00 mm                            |
| Dimension L1                   | 8,00 mm                             |
| Dimension L2                   | 3,50 mm                             |
| explosion-proof                | <input type="checkbox"/>            |
| Thread type: External thread   | PG                                  |
| Thread type: Internal thread   | PG                                  |
| External thread                | Pg 29                               |
| Thread dimension, PG, external | 29,00                               |
| Internal thread                | Pg 16                               |
| Thread dimension, PG, internal | 16,00                               |
| Thread length                  | 8,00 mm                             |
| Nickel-plated                  | <input checked="" type="checkbox"/> |