

TPS5420EVM-175 Regulator Evaluation Module

Contents

1	Introduction	1
2	Test Setup and Results	3
3	Board Layout	8
4	Schematic and Bill of Materials	11

List of Figures

1	Measured Efficiency, TPS5420	4
2	Load Regulation	4
3	Line Regulation	5
4	Load Transient Response, TPS5420	5
5	Measured Loop Response, TPS5420, VIN = 25 V	6
6	Measured Output Voltage Ripple, TPS5420	6
7	Input Voltage Ripple, TPS5420	7
8	Power Up, VOUT Relative to VIN	7
9	Start-Up Waveform, VOUT Relative to ENA	8
10	Top-Side Layout	9
11	Bottom-Side Layout (Looking From Top Side)	10
12	Top-Side Assembly	11
13	TPS5420EVM-175 Schematic	12

List of Tables

1	Input Voltage and Output Current Summary	2
2	TPS5420EVM-175 Performance Specification Summary	2
3	Output Voltages Available	3
4	EVM Connectors and Test Points	3
5	TPS5420EVM-175 Bill of Materials	13

1 Introduction

This user's guide contains background information for the TPS5420 as well as support documentation for the TPS5420EVM-175 evaluation module (HPA175). Also included are the performance specifications, the schematic, and the bill of materials for the TPS5420EVM-175.

PowerPAD is a trademark of Texas Instruments.



1.1 Background

The TPS5420 dc/dc converter is designed to provide up to a 2-A continuous, 3-A peak output from an input voltage source of 5.5 V to 36 V. Rated input voltage and output current range for the evaluation module is given in Table 1. This evaluation module is designed to demonstrate the small printed-circuitboard areas that may be achieved when designing with the TPS5420 regulator and does not reflect the high input voltages that may be used when designing with this part. The switching frequency is internally set at a nominal 500 kHz. The high-side MOSFET is incorporated inside the TPS5420 package along with the gate drive circuitry. The low drain-to-source on resistance of the MOSFET allows the TPS5420 to achieve high efficiencies and helps to keep the junction temperature low at high output currents. The compensation components are provided internal to the integrated circuit (IC), whereas an external divider allows for an adjustable output voltage. Additionally, the TPS5420 provides an enable input. The absolute maximum input voltage is 36 V.

Table 1. Input Voltage and Output Current Summary

EVM	INPUT VOLTAGE RANGE	OUTPUT CURRENT RANGE
TPS5420EVM-175	VIN = 10 V to 36 V	0 A to 2 A

1.2 Performance Specification Summary

A summary of the TPS5420EVM-175 performance specifications is provided in Table 2. Specifications are given for an input voltage of VIN = 12 V and an output voltage of 5 V, unless otherwise specified. The TPS5420EVM-175 is designed and tested for VIN = 10 V to 36 V. The ambient temperature is 25° C for all measurements, unless otherwise noted. Maximum input voltage for the TPS5420EVM-175 is 36 V.

SPECIFICATION		TEST CONDITIONS	MIN	TYP	MAX	UNIT
VIN voltage range			10		36	V
Output voltage set point				5.0		V
Output current range		V _{IN} = 10 V to 36 V	0		2.5	А
Line regulation		I _o = 1 A, VIN = 3 V - 6 V		±0.11%		
Load regulation		$VIN = 25 V, I_0 = 0 A \text{ to } 2.5 A$		±0.1%		
Load transient response	Voltage change	I _o = 0.75 A to 2.25 A		-40		mV
	Recovery time			200		μs
	Voltage change	I _o = 2.25 A to 0.75 A		+40		mV
	Recovery time			200		μs
Loop bandwidth		VIN = 25 V		25.0		kHz
Phase margin		VIN = 25 V		55		٥
Input ripple voltage		$I_{O} = 3 \text{ A}$		275	300	mVpp
Output ripple voltage				32		mVpp
Output rise time				7		ms
Operating frequency				500		kHz
Maximum efficiency		$VIN = 10 V, V_0 = 5 V, I_0 = 0.75 A$		93.2%		

Table 2. TPS5420EVM-175 Performance Specification Summary

1.3 Modifications

The TPS5420EVM-175 is designed to demonstrate the small size that can be attained when designing with the TPS5420. A few changes can be made to this module.

1.3.1 Output Voltage Set Point

To change the output voltage of the EVM, it is necessary to change the value of resistor R2. Changing the value of R2 can change the output voltage above 1.25 V. The value of R2 for a specific output voltage can be calculated using Equation 1.

$$R2 = 10 \text{ k}\Omega \times \frac{1.221 \text{ V}}{\text{V}_{\text{O}} - 1.221 \text{ V}}$$

(1)

Test Setup and Results

Table 3 lists the R2 values for some common output voltages. Note that VIN must be in a range so that the minimum on-time is greater than 200 ns, and the maximum duty cycle is less than 87%. The values given in Table 3 are standard values, not the exact value calculated using Equation 1.

Output Voltage (V)	R2 Value (kΩ)
1.8	21.5
2.5	9.53
3.3	5.90
5	3.24

Table 3. Output Voltages Available

1.3.2 Input Voltage Range

The EVM is designed to operate from a 10-V to 36-V input voltage range. The TPS5420 is specified to operate over an input voltage range of 5.5 V to 36 V.

2 Test Setup and Results

This section describes how to properly connect, set up, and use the TPS5420EVM-175 evaluation module. The section also includes test results typical for the TPS5420EVM-175 and covers efficiency, output voltage regulation, load transients, loop response, output ripple, input ripple, and start-up.

2.1 Input / Output Connections

The TPS5420EVM-175 is provided with input/output connectors and test points as shown in Table 4. A power supply capable of supplying 2 A should be connected to J1 through a pair of 20 AWG wires. The load should be connected to J3 through a pair of 20 AWG wires. The maximum load current capability should be 2 A. Wire lengths should be minimized to reduce losses in the wires. Test-point TP1 provides a place to monitor the VIN input voltages with TP2 providing a convenient ground reference. TP3 is used to monitor the output voltage with TP4 as the ground reference.

Reference Designator	Function
J1	VIN, 10 V to 36 V
J2	OUT, 5 V at 2 A maximum
JP1	2-pin header for enable. Connect EN to ground to disable, open to enable.
TP1	VIN test point at VIN connector
TP2	GND test point at VIN
TP3	Output voltage test point at OUT connector
TP4	GND test point at OUT connector
TP5	Test point between voltage divider network and R3. Used for loop response measurements.
TP6	PH test point

Table 4. EVM Connectors and Test Points

Test Setup and Results

2.2 Efficiency

The TPS5420EVM-175 efficiency peaks at load current of about 0.75 A, and then decreases as the load current increases towards full load. Figure 1 shows the efficiency for theTPS5420EVM-175 at an ambient temperature of 25°C. The efficiency is lower at higher ambient temperatures, due to temperature variation in the drain-to-source resistance of the MOSFETs.




Figure 1. Measured Efficiency, TPS5420

2.3 Output Voltage Regulation

The output voltage load regulation of the TPS5420EVM-175 is shown in Figure 2; the output voltage line regulation is shown in Figure 3. Measurements are given for an ambient temperature of 25°C.




Figure 2. Load Regulation






Figure 3. Line Regulation

2.4 Load Transients

The TPS5420EVM-175 response to load transients is shown in Figure 4. The current step is from 25% to 75% of maximum rated load. Total peak-to-peak voltage variation is as shown, including ripple and noise on the output.




Figure 4. Load Transient Response, TPS5420



Test Setup and Results

2.5 Loop Characteristics

The TPS5420EVM-175 loop-response characteristics are shown in Figure 5. Gain and phase plots are shown for VIN voltage of 25 V and a 1-A load current.




Figure 5. Measured Loop Response, TPS5420, VIN = 25 V

2.6 Output Voltage Ripple

The TPS5420EVM-175 output voltage ripple is shown in Figure 6. The input voltage is VIN = 25 V for the TPS5420. Output current is the rated full load of 2 A. Voltage is measured directly across output capacitors.




Figure 6. Measured Output Voltage Ripple, TPS5420



2.7 Input Voltage Ripple

The TPS5420EVM-175 input voltage ripple is shown in Figure 7. The input voltage is VIN = 10 V for the TPS5420. Output current for each device is at full rated load of 2 A.




Figure 7. Input Voltage Ripple, TPS5420

2.8 Powering Up

The TPS5420EVM-175 start-up waveforms are shown in Figure 8 and Figure 9. In Figure 8 the top trace shows VIN whereas the bottom trace shows VOUT. VIN increases from 0 V toward 25 V. When the input voltage reaches the internally set UVLO threshold voltage of 5.3 V, the slow-start sequence begins. The internal reference begins to ramp up linearly at the internally set slow-start rate towards 1.221 V, and the output ramps up toward the set voltage of 5 V. The output may be inhibited by using a jumper at JP1 to tie ENA to GND. When the jumper is removed, ENA is released and the slow-start sequence begins as shown in Figure 9. The top trace shows the ENA signal and the bottom trace shows VOUT. When the ENA voltage reaches the enable-threshold voltage of 1.06 V, the start-up sequence begins as described above.




Figure 8. Power Up, VOUT Relative to VIN

Copyright © 2006, Texas Instruments Incorporated




Figure 9. Start-Up Waveform, VOUT Relative to ENA

3 Board Layout

This section provides a description of the TPS5420EVM-175 board layout and layer illustrations.

3.1 Layout

The board layout for the TPS5420EVM-175 is shown in Figure 10 through Figure 12. The top-side layer of the TPS5420EVM-175 is laid out in a manner typical of a user application. The top and bottom layers are 2-oz. copper.

The top layer contains the main power traces for VIN, OUT, and VPHASE. Also on the top layer are connections for the remaining pins of the TPS5420 and a large area filled with ground. The bottom layer contains ground and some signal routing. The top and bottom and internal ground traces are connected with multiple vias placed around the board including four vias directly under the TPS5420 device to provide a thermal path from the PowerPAD[™] land to ground.

The input decoupling capacitors (C1 and C4) and bootstrap capacitor (C3) are all located as close to the IC as possible. In addition, the voltage set-point resistor divider components are also kept close to the IC. The voltage divider network ties to the output voltage at the point of regulation, adjacent to the output capacitor C3.








Figure 10. Top-Side Layout






Figure 11. Bottom-Side Layout (Looking From Top Side)






Figure 12. Top-Side Assembly


4 Schematic and Bill of Materials

The TPS5420EVM-175 schematic and bill of materials are presented in this section.

Schematic and Bill of Materials

4.1 Schematic

The schematic for the TPS5420EVM-175 is shown in Figure 13.







4.2 Bill of Materials

The bill of materials for the TPS5420EVM-175 is given by Table 5.

Count	REF DES	Value	Description	Size	Part Number	MFR
2	C1, C4	4.7 µF	Capacitor, Ceramic, 50V, X7R, 20%	1812	C4532X5R1H475MT	TDK
1	C2	0.01 µF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H103K	TDK
1	C3	100 µF	Capacitor, Tantalum, 10V, 20%	7343(D)	TPSD107M010R0080	AVX
1	D1		Diode, Schottky, 3A, 40V	SMA	B340A	Diodes Inc
2	J1, J2		Terminal Block, 2 pin, 6A, 3,5mm	0.27 x 0.25	ED1514	OST
1	JP1		Header, 2-pin, 100mil spacing, (36-pin strip)	0.100 x 2	PTC36SAAN	Sullins
1	L1	33 µH	Inductor, SMT, 2.2A, 75milliohm	0.484 x 0.484	MSS1260-333	Coilcraft
1	R1	10.0 k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R2	3.24 k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R3	0	Resistor, Chip, 1/16W, 1%	0603	Std	Std
4	TP1, TP3, TP5, TP6		Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100	5000	Keystone
2	TP2, TP4		Test Point, Black, Thru Hole Color Keyed	0.100 x 0.100	5001	Keystone
1	U1	1	IC, Switching Step-Down Regulator, 36V, 2A	SO8	TPS5420D	TI
1	-		PCB, 1.95 ln x 1.95 ln x 0.062 ln		HPA175	Any
1	-		Shunt, 100-mil, Black	0.100	929950-00	3M

Table 5. TPS5420EVM-175 Bill of Materials

Schematic and Bill of Materials

EVALUATION BOARD/KIT/MODULE (EVM) ADDITIONAL TERMS

Texas Instruments (TI) provides the enclosed Evaluation Board/Kit/Module (EVM) under the following conditions:

The user assumes all responsibility and liability for proper and safe handling of the goods. Further, the user indemnifies TI from all claims arising from the handling or use of the goods.

Should this evaluation board/kit not meet the specifications indicated in the User's Guide, the board/kit may be returned within 30 days from the date of delivery for a full refund. THE FOREGOING LIMITED WARRANTY IS THE EXCLUSIVE WARRANTY MADE BY SELLER TO BUYER AND IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESSED, IMPLIED, OR STATUTORY, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE. EXCEPT TO THE EXTENT OF THE INDEMNITY SET FORTH ABOVE, NEITHER PARTY SHALL BE LIABLE TO THE OTHER FOR ANY INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES.

Please read the User's Guide and, specifically, the Warnings and Restrictions notice in the User's Guide prior to handling the product. This notice contains important safety information about temperatures and voltages. For additional information on TI's environmental and/or safety programs, please visit www.ti.com/esh or contact TI.

No license is granted under any patent right or other intellectual property right of TI covering or relating to any machine, process, or combination in which such TI products or services might be or are used. TI currently deals with a variety of customers for products, and therefore our arrangement with the user is not exclusive. TI assumes no liability for applications assistance, customer product design, software performance, or infringement of patents or services described herein.

REGULATORY COMPLIANCE INFORMATION

As noted in the EVM User's Guide and/or EVM itself, this EVM and/or accompanying hardware may or may not be subject to the Federal Communications Commission (FCC) and Industry Canada (IC) rules.

For EVMs **not** subject to the above rules, this evaluation board/kit/module is intended for use for ENGINEERING DEVELOPMENT, DEMONSTRATION OR EVALUATION PURPOSES ONLY and is not considered by TI to be a finished end product fit for general consumer use. It generates, uses, and can radiate radio frequency energy and has not been tested for compliance with the limits of computing devices pursuant to part 15 of FCC or ICES-003 rules, which are designed to provide reasonable protection against radio frequency interference. Operation of the equipment may cause interference with radio communications, in which case the user at his own expense will be required to take whatever measures may be required to correct this interference.

General Statement for EVMs including a radio

User Power/Frequency Use Obligations: This radio is intended for development/professional use only in legally allocated frequency and power limits. Any use of radio frequencies and/or power availability of this EVM and its development application(s) must comply with local laws governing radio spectrum allocation and power limits for this evaluation module. It is the user's sole responsibility to only operate this radio in legally acceptable frequency space and within legally mandated power limitations. Any exceptions to this are strictly prohibited and unauthorized by Texas Instruments unless user has obtained appropriate experimental/development licenses from local regulatory authorities, which is responsibility of user including its acceptable authorization.

For EVMs annotated as FCC – FEDERAL COMMUNICATIONS COMMISSION Part 15 Compliant

Caution

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

FCC Interference Statement for Class A EVM devices

This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instruction manual, may cause harmful interference to radio communications. Operation of this equipment in a residential area is likely to cause harmful interference in which case the user will be required to correct the interference at his own expense.

FCC Interference Statement for Class B EVM devices

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- · Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

For EVMs annotated as IC – INDUSTRY CANADA Compliant

This Class A or B digital apparatus complies with Canadian ICES-003.

Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

Concerning EVMs including radio transmitters

This device complies with Industry Canada licence-exempt RSS standard(s). Operation is subject to the following two conditions: (1) this device may not cause interference, and (2) this device must accept any interference, including interference that may cause undesired operation of the device.

Concerning EVMs including detachable antennas

Under Industry Canada regulations, this radio transmitter may only operate using an antenna of a type and maximum (or lesser) gain approved for the transmitter by Industry Canada. To reduce potential radio interference to other users, the antenna type and its gain should be so chosen that the equivalent isotropically radiated power (e.i.r.p.) is not more than that necessary for successful communication.

This radio transmitter has been approved by Industry Canada to operate with the antenna types listed in the user guide with the maximum permissible gain and required antenna impedance for each antenna type indicated. Antenna types not included in this list, having a gain greater than the maximum gain indicated for that type, are strictly prohibited for use with this device.

Cet appareil numérique de la classe A ou B est conforme à la norme NMB-003 du Canada.

Les changements ou les modifications pas expressément approuvés par la partie responsable de la conformité ont pu vider l'autorité de l'utilisateur pour actionner l'équipement.

Concernant les EVMs avec appareils radio

Le présent appareil est conforme aux CNR d'Industrie Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes : (1) l'appareil ne doit pas produire de brouillage, et (2) l'utilisateur de l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.

Concernant les EVMs avec antennes détachables

Conformément à la réglementation d'Industrie Canada, le présent émetteur radio peut fonctionner avec une antenne d'un type et d'un gain maximal (ou inférieur) approuvé pour l'émetteur par Industrie Canada. Dans le but de réduire les risques de brouillage radioélectrique à l'intention des autres utilisateurs, il faut choisir le type d'antenne et son gain de sorte que la puissance isotrope rayonnée équivalente (p.i.r.e.) ne dépasse pas l'intensité nécessaire à l'établissement d'une communication satisfaisante.

Le présent émetteur radio a été approuvé par Industrie Canada pour fonctionner avec les types d'antenne énumérés dans le manuel d'usage et ayant un gain admissible maximal et l'impédance requise pour chaque type d'antenne. Les types d'antenne non inclus dans cette liste, ou dont le gain est supérieur au gain maximal indiqué, sont strictement interdits pour l'exploitation de l'émetteur.

[Important Notice for Users of EVMs for RF Products in Japan]

This development kit is NOT certified as Confirming to Technical Regulations of Radio Law of Japan

If you use this product in Japan, you are required by Radio Law of Japan to follow the instructions below with respect to this product:

- Use this product in a shielded room or any other test facility as defined in the notification #173 issued by Ministry of Internal Affairs and Communications on March 28, 2006, based on Sub-section 1.1 of Article 6 of the Ministry's Rule for Enforcement of Radio Law of Japan,
- 2. Use this product only after you obtained the license of Test Radio Station as provided in Radio Law of Japan with respect to this product, or
- 3. Use of this product only after you obtained the Technical Regulations Conformity Certification as provided in Radio Law of Japan with respect to this product. Also, please do not transfer this product, unless you give the same notice above to the transferee. Please note that if you could not follow the instructions above, you will be subject to penalties of Radio Law of Japan.

Texas Instruments Japan Limited (address) 24-1, Nishi-Shinjuku 6 chome, Shinjuku-ku, Tokyo, Japan

http://www.tij.co.jp

【無線電波を送信する製品の開発キットをお使いになる際の注意事項】

本開発キットは技術基準適合証明を受けておりません。

本製品のご使用に際しては、電波法遵守のため、以下のいずれかの措置を取っていただく必要がありますのでご注意ください。

- 1. 電波法施行規則第6条第1項第1号に基づく平成18年3月28日総務省告示第173号で定められた電波暗室等の試験設備でご使用いただく。
- 2. 実験局の免許を取得後ご使用いただく。
- 3. 技術基準適合証明を取得後ご使用いただく。

なお、本製品は、上記の「ご使用にあたっての注意」を譲渡先、移転先に通知しない限り、譲渡、移転できないものとします。

上記を遵守頂けない場合は、電波法の罰則が適用される可能性があることをご留意ください。

日本テキサス・インスツルメンツ株式会社 東京都新宿区西新宿6丁目24番1号 西新宿三井ビル http://www.tij.co.jp

EVALUATION BOARD/KIT/MODULE (EVM) WARNINGS, RESTRICTIONS AND DISCLAIMERS

For Feasibility Evaluation Only, in Laboratory/Development Environments. Unless otherwise indicated, this EVM is not a finished electrical equipment and not intended for consumer use. It is intended solely for use for preliminary feasibility evaluation in laboratory/development environments by technically qualified electronics experts who are familiar with the dangers and application risks associated with handling electrical mechanical components, systems and subsystems. It should not be used as all or part of a finished end product.

Your Sole Responsibility and Risk. You acknowledge, represent and agree that:

- 1. You have unique knowledge concerning Federal, State and local regulatory requirements (including but not limited to Food and Drug Administration regulations, if applicable) which relate to your products and which relate to your use (and/or that of your employees, affiliates, contractors or designees) of the EVM for evaluation, testing and other purposes.
- 2. You have full and exclusive responsibility to assure the safety and compliance of your products with all such laws and other applicable regulatory requirements, and also to assure the safety of any activities to be conducted by you and/or your employees, affiliates, contractors or designees, using the EVM. Further, you are responsible to assure that any interfaces (electronic and/or mechanical) between the EVM and any human body are designed with suitable isolation and means to safely limit accessible leakage currents to minimize the risk of electrical shock hazard.
- 3. Since the EVM is not a completed product, it may not meet all applicable regulatory and safety compliance standards (such as UL, CSA, VDE, CE, RoHS and WEEE) which may normally be associated with similar items. You assume full responsibility to determine and/or assure compliance with any such standards and related certifications as may be applicable. You will employ reasonable safeguards to ensure that your use of the EVM will not result in any property damage, injury or death, even if the EVM should fail to perform as described or expected.
- 4. You will take care of proper disposal and recycling of the EVM's electronic components and packing materials.

Certain Instructions. It is important to operate this EVM within TI's recommended specifications and environmental considerations per the user guidelines. Exceeding the specified EVM ratings (including but not limited to input and output voltage, current, power, and environmental ranges) may cause property damage, personal injury or death. If there are questions concerning these ratings please contact a TI field representative prior to connecting interface electronics including input power and intended loads. Any loads applied outside of the specified output range may result in unintended and/or inaccurate operation and/or possible permanent damage to the EVM and/or interface electronics. Please consult the EVM User's Guide prior to connecting any load to the EVM output. If there is uncertainty as to the load specification, please contact a TI field representative. During normal operation, some circuit components may have case temperatures greater than 60°C as long as the input and output are maintained at a normal ambient operating temperature. These components include but are not limited to linear regulators, switching transistors, pass transistors, and current sense resistors which can be identified using the EVM schematic located in the EVM User's Guide. When placing measurement probes near these devices during normal operation, please be aware that these devices may be very warm to the touch. As with all electronic evaluation tools, only qualified personnel knowledgeable in electronic measurement and diagnostics normally found in development environments should use these EVMs.

Agreement to Defend, Indemnify and Hold Harmless. You agree to defend, indemnify and hold TI, its licensors and their representatives harmless from and against any and all claims, damages, losses, expenses, costs and liabilities (collectively, "Claims") arising out of or in connection with any use of the EVM that is not in accordance with the terms of the agreement. This obligation shall apply whether Claims arise under law of tort or contract or any other legal theory, and even if the EVM fails to perform as described or expected.

Safety-Critical or Life-Critical Applications. If you intend to evaluate the components for possible use in safety critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, such as devices which are classified as FDA Class III or similar classification, then you must specifically notify TI of such intent and enter into a separate Assurance and Indemnity Agreement.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2013, Texas Instruments Incorporated

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products		Applications	
Audio	www.ti.com/audio	Automotive and Transportation	www.ti.com/automotive
Amplifiers	amplifier.ti.com	Communications and Telecom	www.ti.com/communications
Data Converters	dataconverter.ti.com	Computers and Peripherals	www.ti.com/computers
DLP® Products	www.dlp.com	Consumer Electronics	www.ti.com/consumer-apps
DSP	dsp.ti.com	Energy and Lighting	www.ti.com/energy
Clocks and Timers	www.ti.com/clocks	Industrial	www.ti.com/industrial
Interface	interface.ti.com	Medical	www.ti.com/medical
Logic	logic.ti.com	Security	www.ti.com/security
Power Mgmt	power.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video
RFID	www.ti-rfid.com		
OMAP Applications Processors	www.ti.com/omap	TI E2E Community	e2e.ti.com
Wireless Connectivity	www.ti.com/wirelessconne	ectivity	

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2013, Texas Instruments Incorporated