


PRODUCT NUMBER  
SEE TABLE


mat'l. code		surface / tolerance		projection		product family	
ISO 1302		ISO 1101		ISO 1101		QUICKIE	
tolerances unless otherwise specified		line		INCH/MM		title	
angles		±2°		scale 1:1		HEADER QUICKIE SLIM LINE	
date		engr		sheet		type	
LSS 1/25/95		M. SMYK		1/25/95		Product Customer Drawing	
MRC 5/25/95		CHR J. ROMBERGER		1/25/95		dwg no	
ERE 8/08/05		L. SANDERS		1/25/95		66506	
AG 10/6-02/06		1/22/06		1/25/95		sheet of 10 size	
MHT 8/17/07		1/25/95		1/25/95		A3	
R.B 07/08/08		1/25/95		1/25/95		type	
J.Z. 2012-07-04		1/25/95		1/25/95		Product Customer Drawing	
sheet		AK		AK		AK	
index		1		2		3	
sheet		4		5		6	
index		7		8		9	
sheet		10		11		12	

PRODUCT NUMBER  
SEE TABLE



NOTES:

1. SAME POSITION TOLERANCE APPLIES TO BOTH ENDS OF PINS.
2. MOLDING MATERIAL: GLASS-FILLED POLYESTER, FLAME RETARDANT PER UL 94 V-0, COLOR: BLACK.
3. 1" MAX. DRAFT PERMISSIBLE ON ALL SURFACES.
4. 3 LBS./1.36 KG MIN. TERMINAL PULL-OUT FORCE.
5. TERMINAL MATERIAL: PHOSPHORUS BRONZE.
6. TO DETERMINE DIMENSIONS:  
N = NUMBER OF POSITIONS PER ROW
7. UNDER PLATING: 50µ"/1.27µm Ni.
8. PART NUMBERS WITH "R" FOLLOWING THE PART NUMBER (EXAMPLE 66506-326 R ) HAS RETENTION. (ONLY PARTS WITH .105, .120, AND .150 ROUND OR SQUARE TAILS CAN HAVE RETENTION.) LOCATION IS MANUFACTURER'S OPTION.  
FOR CONNECTORS:  
RETENTIVE LEG APPLICABLE TO TAIL LENGTHS .125/3.18 MAX. 5LB/2.3KG MAX INSERTION FORCE AND .25LB./1KG MIN RETENTION FORCE PER RETENTIVE PIN USING .062/1.57 THICK CIRCUIT BOARD AND RECOMMENDED HOLE PATTERN. RETENTIVE LOCATION AT THE DISCRETION OF THE MANUFACTURER. RETENTION PIN MAY BE SHIFTED TO NEXT POSITION.
9. PART NUMBERS WITH "T" FOLLOWING PART NUMBER (EXAMPLE 66506-068 T IS PACKED IN TUBES.) (CALL PRODUCT MANAGER FOR AVAILABILITY.)
10. SEE 68751 FOR LATCHES.
11. MAY BE ORDERED WITH "G" PACK PACKAGING BY ADDING "G" TO DASH NUMBER.
12. ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION & PART NUMBERS WITH "LF" SUFFIX ADDED IN THE TABLE ARE LEAD FREE.
13. IF "LF" P/N THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
14. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.57mm MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
15. THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS.
16. PLATING OPTIONS:  
PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON CONTACT OR TAIL, OPTIONALLY TIN ON TAIL.



mat'l. code	surface / tolerance	projection	product family
AK	ISO 1302 / ISO 406 / ISO 101	QUICKIE	QUICKIE
date	tolerances unless otherwise specified	title	HEADER QUICKIE SLIM LINE VERTICAL 4 WALL
angles	XX±01/XX±03	INCH/MM	dwg no 66506 sheet 2 of 10 size A3
linea	XXX±.003/XXX±.013	scale 1:1	type Product Customer Drawing
±2"	XXX±.003/XXX±.013	FCI	
dr	L. SANDERS 1/25/95		
engt	M. SMYK 1/25/95		
chr	J. ROMBERGER 1/25/95		
appd	M. SMYK 1/25/95		
sheet index	revision		
sheet	sheet		


PRODUCT NUMBER NOTE 8, 9 & 12	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
66506-001	2 X 5	B	.400/10.16	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-002				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-003				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-004				.105/2.67	120/200u" TIN LEAD	
-004LF				.105/2.67	100/160u" TIN	
-005				.150/3.81	120/200u" TIN LEAD	
-005LF				.150/3.81	100/160u" TIN	
-006				.675/17.15	120/200u" TIN LEAD	
-006LF	2 X 5	B	.400/10.16	.675/17.15	100/160u" TIN	
-007	2 X 10	D	.900/22.86	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-008				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-009				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-010				.105/2.67	120/200u" TIN LEAD	
-010LF				.105/2.67	100/160u" TIN	
-011				.150/3.81	120/200u" TIN LEAD	
-011LF				.150/3.81	100/160u" TIN	
-012				.675/17.15	120/200u" TIN LEAD	
-012LF	2 X 10		.900/22.86	.675/17.15	100/160u" TIN	
-013	2 X 13		1.200/30.48	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-014				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-015				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-016				.105/2.67	120/200u" TIN LEAD	
-016LF				.105/2.67	100/160u" TIN	
-017				.150/3.81	120/200u" TIN LEAD	
-017LF				.150/3.81	100/160u" TIN	
-018				.675/17.15	120/200u" TIN LEAD	
-018LF	2 X 13		1.200/30.48	.675/17.15	100/160u" TIN	
-019	2 X 17		1.600/40.64	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-020				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-021				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-022				.105/2.67	120/200u" TIN LEAD	
-022LF				.105/2.67	100/160u" TIN	
-023				.150/3.81	120/200u" TIN LEAD	
-023LF				.150/3.81	100/160u" TIN	
-024				.675/17.15	120/200u" TIN LEAD	
66506-024LF	2 X 17	D	1.600/40.64	.675/17.15	100/160u" TIN	NOTE 2

mat'l. code	AK	surface	ISO 1302	tolerance	ISO 406 ISO 101	projection	QUICKIE	product family	QUICKIE
trcn nopr date		angles		tolerances unless otherwise specified		title			
		line	XXL/01/XXL03			INCH/MM			
		±2"	XXX/000/XXX001			scale 1:1			
		dr	L. SANDERS	1/25/95		dwg no	66506	sheet	of 10 size
		engr	M. SMYK	1/25/95					A3
		chr	J. ROMBERGER	1/25/95					
		appd	M. SMYK	1/25/95					
sheet index		revision				type	Product Customer Drawing		
sheet									



PRODUCT NUMBER NOTE 8, 9 & 12	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
66506 -025	2 X 20	D	1.900/48.26	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-026				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-027				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-028				.105/2.67	120/200u" TIN LEAD	
-028LF				.105/2.67	100/160u" TIN	
-029				.150/3.81	120/200u" TIN LEAD	
-029LF				.150/3.81	100/160u" TIN	
-030				.675/17.15	120/200u" TIN LEAD	
-030LF	2 X 20		1.900/48.26	.675/17.15	100/160u" TIN	
-031	2 X 25		2.400/60.96	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-032				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-033				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-034				.105/2.67	120/200u" TIN LEAD	
-034LF				.105/2.67	100/160u" TIN	
-035				.150/3.81	120/200u" TIN LEAD	
-035LF				.150/3.81	100/160u" TIN	
-036				.675/17.15	120/200u" TIN LEAD	
-036LF	2 X 25	D	2.400/60.96	.675/17.15	100/160u" TIN	
-037	2 X 7	C	.600/15.24	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-038				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-039				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-040				.105/2.67	120/200u" TIN LEAD	
-040LF				.105/2.67	100/160u" TIN	
-041				.150/3.81	120/200u" TIN LEAD	
-041LF				.150/3.81	100/160u" TIN	
-042				.675/17.15	120/200u" TIN LEAD	
-042LF	2 X 7	C	.600/15.24	.675/17.15	100/160u" TIN	
-043	2 X 8	D	.700/17.78	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-044				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-045				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-046				.105/2.67	120/200u" TIN LEAD	
-046LF				.105/2.67	100/160u" TIN	
-047				.150/3.81	120/200u" TIN LEAD	
-047LF				.150/3.81	100/160u" TIN	
-048				.675/17.15	120/200u" TIN LEAD	
66506 -048LF	2 X 8	D	.700/17.78	.675/17.15	100/160u" TIN	NOTE 2


mat'l. code	AK	surface	ISO 1302	tolerance	ISO 1101	projection	product family	QUICKIE
tech ngr date		angles		unless otherwise specified		title		
		linea	XXX:XXX/XXX:XXX			INCH/MM	HEADER QUICKIE SLIM LINE	
		±2"	XXX:XXX/XXX:XXX			scale 1:1	VERTICAL 4 WALL	
		dr	L. SANDERS	1/25/95		dwg no	66506	sheet # of 10 size
		engt	M. SMYK	1/25/95				A3
		chr	J. ROMBERGER	1/25/95				
		appd	M. SMYK	1/25/95				
sheet index		revision				type	Product Customer Drawing	
sheet								



Downloaded from Arrow.com

PRODUCT NUMBER NOTE 8, 9 & 12	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
66506 -049	2 X 5	B	.400/10.16	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2
-050	2 X 10	D	.900/22.86			
-051	2 X 13		1.200/30.48			
-052	2 X 17		1.600/40.64			
-053	2 X 20		1.900/48.26			
-054	2 X 25	D	2.400/60.96			
-055	2 X 7	C	.600/15.24			
-056	2 X 8	D	.700/17.78	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-057	2 X 30		2.900/73.66	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-058				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-059				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-060				.105/2.67	120/200u" TIN LEAD	
-060LF				.105/2.67	100/160u" TIN	
-061				.150/3.81	120/200u" TIN LEAD	
-061LF				.150/3.81	100/160u" TIN	
-062				.675/17.15	120/200u" TIN LEAD	
-062LF				.675/17.15	100/160u" TIN	
-063				.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-064				.150/3.81		
-065	2 X 30	D	2.900/73.66	.675/17.15		
-066	2 X 5	B	.400/10.16	.105/2.67		
-067	2 X 5	B	.400/10.16	.675/17.15		
-068	2 X 7	C	.600/15.24	.105/2.67		
-069	2 X 7	C	.600/15.24	.675/17.15		
-070	2 X 8	D	.700/17.78	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-071	2 X 8	D	.700/17.78	.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-072	2 X 10		.900/22.86	.105/2.67		
-073	2 X 10		.900/22.86	.675/17.15		
-074	2 X 13		1.200/30.48	.105/2.67		
-075	2 X 13		1.200/30.48	.675/17.15		
-076	2 X 17		1.600/40.64	.105/2.67		
-077	2 X 17		1.600/40.64	.675/17.15		
-078	2 X 20		1.900/48.26	.105/2.67		
-079	2 X 20		1.900/48.26	.675/17.15		
-080	2 X 25		2.400/60.96	.105/2.67		
66506 -081	2 X 25	D	2.400/60.96	.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2

mat'l. code	AK	surface	ISO 1302	tolerance	ISO 406 ISO 101	projection	1st angle	product family	QUICKIE
tech ngr		date		angles	tolerances unless otherwise specified	INCH/MM		title	HEADER QUICKIE SLIM LINE VERTICAL 4 WALL
sheet index		revision		line	XXL/01/XXL03 XXX/001/XXX013 XXX/002/XXX016	scale	1:1	dwg no	66506
sheet				±2"				sheet of	5
				dr	L. SANDERS	1/25/95		type	Product Customer Drawing
				engr	M. SMYK	1/25/95			
				chr	J. ROMBERGER	1/25/95			
				appd	M. SMYK	1/25/95			



FCI  
Copyright FCI

PRODUCT NUMBER NOTE 8.9 & 12	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
66506-082	2 X 5	B	.400/10.16	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2
-083	2 X 5	B	.400/10.16	.150/3.81		
-084	2 X 5	B	.400/10.16	.675/17.15		
-085	2 X 7	C	.600/15.24	.105/2.67		
-086	2 X 7	C	.600/15.24	.150/3.81		
-087	2 X 7	C	.600/15.24	.675/17.15		
-088	2 X 8	D	.700/17.78	.105/2.67		
-089	2 X 8	D	.700/17.78	.150/3.81		
-090	2 X 8	D	.700/17.78	.675/17.15		
-091	2 X 10	D	.900/22.86	.105/2.67		
-092	2 X 10	D	.900/22.86	.150/3.81		
-093	2 X 10	D	.900/22.86	.675/17.15		
-094	2 X 13	D	1.200/30.48	.105/2.67		
-095	2 X 13	D	1.200/30.48	.150/3.81		
-096	2 X 13	D	1.200/30.48	.675/17.15		
-097	2 X 17	D	1.600/40.64	.105/2.67		
-098	2 X 17	D	1.600/40.64	.150/3.81		
-099	2 X 17	D	1.600/40.64	.675/17.15		
-100	2 X 20	D	1.900/48.26	.105/2.67		
-101	2 X 20	D	1.900/48.26	.150/3.81		
-102	2 X 20	D	1.900/48.26	.675/17.15		
-103	2 X 25	D	2.400/60.96	.105/2.67		
-104	2 X 25	D	2.400/60.96	.150/3.81		
-105	2 X 25	D	2.400/60.96	.675/17.15	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-106	2 X 30	D	2.900/73.66	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-107	2 X 30	D	2.900/73.66	.150/3.81	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-108	2 X 30	D	2.900/73.66	.675/17.15	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-109	2 X 5	B	.400/10.16	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-110				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-111				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-112				.105/2.67	120/200u" TIN LEAD	
-112LF				.105/2.67	100/160u" TIN	
-113				.150/3.81	120/200u" TIN LEAD	
-113LF				.150/3.81	100/160u" TIN	
-114				.675/17.15	120/200u" TIN LEAD	
66506-114LF	2 X 5	B	.400/10.16	.675/17.15	100/160u" TIN	NOTE 2

mat'l. code	AK	surface	ISO 1302	tolerance	ISO 1101	projection	product family
tech ngr date		angles		tolerances unless otherwise specified		title	QUICKIE
sheet index		line	XXL/01/XXL03		INCH/MM	HEADER QUICKIE SLIM LINE	
revision		±2"	XXX/000/XXX013		scale 1:1	VERTICAL 4 WALL	
sheet		dr	L. SANDERS	1/25/95		dwg no	66506
		engr	M. SMYK	1/25/95		sheet of	6 of 10
		chr	J. ROMBERGER	1/25/95		size	A3
		appd	M. SMYK	1/25/95		type	Product Customer Drawing

PRODUCT NUMBER NOTE 8,9 & 12	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
66506-115	2 X 5	B	.400/10.16	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2
-116				.150/3.81	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-117				.675/17.15	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-118				.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-119				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-120	2 X 5	B	.400/10.16	.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2
-121						
THRU						
-216						
DISCONTINUED						
-217	2 X 12	D	1.100/27.94	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2
-218					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-219					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-220				.105/2.67	120/200u* TIN LEAD	
-220LF				.105/2.67	100/160u* TIN	
-221				.150/3.81	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-222					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-223					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-224				.150/3.81	120/200u* TIN LEAD	
-224LF				.150/3.81	100/160u* TIN	
-225				.675/17.15	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-226					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-227					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-228					120/200u* TIN LEAD	
-228	2 X 12		1.100/27.94	.675/17.15	100/160u* TIN	
-229	2 X 15		1.400/35.56	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-230					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-231					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-232				.105/2.67	120/200u* TIN LEAD	
-232LF				.105/2.67	100/160u* TIN	
-233	2 X 15	D	1.400/35.56	.150/3.81	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-234	2 X 15	D	1.400/35.56	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-235				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-236				.150/3.81	120/200u* TIN LEAD	
-236LF				.150/3.81	100/160u* TIN	
66506-237	2 X 15	D	1.400/35.56	.675/17.15	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2

mat'l. code	surface	tolerance	projection	product family
trtecn n0dr	ISO 1302	ISO 1101	1st angle	QUICKIE
date	tolerances unless otherwise specified			
	angles	LINEAR	INCH/MM	title
	±2°	XXX:XXX/XXX:XXX	scale 1:1	HEADER QUICKIE SLIM LINE
	dr	L. SANDERS	1/25/95	VERTICAL 4 WALL
	engr	M. SMYK	1/25/95	dwg no
	chr	J. ROMBERGER	1/25/95	66506
	appd	M. SMYK	1/25/95	sheet
sheet index	revision			Customer Drawing
	sheet			

PRODUCT NUMBER NOTE 8,9 & 12	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL	NOTE 2
66506-238	2 X 5	B	.400/10.16	.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI		
-239					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI		
-240					120/200u" TIN LEAD		
-240LF	2 X 15		1.400/35.56	.675/17.15	100/160u" TIN		
-241	2 X 22		2.100/53.34	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI		
-242					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI		
-243					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI		
-244				.105/2.67	120/200u" TIN LEAD		
-244LF				.105/2.67	100/160u" TIN		
-245				.150/3.81	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI		
-246				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI		
-247					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI		
-248				.150/3.81	120/200u" TIN LEAD		
-248LF				.150/3.81	100/160u" TIN		
-249				.675/17.15	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI		
-250					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI		
-251					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI		
-252	2 X 22		2.100/53.34	.675/17.15	120/200u" TIN LEAD		
66506-252LF	2 X 22		2.100/53.34	.675/17.15	100/160u" TIN		
66506-253	2 X 17	D	1.600/40.64	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI		NOTE 2
66506-254							
THRU					UNAVAILABLE		
66506-279							
66506-280	2 X 10	D	.900/22.86	.105/2.67	120/200u" TIN LEAD		NOTE 2
66506-280LF	2 X 10	D	.900/22.86	.105/2.67	100/160u" TIN		NOTE 2
66506-281							
THRU					UNAVAILABLE		
66506-306							
66506-307	2 X 5	B	.400/10.16	.097/2.46	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI		NOTE 2
-308	2 X 5	B	.400/10.16				
-309	2 X 7	C	.600/15.24				
-310	2 X 8	D	.700/17.78				
-311	2 X 10		.900/22.86				
-312	2 X 12		1.100/27.94				
-66506-313	2 X 13	D	1.200/30.48	.097/2.46	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI		NOTE 2

mat'l. code		surface	tolerance	projection	product family
AK	AK	ISO 1302	ISO 1101	ISO 1:1	QUICKIE
date		angles	line ar	INCH/MM	title
		±2°	XXX/XXX/XXX/061	scale 1:1	HEADER QUICKIE SLIM LINE
		dr L. SANDERS	1/25/95		VERTICAL 4 WALL
		engt M. SMYK	1/25/95		dwg no
		chr J. ROMBERGER	1/25/95		66506
		appd M. SMYK	1/25/95		sheet of 10 size
sheet index					A3
revision					Product Customer Drawing
sheet					



PRODUCT NUMBER NOTE 8.9 & 12	SIZE	STYLE	DIM C	DIM J	PIN PLATING (NOTE 16)	PLASTIC MATERIAL NOTE 2
66506-314	2 X 15	D	1.400/35.56	.097/2.46	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 17		1.600/40.64			
	2 X 20		1.900/48.26			
	2 X 22		2.100/53.34			
	2 X 25		2.400/60.96			
	2 X 30		2.900/73.66	.097/2.46	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 8		.700/17.78	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 25		2.400/60.96		30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 8		.700/17.78		50u"/1.27u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 17		1.600/40.64	.105/2.67	50u"/1.27u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 25		2.400/60.96	.120/3.05	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 25		2.400/60.96	.150/3.81	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 25		2.400/60.96		15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 30		2.900/73.66		15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 17		1.600/40.64		15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 20		1.900/48.26	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 10		.900/22.86	.105/2.67	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 20		1.900/48.26	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 22		2.100/53.34	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 12	D	1.100/27.94	.150/3.81	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 5	B	.400/10.16	.150/3.81	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 4	B	.300/7.62	.105/2.67	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
	2 X 10	D	.900/22.86	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
66506-340						NOTE 2

mat'l. code	surface	tolerance	projection	product family
AK	ISO 1302	ISO 1101	1st angle	QUICKIE
	angles	linea	INCH/MM	title
	±2°	XXX:XXX/XXX:XXX	scale 1:1	HEADER QUICKIE SLIM LINE
	dr L. SANDERS	1/25/95		VERTICAL 4 WALL
	enrt M. SMYK	1/25/95		dwg no 66506
	chr J. ROMBERGER	1/25/95		sheet of 10 size A3
	appd M. SMYK	1/25/95		type Product Customer Drawing
sheet index	revision			
	sheet			

PRODUCT NUMBER	SIZE	STYLE	DIM C	DIM J	PIN PLATING (NOTE 16)	PLASTIC MATERIAL
NOTE 8, 9 & 12						
66506-341	2 X 17	D	1.600/40.64	.150/3.81	30u"/.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-342	2 X 10	D	.900/22.86	.150/3.81	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-343	2 X 17	D	1.600/40.64	.150/3.81	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-344	UNASSIGNED					
-345	2 X 20	D	1.900/48.26	.120/3.05	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-346	UNASSIGNED					
-347	UNASSIGNED					
-348	2 X 5	B	.400/10.16	.105/2.67	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-349	2 X 7	C	.600/15.24			
-350	2 X 8	D	.700/17.78			
-351	2 X 10		.900/22.86			
-352	2 X 13		1.200/30.48			
-353	2 X 17		1.600/40.64			
-354	2 X 20		1.900/48.26			
-355	2 X 22		2.100/53.34			
-356	2 X 25		2.400/60.96			
-357	2 X 30		2.900/73.66	.105/2.67	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-358	2 X 10		.900/22.86	.150/3.81	30u"/.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-359	2 X 17		1.600/40.64	.150/3.81	30u"/.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 11
-360	2 X 12	D	1.100/27.94	.295/7.49	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-361	2 X 5	B	.400/10.16	.105/2.67	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-362	2 X 5	B	.400/10.16	.105/2.67	30u"/.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-363	2 X 8	D	.700/17.78	.105/2.67		
-364	2 X 10	D	.900/22.86	.105/2.67		
-365	2 X 15	D	1.400/35.56	.105/2.67		
-366	2 X 17	D	1.600/40.64	.105/2.67		
-367	2 X 5	B	.400/10.16	.150/3.81		
-368	2 X 17	D	1.600/40.64	.150/3.81		
66506-369	2 X 25	D	2.400/60.96	.150/3.81	30u"/.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2

NOTE 11  
NOTE 11

mat'l. code	surface / tolerance	projection	product family
AK	ISO 1302 / 406 ISO 1101		QUICKIE
	tolerances unless otherwise specified		
	angles	INCH/MM	title
	line	scale 1:1	HEADER QUICKIE SLIM LINE VERTICAL 4 WALL
	±2°		dwg no 66506
	dr L. SANDERS 1/25/95		sheet 10 of 10 size A3
	engr M. SMYK 1/25/95		Product Customer Drawing
	chr J. ROMBERGER 1/25/95		
	appd M. SMYK 1/25/95		
sheet index	revision		
	sheet		