


REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
I		INITIAL RELEASE	28FEB2022	SJ CY
A		REVISED	03JUN2022	SJ CY
AI		REVISED PER ECN-22-162711	05JUL2022	SJ CY



- NOTES: UNLESS OTHERWISE SPECIFIED.
- FABRICATE TO MEET IPC - 6013, CLASS 2. INSPECT TO MEET IPC - A - 600, CLASS 2.
 - MATERIAL :
 - A. PI FILM + VHB DOUBLE SIDED ADHESIVE.
 - B. CABLE : COAX CABLE DIA 1.13 or 1.37, CABLE CONN: I-PEX or TE APPROVED EQUIVALENT.
 - FINISH:
 - A: SOLDERMASK BOTH SIDES: ORANGE.
 - PACKAGING: SINGULATED PARTS TO BE SECURELY BAG WRAPPED, BAGGED OR VACUUM PACKED IN BULK.
 - CONSULT TE CONNECTIVITY DATA SHEET DS-2108965.
 - SILKSCREEN; WHITE EPOXY INK
 - A. TE LOGO, TE P/N
 - B. WORD REV., FOLLOWED BY THE LATEST REVISION LETTER, AS SHOWN.
 - C. 4 DIGIT DATE CODE: FIRST 2 DIGITS FOR THE WEEK CODE AND THE 2ND TWO DIGITS FOR THE YEAR CODE.
 - OTHERS: SPECIFIC TE SOURCE CODE NUMBER DIGITS AS REQUIRED

MHF 4L	(207.80)	1.13	200.00	2108965-8
	(157.80)	1.13	150.00	2108965-7
	(107.80)	1.13	100.00	2108965-6
	(57.80)	1.13	50.00	2108965-5
MHF	(207.80)	1.37	200.00	2108965-4
	(157.80)	1.37	150.00	2108965-3
	(107.80)	1.37	100.00	2108965-2
	(57.80)	1.37	50.00	2108965-1
CONNECTOR TYPE "C"	(C)	"B" CABLE OD	"A" CABLE LENGTH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	SJ, NOH	28FEB2022	TE Connectivity
DIMENSIONS: mm		CHK	H, SHIN	28FEB2022	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	CY, PARK	28FEB2022	
0 PLC ±- 1 PLC ±0,1 2 PLC ±0,01 3 PLC ±0,001 4 PLC ±0,0001 ANGLES ±- FINISH -		NAME	FPC ANT, MHF/MHF4L, UWB 6-8.5GHz		
MATERIAL	SEE NOTE	PRODUCT SPEC	-		RESTRICTED TO
-		APPLICATION SPEC	-		SIZE
-		WEIGHT	-		CAGE CODE
-		CUSTOMER DRAWING	A200779		DRAWING NO
-		SCALE	3:1		SHEET
-		OF	1		REV
-		REV	AI		