

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Contaclean

Revision date: 18.11.2019

Product code: 101

Page 2 of 9

Pictograms:

Hazard statements

H222	Extremely flammable aerosol.
H229	Pressurised container: May burst if heated.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.

Precautionary statements

P211	Do not spray on an open flame or other ignition source.
P410+P412	Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P273	Avoid release to the environment.
P271	Use only outdoors or in a well-ventilated area.
P251	Do not pierce or burn, even after use.
P332+P313	If skin irritation occurs: Get medical advice/attention.
P210	Keep away from heat. No Smoking.

2.3. Other hazards

No information available.

SECTION 3: Composition/information on ingredients
3.2. Mixtures
Hazardous components

CAS No	Chemical name	Quantity
	EC No	
	Index No	
	REACH No	
	GHS Classification	
	Hydrocarbons, C6, isoalkanes, <5% n-hexane	40-60 %
	931-254-9	01-2119484651-34
	Flam. Liq. 2, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2; H225 H315 H336 H304 H411	
67-63-0	propan-2-ol; isopropyl alcohol; isopropanol	20-40 %
	200-661-7	603-117-00-0
	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3; H225 H319 H336	
124-38-9	Carbondioxide	<5%
	204-696-9	
	Compressed gas; H280	

Full text of H and EUH statements: see section 16.

SECTION 4: First aid measures
4.1. Description of first aid measures
General information

No data available

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Contaclean

Revision date: 18.11.2019

Product code: 101

Page 3 of 9

After inhalation

Provide fresh air. In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).

After contact with skin

Wash with plenty of water. Take off contaminated clothing and wash it before reuse.

After contact with eyes

After contact with the eyes, rinse with water with the eyelids open for a sufficient length of time, then consult an ophthalmologist immediately.

After ingestion

Rinse mouth immediately and drink plenty of water.

4.2. Most important symptoms and effects, both acute and delayed

No data available

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically. No data available

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media**

Water spray jet, Carbon dioxide (CO₂), Foam, Extinguishing powder.

Unsuitable extinguishing media

Water with tenside additive. Water.

5.2. Special hazards arising from the substance or mixture

Extremely flammable aerosol. Vapours can form explosive mixtures with air. Heating causes rise in pressure with risk of bursting.

5.3. Advice for firefighters

In case of fire: Wear self-contained breathing apparatus.

Additional information

Use water spray jet to protect personnel and to cool endangered containers. Suppress gases/vapours/mists with water spray jet. Collect contaminated fire extinguishing water separately. Do not allow entering drains or surface water.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Remove all sources of ignition. Provide adequate ventilation. Wear a self-contained breathing apparatus and chemical protective clothing.

6.2. Environmental precautions

Do not allow uncontrolled discharge of product into the environment. Danger of explosion

6.3. Methods and material for containment and cleaning up

Ventilate affected area.

6.4. Reference to other sections

Safe handling: see section 7

Personal protection equipment: see section 8

Disposal: see section 13

SECTION 7: Handling and storage**7.1. Precautions for safe handling****Advice on safe handling**

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Contaclean

Revision date: 18.11.2019

Product code: 101

Page 4 of 9

Advice on protection against fire and explosion

Do not spray on naked flames or any incandescent material. Keep away from sources of ignition - No smoking. Take precautionary measures against static discharges. Vapours can form explosive mixtures with air.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep container tightly closed. Keep in a cool, well-ventilated place. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

Hints on joint storage

Do not store together with: Oxidising agent. Pyrophoric or self-heating substances.

7.3. Specific end use(s)

Elektronikspray/Electronic Spray

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits (EH40)

CAS No	Substance	ppm	mg/m ³	fibres/ml	Category	Origin
124-38-9	Carbon dioxide	5000	9150		TWA (8 h)	WEL
		15000	27400		STEL (15 min)	WEL
67-63-0	Propan-2-ol	400	999		TWA (8 h)	WEL
		500	1250		STEL (15 min)	WEL

8.2. Exposure controls



Appropriate engineering controls

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Protective and hygiene measures

Remove contaminated, saturated clothing immediately. Draw up and observe skin protection programme. Wash hands and face before breaks and after work and take a shower if necessary. When using do not eat or drink.

Eye/face protection

Suitable eye protection: goggles. Tightly sealed safety glasses.

Hand protection

When handling with chemical substances, protective gloves must be worn with the CE-label including the four control digits. The quality of the protective gloves resistant to chemicals must be chosen as a function of the specific working place concentration and quantity of hazardous substances. For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves. DIN EN 374 Tested protective gloves are to be worn: NBR (Nitrile rubber) For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves. NBR (Nitrile rubber)

Skin protection

Flame-retardant protective clothing. Wear anti-static footwear and clothing Protective clothing:

Respiratory protection

In case of inadequate ventilation wear respiratory protection. In case of inadequate ventilation wear respiratory

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Contaclean

Revision date: 18.11.2019

Product code: 101

Page 5 of 9

protection.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Physical state: Aerosol
Colour: colourless
Odour: characteristic
pH-Value: not determined

Changes in the physical state

Melting point: not determined
Initial boiling point and boiling range: 60 °C
Flash point: < -20 °C

Flammability

Solid: not applicable
Gas: not determined

Lower explosion limits: 1,2 vol. %
Upper explosion limits: 7 vol. %

Auto-ignition temperature

Solid: not applicable
Gas: not determined

Decomposition temperature: not determined

Oxidizing properties

Not oxidising.

Vapour pressure: not determined

Vapour pressure:
(at 50 °C) 719 hPa

Density: not determined

Water solubility: The study does not need to be conducted
because the substance is known to be
insoluble in water.

Solubility in other solvents

not determined

Partition coefficient: not determined

Vapour density: not determined

Evaporation rate: not determined

9.2. Other information

Solid content: not determined

SECTION 10: Stability and reactivity**10.1. Reactivity**

Extremely flammable aerosol. No data available

10.2. Chemical stability

No data available

10.3. Possibility of hazardous reactions

No data available

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Contaclean

Revision date: 18.11.2019

Product code: 101

Page 6 of 9

10.4. Conditions to avoid

Keep away from sources of heat (e.g. hot surfaces), sparks and open flames. Vapours can form explosive mixtures with air.

10.5. Incompatible materials

No data available

10.6. Hazardous decomposition products

No data available

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity

Based on available data, the classification criteria are not met.

CAS No	Chemical name				
	Exposure route	Dose	Species	Source	Method
	Hydrocarbons, C6, isoalkanes, <5% n-hexane				
	oral	LD50 >1000 mg/kg	Fisch 1		

Irritation and corrosivity

Causes skin irritation.
Causes serious eye irritation.

Sensitising effects

Based on available data, the classification criteria are not met.

Carcinogenic/mutagenic/toxic effects for reproduction

Based on available data, the classification criteria are not met.

STOT-single exposure

May cause drowsiness or dizziness. (Hydrocarbons, C6, isoalkanes, <5% n-hexane; propan-2-ol; isopropyl alcohol; isopropanol)

STOT-repeated exposure

Based on available data, the classification criteria are not met.

Aspiration hazard

Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

12.1. Toxicity

Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

CAS No	Chemical name					
	Aquatic toxicity	Dose	[h] [d]	Species	Source	Method
	Hydrocarbons, C6, isoalkanes, <5% n-hexane					
	Acute algae toxicity	ErC50 >1000 mg/l	72 h	Alge		
	Acute crustacea toxicity	EC50 >1000 mg/l	48 h	Daphnia pulex (water flea)		

12.2. Persistence and degradability

The product has not been tested.

12.3. Bioaccumulative potential

The product has not been tested.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Contaclean

Revision date: 18.11.2019

Product code: 101

Page 7 of 9

12.4. Mobility in soil

The product has not been tested.

12.5. Results of PBT and vPvB assessment

The product has not been tested.

12.6. Other adverse effects

No information available.

Further information

Do not allow to enter into surface water or drains. Do not allow to enter into soil/subsoil.

SECTION 13: Disposal considerations**13.1. Waste treatment methods****Advice on disposal**

Do not allow to enter into surface water or drains. Do not allow to enter into soil/subsoil. Dispose of waste according to applicable legislation.

Waste disposal number of waste from residues/unused products

160504 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; gases in pressure containers and discarded chemicals; gases in pressure containers (including halons) containing hazardous substances; hazardous waste

Waste disposal number of contaminated packaging

150104 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); metallic packaging

Contaminated packaging

Non-contaminated packages may be recycled. Handle contaminated packages in the same way as the substance itself.

SECTION 14: Transport information**Land transport (ADR/RID)**

14.1. UN number:	UN1950
14.2. UN proper shipping name:	AEROSOLS
14.3. Transport hazard class(es):	2
Hazard label:	2.1



Classification code:	5F
Special Provisions:	190 327 625
Limited quantity:	1 L
Transport category:	2
Tunnel restriction code:	D

Other applicable information (land transport)

E0

Inland waterways transport (ADN)

14.1. UN number:	UN1950
14.2. UN proper shipping name:	AEROSOLS
14.3. Transport hazard class(es):	2
Hazard label:	2.1

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Contaclean

Revision date: 18.11.2019

Product code: 101

Page 8 of 9



Classification code: 5F
Special Provisions: 190 327 344 625
Limited quantity: 1 L

Other applicable information (inland waterways transport)

E0

Marine transport (IMDG)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
14.4. Packing group: -
Hazard label: 2, see SP63

Special Provisions: 63, 190, 277, 327, 344, 959
Limited quantity: See SP277
EmS: F-D, S-U

Other applicable information (marine transport)

E0

Air transport (ICAO-TI/IATA-DGR)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS, flammable
14.3. Transport hazard class(es): 2.1
Hazard label: 2.1



Special Provisions: A145 A167
Limited quantity Passenger: 30 kg G
IATA-packing instructions - Passenger: 203
IATA-max. quantity - Passenger: 75 kg
IATA-packing instructions - Cargo: 203
IATA-max. quantity - Cargo: 150 kg

Other applicable information (air transport)

E0

: Y203

14.5. Environmental hazards

ENVIRONMENTALLY HAZARDOUS: yes



Danger releasing substance: Hydrocarbons

14.6. Special precautions for user

Warning: Flammable gases.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Contaclean

Revision date: 18.11.2019

Product code: 101

Page 9 of 9

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulatory information**

Restrictions on use (REACH, annex XVII):

Entry 28: Hydrocarbons, C6, isoalkanes, <5% n-hexane

National regulatory information

Employment restrictions:

Observe restrictions to employment for juvenils according to the 'juvenile work protection guideline' (94/33/EC).

Water contaminating class (D):

2 - clearly water contaminating

15.2. Chemical safety assessment

Chemical safety assessments for substances in this mixture were not carried out.

SECTION 16: Other information**Abbreviations and acronyms**ADR: Accord européen sur le transport des marchandises dangereuses par Route
(European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonized System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service

LC50: Lethal concentration, 50%

LD50: Lethal dose, 50%

Relevant H and EUH statements (number and full text)

H222	Extremely flammable aerosol.
H225	Highly flammable liquid and vapour.
H229	Pressurised container: May burst if heated.
H280	Contains gas under pressure; may explode if heated.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.

Further Information

The information is based on present level of our knowledge. It does not, however, give assurances of product properties and establishes no contract legal rights. The receiver of our product is singularly responsible for adhering to existing laws and regulations.

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)