



**CONNECTORS**

**STANDARD CIRCULAR CONNECTORS**



✓ Active

TE CONNECTIVITY (TE)

## M12,FRONT MOUNT,MALE,A,4P,SOLDER WIRE

M8/M12 Connector System | M12 , M12 Connector , M12 PCB/Panel Mount

T4132012041-000

TE Internal Number: T4132012041-000

EU RoHS Compliant with Exemptions

EU ELV Compliant with Exemptions

Connector System Wire-to-Panel

Product Type Connector

Sealable Yes

Reverse Gender Reverse

Shell Plating Material Nickel

[↓ PRODUCT DRAWING](#)  
English

[↓ 3D PDF](#)

### DOCUMENTATION

Product Drawings

#### M12 PANEL MOUNT CONNECTOR A CODE, MALE, FRONT MOUNTING WIRE SOLDERING

PDF

English

CAD Files

#### 3D PDF

PDF

3D

#### Customer View Model

2D\_DXF.ZIP

English

### Customer View Model

3D\_IGS.ZIP

English

### Customer View Model

3D\_STP.ZIP

English

---

Product Specifications

Product Specification

### Industrial M8 & M12 Series Circular Connector

PDF

English

Application Specification

### M12 Screw Connection Application Specification

PDF

English

---

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

Product Type Features

**Connector System** Wire-to-Panel

**Product Type** Connector

**Sealable** Yes

**Terminates To** Printed Circuit Board

**Shell Size** 18

**Shielded** No

**Connector Style** Plug

**Shell Type** Metal

**Accessory Color** Black

**Assembly Type** Electrical Connector

---

Configuration Features

**Number of Positions** 4

**Number of Power Positions** 0

**Number of Signal Positions** 4

**Preloaded** Yes

**Position Keyed** A

**Keying** A

**Factory Installed Backshell** No

---

Electrical Characteristics

**Operating Voltage (VAC)** 250

---

Body Features

**Shell Plating Material** Nickel  
**Shell Material** Copper Alloy  
**Insulation Material** Polyamide  
**Environmental Protection Type** Sealed  
**Peripheral Seal Material** Silicone  
**O-Ring Material** Silicone

---

#### Contact Features

**Reverse Gender** Reverse  
**Contact Type** Male

---

#### Mechanical Attachment

**Polarization Code** A  
**Mating Alignment Type** Keyed  
**Flange** Without

---

#### Dimensions

**Wire/Cable Size (AWG)** 18 – 24

---

#### Usage Conditions

**Operating Temperature Range (°F)** -40 – 85

---

#### Industry Standards

**IP Water Sealing Level** IP67

---

#### Packaging Features

**Packaging Quantity** 1

---

#### Other

**Field Serviceable** No

---

#### Statement of Compliance

**Statement of Compliance**

PDF