



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
G	02	P	LTR	DESCRIPTION	DATE	DWN	APVD
		J2		REVISED PER ECR-08-016589	02JUL08	HMR	TM

AMP WIRE RANGE	AMP INSULATION RANGE
22-16 AWG 0.3-1.5 mm ²	.140 MAX DIA 3.5 MAX DIA



△1 ASTERISK * FOR PHOS BRONZE VERSION ONLY
 △2 OBSOLETE W/O REPLACEMENT



△2	OBSOLETE		TIN-LEAD	PHOS BRONZE	165566-7
△2	OBSOLETE		GOLD	PHOS BRONZE	165566-6
△2	OBSOLETE		GOLD	BRASS	165566-5
			SILVER	PHOS BRONZE	165566-4
△2	OBSOLETE		SILVER	BRASS	165566-3
		2-165566-2	TIN	PHOS BRONZE	165566-2
		2-165566-1	TIN	BRASS	165566-1
		PN ON TAPE	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr_ruth 15APR05	Tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm		CHK T MICHIELUTTI 15APR05	NAME RECEPTACLE, FASTON, PIDG, .110 SERIES	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.2 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± 5'		APVD T MICHIELUTTI 15APR05	PRODUCT SPEC -	
MATERIAL -		FINISH -	APPLICATION SPEC -	RESTRICTED TO -
		WEIGHT -	SIZE A3	CAGE CODE 00779
		DRAWING NO 165566		REV J2
		CUSTOMER DRAWING		SCALE 1:1 SHEET 1 OF 1