


REV	REV.LIR	BEFORE REVISION	AFTER REVISION	SIGN	DATE
V1.0					2022/12/5

TABLE A



Pin Assignment

P1		P2
1	Brown	12
3	White	10
2	Drain	11
4	Red	9
6	White	7
5	Drain	8
7	Green	6
9	White	4
8	Drain	5
10	Blue	3
12	White	1
11	Drain	2
15	Black	15
17	Drain	17
16	Drain	16
13	Red	13
14	Yellow	14
18	White	18
19	Orange	19
20	Braid+Drain	20
SHELL		SHELL

NOTES:
 1.100% OPEN,SHORT & MISWIRE TESE
 2.CONDUCTIVE RESISTANCE:TABLE A/MAX
 3.INSULATION RESISTANCE:10MΩ/MIN.AT DC300V/10ms

TABLE A

P/NO.	Length of finished product	Impedance of conduction
	1500±20mm	3Ω
	1800±20mm	3Ω
	2000±30mm	4Ω
	3000±40mm	4Ω

Unil	mm	The general tolerance								
Scale	5:1	xx.:±0.3	5	shell	H01-0024	DP ABS Shell,Color:Black	2	pcs		
Third angle projection		x.x.:±0.1	4	PVC	SPVBK-002	PVC 45Pa Black UL94V-0	N/A	g		
			3	PE	SPETR	PE Low density	N/A	g		
			2	CONN	CDP2-012	DP/M PIN:G/F SHELL:G/F Insulator:Black	2	pcs		
		.xx.:±0.05	1	WIRE	WUDT55930C1-003	(30AWG(tc)*1P*1C+AL)*5C+30AWG(tc)*5C+F+ADB OD:7.3mm Jack Black	TABLE A	mm		
			NO.	NAME	PAPT NO	SPECIFICATIONS	QTY	UNIT		

APPROVED BY: **XIANG**
 CHECKED BY:
 DRAWN BY: **CHEN**

VCOM VCOM INTERNATIONAL LTD.

DESCRIPTION: DP 1.2 M TO M
 P/N: CG631-B
 DRAWN NO: