



1212 TWIST TIE



Material: UL approved Nylon 66, 94V-2 (Available in P.P. or P.E.)
 Colors available upon request.
 Tie-up cables at economical cost.
 Open the ties to feed cable and twist on to fix.



Unit:mm Item No.	Dimension			Bundis Dimension	Packing
	A	B	C		
<input type="checkbox"/> TT-05	5.1	21.6	1.5	4.4	100pcs (1000pcs)
<input type="checkbox"/> TT-08	7.0	25.0	2.0	7.0	
<input type="checkbox"/> TT-11	11.6	29.8	1.7	10.1	
<input type="checkbox"/> TT-15	15.0	33.8	1.9	13.4	
<input type="checkbox"/> TT-18	18.6	40.0	1.9	16.2	
<input type="checkbox"/> TT-24	23.6	45.0	2.0	21.3	
<input type="checkbox"/> TTU-05	5.0	22.0	1.8	4.2	
<input type="checkbox"/> TTU-08	8.1	26.2	2.3	7.2	
<input type="checkbox"/> TTU-11	11.3	29.7	2.3	10.0	
<input type="checkbox"/> TTU-15	14.8	32.6	2.0	13.2	

<input type="checkbox"/> TTU-18	18.0	38.0	2.0	16.5	
<input type="checkbox"/> TTU-22	22.0	42.3	2.0	19.8	
<input type="checkbox"/> TTU-28	28.0	55.1	2.0	26.7	